




4

3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A	REVISED PER EC OS14-0150-05	30AUG05	BM	JL




RECOMMENDED
PANEL CUTOUT

- 1 POLYESTER, PBT, 15% GLASS FIBER REINFORCED, NATURAL, PER MIL-M-24519.
- 2 ZINC PER QQ-Z-363.
- 3 POLYMETHYLPENTENE,GENERAL PURPOSE.
- 4 PHOSPHOR BRONZE PER QQ-B-750.
- 5 BRASS PER QQ-B-626.
- 6 BRASS PER ASTM-B-453.
- 7 NICKEL PL PER QQ-N-290, 3.81µm[.000150] MINIMUM THICK
- 8 GOLD PL PER MIL-G-45204, 0.76µm[.000030] MINIMUM THICK
- 9 TIN PLATE PER ASTM-B-545, 3.81µm[.000150] MINIMUM THICK

PCB CONFIGURATION

5221198-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA – DOCK5	21APR2005	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105–3608		
		CHK J. HAVENER	21APR2005			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. LIPPERT	21APR2005	NAME JACK,VERTICAL,PCB, SERIES TWIN BNC —		
		PRODUCT SPEC —				
	0 PLC ± – 1 PLC ± – 2 PLC ± 0.20[.008] 3 PLC ± – 4 PLC ± – ANGLES ± –	APPLICATION SPEC —		SIZE A3		
		WEIGHT —				
MATERIAL 	FINISH 	CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV A