






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B	EC 0G3C-0004-04	19JUL04	BSV	MSS

D

C

B

A



SPECIFICATIONS: UNLESS OTHERWISE SPECIFIED:

CONTACT RATING: 0.4VA @ 20VDC (MAX.).
INITIAL CONTACT RESISTANCE: 50 MILLIOHMS (MAX).
INSULATION RESISTANCE: 100 MEGOHMS (MIN.) @ 100VDC.
DIELECTRIC STRENGTH: 500VDC AT SEA LEVEL.
OPERATING FORCE: 400 GRAMS MAX..
LIFE EXPECTANCY: 1,000 CYCLES.
ACTUATOR TRAVEL: 30° .
OPERATING TEMPERATURE: -20°C TO +85°C
SOLDER HEAT RESISTANCE:
260°C ±5°C FOR TEN SECONDS WHEN MOUNTED
ON A .062" THICK PCB WITH SWITCH IN
"OFF" POSITION.
HAND SOLDERING: 500°F (260°C) -660°F (350°C)
UTILIZING A CONTROLLED 40 WATT
IRON FOR 3-5 SECONDS MAX.
STORAGE TEMPERATURE: -55°C TO +85°C

MATERIAL: UNLESS OTHERWISE SPECIFIED:

BASE: PPS UL94 V-0, BLACK.
HOUSING: PPS UL94 V-0, BLACK.
ACTUATOR: POLYIMIDE 94V-0, WHITE
CONTACTS: COPPER ALLOY, GOLD/NICKEL PLATE
TERMINALS: COPPER ALLOY, GOLD/NICKEL PLATE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	BSV		19JUL04		tyco Electronics		Tyco Electronics Corporation		
		CHK	—		—		NAME		Harrisburg, Pa 17105-3808		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		M.S. SARVER		NAME		DPU-SERIES DIP SWITCH	
		0 PLC ± —		PRODUCT SPEC		—		DPU06		DPU06	
		1 PLC ± —		APPLICATION SPEC		—		SIZE		CAGE CODE	
		2 PLC ± —		—		—		DRAWING NO		RESTRICTED TO	
		3 PLC ± .012		—		—		A2 00779		C= 1-1437583-4	
MATERIAL		FINISH		WEIGHT		—		A2 00779		C= 1-1437583-4	
SEE NOTES		—		CUSTOMER DRAWING		SCALE		4:1		SHEET 1 OF 1	
										REV B	