


4

3

2

1

LOC AP	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005139	19MAR11	RK	HMR



SECTION A-A

- ① - ELASTÔMERO SAE J200, 2BC 414, A14, B14, C12, E014, F17, Z1
Z1=RESISTÊNCIA RASGO, ASTM D624 - 20kg/cm MIN.
- ② - ELASTÔMERO SAE J200, 2BC 514, A14, B14, C12, E014, F17, Z1
Z1=RESISTÊNCIA RASGO, ASTM D624 - 20kg/cm MIN.
- ① -ELASTOMER SAE J200, 2BC 414, A14, B14, C12, E014, F17, Z1
Z1= TEAR RESISTANCE, ASTM D624 -20kg/cm MIN.
- ② -ELASTOMER SAE J200, 2BC 514, A14, B14, C12, E014, F17, Z1
Z1= TEAR RESISTANCE, ASTM D624 -20kg/cm MIN.

PRETO/BLACK		40±5 SHORE A	ELASTOMER 1	880810-2		
PRETO/BLACK		50±5 SHORE A	ELASTOMER 2	880810-1		
FINISH		HARDNESS	MATERIAL	PART NUMBER		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±• 1 PLC ±0.3 2 PLC ±• 3 PLC ±• 4 PLC ±• ANGLES ±°		DWN M.L. OGAWA 09JUN99				
		CHK P.L. FARIA 10JUN99				
0 PLC ±• 1 PLC ±0.3 2 PLC ±• 3 PLC ±• 4 PLC ±• ANGLES ±°		APVD J.M.M. NETO 10JUN99				
		NAME COVER CAP 2 POSN				
		PRODUCT SPEC -				
		APPLICATION SPEC -				
FINISH		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-880810	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 1	OF 1	REV B1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		±0.3	
0 PLC		±0.3	
1 PLC		±0.3	
2 PLC		±0.3	
3 PLC		±0.3	
4 PLC		±0.3	
ANGLES		±1°	
FINISH		SEE TABLE	
MATERIAL		SEE TABLE	

