


**NEW!**

Flyback Transformer

For ON Semiconductor
NCP1351 Controller



- Dual-output flyback transformer for ON Semiconductor's NCP1351 Variable Off Time PWM Controller.
- 32 V, 1.0 A and 16 V, 0.75 A Outputs. Output of the auxiliary winding is 16 V.
- Operates in a discontinuous mode with a universal input
- 3000 Vrms primary to secondary isolation.

Core material Ferrite

Terminations RoHS tin-silver over tin over phos bronze. Other terminations available at additional cost.

Weight 23.5 g

Ambient temperature -40°C to +85°C

Storage temperature Component: -40°C to +85°C.
Packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)
38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 64 parts per tray

PCB washing Only pure water or alcohol recommended

Part number	L at 0 A ¹ ±10% (μH)	L at I _{pk} ² min (μH)	DCR max (Ohms)				Leakage L ³ max (μH)	Turns ratio pri : sec1 : sec2 : aux	I _{pk} ² (A)
			pri	sec1	sec2	aux			
GA0007-AL	270	243	0.25	0.027	0.045	0.26	8.16	5 : 1 : 1 : 1	3.0

1. Inductance is for the primary, measured at 45 kHz, 0.8 Vrms, 0 Adc.



2. I_{pk} is the peak current drawn at minimum input voltage.

3. Leakage inductance measured on the primary winding with all secondary pins shorted.


4. Ambient operating temperature range -40°C to +85°C.

5. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



**Recommended
Board Layout**



Secondary windings to be connected in series on the PC board.

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 605 Revised 04/26/07

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web http://www.coilcraft.com