




N-Channel 60-V (D-S), 175°C MOSFET, Logic Level

PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
60	0.035 @ $V_{GS} = 10$ V	25
	0.045 @ $V_{GS} = 4.5$ V	22


175°C Rated
Maximum Junction Temperature
TrenchFET®
Power MOSFETs



Top View

Order Number:
SUD25N06-45L

Drain Connected to Tab



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)				
Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	25	A
	$T_C = 100^\circ\text{C}$		16	
Pulsed Drain Current		I_{DM}	30	
Continuous Source Current (Diode Conduction)		I_S	25	
Avalanche Current		I_{AR}	25	mJ
Repetitive Avalanche Energy (Duty Cycle $\leq 1\%$)		E_{AR}	31	
Maximum Power Dissipation	$T_C = 25^\circ\text{C}$	P_D	50	W
	$T_A = 25^\circ\text{C}$		2.5 ^a	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS			
Parameter	Symbol	Limit	Unit
Maximum Junction-to-Ambient ^a	R_{thJA}	60	$^\circ\text{C/W}$
Maximum Junction-to-Case	R_{thJC}	3.0	

Notes:

a. Surface mounted on 1" x 1" FR4 Board.







For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>








SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ ^a	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA	60			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	1.0		3.0	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ±20 V			±100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 60 V, V _{GS} = 0 V			1	μA
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 125°C			50	
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 175°C			150	
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10V	20			A
Drain-Source On-State Resistance ^b	r _{DS(on)}	V _{GS} = 10 V, I _D = 12 A		0.025	0.035	Ω
		V _{GS} = 10 V, I _D = 12 A, T _J = 125°C		0.045	0.063	
		V _{GS} = 10 V, I _D = 12 A, T _J = 175°C		0.058	0.081	
		V _{GS} = 4.5 V, I _D = 12 A		0.036	0.045	
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 12 A	15	25		S
Dynamic						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 25 V, f = 1 MHz		1320		pF
Output Capacitance	C _{oss}			210		
Reverse Transfer Capacitance	C _{rss}			56		
Total Gate Charge ^c	Q _g	V _{DS} = 30 V, V _{GS} = 10 V, I _D = 25 A		26	40	nC
Gate-Source Charge ^c	Q _{gs}			7.5		
Gate-Drain Charge ^c	Q _{gd}			4.5		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 30 V, R _L = 1.2 Ω I _D ≅ 25 A, V _{GEN} = 10 V, R _G = 7.5 Ω		10	20	ns
Rise Time ^c	t _r			10	20	
Turn-Off Delay Time ^c	t _{d(off)}			31	45	
Fall Time ^c	t _f			10	20	
Source-Drain Diode Ratings and Characteristics (T _C = 25 °C) ^a						
Pulsed Current	I _{SM}				30	A
Diode Forward Voltage	V _{SD}	I _F = 25 A, V _{GS} = 0 V			1.5	V
Reverse Recovery Time	t _{rr}	I _F = 25 A, di/dt = 100 A/μs		60	90	ns
Reverse Recovery Charge	Q _{rr}			0.13		μC

Notes:

- For design aid only; not subject to production testing.
- Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.
- Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

THERMAL RATINGS




Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SUD25N06-45L](#) [SUD25N06-45L-E3](#)