

DC Axial Fans

ebmpapst



Series 400, Type 412 40 x 40 x 20 mm



- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics.
- With electronic protection against reverse polarity. The fan only operates when the polarity is correct. Impedance-protected against blocking and overloading. Type 412 H and 414 H with electronic protection against blocking
- Fan of fibreglass reinforced plastic. PBT housing, PA impeller.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Electrical connection via 2 leads AWG 28, TR 64. Stripped and tinned ends.
- Mass 27 g.

ebm-papst • St. Georgen

Nominal Data	Air Flow	Air Flow	Nominal Voltage	Voltage Range	Noise		Sinter-Sleeve Bearings Ball Bearings	Power Input	Nominal Speed	Temperature Range	Service Life L ₁₀ at 20 °C	at 60 °C	Curve
Type	m ³ /h	CFM	V DC	V DC	dB(A)	Bel	□/■	Watt	min ⁻¹	°C	Hours	Hours	
405	10	5.9	5	4.5...5.5	18	3.8	■	0.9	6 000	-20...+70	50 000 / 20 000		1
412	10	5.9	12	10...14	18	3.8	■	0.9	6 000	-20...+70	50 000 / 20 000		1
412 H	13.5	7.9	12	10...14	29	4.7	■	1.6	8 100	-20...+60	45 000 / 15 000		2
414	10	5.9	24	20...28	18	3.8	■	1.0	6 000	-20...+70	50 000 / 20 000		1
414 H	13.5	7.9	24	20...26.5	29	4.7	■	1.6	8 100	-20...+60	45 000 / 15 000		2






- Speed-proportional rectangular pulse for external speed monitoring of fan motor
- 2 pulses per revolution
- Open-Collector signal output
- Extremely wide operating voltage range (5 ... 60 V)
- Easy adaptation to user interface
- Connection via separate lead
- The sensor signal also serves as a major comparison variable for setting and maintaining the desired speed for interactive or controlled cooling with one or several interconnected fans.

ebm-papst • St. Georgen


Electrical connection




$$R_a = \frac{U_{BS} - U_{SLOW}}{I_{SINK}}$$

All voltages measured to ground.
External load resistance R_a from U_S to U_{BS} required.

Signal output voltage



Fan speed



Signal symmetry $[t_1, t_2] = 0.8 \dots 1.2$
Signal frequency $[F] = 2 \times n/60 \text{ Hz}$

Attention:

With these fan options, deviations in regard to temperature range, voltage range and power consumption are possible compared with standard fan data.

Signal data

Type	Sensor signal $U_{S \text{ Low}}$		Condition: I_{sink}		Sensor signal $U_{S \text{ High}}$		Condition: I_{source}		Sensor operating voltage U_{BS}		Perm. sink current $I_{\text{sink max.}}$	
	V DC	mA	V DC	mA	V DC	mA	V DC	mA	V DC	mA	V DC	mA
255 N/2	≤ 0.4	≤ 2	30	0	≤ 30	2						
255 H/2	≤ 0.4	≤ 2	30	0	≤ 30	2						
252 N/2	≤ 0.4	≤ 2	30	0	≤ 30	2						
405 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
405 F/2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
412 F/2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
414 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
405 /2	≤ 0.4	1	30	0	≤ 30	≤ 2						
412 /2	≤ 0.4	1	30	0	≤ 30	≤ 2						
414 /2	≤ 0.4	1	30	0	≤ 30	≤ 2						
414 /2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
412 J/2 H	≤ 0.4	1	30	0	≤ 30	≤ 4						
412 J/2 HH	≤ 0.4	1	30	0	≤ 30	≤ 4						
414 J/2 H	≤ 0.4	2	30	0	≤ 30	≤ 4						
414 J/2 HH	≤ 0.4	2	30	0	≤ 30	≤ 4						
512 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
514 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
612 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
612 F/2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
614 F/2	≤ 0.4	1	30	0	≤ 30	≤ 2						
612 N/2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
612 N/2 NHH-120	≤ 0.4	1	30	0	≤ 30	≤ 2						
612 N/2 N	≤ 0.4	1	30	0	≤ 30	≤ 2						
614 N/2 H	≤ 0.4	1	30	0	≤ 30	≤ 2						
614 N/2 HH-121	≤ 0.4	1	30	0	≤ 30	≤ 2						
614 N/2 M	≤ 0.4	2	28	0	≤ 30	≤ 4						
712 F/2 L	≤ 0.4	1	30	0	≤ 30	≤ 2						
712 F/2 M	≤ 0.4	1	30	0	≤ 30	≤ 2						
8412 N/2 GL	≤ 0.4	2	28	0	≤ 28	≤ 4						
8412 N/2 GM	≤ 0.4	2	28	0	≤ 28	≤ 4						
8412 N/2 G	≤ 0.4	2	28	0	≤ 28	≤ 4						
8414 N/2 GL	≤ 0.4	2	28	0	≤ 28	≤ 4						
8414 N/2 GM	≤ 0.4	2	28	0	≤ 28	≤ 4						
8414 N/2 G	≤ 0.4	2	28	0	≤ 28	≤ 4						
8414 N/2	≤ 0.4	2	28	0	≤ 28	≤ 4						
8412 N/2	≤ 0.4	2	28	0	≤ 28	≤ 4						
8412 N/2 H	≤ 0.4	2	28	0	≤ 28	≤ 4						
8414 N/2 H	≤ 0.4	2	28	0	≤ 28	≤ 4						
8312 /2 HL	≤ 0.4	2	30	0	≤ 30	≤ 4						
8314 /2	≤ 0.4	2	30	0	≤ 30	≤ 4						
8314 /2 H	≤ 0.4	2	30	0	≤ 30	≤ 4						

Available on request:

- Galvanically separated sensor signal circuit
- Varying voltage potentials for power and logic circuit.

Signal data	Sensor signal $U_{S, Low}$	Condition: I_{Sink}	Sensor signal $U_{S, High}$	Condition: I_{Source}	Sensor operating voltage U_{ES}	Perm. sink current $I_{Sink, max.}$
Type	V DC	mA	V DC	mA	V DC	mA
8318 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
8318 /2 HL	≤ 0.4	2	30	0	≤ 30	≤ 4
8318 /2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
3412 N/2 GL	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2 GM	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2 G	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2 HH	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2 GHH	≤ 0.4	2	28	0	≤ 28	≤ 4
3412 N/2 H	≤ 0.4	2	28	0	≤ 28	≤ 4
3414 N/2 GH	≤ 0.4	2	28	0	≤ 28	≤ 4
3414 N/2	≤ 0.4	2	28	0	≤ 28	≤ 4
3312 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
3318 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
4412 F/2 GL	≤ 0.4	2	30	0	≤ 30	≤ 4
4412 F/2 GML	≤ 0.4	2	30	0	≤ 30	≤ 4
4412 F/2 M	≤ 0.4	2	30	0	≤ 30	≤ 4
4412 F/2	≤ 0.4	2	30	0	≤ 30	≤ 4
4414 F/2 L	≤ 0.4	2	30	0	≤ 30	≤ 4
4414 F/2 M	≤ 0.4	2	30	0	≤ 30	≤ 4
4414 F/2 G	≤ 0.4	2	30	0	≤ 30	≤ 4
4414 F/2	≤ 0.4	2	30	0	≤ 30	≤ 4
4418 F/2	≤ 0.4	2	30	0	≤ 30	≤ 4
4312 N/2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
4312 N/2 HH	≤ 0.4	2	30	0	≤ 30	≤ 4
4312 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
4314 /2 G	≤ 0.4	2	30	0	≤ 30	≤ 4
4314 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
4318 /2 G	≤ 0.4	2	30	0	≤ 30	≤ 4
4318 /2 M	≤ 0.4	2	30	0	≤ 30	≤ 4
4318 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
4212 N/2 GN	≤ 0.4	2	30	0	≤ 30	≤ 4
4212 N/2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
4214 N/2 GN	≤ 0.4	2	30	0	≤ 30	≤ 4
4214 N/2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
4218 N/2 GN	≤ 0.4	2	30	0	≤ 30	≤ 4
4218 N/2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
4212 /2 M	≤ 0.4	2	30	0	≤ 30	≤ 4
4212 /2	≤ 0.4	2	30	0	≤ 30	≤ 4
4212 /2 H	≤ 0.4	2	30	0	≤ 30	≤ 4
4214 /2	≤ 0.4	2	30	0	4–30	≤ 4

Signal data	Sensor signal $U_{S, Low}$	Condition: I_{Sink}	Sensor signal $U_{S, High}$	Condition: I_{Source}	Sensor operating voltage U_{ES}	Perm. sink current $I_{Sink, max.}$
Type	V DC	mA	V DC	mA	V DC	mA
4214 /2 H	≤ 0.4	2	30	0	4–30	≤ 4
4218 /2	≤ 0.4	2	30	0	4–30	≤ 4
4218 /2 H	≤ 0.4	2	30	0	4–30	≤ 4
4182 N/2 X	≤ 0.4	2	30	0	4–30	≤ 4
4184 N/2 GX	≤ 0.4	2	30	0	4–30	≤ 4
4184 N/2 X	≤ 0.4	2	30	0	4–30	≤ 4
4184 N/2 XH	≤ 0.4	2	30	0	4–30	≤ 4
5112 N/2	≤ 0.4	2	15	0	≤ 5	≤ 20
5114 N/2	≤ 0.4	2	60	0	≤ 60	≤ 20
5118 N/2	≤ 0.4	2	60	0	≤ 60	≤ 20
5212 N/2 H	≤ 0.4	2	30	0	4–30	≤ 2
5212 N/2 N	≤ 0.4	2	30	0	4–30	≤ 2
5214 N/2 N	≤ 0.4	2	30	0	4–30	≤ 2
5218 N/2 H	≤ 0.4	2	30	0	4–30	≤ 2
7112 N/2	≤ 0.4	2	60	0	≤ 60	≤ 20
7114 N/2	≤ 0.4	2	30	0	≤ 30	≤ 20
7118 N/2	≤ 0.4	2	60	0	≤ 60	≤ 20
6224 N/2	≤ 0.4	8	30	0	≤ 30	≤ 20
6248 N/2	≤ 0.4	8	60	0	≤ 30	≤ 20
DV 6224 /2	≤ 0.4	2	30	0	≤ 60	≤ 20
6424 /2	≤ 0.4	2	60	0	≤ 60	≤ 20
6448 /2	≤ 0.4	2	60	0	≤ 60	≤ 20
6448 /2 T	≤ 0.4	2	60	0	≤ 60	≤ 20
RL 48-19/12/2	≤ 0.4	2	28	0	4–30	≤ 4
RL 48-19/14/2	≤ 0.4	2	28	0	4–30	≤ 4
RL 90-18/12N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RL 90-18/14N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RG 90-18/12N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RG 90-18/14N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RG 125-19/14N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RG 125-19/18N/2	≤ 0.4	2	60	0	≤ 30	≤ 4
RER 125-19/14N/2	≤ 0.4	2	30	0	≤ 30	≤ 4
RG 160-28/14N/2	≤ 0.4	2	30	0	≤ 30	≤ 20

Attention:

With these fan options, deviations in regard to temperature range, voltage range and power consumption are possible compared with standard fan data.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[DV6224/2](#)