


Data Sheet

Type Number: 6237
Designation IEC: ---
System: Li-Manganese dioxide /
 Organic Electrolyte
UL Recognition: MH 13654 (N)
Nominal Voltage [V]: 3
Typical Capacity C [mAh]: 1350

Load 1.0 kOhm, at 20 °C down to 2.0 V

Weight, approx [g]: 15
Volume [ccm]: 5,6
Coding: Date of Manufacturing
 Quarter/Year



Temperature Ranges [°C]: **min.** **max.**
Storage: -55 75
Discharge: -30 75
Dimensions [mm]: **min.** **max.**
Diameter [A]: 14,45 14,75
Height [B]: 33,1 33,5
Shoulder Diameter[L]: 7
Shoulder Height [M]: 0,6

Segment: Electronic

Main Applications: Watch
 Photo
 Electronic

Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage:	2.0 V
Continuous	1000	Ω Time:	500 h
24h/d, 7d/w		Capacity [mAh]:	1350
Current [μA]:		Energy [mWh]:	3600