


## 100V COMPLEMENTARY MEDIUM POWER TRANSISTOR IN SM-8

## Features

- NPN Transistor
  - $BV_{CEO} > 100$
  - $I_C = 2A$  High Continuous Current
  - Low Saturation Voltage  $V_{CE(sat)} < 300mV$  @ 1A
- PNP Transistor
  - $BV_{CEO} > -100V$
  - $I_C = -2A$  High Continuous Current
  - Low Saturation Voltage  $V_{CE(sat)} < -300mV$  @ -1A
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

## Mechanical Data

- Case: SM-8 (8 LEAD SOT223)
- Case Material: Molded Plastic, "Green" Molding Compound; UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208 (E3)
- Weight: 0.117 grams (Approximate)



## Ordering Information (Note 4)


| Part Number | Marking | Reel size (inches) | Tape width (mm) | Quantity per reel |
|-------------|---------|--------------------|-----------------|-------------------|
| ZDT6753TA   | T6753   | 7                  | 12              | 1,000             |
| ZDT6753TC   | T6753   | 13                 | 12              | 4,000             |

Notes:

1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
2. See [http://www.diodes.com/quality/lead\\_free.html](http://www.diodes.com/quality/lead_free.html) for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. For packaging details, go to our website at <http://www.diodes.com/products/packages.html>.

## Marking Information

SM-8



T6753 = Product Type Marking Code  
YWW = Date Code Marking  
Y or  $\bar{Y}$  = Last Digit of Year (ex: 5= 2015)  
WW or  $\bar{WW}$  = Week Code (01~53)

**Absolute Maximum Ratings** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

| Characteristic               | Symbol    | NPN | PNP  | Unit |
|------------------------------|-----------|-----|------|------|
| Collector-Base Voltage       | $V_{CBO}$ | 120 | -120 | V    |
| Collector-Emitter Voltage    | $V_{CEO}$ | 100 | -100 | V    |
| Emitter-Base Voltage         | $V_{EBO}$ | 7   | -7   | V    |
| Continuous Collector Current | $I_C$     | 2   | -2   | A    |
| Peak Pulse Current (Note 5)  | $I_{CM}$  | 6   | -6   | A    |

**Thermal Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

| Characteristic                          | Symbol          | Value       | Unit |
|---|-----------------|-------------|------|
| Collector Power Dissipation             | $P_D$           | 2.25        | W    |
|   |                 | 2.75        |      |
| Thermal Resistance, Junction to Ambient | $R_{\theta JA}$ | 55.6        | °C/W |
|   |                 | 45.5        |      |
| Thermal Resistance, Junction to Leads   | $R_{\theta JL}$ | 30.7        | °C/W |
| Operating and Storage Temperature Range | $T_J, T_{STG}$  | -55 to +150 | °C   |


**ESD Ratings** (Note 8)

| Characteristic                             | Symbol  | Value | Unit | JEDEC Class |
|--|---------|-------|------|-------------|
| Electrostatic Discharge - Human Body Model | ESD HBM | 4,000 | V    | 3A          |
| Electrostatic Discharge - Machine Model    | ESD MM  | 400   | V    | C           |


Notes:

- 5. For a device with any single die active and mounted with the collector lead on 25mm x 25mm 2oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still air conditions whilst operating in steady-state.
- 6. Same as Note 5, except both die are active and equally sharing power.
- 7. Thermal resistance from junction to solder-point (at the end of the collector lead).
- 8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.


## Thermal Characteristics and Derating Information




**Safe Operating Area**




**Safe Operating Area**



**Transient Thermal Impedance**



**Derating Curve**




**Pulse Power Dissipation**

**NPN - Electrical Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

| Characteristic                                | Symbol                      | Min | Typ  | Max  | Unit          | Test Condition   |
|---|-----------------------------|-----|------|------|---------------|--|
| Collector-Base Breakdown Voltage              | $\text{BV}_{\text{CBO}}$    | 120 | —    | —    | V             | $I_C = 100\mu\text{A}$   |
| Collector-Emitter Breakdown Voltage (Note 9)  | $\text{BV}_{\text{CEO}}$    | 100 | —    | —    | V             | $I_C = 10\text{mA}$  |
| Emitter-Base Breakdown Voltage                | $\text{BV}_{\text{EBO}}$    | 7   | —    | —    | V             | $I_E = 100\mu\text{A}$   |
| Collector Cut-Off Current                     | $I_{\text{CBO}}$            | —   | < 1  | 0.1  | $\mu\text{A}$ | $V_{\text{CB}} = 100\text{V}$  |
|   |                             | —   | —    | 10   | $\mu\text{A}$ | $V_{\text{CB}} = 100\text{V}, T_A = +125^\circ\text{C}$                          |
| Emitter Cut-Off Current                       | $I_{\text{EBO}}$            | —   | < 1  | 0.1  | $\mu\text{A}$ | $V_{\text{EB}} = 5.6\text{V}$  |
| DC Current Transfer Static Ratio (Note 9)     | $h_{\text{FE}}$             | 70  | 200  | —    | —             | $I_C = 50\text{mA}, V_{\text{CE}} = 2\text{V}$                                   |
|   |                             | 100 | 200  | 300  |               | $I_C = 500\text{mA}, V_{\text{CE}} = 2\text{V}$                                  |
|   |                             | 55  | 110  | —    |               | $I_C = 1\text{A}, V_{\text{CE}} = 2\text{V}$                                     |
|   |                             | 25  | 55   | —    |               | $I_C = 2\text{A}, V_{\text{CE}} = 2\text{V}$                                     |
| Collector-Emitter Saturation Voltage (Note 9) | $V_{\text{CE}(\text{sat})}$ | —   | 0.13 | 0.30 | V             | $I_C = 1\text{A}, I_B = 100\text{mA}$  |
|   |                             | —   | 0.23 | 0.50 |               | $I_C = 2\text{A}, I_B = 200\text{mA}$  |
| Base-Emitter Saturation Voltage (Note 9)      | $V_{\text{BE}(\text{sat})}$ | —   | 0.9  | 1.25 | V             | $I_C = 1\text{A}, I_B = 100\text{mA}$  |
| Base-Emitter Turn-on Voltage (Note 9)         | $V_{\text{BE}(\text{on})}$  | —   | 0.8  | 1.0  | V             | $I_C = 1\text{A}, V_{\text{CE}} = 2\text{V}$                                     |
| Transitional Frequency                        | $f_T$                       | 140 | 175  | —    | MHz           | $I_C = 100\text{mA}, V_{\text{CE}} = 5\text{V}, f = 100\text{MHz}$               |
| Output Capacitance                            | $C_{\text{obo}}$            | —   | —    | 30   | pF            | $V_{\text{CB}} = 10\text{V}, f = 1\text{MHz}$                                    |
| Switching Time                                | $t_{\text{on}}$             | —   | 80   | —    | Ns            | $V_{\text{CC}} = 10\text{V}, I_C = 500\text{mA}, I_{B1} = -I_{B2} = 50\text{mA}$ |
|   | $t_{\text{off}}$            | —   | 1200 | —    | ns            |  |


Note: 9. Measured under pulsed conditions. Pulse width  $\leq 300\mu\text{s}$ . Duty cycle  $\leq 2\%$ .

**NPN – Typical Electrical Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)




Ic - Collector Current (Amps)

**$V_{CE(sat)}$  v  $I_C$**




Ic - Collector Current (Amps)

**$h_{FE}$  v  $I_C$**




Ic - Collector Current (Amps)

**$V_{BE(sat)}$  v  $I_C$**



Ic - Collector Current (Amps)

**$V_{BE(on)}$  v  $I_C$**



Ic - Collector Current (Amps)


**Switching Speeds**

**PNP - Electrical Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)


| Characteristic                                | Symbol                      | Min  | Typ   | Max   | Unit          | Test Condition  |
|---|-----------------------------|------|-------|-------|---------------|---|
| Collector-Base Breakdown Voltage              | $\text{BV}_{\text{CBO}}$    | -120 | —     | —     | V             | $I_C = -100\mu\text{A}$   |
| Collector-Emitter Breakdown Voltage (Note 9)  | $\text{BV}_{\text{CEO}}$    | -100 | —     | —     | V             | $I_C = -10\text{mA}$  |
| Emitter-Base Breakdown Voltage                | $\text{BV}_{\text{EBO}}$    | -7   | —     | —     | V             | $I_E = -100\mu\text{A}$   |
| Collector Cut-Off Current                     | $I_{\text{CBO}}$            | —    | < 1   | -0.1  | $\mu\text{A}$ | $V_{\text{CB}} = -100\text{V}$  |
|   |                             | —    | —     | -10   | $\mu\text{A}$ | $V_{\text{CB}} = -100\text{V}, T_A = +125^\circ\text{C}$                            |
| Emitter Cut-Off Current                       | $I_{\text{EBO}}$            | —    | < 1   | -0.1  | $\mu\text{A}$ | $V_{\text{EB}} = -5.6\text{V}$  |
| DC Current Transfer Static Ratio (Note 8)     | $h_{\text{FE}}$             | 70   | 200   | —     | —             | $I_C = -50\text{mA}, V_{\text{CE}} = -2\text{V}$                                    |
|   |                             | 100  | 200   | 300   |               | $I_C = -500\text{mA}, V_{\text{CE}} = -2\text{V}$                                   |
|   |                             | 55   | 170   | —     |               | $I_C = -1\text{A}, V_{\text{CE}} = -2\text{V}$                                      |
|   |                             | 25   | 55    | —     |               | $I_C = -2\text{A}, V_{\text{CE}} = -2\text{V}$                                      |
| Collector-Emitter Saturation Voltage (Note 9) | $V_{\text{CE}(\text{sat})}$ | —    | -0.17 | -0.30 | V             | $I_C = -1\text{A}, I_B = -100\text{mA}$   |
|   |                             | —    | -0.30 | -0.50 |               | $I_C = -2\text{A}, I_B = -200\text{mA}$   |
| Base-Emitter Saturation Voltage (Note 9)      | $V_{\text{BE}(\text{sat})}$ | —    | -0.90 | -1.25 | V             | $I_C = -1\text{A}, I_B = -100\text{mA}$   |
| Base-Emitter Turn-On Voltage (Note 9)         | $V_{\text{BE}(\text{on})}$  | —    | -0.80 | -1.0  | V             | $I_C = -1\text{A}, V_{\text{CE}} = -2\text{V}$                                      |
| Transitional Frequency                        | $f_T$                       | 100  | 140   | —     | MHz           | $I_C = -100\text{mA}, V_{\text{CE}} = -5\text{V}, f = 100\text{MHz}$                |
| Output Capacitance                            | $C_{\text{obo}}$            | —    | —     | 30    | pF            | $V_{\text{CB}} = -10\text{V}, f = 1\text{MHz},$                                     |
| Switching Time                                | $t_{\text{on}}$             | —    | 35    | —     | ns            | $V_{\text{CC}} = -10\text{V}, I_C = -500\text{mA}, I_{B1} = -I_{B2} = -50\text{mA}$ |
|   | $t_{\text{off}}$            |      | 600   |       | ns            |   |

Note: 9. Measured under pulsed conditions. Pulse width  $\leq 300\mu\text{s}$ . Duty cycle  $\leq 2\%$ .


**PNP – Typical Electrical Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)




Ic - Collector Current (Amps)




$h_{FE}$  v  $I_c$



Ic - Collector Current (Amps)



$V_{BE(\text{sat})}$  v  $I_c$




Ic - Collector Current (Amps)

**Switching Speeds**


## Package Outline Dimensions

Please see AP02002 at <http://www.diodes.com/datasheets/ap02002.pdf> for the latest version.



## Suggested Pad Layout

Please see AP02001 at <http://www.diodes.com/datasheets/ap02001.pdf> for the latest version.



Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device terminals and PCB tracking.

**IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

**LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)