






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		F2	REVISED PER ECR-12-010267	05JUN12	JR	TM
			G	REVISED PER ECR-13-011599	08NOV13	AV	RP



- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.05 – 0.15MM² (30–26 AWG).
- 3 INSULATION RANGE: 0.89–1.27[.035–.050] DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



5	0.25[.010] BRASS	1-794217-0
1	0.25[.010] BRASS	794217-3
PRE-TIN	0.25[.010] BRASS	794217-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		PRODUCT SPEC			
	1 PLC ± -		APPLICATION SPEC			
MATERIAL		2 PLC ± -	SIZE		DRAWING NO	
SEE TABLE		3 PLC ± 0.30 [.012]	A2		00779	
FINISH		4 PLC ± -	WEIGHT		C=794217	
SEE TABLE		ANGLES ± -	CUSTOMER DRAWING		SCALE 10:1	
					SHEET 1 of 1	
					REV G	