

SD006

Doc. # SD-19193-006


Customer Dwg:

MATERIAL: Copper
 PLATING: Electro-Tin
 STUD SIZE: "D" $\pm .005$

10 - .198
 14 - .265
 56 - .328
 38 - .390
 76 - .453
 12 - .515
 58 - .656
 34 - .781
 209 = .209
 413 = .413

VERSAKRIMP

BRAZE SEAM



Customer Dimensions

Part No.	Wire Size	"W"	"C" Min	"E" Max	"B" Min	"L" Max	"A" Min	Stock Thkns. (A)	"F" Max	AVAILABLE STUD SIZE
F-366-	#4	$\frac{.652}{.678}$	.520	1.028	.425	1.385	.280	REF. .075	.470	209, 413 10, 14, 56, 38, 76, 12,
F-367-	#4	$\frac{.465}{.485}$	.520	1.028	.425	1.288	.280	REF. .075	.470	10, 14, 56
F-369-	#4	$\frac{.875}{.895}$	.989	1.497	.425	1.970	.280	REF. .075	.470	14, 56, 38, 76, 12, 58
F-370-	#4	$\frac{1.250}{1.270}$	.989	1.497	.425	2.158	.280	REF. .075	.470	14, 56, 38, 76, 12, 58, 34

For parts to be on tape add "T" at end of part number.

ETC molex
 INCORPORATED

TITLE:

"F" RING TONGUE
 TERMINAL

DIMENSIONAL TOLERANCE
 UNLESS OTHERWISE SPECIFIED

FRAC.

DEC.

ANG.

 $\pm$ $\pm$ $\pm$

REVISION

SCALE: NONE

DATE

DRWN. BY: LEM

3/2/70

CHKD. BY:

APPRD. BY:

DRAWING NO.:

A ETC 30245
11/7 RGM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19193-0277](#) [19193-0286](#)