

NOTES :

1- MATERIAL:

-HOUSING: POLYESTER FIBER GLASS FILLED UL 94-V0
COLOR BLACK.

-TERMINAL: PHOSPHOR BRONZE.

PLATING:

POST PLATE 0.00127-0.00152/.000050-.000060 GOLD IN
CONTACT AREA , 0.00190/.000075 MIN PURE TIN
IN TAIL AREA BOTH OVER 0.00127/.000050 MIN NICKEL
OVERALL.

-SHIELD: BRASS PLATED WITH 0.0020/.00078 TIN

2- JACK FOR MATING WITH F.C.C. 68 SHIELDED PLUGS (95043 MOLEX SERIES).

3- PRODUCT SPECIFICATION PS-95040 AND PS-85505 (SECTION 5.2).

4- APPLICATION SPECIFICATION AS-95001.

5- PACKAGING SPECIFICATION PK-95022 (TRAY PACKAGING).

6- EXCEEDS CATEGORY 5E PERFORMANCE.



7- PC BOARD THICKNESS: 1.57/.062

OPTIONAL RIBS

JACK WITH RIBS
MATERIAL NR.: 85507-0001

JACK WITHOUT RIBS
MATERIAL NR.: 85507-0002

P.C.B. MOUNTING PATTERN
(see from component side)
SCALE 2:1



ENTER DESCRIPTION EC NO: MG2005-0147 DRWN:CEBASTI CHKD:FCARABET APPR:KNOLLER	2004/10/21 2004/10/22 2004/11/04	DESCRIPTION REVISION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
						MM/IN		4:1	METRIC	◎ □		
				mm	INCH	DRAWN BY	DATE	TITLE TOP ENTRY HIGH SPEED SHIELDED MODULAR JACK THROUGH HOLE 8 CIRCUIT				
				4 PLACES ± --- ± ---	FB	98/08/05	CHECKED BY					DATE
				3 PLACES ± --- ± .006	FM	98/08/05	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED			
				2 PLACES ± 0.15 ± .010	FB	98/08/05	MATERIAL NO.	DOCUMENT NO.				
				1 PLACE ± 0.25 ± ---	ANGULAR ± 2 °		SEE CHART		SD-85507-001		1 OF 1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										