



- | | | | |
|------|------|-------|-------|
| .065 | 1.65 | 2.808 | 71.32 |
| .063 | 1.60 | .650 | 16.51 |
| .060 | 1.52 | .500 | 12.70 |
| .045 | 1.14 | .450 | 11.43 |
| .030 | 0.76 | .425 | 10.80 |
| .028 | 0.71 | .312 | 7.92 |
| .015 | 0.38 | .300 | 7.62 |
| .012 | 0.30 | .180 | 4.57 |
| .010 | 0.25 | .157 | 3.99 |
| .008 | 0.20 | .156 | 3.96 |
| .005 | 0.13 | .125 | 3.18 |
| .003 | 0.08 | .078 | 1.98 |
| .001 | 0.03 | .073 | 1.85 |
| .000 | 0.00 | .070 | 1.78 |
| IN | MM | IN | MM |
- CONVERSION TABLE

4,8,12,16	644960-1
POST NO. OMITTED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL	28MAR96	 TE Connectivity	
		CHE R. SWING	28MAR96		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: DECIMALS ± .005 FRACTIONS ± .005 ANGLES ± .005	APPROV D. CLARK	28MAR96	NAME	MTA-156 HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE, REAR BEND, .045 SQUARE POST, TIN PLATED, 18 POSITION, OMITTED POST
		PRODUCT SPEC			
		APPLICATION SPEC		SIZE CASE CODE DRAWING NO A1 00779 C 644960	RESTRICTED TO
		WEIGHT			
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	SHEET 1 of 1 REV C
					