


	DIN 7500 C			450-550 HV
---	------------	--	--	------------



1) Tapered thread end max. 4P
2) Trilobular

BN 2724

Pozi pan head thread forming screws

type C, form Z, metric thread

Steel case-hardened 450-550 HV

zinc plated blue, waxed

- ~UNI 8112



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.



Application: steel, aluminum, aluminum die-casting, zinc, zinc die-casting, non ferrous materials.
A technical brochure is available on request.

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
5001676	M2	4	1,72	1	2,4	1,1	1,35	5
5001684								6
5309518								8
1473603	M2,5	5	2,12	1	2,6	1,27	1,52	4
1669745								5
1473611								6
1473638								8
1473646								10
1473654								12
1473662								16
1473670								20
1669753	M3	6	2,52	1	3	1,68	1,93	5
1473689								6
1473697								8
1473700								10
1473719								12
3642088								14
1473727								16
1473735								20
3059820								25
1473743	M4	8	3,25	2	4,3	1,9	2,36	6
1473751								8
1473778								10
1473786								12
3642089								14

1473794								16
---------	--	--	--	--	--	--	--	----

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1473808	M4	8	3,25	2	4,3	1,9	2,36	20
1473816								25
1473824								30
3642092								40
5001692	M5	10	3,95	2	5	2,64	3,1	6
1473832								8
1473840								10
1473859								12
1473867								16
1473875								20
1473883								25
1473891								30
3642093								40
1473905	M6	12	4,75	3	6,7	3,02	3,48	10
1473913								12
1473921								16
1473948								20
1473956								25
1473964								30
1473972								40