






WAFER: 15% GLASS FILLED POLYESTER
TO UL 94v-0.
COLOUR: BLACK.



- NOTES
1. PLEASE REFER TO SHT 2 FOR PLATING DETAILS.
 2. PLEASE REFER TO SHT 3-8 FOR DIMENSIONS C & D.
 3. RECOMMENDED PCB THICKNESS 1.60MM
 4. PRODUCT SPECIFICATION: PS-99020-0001

CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) _{-0.008}		CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) _{-0.008}	
2X 1			(2.54)	.100	2X21	(50.80)	2.000	(53.34)	2.100
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34)	2.100	(55.88)	2.200
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88)	2.200	(58.42)	2.300
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42)	2.300	(60.96)	2.400
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96)	2.400	(63.50)	2.500
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50)	2.500	(66.04)	2.600
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04)	2.600	(68.58)	2.700
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58)	2.700	(71.12)	2.800
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12)	2.800	(73.66)	2.900
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66)	2.900	(76.20)	3.000
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20)	3.000	(78.74)	3.100
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74)	3.100	(81.28)	3.200
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28)	3.200	(83.82)	3.300
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82)	3.300	(86.36)	3.400
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36)	3.400	(88.90)	3.500
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90)	3.500	(91.44)	3.600
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44)	3.600	(93.98)	3.700
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98)	3.700	(96.52)	3.800
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52)	3.800	(99.06)	3.900
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06)	3.900	(101.60)	4.000



CHANGE DOC. NO EC NO: S2012-0490 DRWN:ATSEE CHKD:SKANG APPR:MLONG REV O	2011/12/21 2011/12/28 2012/02/24	DESCRIPTION	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
						DRAWN BY DATE		TITLE C GRID III DUAL ROW STRAIGHT PIN HEADER			
						CHECKED BY DATE					
				4 PLACES ± --- ± ---		DB 1987/07/16		MOLEX INCORPORATED			
				3 PLACES ± --- ± ---		DB 1987/07/16					
				2 PLACES ± 0.20 ± ---		APPROVED BY DATE		DOCUMENT NO. SD-90131-001			
1 PLACE ± --- ± ---		MLONG 2012/02/24		SHEET NO. 1 OF 8							
ANGULAR ± 3 °		MATERIAL NO.					SEE TABLE				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10		9		8		7		6		5		4		3		2		1	
F	CIRCUIT SIZE	PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.													
		90131-0121		90131-0761		90131-0921													
		2 X 1		2 X 2		2 X 3													
		2 X 3		2 X 4		2 X 5													
		2 X 4		2 X 5		2 X 6													
		2 X 5		2 X 6		2 X 7													
		2 X 6		2 X 7		2 X 8													
		2 X 7		2 X 8		2 X 9													
		2 X 8		2 X 9		2 X 10													
		2 X 9		2 X 10		2 X 11													
E	DIM C (+0.20 ±.008 (6.75) .266	2 X 11		2 X 12		2 X 13													
		2 X 12		2 X 13		2 X 14													
		2 X 13		2 X 14		2 X 15													
		2 X 14		2 X 15		2 X 16													
		2 X 15		2 X 16		2 X 17													
		2 X 16		2 X 17		2 X 18													
		2 X 17		2 X 18		2 X 19													
		2 X 18		2 X 19		2 X 20													
		2 X 19		2 X 20		2 X 21													
		2 X 20		2 X 21		2 X 22													
D	DIM D (+0.20 0.30 ±.008 -.012 (2.90) .114	2 X 21		2 X 22		2 X 23													
		2 X 22		2 X 23		2 X 24													
		2 X 23		2 X 24		2 X 25													
		2 X 24		2 X 25		2 X 26													
		2 X 25		2 X 26		2 X 27													
		2 X 26		2 X 27		2 X 28													
		2 X 27		2 X 28		2 X 29													
		2 X 28		2 X 29		2 X 30													
		2 X 29		2 X 30		2 X 31													
		2 X 30		2 X 31		2 X 32													
C		2 X 31		2 X 32		2 X 33													
		2 X 32		2 X 33		2 X 34													
		2 X 33		2 X 34		2 X 35													
		2 X 34		2 X 35		2 X 36													
		2 X 35		2 X 36		2 X 37													
		2 X 36		2 X 37		2 X 38													
		2 X 37		2 X 38		2 X 39													
		2 X 38		2 X 39		2 X 40													
		2 X 39		2 X 40		90131-0160		90131-0800		90131-0960									
		2 X 40		90131-0160		90131-0800		90131-0960											
B																			
A	STANDARD PRODUCTS																		


tb_frame_A3_P_AM_T
Rev. F 2009/06/18


NON-STANDARD PRODUCTS
NOT FOR GENERAL RELEASE

CIRCUIT SIZE	PLATING TYPE A PART NO.	PIN PART NUMBER	WAFER PART NUMBER	DIM C ^(±0.20) ±.008	DIM D ^(±0.20) ±.008 -.012
2 X 6	90131-3126	90129-2008	90131-0040	(14.60) .575	(2.38) .094
2 X 36	90131-3128	90129-2008	90131-0040	(14.60) .575	(2.38) .094
2 X 40	90131-3127	90129-2008	90131-0040	(14.60) .575	(2.38) .094



STANDARD PRODUCTS

CHANGE DOC. NO EC NO: S2012-0490 DRWN:ATSEE 2011/12/21 CHKD:SKANG 2011/12/28 APPR:MLONG 2012/02/24 O	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY DB	DATE 1987/07/16	C GRID III DUAL ROW STRAIGHT PIN HEADER				
			4 PLACES	± ---	± ---	CHECKED BY	DATE					
			3 PLACES	± ---	± ---	DB	1987/07/16	MOLEX INCORPORATED				
			2 PLACES	± 0.20	± ---	APPROVED BY	DATE					
			1 PLACE	± ---	± ---	MLONG	2012/02/24					
			ANGULAR ± 3 °			MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-90131-001				8 OF 8
SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												





CKT SIZE	A	B
2	5.00	9.90
3	10.00	14.90
4	15.00	19.90




KEYING, CODING, & LATCH IDENTIFICATION
(7 CKT EXAMPLE SHOWN)

- NOTES:
- MATERIALS:
HOUSING: PA 6, UL94 V-2
COLOUR: SEE SHEET 2
TERMINAL: PHOSPHOR BRONZE, (0.50)/.020 THICK REF
PLATING: (2 µm)/79 µm MIN SILVER IN CONTACT AREA
(0.10 µm)/.004 µm MIN SILVER FLASH ALLOW
 - PRODUCT CONFORMS TO SPECIFICATION PS-99020-0037
 - ACCEPTS CABLE, PER ES-99036-0010
 - SEE SUBSEQUENT SHEETS FOR PART NUMBERS SHOWING THE VARIOUS CODING, KEYING AND LATCHING OPTIONS.
 - PACKAGING SPECIFICATION PK-90833-001
 - APPLICATION SPECIFICATION AS-99033-0004

ADDED PART NUMBERS		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
					MM ONLY		1:1	METRIC		
EC NO: IPG2014-1233		AC	▽=0 ▽=0	mm	INCH	DRAWN BY	DATE	TITLE		
2014/01/06										
CHYKD: DRWNCMONAHAN				4 PLACES	±---	±---	GMC SWEEN	2004/10/14		
APPR: STIGLITZ				3 PLACES	±---	±---	CHECKED BY	DATE		
2014/01/20				2 PLACES	±0.05	±---	BMAGUIRE	2005/01/07		
		1 PLACE	±0.1	±---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED			
		ANGULAR ±---°		BMAGUIRE 2010/10/20						
				MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE FOLLOWING SHEETS		SD-91779-001		
				SIZE		A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		


13	12	11	10	9								
MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP	REF.			
91779-0001	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		NONE	K00			
91779-0002	91779-9001	2	NATURAL	1b, 2a	01c, d20	1/2		NONE	K01			
91779-0003	91779-9001	2	NATURAL	1a, 2b	d20	1/2		NONE	K05			
91779-0004	91779-9001	2	NATURAL	1a	01c, d20	1/2		NONE	K12			
91779-0005	91779-9001	2	NATURAL	1a, 2b	01c, d20	1/2		BLUE	K48			
91779-0006	91779-9004	2	RED	1a, 1b 2a, 2b	NONE	1/2		NONE	K41			
91779-0007	91779-9001	2	NATURAL	2a	01c	1/2		NONE	K42			
91779-0008	91779-9004	2	RED	1a, 1b 2a, 2b	d20	1/2		NONE	K34			
91779-0009	PART NUMBER OBSOLETE, REPLACED WITH 91779-0006.											
91779-0010	91779-9003	2	BLACK	1a, 1b 2a, 2b	NONE	1/2		NONE	K41			
91779-0011	91779-9001	2	NATURAL	1a	d20	1/2		NONE	K66			
91779-0012	91779-9001	2	NATURAL	1b	01c, d20	1/2		NONE	K16			
91779-0013	91779-9001	2	NATURAL	1a	NONE	1/2		NONE	K70			
91779-0014	91779-9001	2	NATURAL	1b 2a 2b	d20	1/2		NONE	K--			
91779-0015	91779-9001	2	NATURAL	1a, 1b 2a, 2b	d20	1/2		NONE	K34			
91779-0016	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c	1/2		NONE	K33			
91779-0017	91779-9004	2	RED	1a 1b 2b	NONE	1/2		NONE	K43			
91779-0018	91779-9001	2	NATURAL	1b 2b	01c	1/2		NONE	K09			
91779-0019	91779-9001	2	NATURAL	1b 2b	01c	1/2		GREEN	K--			
91779-0020	91779-9001	2	NATURAL	1a 2b	d20	1/2		GREEN	K--			
91779-0021	91779-9001	2	NATURAL	2a	01c, d20	1/2		BLACK	K--			
91779-0022	91779-9001	2	NATURAL	1b	d20	1/2		RED	K--			
91779-0023	91779-9001	2	NATURAL	1b 2b	01c	1/2		BLUE	K--			

MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	colour stripe	REF.
91779-0024	91779-9001	2	NATURAL	1b 2b	01c	1/2		ORANGE	K--
91779-0025	91779-9001	2	NATURAL	1a 1b	d20	1/2		NONE	K--
91779-0026	91779-9001	2	NATURAL	1a 2b	01c	1/2		NONE	K--
91779-0027	91779-9003	2	BLACK	1a 2b	NONE	1/2		NONE	K06
91779-0028	91779-9004	2	RED	2a 2b	NONE	1/2		NONE	K31
91779-0029	91779-9001	2	NATURAL	NONE	01c, d20	1/2		NONE	K--
91779-0030	91779-9001	2	NATURAL	1a 2a 2b	01c, d20	1/2		NONE	K62
91779-0031	91779-9001	2	NATURAL	1a 2a	01c, d20	1/2		NONE	K--
91779-0032	91779-9001	2	NATURAL	1b 2b	01c, d20	1/2		NONE	K--
91779-0033	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		RED	K09
91779-0034	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		GREEN	K--
91779-0035	91779-9001	2	NATURAL	2b	NONE	1/2		NONE	K--
91779-0036	91779-9001	2	NATURAL	1a, 1b 2a, 2b	NONE	1/2		NONE	K41
91779-0038	91779-9001	2	NATURAL	1b	NONE	1/2		NONE	K--



SEE SHEET 1 EC NO: IPG2014-4233 DRWN: MONAHAN 2014/01/06 CHKD: CHIKO APPR: STIGLITZ 2014/01/20 AC	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
	▽=0	4 PLACES ± --- ± ---	mm	INCH	DRAWN BY GMC/SWEEN	DATE 2004/10/14	TITLE RAST 5 INDIRECT FEMALE ASSEMBLY 16 AMPS
	▽=0	3 PLACES ± --- ± ---			CHECKED BY BMAGUIE	DATE 2005/01/07	
		2 PLACES ± 0.05 ± ---			APPROVED BY BMAGUIE	DATE 2010/10/20	
		1 PLACE ± 0.1 ± ---			MATERIAL NO.	DOCUMENT NO.	SHEET NO. 2 OF 5
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLES		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

CIRCUIT 2 CONTIN'D									
MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIPE	REF.
91779-0039	91779-9001	2	NATURAL	1a 2b	NONE	1/2		NONE	K06



SEE SHEET 1 EC NO: IPG2014-4233 DRAWN: MONAHAN CHKD: APPR: STRIFFLIN AC	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	TITLE RAST 5 INDIRECT FEMALE ASSEMBLY 16 AMPS molex DOCUMENT NO. SD-91779-001			
			4 PLACES	± ---	± ---	GMC SWEEN	2004/10/14				
			3 PLACES	± ---	± ---	CHECKED BY	DATE				
			2 PLACES	± 0.05	± ---	BMAGUIE	2005/01/07				
			1 PLACE	± 0.1	± ---	APPROVED BY	DATE	SHEET NO. 3 OF 5			
			0 PLACE	±	±	BMAGUIRE	2010/10/20				
			ANGULAR ± ---°			MATERIAL NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLES					
						SIZE A2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

