


ADSL Transformers

For Analog Devices
chip sets



These transformers have been designed to provide optimum performance with various ADSL chip sets from Analog Devices.

They feature a compact size, minimum DC resistance and very low leakage inductance. Primary inductance is stable from -40° C to +85° C and the longitudinal balance is optimized for the best overall performance at the ADSL transmission speed. Most parts have been designed to meet UL 1950 requirements.

For free evaluation samples or to discuss custom designs, please contact Coilcraft.

SPECIFICATIONS

Part number	Style	Chip set	Line side inductance (mH)	Leakage inductance (μH) max	DCR (Ω) max	
					Chip side	Line side
AS7787-A	Leaded	AD20MSP910/918 CO/CPE	5.0 ± 10%	16	1.21 (10-8), 1.65 (9-7)	1.42 (1-3, 2-4)
AS8456-A	SMT	AD20MSP910/918 CO/CPE	5.0 ± 10%	16	1.21 (10-8), 1.65 (9-7)	1.42 (1-3, 2-4)
AS8923-A	Leaded	AD20MSP930 CO	2.03 min	7.5	.60 (1-3, 2-4)	.60 (10-8), .60 (9-7)
AS8908-A	SMT	AD20MSP930 CO	2.03 min	7.5	.60 (1-3, 2-4)	.60 (10-8), .60 (9-7)
AS8925-A	Leaded	AD20MSP930 CPE	2.42 min	7.5	.55 (1-3, 2-4)	.58 (10-8), .58 (9-7)
AS8924-A	SMT	AD20MSP930 CPE	2.42 min	7.5	.55 (1-3, 2-4)	.58 (10-8), .58 (9-7)

Part number	Dielectric strength (V)	Turns ratio line:chip	Capacitance (pF) max	Longitudinal balance (dB) min	THD @ 20 kHz (dB) typ	Designed to meet
AS7787-A	1875	1:1	55	40 (20 kHz - 1 MHz)	-89	UL 1459, 1950
AS8456-A	1875	1:1	55	40 (20 kHz - 1 MHz)	-89	UL 1459, 1950
AS8923-A	2300	1.1:1		40 (20 kHz - 1 MHz)	-85	UL 1459, 1950
AS8908-A	2300	1.1:1		40 (20 kHz - 1 MHz)	-85	UL 1459, 1950
AS8925-A	2300	1.2:1		40 (20 kHz - 1 MHz)	-85	UL 1459, 1950
AS8924-A	2300	1.2:1		40 (20 kHz - 1 MHz)	-85	UL 1459, 1950

1. All electrical specifications referenced to line side.

2. Operating temperature range -40° C to +85° C.

3. Electrical specifications at 25° C.

Coilcraft


Specifications subject to change without notice. Document 244-1 Revised 1/15/01

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469
E-mail info@coilcraft.com Web http://www.coilcraft.com

NEW!


ADSL Transformers for Analog Devices

Leaded Transformers




A max	B max	C max	D min	E	F typ	G max
.550	.550	.500	.100	.400	.100	.032
13,97	13,97	12,70	3,0	10,16	2,54	0,82

Surface Mount Transformers



A max	B max	C max	E	F typ	G typ
.530	.705	.500	.629	.098	.053 x .034
13,46	17,91	12,70	15,98	2,49	1,35 x 0,86

Schematic



Coilcraft

Specifications subject to change without notice. Document 244-2 Revised 1/15/01

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469
E-mail info@coilcraft.com Web <http://www.coilcraft.com>