



Description:

A Widely used "Industry Standard" silicon NPN transistor in a TO-18 type case designed for applications such as medium-speed switching and amplifiers from audio to VHF frequencies.



Features:

Low collector saturation Voltage : 1V (Max.)

High current gain-bandwidth product: $f_T = 300\text{MHz}$ (Min.) at $I_C = 20\text{mA}$

Absolute Maximum Ratings:

Collector-Base Voltage, V_{CBO}	: 60V
Collector-Emitter Voltage, V_{CEO}	: 60V
Emitter-Base Voltage, V_{EBO}	: 6V
Continuous Collector Current, I_C	: 50mA
Base Current I_B	: 15A
Total Device Dissipation ($T_C = +25^\circ\text{C}$), P_D	: 360mW
Derate above 25°C	: $>2.06/^\circ\text{C}$
Total Device Dissipation ($T_C = +25^\circ\text{C}$), P_D	: 1.2W
Derate above 25°C	: $6.85\text{mW}/^\circ\text{C}$

Operating Junction Temperature Range, T_J : -65°C to $+200^\circ\text{C}$

Storage Temperature Range, T_{stg} : -65°C to $+200^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min.	Max.	Unit
-----------	--------	-----------------	------	------	------

OFF Characteristics

Collector-Emitter Breakdown Voltage	V _{(BR)CEO}	I _C = 10mA, I _B = 0	60	-	V
Collector-Base Breakdown Voltage	V _{(BR)CBO}	I _C = 10μA, I _E = 0	60	-	
Emitter-Base Breakdown Voltage	V _{(BR)EBO}	I _C = 10μA, I _C = 0	6	-	
Collector Cut-off Current	I _C EX	V _{CB} = 45V, I _E = 0	-	-	-
	I _C BO		-	0.01	μA
		V _{CB} = 45V, I _E = 0, T _A = +150°C		-	
Emitter Cut-Off Current	I _E BO	V _{EB} = 5V, I _C = 0	-	10	nA
Base Cut-Off Current	I _B L		-	-	-

Parameter	Symbol	Test Conditions	Min.	Max.	Unit
-----------	--------	-----------------	------	------	------

ON Characteristics



DC Current Gain	h_{FE}	$V_{CE} = 2V, I_C = 25A$	15	60	-
		$V_{CE} = 5V, I_C = 50A$	5	-	-
		$V_{CE} = 5V, I_C = 10mA, (Note\ 1)$	-	800	-
		$V_{CE} = 5V, I_C = 10mA, T_A = -55^{\circ}C$	20	-	-
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 1mA, I_B = 0.1mA, (Note\ 1)$	-	0.35	V
	$V_{BE(sat)}$		-	-	-

Small-Signal Characteristics

Current Gain-Bandwidth Product	f_T	$V_{CE} = 5V, I_C = 5mA, f = 20MHz, (Note\ 2)$	60	-	MHz
Output Capacitance	C_{obo}	$V_{CB} = 5V, I_E = 0, f = 1MHz$	-	6	pF
Input Capacitance	C_{ibo}	$V_{BE} = 500mV, I_C = 0, f = 1MHz$	-	6	pF
Input Impedance	h_{ie}	$V_{CE} = 5V, I_C = 1mA, f = 1kHz$	3.5	24	kOhm
Voltage Feedback Ratio	h_{re}		-	-	-
Small-Signal Current Gain	h_{fe}	$V_{CE} = 5V, I_C = 1mA, f = 1kHz$	150	900	-
Output Admittance	h_{oe}	$V_{CE} = 5V, I_C = 1mA, f = 1kHz$	-	40	$\mu mhos$
Collector-Base Time Constant	rbC_c		-	-	-
Noise Figure	NF	$V_{CE} = 5V, I_C = 10\mu A, f = 1kHz, R_s = 10k\Omega$	-	3	dB


Note 1. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.

Note 2. f_T is defined as the frequency at which $|h_{fe}|$ extrapolates to unity.



Pin

1. Emitter
2. Base
3. Collector



Dim.	Min.	Max.
A	5.24	5.84
B	4.52	4.97
C	4.31	5.33
D	0.40	0.53
E	-	0.76
F	-	1.27
G	-	2.97
H	0.91	1.17
J	0.71	1.21
K	12.70	-
L	45°	45°

Dimensions : Millimetres

Part Number Table

Description	Part Number
Bipolar Transistor, NPN, 60V, TO-18	2N2484

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.