


# PCI-1721

## 12-bit, 4-ch Analog Output PCI Card with 16-ch Digital I/O



RoHS  
COMPLIANT  
2002/95/EC

FCC CE

### Features

- 10 MHz maximum digital update rate
- PCI-bus mastering for data transfer
- Auto calibration function
- Four analog output channels with 1,024 samples FIFO buffer
- A 12-bit DAC is equipped for each of analog output channels
- Real-time waveform output function with internal/external pacer
- Synchronized output function
- Flexible output types and range settings
- Keeps the output settings and values after system hot reset
- 16-ch DI/O and one 10 MHz 16-bit resolution counter
- BoardID™ switch

### Introduction

PCI-1721 is an advanced high-speed analog output card for the PCI bus, and each of analog output channels are equipped with a 12-bit, double-buffered DAC. It features many powerful and unique functions, like a waveform output function with 10 MHz maximum update rate, auto-calibration and a BoardID switch. PCI-1721 is an ideal solution for industrial applications where high-speed continuous analog output or real-time waveform output functions are required.

### Specifications

#### Analog Output

- **Channels** 4
- **Resolution** 12 bits
- **FIFO Size** 1,024 samples
- **Output Rate** 10 MHz or static update
- **Reference Clock** Internal: 10 MHz  
External Clock Frequency: 10 MHz max.  
External Voltage Range: 0.8 V max., 2 V min.
- **Output Range** (Software programmable)

|                    |                                 |                      |
|--------------------|---------------------------------|----------------------|
| Internal Reference | Unipolar                        | 0 ~ 5 V, 0 ~ 10 V,   |
|                    | Bipolar                         | ±5 V, ±10 V          |
|                    | Current Loop                    | 0 ~ 20 mA, 4 ~ 20 mA |
| External Reference | 0 ~ +x V @ +x V (-10 ≤ x ≤ 10)  |                      |
|                    | -x ~ +x V @ +x V (-10 ≤ x ≤ 10) |                      |

- **Slew Rate** 10 V/μs
- **Driving Capability** 10 mA
- **Output Impedance** 0.1 Ω max.
- **Operation Modes** Single/continuous/waveform/synchronized output
- **Accuracy** Relative: ±1 LSB  
Differential Non-linearity: ±1 LSB (monotonic)

#### Digital Input/Output

- **Channels** 16 (shared by input/output)
- **Compatibility** 5 V/TTL
- **Input Voltage** Logic 0: 0.8 V max.  
Logic 1: 2.0 V min.
- **Output Capability** Sink: 0.5 V @ 24 mA  
Source: 2.0 V @ -15 mA

#### Counter/Timer

- **Channels** 1
- **Resolution** 16 bits
- **Compatibility** 5 V/TTL
- **Max. Input Frequency** 10 MHz
- **Reference Clock** Internal: 10 MHz  
External Clock Frequency: 10 MHz max.  
External Voltage Range: 0.8 V max, 2.0 V min.

#### General

- **Bus Type** PCI V2.2
- **I/O Connectors** 1 x 68-pin SCSI female connector
- **Dimensions (L x H)** 175 x 100 mm (6.9" x 3.9")
- **Power Consumption** Typical: 5 V @ 850 mA, 12 V @ 600 mA  
Max.: 5 V @ 1 A, 12 V @ 700 mA
- **Operating Temperature** 0 ~ 60° C (32 ~ 140° F) (refer to IEC 68-2-1, 2)
- **Storage Temperature** -20 ~ 85° C (-4 ~ 185° F)
- **Storage Humidity** 5 ~ 95% RH, non-condensing (refer to IEC 68-2-3)

### Ordering Information

- **PCI-1721** 12-bit, 4-ch Advanced PCI Analog Output Card

#### Accessories

- **PCL-10168-1** 68-pin SCSI Shielded Cable, 1 m
- **PCL-10168-2** 68-pin SCSI Shielded Cable, 2 m
- **ADAM-3968** 68-pin DIN-rail SCSI Wiring Board