







NOTES:

1. MATERIAL: A - NYLON, UL94V-0, COLOR: WHITE
B - NYLON, UL94V-0, COLOR: MOLDED BLACK
2. FINISH: SEE TERMINAL DRAWING
3. PRODUCT SPECIFICATION: PS-10-07.
4. PACKAGING: PER PK-2695-001
5. HOUSING TO BE USED WITH CRIMP TERMINAL SERIES 2759, 6459, 41572. PARTS MADE AFTER 4/19/2012 WILL ALSO ACCEPT 4809 AND 8088 SERIES TERMINALS. FOR USE WITH 22-30 GAUGE WIRE WITH (1.57)/.062 DIAMETER MAXIMUM WIRE INSULATION.
6. LAST CIRCUIT NUMBER NOT PRESENT ON 2-6 CKT AND MAY OR MAY NOT BE PRESENT ON 7-16 CKT SIZES.
7. CIRCUIT NUMBER "1" AND ENGINEERING NUMBER TO APPEAR ON PARTS 3 CKTS AND HIGHER.
8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
9. THE PARTS LISTED ON THIS DRAWING ARE CONSTRUCTED TO MEET THE REQUIREMENT FOR DIRECT SUPPORT OF UNINSULATED LIVE PARTS AS DESCRIBED IN UL508C.
10. THIS DRAWING REPLACES 26950000-SD.

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
= 0	REDRAWN IN NX EC NO: 115759 DRWN: JQUILES CHKD: MKIPPER REV APPR: FSMITH	2017/06/01 2017/06/08 2017/06/15	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex® KK 2.54/.100 CRIMP HOUSING 2695 SERIES HALOGEN FREE			
= 0						MM/IN		5:1					
= 0				MM	INCH	DRWN BY		DATE		PRODUCT CUSTOMER DRAWING SERIES MATERIAL NUMBER CUSTOMER 2695 SEE CHART GENERAL MARKET			
= 0			4 PLACES ± ±			JQUILES		2017/06/02					
= 0			3 PLACES ± ± 0.005			CHK'D BY		DATE		SHEET NUMBER 1 OF 2			
= 0			2 PLACES ± 0.13 ± 0.01			MKIPPER		2017/06/08					
= 0			1 PLACES ± 0.25 ±			APPR BY		DATE		DOCUMENT NUMBER 26950000-SD DOC TYPE PSD DOC PART 000			
= 0			0 PLACES ± ±			FSMITH		2017/06/09					
= 0			ANGULAR TOL ± 0.5			DRAWING SIZE		THIRD ANGLE PROJECTION					
= 0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			C							

H	12			11			10			9			8			7			6			5			4			3			2			1		
	2695-N						2695-NR						2695-NRP						2695-NRP-BK																	
	PART NUMBER	ENGINEERING NUMBER	VOID	PART NUMBER	ENGINEERING NUMBER	VOID	PART NUMBER	ENGINEERING NUMBER	VOID	PART NUMBER	ENGINEERING NUMBER	VOID																								
	22-01-2021	2695-2		22-01-2027	2695-2R		22-01-3027	2695-2RP		50-29-1557	2695-2RP-BK																									
	22-01-2031	2695-3		22-01-2037	2695-3R		22-01-3037	2695-3RP		50-29-1558	2695-3RP-BK																									
	22-01-2041	2695-4		22-01-2047	2695-4R		22-01-3047	2695-4RP		50-29-1559	2695-4RP-BK																									
	22-01-2051	2695-5		22-01-2057	2695-5R		22-01-3057	2695-5RP		50-29-1560	2695-5RP-BK																									
	22-01-2061	2695-6		22-01-2067	2695-6R		22-01-3067	2695-6RP		50-29-1561	2695-6RP-BK																									
	22-01-2071	2695-7		22-01-2077	2695-7R		22-01-3077	2695-7RP		50-29-1562	2695-7RP-BK																									
	22-01-2081	2695-8		22-01-2087	2695-8R		22-01-3087	2695-8RP		50-29-1563	2695-8RP-BK																									
22-01-2091	2695-9		22-01-2097	2695-9R		22-01-3097	2695-9RP		50-29-1564	2695-9RP-BK																										
G	22-01-2101	2695-10		22-01-2107	2695-10R		22-01-3107	2695-10RP		50-29-1565	2695-10RP-BK																									
	22-01-2111	2695-11		22-01-2117	2695-11R		22-01-3117	2695-11RP		50-29-1566	2695-11RP-BK																									
	22-01-2121	2695-12		22-01-2127	2695-12R		22-01-3127	2695-12RP		50-29-1567	2695-12RP-BK																									
	22-01-2131	2695-13		22-01-2137	2695-13R		22-01-3137	2695-13RP		50-29-1568	2695-13RP-BK																									
	22-01-2141	2695-14		22-01-2147	2695-14R		22-01-3147	2695-14RP		50-29-1569	2695-14RP-BK																									
	22-01-2151	2695-15		22-01-2157	2695-15R		22-01-3157	2695-15RP		50-29-1570	2695-15RP-BK																									
	22-01-2161	2695-16		22-01-2167	2695-16R		22-01-3167	2695-16RP		50-29-1571	2695-16RP-BK																									



	RAMP	POLARIZING RIBS	MATERIAL
BLANK	NO	NO	NOTE 1A
R	YES	NO	NOTE 1A
RP	YES	YES	NOTE 1A
RP-BK	YES	YES	NOTE 1B

[illegible]