




- NOTES
- 1 MATERIAL:
-HOUSING: THERMOPLASTIC POLYESTER, COLOR GREY.
-CONTACTS: BRASS.
 - 2 PLATING CONTACT: 1,25 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn/Pb over 1,25 µm Ni ON SOLDER POST.
 - 3 PLATING CONTACT: 0,8 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn/Pb over 1,25 µm Ni ON SOLDER POST.
 - 4 PLATING CONTACT: 2,0 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn/Pb over 1,25 µm Ni ON SOLDER POST.
 - 5 PLATING CONTACT: 0,4 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn/Pb over 1,25 µm Ni ON SOLDER POST.
 - 6 SOLDER POSTS SUITABLE FOR P.C.B. HOLES
0,8±0,05 OR 1,0±0,1 DIA.
 - 7 8 HOLES SUITABLE FOR KEYING PIN PN. 215916-1.
 - 8 KEYING HOLES TO BE DRILLED BY CUSTOMER.

2--8 OBSOLETE	SEE NOTE 5	SEE NOTE 1	2-164306-8
2--7 OBSOLETE	SEE NOTE 4	SEE NOTE 1	2-164306-7
	SEE NOTE 3		2-164306-4
	SEE NOTE 2		2-164306-1
FINISH		MATERIAL	PARTNUMBER
-	-	-	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED
-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
-	-	-	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19
H	EH-0467-96	J.G. J.G. 21-05-97	AMP AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.
G	EH-1261-95	J.G. R.v.L 24-10-95	
F	H-9853	R.v.L J.v.G 31.03.93	
LTR.	REVISION RECORD	DR. CHK. DATE	32 POS. DIN 41612 F MALE 90° SOLDER CONNECTOR
DR. : R.v.Lokven	CHK. : J.GIBBELS	APP. : -	DWG.No. C-164306
DATE: 31.03.93	DATE: 27-5-97	DATE: -	REV.LTR. H
			SHEET 1 OF 1