


# DIK 1,5-LA 24GN/O-M

Order No.: 2715762

The illustration shows the product version DIK 1,5-LA 24RD/O-M



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2715762>

Sensor/actuator terminal block, Cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>,  
AWG: 24 - 12, Connection type: Screw connection, Width: 6.2 mm,  
Color: gray, Mounting type: NS 35/7.5, NS 35/15

## Commercial data

|                          |                                                                                     |
|--------------------------|-------------------------------------------------------------------------------------|
| GTIN (EAN)               |  |
| sales group              | A220                                                                                |
| Pack                     | 50 pcs.                                                                             |
| Customs tariff           | 85369010                                                                            |
| Catalog page information | Page 362 (CL-2009)                                                                  |

## Product notes

WEEE/RoHS-compliant since:  
08/01/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### General

|                       |      |
|-----------------------|------|
| Number of levels      | 3    |
| Number of connections | 4    |
| Color                 | gray |

|                                    |    |
|------------------------------------|----|
| Insulating material                | PA |
| Inflammability class acc. to UL 94 | V2 |

#### Dimensions

|                  |         |
|------------------|---------|
| Width            | 6.2 mm  |
| Length           | 55 mm   |
| Height NS 35/7.5 | 54.5 mm |
| Height NS 35/15  | 62 mm   |

#### Technical data

|                           |       |
|---------------------------|-------|
| Rated surge voltage       | 4 kV  |
| Pollution degree          | 3     |
| Surge voltage category    | III   |
| Insulating material group | I     |
| Nominal current $I_N$     | 24 A  |
| Nominal voltage $U_N$     | 250 V |

#### Connection data

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                         | 4 mm <sup>2</sup>    |
| Conductor cross section stranded min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                      | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                     | 24                   |
| Conductor cross section AWG/kcmil max                                      | 12                   |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid min.                           | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                           | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded min.                        | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                        | 1 mm <sup>2</sup>    |

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1 mm <sup>2</sup>    |
| Cross-section with insertion bridge, solid max.                                         | 4 mm <sup>2</sup>    |
| Cross-section with insertion bridge, stranded max.                                      | 2.5 mm <sup>2</sup>  |
| Type of connection                                                                      | Screw connection     |
| Stripping length                                                                        | 8 mm                 |
| Internal cylindrical gage                                                               | A3                   |
| Screw thread                                                                            | M3                   |
| Tightening torque, min                                                                  | 0.5 Nm               |
| Tightening torque max                                                                   | 0.6 Nm               |

#### Certificates / Approvals



Certification

CSA, CUL, GOST, UL

#### Accessories

| Item            | Designation                 | Description                                                                                                                                                                    |
|-----------------|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Assembly</b> |                             |                                                                                                                                                                                |
| 1413272         | ATP-DIK 1,5                 | Partition plate, Length: 65.3 mm, Width: 2 mm, Height: 60 mm, Color: gray                                                                                                      |
| 3022218         | CLIPFIX 35                  | Snap-on end bracket, for 35 mm NS 35/7.5 or NS 35/15 DIN rail, can be fitted with Zack strip ZB 8 and ZB 8/27, terminal strip marker KLM 2 and KLM, width: 9.5 mm, color: gray |
| 1201413         | E/UK 1                      | End clamps, for supporting the ends of double-level and three-level terminal blocks, width: 10 mm, color: gray                                                                 |
| 0801762         | NS 35/ 7,5 CU UNPERF 2000MM | DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                                                                              |
| 0801733         | NS 35/ 7,5 PERF 2000MM      | DIN rail, material: Steel, galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2 m                                                   |

|         |                            |                                                                                                                           |
|---------|----------------------------|---------------------------------------------------------------------------------------------------------------------------|
| 0801681 | NS 35/ 7,5 UNPERF 2000MM   | DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m                                          |
| 1201756 | NS 35/15 AL UNPERF 2000MM  | DIN rail, deep-drawn, high profile, unperforated, 1.5 mm thick, material: Aluminum, height 15 mm, width 35 mm, length 2 m |
| 1201895 | NS 35/15 CU UNPERF 2000MM  | DIN rail, material: Copper, unperforated, 1.5 mm thick, height 15 mm, width 35 mm, length: 2 m                            |
| 1201730 | NS 35/15 PERF 2000MM       | DIN rail, material: Steel, perforated, height 15 mm, width 35 mm, length: 2 m                                             |
| 1201714 | NS 35/15 UNPERF 2000MM     | DIN rail, material: Steel, unperforated, height 15 mm, width 35 mm, length: 2 m                                           |
| 1201798 | NS 35/15-2,3 UNPERF 2000MM | DIN rail, material: Steel, unperforated, 2.3 mm thick, height 15 mm, width 35 mm, length: 2 m                             |

#### Bridges


|         |               |                                                        |
|---------|---------------|--------------------------------------------------------|
| 2715940 | EB 80- DIK BU | Insertion bridge, Number of positions: 80, Color: blue |
| 2715953 | EB 80- DIK RD | Insertion bridge, Number of positions: 80, Color: red  |

#### Marking


|         |                         |                                                                                                                                                     |
|---------|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| 1007222 | SBS 6:UNBEDRUCKT        | Marker cards for modular terminal blocks, color: white                                                                                              |
| 0804374 | SK 6,2/3,8:FORTL.ZAHLEN | Marker card, printed horizontally, self-adhesive, 12 identical decades marked 1-10, 11-20 etc. up to 91-(99)100, sufficient for 120 terminal blocks |
| 1050499 | ZB 6:SO/CMS             | Zack strip, 10-section, divisible, special printing, marking according to customer requirements                                                     |

#### Diagrams/Drawings

Circuit diagram



- 1 = fixed bridge
- 2 = insertion bridge
- 3 = partition plate



**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachsmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact  
Technical modifications reserved;