

ZLLS1000


40V SILICON HIGH CURRENT LOW LEAKAGE SCHOTTKY DIODE

SUMMARY

Schottky Diode $V_R = 40V$; $I_F = 1.16A$; $I_R = 20\mu A$

DESCRIPTION

This compact SOT23 packaged Schottky diode offers users an excellent performance combination comprising high current operation, extremely low leakage and low forward voltage ensuring suitability for applications requiring efficient operation at higher temperatures (above 85°C) see Operational Efficiency chart on page 4.



Key benefits:

Performance capability equivalent to much larger packages

Improved circuit efficiency & power levels

PCB area savings

FEATURES

Low Equivalent On Resistance

Extremely Low Leakage ($20\mu A$ @30V)

High current capability ($I_F = 1.16A$)

Low V_F , Fast switching Schottky

SOT23 Package

ZLLS1000 complements low temperature equivalent ZHCS1000

Package thermally rated to 150°C

Cathode



Anode

APPLICATIONS

DC - DC Converters

Strobes


Mobile Phones

Charging Circuits

Motor control

ORDERING INFORMATION

DEVICE	REEL (inches)	TAPE WIDTH (mm)	QUANTITY PER REEL
ZLLS1000TA	7	8mm embossed	3000 units
ZLLS1000TC	13	8mm embossed	10000 units



Top view

DEVICE MARKING

L10

ZLS1000

ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Schottky Diode			
Continuous Reverse Voltage	V _R	40	V
Forward Current	I _F	1.16	A
Peak Repetitive Forward Current	I _{FPK}	1.88	A
Rectangular Pulse Duty Cycle			
Non Repetitive Forward Current t ≤ 100μs	I _{FSM}	22	A
t ≤ 10ms		6.4	A
Package			
Power Dissipation at T _{amb} =25°C single die continuous	P _D	625	mW
single die measured at t<5 secs		840	mW
Storage Temperature Range	T _{stg}	-55 to +150	°C
Junction Temperature	T _j	150	°C

THERMAL RESISTANCE

PARAMETER	SYMBOL	VALUE	UNIT
Junction to Ambient (a)	$R_{\theta JA}$	200	°C/W
Junction to Ambient (b)	$R_{\theta JA}$	149	°C/W


Notes

(a) For a device surface mounted on 25mm x 25mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.

(b) For a device surface mounted on FR4 PCB measured at $t < 5$ secs.

ZLLS1000

TYPICAL CHARACTERISTICS



ZLLS1000


ELECTRICAL CHARACTERISTICS (at Tamb = 25°C unless otherwise stated).

SCHOTTKY DIODE CHARACTERISTICS						
Reverse Breakdown Voltage	$V_{(BR)R}$	40			V	$I_R=500\mu A$
Forward Voltage	V_F		280	310	mV	$I_F=50\text{ mA}^*$
			310	340	mV	$I_F=100\text{ mA}^*$
			355	390	mV	$I_F=250\text{mA}^*$
			405	460	mV	$I_F=500\text{mA}^*$
			450	510	mV	$I_F=750\text{mA}^*$
			490	560	mV	$I_F=1\text{A}^*$
			570	660	mV	$I_F=1.5\text{A}^*$
			492		mV	$I_F=1000\text{mA}^*, T_a = 100^\circ\text{C}$
Reverse Current	I_R		11	20	μA	$V_R=30\text{V}$
			750		μA	$V_R=30\text{V}, T_a = 85^\circ\text{C}$
Diode Capacitance	C_D		26		pF	$f=1\text{MHz}, V_R=30\text{V}$
Reverse Recovery Time	t_{rr}		4		ns	Switched from
Reverse Recovery Charge	Q_{rr}		335		nC	$I_F = 500\text{mA}$ to $V_R = 5.5\text{V}$ Measured @ $I_R 50\text{mA}$. $di/dt = 500\text{mA/ns}$. $R_{source} = 6\Omega; R_{load} = 10\Omega$

*Measured under pulsed conditions. Pulse width = 300 μ S. Duty Cycle \leq 2%.

Operational Efficiency chart

The operational efficiency chart indicates the beneficial use of the ZLLS Series diodes in applications requiring higher voltage, higher temperature operation. Circuits requiring Low voltage Low temperature operation will benefit from using Zetex low V_F ZHCS Series diodes.




Operational Efficiency Example



ISSUE 2 - DECEMBER 2002


ZLLS1000

TYPICAL CHARACTERISTICS




ZLLS1000

Package Outline



Pad Layout



Package Dimensions

DIM	Millimetres		Inches	
	Min	Max	Min	Max
A	2.67	3.05	0.105	0.120
B	1.20	1.40	0.047	0.055
C	–	1.10	–	0.043
D	0.37	0.53	0.0145	0.021
F	0.085	0.15	0.0033	0.0059
G	NOM 1.9		NOM 0.075	
K	0.01	0.10	0.0004	0.004
L	2.10	2.50	0.0825	0.0985
N	NOM 0.95		NOM 0.037	

© Zetex plc 2001

Zetex plc Fields New Road Chadderton Oldham, OL9 8NP United Kingdom Telephone (44) 161 622 4422 Fax: (44) 161 622 4420	Zetex GmbH Streitfeldstraße 19 D-81673 München Germany Telefon: (49) 89 45 49 49 0 Fax: (49) 89 45 49 49 49	Zetex Inc 700 Veterans Memorial Hwy Hauppauge, NY11788 USA Telephone: (631) 360 2222 Fax: (631) 360 8222	Zetex (Asia) Ltd 3701-04 Metroplaza, Tower 1 Hing Fong Road Kwai Fong Hong Kong Telephone: (852) 26100 611 Fax: (852) 24250 494
------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

For the latest product information, log on to www.zetex.com



ISSUE 2 - DECEMBER 2002