

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		J	REVISED PER ECR-13-008204	10DEC2013	KH	TM

1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.


2 WIRE RANGE: 3-6mm² [12-10 AWG].

3 DIMENSIONS IN BRACKETS ARE IN INCHES.



4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN. TIN IN TIN PLATE AREA, 0.00127[.000050] MIN. NICKEL UNDERPLATE ON ENTIRE CONTACT.

5 THIS CONTACT HAS NO INSULATION BARREL.


6 SUPERCEDED BY 1-770246-0.



5.08
[.200] MIN
LOCALIZED GOLD
PLATE AREA
1 4



DETAIL A
SCALE 20:1



SECTION A-A
SCALE 10:1

6	GOLD 4	0.30 [.012] PH BRZ	1-770246-0
	GOLD 1	0.30 [.012] PH BRZ	770246-4
	PRE-TIN	0.30 [.012] PH BRZ	770246-3
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 02APR04	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C.JONES 02APR04				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C.JONES 02APR04	NAME			
	0 PLC ± -	PRODUCT SPEC	PIN, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II			
	1 PLC ± -	APPLICATION SPEC	-			
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-	A2	00779	C=770246	-
CUSTOMER DRAWING				SCALE	SHEET	REV
				5:1	1 of 1	J