








	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
																		CKT NO	PART NO	DIM A	
																		2	170001-0102	8.35	
																		4	170001-0104	12.05	
																		6	170001-0106	17.75	
																		8	170001-0108	23.45 ^{+0.40} _{-0.25}	
																		10	170001-0110	29.15 ^{+0.40} _{-0.25}	
																		12	170001-0112	34.85 ^{+0.40} _{-0.25}	
M																					M
L																					L
K																					K
J																					J
I																					I
H																					H
G																					G
F																					F
E																					E
D																					D
C																					C
B																					B
A																					A



170001-0110



CIRCUIT #

NOTES:

1. MATERIAL:

HOUSING: NYLON, UL94V-2, GLOW WIRE CAPABLE PER IEC-60335-1 5TH EDITION, COLOR: BLACK.

2. FINISH: NOT APPLICABLE.

3. PRODUCT SPECIFICATION PS-76823-100.

4. PACKAGING BULK PACK PER PK-170001-001.

5. PART MATES WITH MOLEX SERIES NUMBER 76825, 172064, 76829 AND 172065.

6. PART IS FOR USE WITH MOLEX FEMALE TERMINALS 76823 OR 172063 SERIES.


7. APPLICATION SPECIFICATION: AS-76823-100.

8. PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC


SPECIFICATION PS-45499-002 WITH THE EXCEPTION OF DISCOLORATION MEETS CLASS 'C' REQUIREMENTS.

UPDATE NOTES IEC NO: UCP2014-5278 DRAWN: DFOX 2014/06/17 CHECKED: J.BELL 2014/06/17 APPROVED: S.MITH 2014/06/23 REV: A9	QUALITY SYMBOLS ∇=0 ∇=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED):		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE MEGA-FIT RECEPTACLE HOUSING 2-12 CKT GLOW WIRE molex	DOCUMENT NO. SD-170001-0100	SHEET NO. 1 OF 2
		4 PLACES ±0.25 3 PLACES ±0.25 2 PLACES ±0.25 1 PLACE ±0.25 0 PLACE ±0.25	mm INCH	DRAWN BY MKARADIMAS	DATE 2010/11/23	CHECKED BY DATE	APPROVED BY APATEL	DATE 2012/06/13			


2 CKTS




4 CKT




6 CKT






8 CKT



10 CKTS



12 CKTS






170001-0102





SEE SHT 1 IEC NO: UCP2014-5278 DRAWN: JFOX 2014/06/17 CHKD: JBEL 2014/06/17 APPR: FSM TH 2014/06/23 A9	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
			4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACE ±	mm	INCH	DRAWN BY MKARADIMAS CHECKED BY DATE	DATE 2010/11/23	TITLE MEGA-FIT RECEPTACLE HOUSING 2-12 CKT GLOW WIRE				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE D	ANGULAR ±1/2°		APPROVED BY APATEL DATE 2012/06/13			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-170001-0100
												SHEET NO. 2 OF 2

20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

CKT NO	PART NO	DIM A
2	171692-0102	8.35
4	171692-0104	12.05
6	171692-0106	17.75
8	171692-0108	23.45 +0.40
10	171692-0110	29.15 +0.40
12	171692-0112	34.85 +0.40




171692-0110




NOTES:

- MATERIAL:
HOUSING: PBT, UL 94V-0, COLOR: BLACK.
- FINISH: NOT APPLICABLE.
- PRODUCT SPECIFICATION: PS-76823-100.
- PACKAGING: BULK PACK PER PK-170001-001
- PART MATES WITH MOLEX SERIES NUMBERS 76825, 76829, 172064, AND 172065.
- PART IS FOR USE WITH MOLEX FEMALE TERMINAL 76823 OR 172063 SERIES.
- APPLICATION SPECIFICATION: AS-76823-100.
- PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002 WITH THE EXCEPTION OF DISCOLORATION MEETS CLASS "C" REQUIREMENTS.


UPDATE NOTE 7 EC NO: UCP2014-5278 DRAWN: DFOX 2014/06/17 CHKD: JELL 2014/06/17 APPROV: SMITH 2014/06/23 A6	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE MEGA-FIT RECEPTACLE HOUSING 2-12 CKT molex			
			mm	INCH	DRAWN BY MKARADIMAS	DATE 2012/08/01	DATE 2012/08/17	DATE 2012/08/17					
			4 PLACES ±.00	±.00	CHECKED BY A. PATEL	DATE							
			3 PLACES ±.00	±.00	APPROVED BY APATEL	DATE							
			2 PLACES ±.025	±.025	ANGULAR ±1/2°		MATERIAL NO.				DOCUMENT NO.		SHEET NO. 1 OF 2
			1 PLACE ±.00	±.00	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART				SD-171692-0100		
			0 PLACE ±.00	±.00	SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						




2 CKTS




4 CKT




6 CKT






8 CKT



10 CKTS



12 CKTS



171692-0102

SEE SHT 1 IEC NO: UCP2014-5278 DRAWN: JFOX 2014/06/17 CHKD: JRELL 2014/06/17 APPR: FSWTH 2014/06/17 A6	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
					DRAWN BY MKARADIMAS		DATE 2012/08/01			TITLE MEGA-FIT RECEPTACLE HOUSING 2-12 CKT molex DOCUMENT NO. SD-171692-0100
					CHECKED BY A. PATEL		DATE			
					APPROVED BY APATEL		DATE 2012/08/17			
					MATERIAL NO.					
					SIZE D					
					SEE CHART					
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					