

- ▶ Compact and low profile
- ▶ Industry Std. Footprint
- ▶ Extended Temp Range Option
- ▶ RoHS Compliant

ECX-53B

SMD QUARTZ CRYSTAL

The ECX-53B is a miniature SMD Crystal with a 3.2 x 5 mm footprint. This package is ideal for todays compact wireless applications where board space is critical.

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

PARAMETERS	CONDITIONS	ECX-53B			UNITS
		MIN	TYP	MAX	
Frequency Range		8.000		150.000	MHz
Frequency Tolerance	at +25°C			± 30 *	ppm
Frequency Stability	-20 to +70°C			± 50 *	ppm
Shunt Capacitance				7	pF
Load Capacitance	Specify in P/N	10	20	Series	pF
Drive Level				100	µW
Operating Temperature		-20		+70	°C
Storage Temperature		-55		+125	°C
Aging (Per Year)	@ +25°C ±3°C			±5	ppm

EQUIVALENT SERIES RESISTANCE/MODE OF OSCILLATION

FREQUENCY RANGE (MHz)	MODE OF OSC	MAX ESR Ω	FREQUENCY RANGE (MHz)	MODE OF OSC	MAX ESR Ω
8.00 ~ 9.999	Fundamental	100	20.000 ~ 23.999	Fundamental	40
10.000 ~ 15.999	Fundamental	80	24.000 ~ 50.000	Fundamental	30
16.000 ~ 19.999	Fundamental	50	50.100 ~ 150.000	3rd Overtone	80

DIMENSIONS (mm)




Figure 1) Top, Side, Bottom and End views




Figure 2) Suggested Land Pattern

PART NUMBERING GUIDE: Example ECS-200-20-30B-TR

ECS - Frequency Abbreviation - Load Capacitance - Package

200 = 20.000 MHz
See P/N Guide

20 = 20 pF
S=Series

30B =
ECX-53B

Custom Options

Tolerance

Blank = Std
A = ± 25 ppm
J = ± 20 ppm
R = ± 15 ppm
C = ± 10 ppm

* Stability

Blank = Std
D = ± 100 ppm
E = ± 50 ppm
G = ± 30 ppm
H = ± 25 ppm
T = ± 20 ppm
W = ± 15 ppm
K = ± 10 ppm

Temp Range

Blank = Std
M = -20 ~ +70°C
N = -40 ~ +85°C
P = -40 ~ +105°C
S = -40 ~ +125°C
U = -55 ~ +125°C

- Packaging

TR= Tape
& Reel
1K/Reel

*Consult Factory for available stability options over extended temp range.

Rev. 8/11