

VIEW ON MATING SIDE

A	=	16	CONTACTS	L=2,8
B	=	16	CONTACTS	L=2,8

S = 32 TOTAL NUMBER OF CONTACTS

16	A	▷	B
15	A	▷	B
14	A	▷	B
13	A	▷	B
12	A	▷	B
11	A	▷	B
10	A	▷	B
9	A	▷	B
8	A	▷	B
7	A	▷	B
6	A	▷	B
5	A	▷	B
4	A	▷	B
3	A	▷	B
2	A	▷	B
1	A	▷	B

Marking	Standard
Performance level	G2/0 = Contact area perform. level2 / Termination tin
Flux proof	no
Fixing clip	no
Dimensions	SDA-85050-0002 sht.1
Technical Data	PS-85052-0001

B	G2/O	b1-16	
A	G2/O	a1-16	
Contact symbol	Perform. level	Contact position number	

ECN 2264 Produkt spec. 96-10-21 KN	LTR	REVISIONS		FOR PREVIOUS REVISIONS SEE MRJ LIST		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ±2° INCH METRIC	DRWG BY	SIGN	REVISE ONLY ON CAD SYSTEM		SH.	REV.
		3D		TITLE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
		3 PLACE ± •	±				CHK'D BY	SIGN				
		2 PLACE ± •	±									
		1 PLACE ± •	±	KN								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APP'D BY	SIGN	MOLEX® MOLEX EUROPE		SHEET NO. 1 OF 1	DATE 96/06/13					
DESIGN DIMENSION ☐ MM ☐ IN.		SCALE		PART NO. 85050-0000	DWG NO. SDA-85050-0000	SIZE A						
EQUIVALENT DIMENSION ☐ MM ☐ IN.		IF TWO DIMENSIONS ARE SHOWN THE UPPER IS THE DESIGN DIMENSION LOWER IS SECONDARY										

