




MARKETING SALES DRAWING
 DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
 DIMENSIONS IN METRIC - []

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4300-007.
 TUSONIX RoHS COMPLIANT PART NUMBER: 4300-007 LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS PART
 NUMBER WHEN ORDERING.
- RoHS COMPLIANT PART MARKED WITH DARK GREEN DOT
 FOR IDENTIFICATION.

MINIMUM Cx (pF)	DC WORKING VOLTAGE		CURRENT	DWV	I.R. MIN. @ 100 VDC	MIN. NO LOAD INSERTION LOSS (dB) @ 25° C PER MIL-STD-220				OPERATING TEMPERATURE RANGE	COLOR CODE
	+85°C	+125°C				10 MHz	100 MHz	1GHz	10 GHz		
1000	300	200	5 A	500 VDC	10	5	20	35	45	-55°C TO +125°C	GRAY

REVISION RECORD		0		RDN TO COMP FMT & ADDED METRIC. S.M. 06-19-02 20020604-3-04 ADDED NOTES 1 & 2. S.M. 05-23-05 20050511-2-13	--TOLERANCES-- Unless Otherwise Specified		Title SOLDER MOUNT EMI FILTER	
Original Release C.O. 5928					DECIMAL ± 			
RDN TO COMP FMT & ADDED METRIC. S.M. 06-19-02					ANGLES ± 		Drawn S.M. 06-19-02	
20020604-3-04					TUSONIX TUCSON, ARIZONA		Approved J.Mc. 06-19-02	
ADDED NOTES 1 & 2. S.M. 05-23-05							Scale 5 X	
20050511-2-13						A		4300-007

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4300-007LF](#)