

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

2011

2011

ALL RIGHTS RESERVED
TOUS DROITS RESERVES

2011

LOC

DIST

F

00

REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	FIRST ISSUE	13SEP2007	PFs	JDrr
	B	ADD NG9K SEALS, HEAD FORMS SET UP.	19SEP2008	PFs	JDrr
	C	SET UP DIM 31, 33, 34 AND 35.	17JUN2011	PFs	JDrr
	D	SET UP DIM 21	15SEP2011	PFs	JDrr

COUPE C-C
SECTION C-C

1

REGLABLE, EN FONCTION DES FI SUR CALIBRE
GAP DEPENDENT MATING FORCE ON GAUGE

21

0.3 B

ECHELLE 1:1
SCALE 1:1

2

PAS = 25
PITCH = 25

IDENTIFICATION DE LA GAMME "C" = DE 7 A 10 MM2
WIRE SIZE IDENTIFICATION "C" = FROM 7 TO 10 MM2

10

10.9

3

11

12

3.2

1.9

13

30

10.9

31

3.5±0.2

32

4.6

33

5.25±0.2

34

7.8±0.15

35

36.45±0.25 EN BANDE
36.45±0.25 IN STRIP

COUPE D-D
SECTION D-D

40

7.8±0.3

41

0.2 A

42

R2.6

43

10.25 MAX (1)
DEGAUCHI / B
UNWARP TO B

COUPE E-E
SECTION E-E

50

0.2 A

51

0.2 A

52

R3.5

LARGEUR ENTREFER REGLER POUR
DES LANGUETTES DE 1mm
WIDTH GAP FOR 1mm TAB

5.44

5.04

NOTA

1 (X) = POUR INFORMATION

2 CONDITIONNEMENT : VOIR SPECIFICATION 107-15602

NOTES

1 (X) = FOR INFORMATION

2 PACKAGING : SEE SPECIFICATION 107-15602

REFERENCE TE PN	REFERENCE CLIENT CUSTOMER PN	Y : REPERE MATIERE MATERIAL REPERE	MATIERE MATERIAL	TRAITEMENT DE SURFACE HEAT TREATMENT
1544966-1		S	CuNiSi SELON SPECIFICATION: 100-1230 CuNiSi ACCORDING TO SPECIFICATION: 100-1230	PRE-ETAME SnAg DE 1 A 3µ SELON SPECIFICATION 112-73-2 PRE-TINNED SnAg FROM 1 TO 3µ ACCORDING SPECIFICATION 112-73-2
1544966-2		T		PRE-ARGENTE Ag DE 1 A 3µ SELON SPECIFICATIONS 212-7, 112-32 ET 118-91 PRE-SILVERED Ag FROM 1 TO 3µ ACCORDING SPECIFICATIONS 212-7, 112-32 AND 118-91

PRODUIT ASSOCIE / APPLIED PRODUCT

DESIGNATION DES JOINTS SEALS DESCRIPTION	REFERENCE TE PN	REFERENCE CUSTOMER PN	COULEUR COLOR
JOINT UNIFILAIRE 7 A 10 MM2 SINGLE WIRE SEAL 7 TO 10 MM2	1544316-2		ORANGE / ORANGE
SUPER JOINT UNIFILAIRE 7 A 10 MM2 SUPER SINGLE WIRE SEAL 7 TO 10 MM2	1544664-2		ORANGE / ORANGE
JOINT UNIFILAIRE NG9K 6 A 7 MM2 NG9K SINGLE WIRE SEAL 6 TO 7 MM2	1544970-2		BLEU / BLUE
JOINT UNIFILAIRE NG9K 10 MM2 NG9K SINGLE WIRE SEAL 10 MM2	1544970-3		JAUNE / YELLOW

INTERFACE MONTABILITE / INTERFACE CAVITY

1544953

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTROLE PAR AMP INCORPORATED.
IL EST SUSCEPTIBLE D'ETRE REVISE, CONTACTER LE SERVICE
TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIERE REVISION.

DIMENSIONS:

mm

1

PLC / DEG ±

2

PLC / DEG ±0.1

3

PLC / DEG ±

ANGLES

±2°

MATERIAL
MATIERE

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES
(SUIVRE DE DECIMALES)

1

PLC / DEG ±

2

PLC / DEG ±0.1

3

PLC / DEG ±

FINISH
FINITION

SEE TABLE

DWN/DESSINE
P. FLORES
CHK/VERIFIE
E. SAPET
APVD/APPROUVE
J. DAHER

13SEP07

13SEP07

13SEP07

PRODUCT SPEC
SPEC, PRODUIT

108-15382

APPLICATION SPEC
SPEC, APPLICATION

114-15107

WEIGHT
MASSE APPROX.

0.0023kg

CUSTOMER DRAWING /PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 5:2

SHEET
FEUILLE 1

OF
DE 1

REV
D

NAME
TITRE

8mm NG1+ FEMALE TERMINAL
WIRE SIZE 7-10 SQUARE MM

SIZE
FORMAT

A2

CAGE CODE

00779

DRAWING NO
No PLAN

C=1544966

RESTRICTED TO
RESERVE A

-

1471-9 (3/11)