

Accessories**TS 35X7.5/LL 2M/ST/SZ****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The active and passive components as well as the intelligent modules are mounted on terminal rails. Terminal rails are made from stainless steel, steel, aluminium, copper or plastic and are available in diverse types to suit different applications.

General ordering data

Order No.	7915060000
Type	TS 35X7.5/LL 2M/ST/SZ
Version	Mounting rail, DIN EN 60715, Steel, 2000 mm, galvanized
GTIN (EAN)	4032248296279
Qty.	2 m

Accessories

TS 35X7.5/LL 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	2,000 mm	Width	35 mm
Height	7.5 mm	Net weight	300 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Direct mounting	Version	with slot
---------------------	-----------------	---------	-----------

Dimensions

TS 35 offset	10 mm
--------------	-------

Rated data

Standards	DIN EN 60715
-----------	--------------

Material data

Surface finish	galvanized	Material	Steel
Colour	Grey		

System specifications

Product family	Accessories	Mounting rail	TS 35
----------------	-------------	---------------	-------

Mounting rail

Drill-hole diameter	5.2 mm	Installation advice	Direct mounting
Material	Steel	Short circuit strength corresponds to E-Cu wire	16 mm ²
Slit gap	11 mm	Slit length	25 mm
Slit width	5.2 mm	Slotted drill holes	Yes
Solder eyelet hole diameter (D)	5.2 mm	Spacing of holes, centre-to-centre	36 mm
Standards	DIN EN 60715	Surface finish	galvanized
Thickness	1 mm		

Classifications

ETIM 2.0	EC001285	ETIM 3.0	EC001285
UNSPSC	30-21-18-01	eClass 4.1	27-14-06-04
eClass 5.1	27-14-06-04	eClass 6.2	27-14-11-43
eClass 7.1	27-14-11-43		

Approvals

Approvals	
ROHS	Conform