





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	C	ECO-07-010885	09MAY07	MB	JG		



- 1 [-Y-] SHALL BE THE INTERSECTION OF THE POST AND THE HOUSING.
- 2 THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED.
- 3 0.00254-0.00508 [0.00100-.000200] MATTE TIN-LEAD OVER 0.00127 [0.000050] NICKEL, ENTIRE POST.
- 4 HOUSING: LCP, COLOR-BLACK.
POST: PHOSPHOR BRONZE.
PICK AND PLACE CAP: PPA, COLOR-BLACK.
- 5. PACKAGED IN TAPE AND REEL PER EIA-481 SPECIFICATIONS. SEE TABLE FOR WIDTHS.
- 6 0.00254-0.00508 [0.00100-.000200] MATTE TIN OVER 0.00127 [0.000050] NICKEL, ENTIRE POST.
- 7 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.



0.15 [0.006] X S
ALL SURFACES



RECOMENDED PCB LAYOUT FOR USE WITH 0.20 [0.008] THICK STENCIL

6	44 mm	17.78 [0.700]	7	19.91 [0.784]	16	5-1571878-1
3	56 mm	20.32 [0.800]	8	22.45 [0.884]	18	1571878-2
3	44 mm	17.78 [0.700]	7	19.91 [0.784]	16	1571878-1
PLATING	TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL		FINISH		WEIGHT		SCALE		SHEET		REV	
mm	[INCHES]	0 PLC	1 PLC	2 PLC	3 PLC	4 PLC	ANGLES	FINISH	WEIGHT	SCALE	SHEET	OF	REV		
0.2	[0.008]	±	±	±	±	±	±	SEE TABLE	-	4:1	1	1	C		
0.05	[0.002]	±	±	±	±	±	±	SEE TABLE	-	4:1	1	1	C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571878-1](#)