



CIRCUIT SIZE	DIM. "A"	DIM. "B"
2	.21 (5.4)	—
4	.38 (9.6)	.17 (4.2)
6	.54 (13.8)	.33 (8.4)
8	.71 (18.0)	.50 (12.6)
10	.87 (22.2)	.66 (16.8)
12	1.04 (26.4)	.83 (21.0)
14	1.20 (30.6)	.99 (25.2)
16	1.37 (34.8)	1.16 (29.4)
18	1.54 (39.0)	1.32 (33.6)
20	1.70 (43.2)	1.49 (37.8)
22	1.87 (47.4)	1.65 (42.0)
24	2.03 (51.6)	1.82 (46.2)



CIRCUIT SIZE LAYOUT



LEGEND

5566 - N * * * * *

BASE NUMBER

CIRCUIT SIZE

ASSY TYPE

A : WITHOUT DRAIN HOLES

B : WITH DRAIN HOLES

TERMINAL MATERIAL

SEE NOTE 1

TERMINAL PLATING

SEE NOTE 2

HOUSING MATERIAL

SEE NOTE 1

COLOR OR PACKAGING

BL : BLACK RE : RED GR : GRAY

BU : BLUE YE : YELLOW GRE : GREEN

V : VIOLET OR : ORANGE


TA : TRAY PACKAGING SEE NOTE 4

TR : TRAY PACKAGING SEE NOTE 4

(NON ACCUM.)

.1654 ±.004 TYP

4.200 ±0.10



RECOMMENDED HOLE LAYOUT FOR .070/(1.78) MAX. THICK P.C. BOARD VIEWED FROM COMPONENT SIDE

ADD P/N'S EC NO: UCP2014-2112 2013/11/13 DRAWN: NGUYEN 2013/11/13 CHKD: JELL 2013/11/27 APPR: FSMITH	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ±.005 2 PLACES ±.13 ±.010 1 PLACE ±.25 ± --- ANGULAR ± 3 °	DIMENSION STYLE IN/MM DRAWN BY DATE H.HIRAMOTO '89/04/03 CHECKED BY DATE M.FUKUSHIMA '94/04/20 APPROVED BY DATE FSMITH 2012/05/04	SCALE 4:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION	MINI FIT JR VERTICAL HEADER ASSEMBLIES WITHOUT PEGS MOLEX INCORPORATED SD-5566-002	SHEET NO. 1 OF 5

NOTES:

- MATERIALS:
HOUSING:
"BLANK"=NYLON 6/6, UL94V-2, COLOR: NATURAL
"210"=NYLON 6/6, UL94V-0, COLOR: NATURAL
"400"=NYLON 6/6, UL94V-0, COLOR: BLACK
TERMINALS:
"BLANK" = BRASS
"PB" = PHOSPHOR BRONZE
2. TERMINAL PLATING:
"BLANK" = BRIGHT TIN 0.00035/(0.00090) MIN. OVER COPPER .000020/(0.00050) MIN. (BRASS)
TIN .000035/(0.00090) MIN. REFLOW TREATMENT OR BRIGHT TIN .000035/(0.00090) MIN. (PHOSPHOR BRONZE)
"S"=.000100/(0.00254) MIN. BRIGHT TIN OVER .000050/(0.00127) MIN NICKEL
"GS2"=.000015/(0.00038) MIN. SELECT GOLD AND .000100/(0.00254) MIN. SELECT MATTE TIN OVER .000050/(0.00127) MIN. NICKEL OVERALL
"GS"=.000030/(0.00076) MIN. SELECT GOLD AND .000100/(0.00254) MIN. SELECT MATTE TIN OVER .000050/(0.00127) MIN. NICKEL OVERALL
3. PRODUCT SPECIFICATION: PS-5556-001
4. PACKAGING: "BLANK"= BULK PACKED,
"TA"=TRAY PACK PER PK-5566-001, "TR"=TRAY PACK PER PK-5566
5. PART MATES WITH MINI-FIT JR. RECEPTACLE NO. 5557.
6. PART IS NOT DESIGNED FOR CURRENT SHARING.
7. PARTS ARE NOT DESIGNED TO BE MATED OR UN-MATED WHILE CIRCUITS ARE LIVE.
8. ANTI-SHINGLING RIB MAY OR MAY NOT APPEAR ON HOUSINGS.
9. PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	39-30-9247	5566-24BGS2-2 IO	39-31-0248	5566-24BGS-2 IO	39-31-0242	5566-24BS-2 IO	39-31-0240	5566-24B-2 IO	39-30-6244	5566-24APBS-2 IO	24			
	▲ -9227	▲ -22BGS2-2 IO	▲ -0228	▲ -22BGS-2 IO	▲ -0222	▲ -22BS-2 IO	▲ -0220	▲ -22B-2 IO	▲ -6224	▲ -22APBS-2 IO	22			
	-9207	-20BGS2-2 IO	-0208	-20BGS-2 IO	-0202	-20BS-2 IO	-0200	-20B-2 IO	-6204	-20APBS-2 IO	20			
	-9187	-18BGS2-2 IO	-0188	-18BGS-2 IO	-0182	-18BS-2 IO	-0180	-18B-2 IO	-6184	-18APBS-2 IO	18			
	-9167	-16BGS2-2 IO	-0168	-16BGS-2 IO	-0162	-16BS-2 IO	-0160	-16B-2 IO	-6164	-16APBS-2 IO	16			
I	-9147	-14BGS2-2 IO	-0148	-14BGS-2 IO	-0142	-14BS-2 IO	-0140	-14B-2 IO	-6144	-14APBS-2 IO	14			
	-9127	-12BGS2-2 IO	-0128	-12BGS-2 IO	-0122	-12BS-2 IO	-0120	-12B-2 IO	-6124	-12APBS-2 IO	12			
	-9107	-10BGS2-2 IO	-0108	-10BGS-2 IO	-0102	-10BS-2 IO	-0100	-10B-2 IO	-6104	-10APBS-2 IO	10			
	-9087	-08BGS2-2 IO	-0088	-08BGS-2 IO	-0082	-08BS-2 IO	-0080	-08B-2 IO	-6084	-08APBS-2 IO	8			
	-9067	-06BGS2-2 IO	-0068	-06BGS-2 IO	-0062	-06BS-2 IO	-0060	-06B-2 IO	-6064	-06APBS-2 IO	6			
H	▼ -9047	▼ -04BGS2-2 IO	▼ -0048	▼ -04BGS-2 IO	▼ -0042	▼ -04BS-2 IO	▼ -0040	▼ -04B-2 IO	▼ -6044	▼ -04APBS-2 IO	4			
	39-30-9027	5566-02BGS2-2 IO	39-31-0028	5566-02BGS-2 IO	39-31-0022	5566-02BS-2 IO	39-31-0020	5566-02B-2 IO	39-30-6024	5566-02APBS-2 IO	2			
	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.				
	5566-NBGS2-2 IO	5566-NBGS-2 IO	5566-NBS-2 IO	5566-NB-2 IO	5566-NAPBS-2 IO	CKT. SIZE								
	39-30-9246	5566-24BGS2	39-31-0247	5566-24BGS	39-31-0241	5566-24BS	39-29-3246	5566-24B	39-30-6243	5566-24APBS	24			
G	▲ -9226	▲ -22BGS2	▲ -0227	▲ -22BGS	▲ -0221	▲ -22BS	▲ -3226	▲ -22B	▲ -6223	▲ -22APBS	22			
	-9206	-20BGS2	-0207	-20BGS	-0201	-20BS	-3206	-20B	-6203	-20APBS	20			
	-9186	-18BGS2	-0187	-18BGS	-0181	-18BS	-3186	-18B	-6183	-18APBS	18			
	-9166	-16BGS2		-16BGS	-0161	-16BS	-3166	-16B	-6163	-16APBS	16			
	-9146	-14BGS2	-0147	-14BGS	-0141	-14BS	-3146	-14B	-6143	-14APBS	14			
F	-9126	-12BGS2	-0127	-12BGS	-0121	-12BS	-3126	-12B	-6123	-12APBS	12			
	-9106	-10BGS2	-0107	-10BGS	-0101	-10BS	-3106	-10B	-6103	-10APBS	10			
	-9086	-08BGS2	-0087	-08BGS	-0081	-08BS	-3086	-08B	-6083	-08APBS	8			
	-9066	-06BGS2	-0067	-06BGS	-0061	-06BS	-3066	-06B	-6063	-06APBS	6			
	▼ -9046	▼ -04BGS2	▼ -0047	▼ -04BGS	▼ -0041	▼ -04BS	▼ -3046	▼ -04B	▼ -6043	▼ -04APBS	4			
E	39-30-9026	5566-02BGS2	39-31-0027	5566-02BGS	39-31-0021	5566-02BS	39-29-3026	5566-02B	39-30-6023	5566-02APBS	2			
	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.				
	5566-NBGS2	5566-NBGS	5566-NBS	5566-NB	5566-NAPBS	CKT. SIZE								
	39-31-0245	5566-24BPBS	39-31-0243	5566-24BPB	39-31-0246	5566-24BPBS-2 IO	39-31-0244	5566-24BPB-2 IO	24					
	▲ -0225	▲ -22BPBS	▲ -0223	▲ -22BPB	▲ -0226	▲ -22BPBS-2 IO	▲ -0224	▲ -22BPB-2 IO	22					
D	-0205	-20BPBS	-0203	-20BPB	-0206	-20BPBS-2 IO	-0204	-20BPB-2 IO	20					
	-0185	-18BPBS	-0183	-18BPB	-0186	-18BPBS-2 IO	-0184	-18BPB-2 IO	18					
	-0165	-16BPBS	-0163	-16BPB	-0166	-16BPBS-2 IO	-0164	-16BPB-2 IO	16					
	-0145	-14BPBS	-0143	-14BPB	-0146	-14BPBS-2 IO	-0144	-14BPB-2 IO	14					
	-0125	-12BPBS	-0123	-12BPB	-0126	-12BPBS-2 IO	-0124	-12BPB-2 IO	12					
C	-0105	-10BPBS	-0103	-10BPB	-0106	-10BPBS-2 IO	-0104	-10BPB-2 IO	10					
	-0085	-08BPBS	-0083	-08BPB	-0086	-08BPBS-2 IO	-0084	-08BPB-2 IO	8					
	-0065	-06BPBS	-0063	-06BPB	-0066	-06BPBS-2 IO	-0064	-06BPB-2 IO	6					
	▼ -0045	▼ -04BPBS	▼ -0043	▼ -04BPB	▼ -0046	▼ -04BPBS-2 IO	▼ -0044	▼ -04BPB-2 IO	4					
	39-31-0025	5566-02BPBS	39-31-0023	5566-02BPB	39-31-0026	5566-02BPBS-2 IO	39-31-0024	5566-02BPB-2 IO	2					
B	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO				
	5566-NBPBS	5566-NBPB	5566-NBPBS-2 IO	5566-NBPB-2 IO	CKT. SIZE									
	39-31-0245	5566-24BPBS	39-31-0243	5566-24BPB	39-31-0246	5566-24BPBS-2 IO	39-31-0244	5566-24BPB-2 IO	24					
	▲ -0225	▲ -22BPBS	▲ -0223	▲ -22BPB	▲ -0226	▲ -22BPBS-2 IO	▲ -0224	▲ -22BPB-2 IO	22					
	-0205	-20BPBS	-0203	-20BPB	-0206	-20BPBS-2 IO	-0204	-20BPB-2 IO	20					
A	-0185	-18BPBS	-0183	-18BPB	-0186	-18BPBS-2 IO	-0184	-18BPB-2 IO	18					
	-0165	-16BPBS	-0163	-16BPB	-0166	-16BPBS-2 IO	-0164	-16BPB-2 IO	16					
	-0145	-14BPBS	-0143	-14BPB	-0146	-14BPBS-2 IO	-0144	-14BPB-2 IO	14					
	-0125	-12BPBS	-0123	-12BPB	-0126	-12BPBS-2 IO	-0124	-12BPB-2 IO	12					
	-0105	-10BPBS	-0103	-10BPB	-0106	-10BPBS-2 IO	-0104	-10BPB-2 IO	10					
A	-0085	-08BPBS	-0083	-08BPB	-0086	-08BPBS-2 IO	-0084	-08BPB-2 IO	8					
	-0065	-06BPBS	-0063	-06BPB	-0066	-06BPBS-2 IO	-0064	-06BPB-2 IO	6					
	▼ -0045	▼ -04BPBS	▼ -0043	▼ -04BPB	▼ -0046	▼ -04BPBS-2 IO	▼ -0044	▼ -04BPB-2 IO	4					
	39-31-0025	5566-02BPBS	39-31-0023	5566-02BPB	39-31-0026	5566-02BPBS-2 IO	39-31-0024	5566-02BPB-2 IO	2					
	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO				
A	5566-NBPBS	5566-NBPB	5566-NBPBS-2 IO	5566-NBPB-2 IO	CKT. SIZE									
	39-31-0245	5566-24BPBS	39-31-0243	5566-24BPB	39-31-0246	5566-24BPBS-2 IO	39-31-0244	5566-24BPB-2 IO	24					
	▲ -0225	▲ -22BPBS	▲ -0223	▲ -22BPB	▲ -0226	▲ -22BPBS-2 IO	▲ -0224	▲ -22BPB-2 IO	22					
	-0205	-20BPBS	-0203	-20BPB	-0206	-20BPBS-2 IO	-0204	-20BPB-2 IO	20					
	-0185	-18BPBS	-0183	-18BPB	-0186	-18BPBS-2 IO	-0184	-18BPB-2 IO	18					
A	-0165	-16BPBS	-0163	-16BPB	-0166	-16BPBS-2 IO	-0164	-16BPB-2 IO	16					
	-0145	-14BPBS	-0143	-14BPB	-0146	-14BPBS-2 IO	-0144	-14BPB-2 IO	14					
	-0125	-12BPBS	-0123	-12BPB	-0126	-12BPBS-2 IO	-0124	-12BPB-2 IO	12					
	-0105	-10BPBS	-0103	-10BPB	-0106	-10BPBS-2 IO	-0104	-10BPB-2 IO	10					
	-0085	-08BPBS	-0083	-08BPB	-0086	-08BPBS-2 IO	-0084	-08BPB-2 IO	8					
A	-0065	-06BPBS	-0063	-06BPB	-0066	-06BPBS-2 IO	-0064	-06BPB-2 IO	6					
	▼ -0045	▼ -04BPBS	▼ -0043	▼ -04BPB	▼ -0046	▼ -04BPBS-2 IO	▼ -0044	▼ -04BPB-2 IO	4					
	39-31-0025	5566-02BPBS	39-31-0023	5566-02BPB	39-31-0026	5566-02BPBS-2 IO	39-31-0024	5566-02BPB-2 IO	2					
	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO	EDP NO.	ENG. NO				
	5566-NBPBS	5566-NBPB	5566-NBPBS-2 IO	5566-NBPB-2 IO	CKT. SIZE									
A	39-31-0245	5566-24BPBS	39-31-0243	5566-24BPB	39-31-0246	5566-24BPBS-2 IO	39-31-0244	5566-24BPB-2 IO	24					
	▲ -0225	▲ -22BPBS	▲ -0223	▲ -22BPB	▲ -0226	▲ -22BPBS-2 IO	▲ -0224	▲ -22BPB-2 IO	22					
	-0205	-20BPBS	-0203	-20BPB	-0206	-20BPBS-2 IO	-0204	-20BPB-2 IO	20					
	-0185	-18BPBS	-0183	-18BPB	-0186	-18BPBS-2 IO	-0184	-18BPB-2 IO	18					
	-0165	-16BPBS	-0163	-16BPB	-0166	-16BPBS-2 IO	-0164	-16BPB-2 IO	16					
A	-0145	-14BPBS	-0143	-14BPB	-0146	-14BPBS-2 IO	-0144	-14BPB-2 IO	14					
	-0125	-12BPBS	-0123	-12BPB	-0126	-12BPBS-2 IO	-0124	-12BPB-2 IO	12					
	-0105	-10BPBS	-0103	-10BPB	-0106	-10BPBS-2 IO	-0104	-10BPB-2 IO	10					
	-0085	-08BPBS	-0083	-08BPB	-0086	-08BPBS-2 IO	-0084	-08BPB-2 IO	8					
	-0065	-06BPBS	-0063	-06BPB	-0066	-06BPBS-2 IO	-0064	-06BPB-2 IO	6</					

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J														J
I														I
H														H
G														G
F														F
E														E
D														D
C														C
B														B
A														A

COLORED PART NUMBERS

										24	
											22
											20
				46999-0085	5566-18AS-RE						18
											16
											14
											12
											10
						46999-0089	5566-08AS-OR		46999-0087	5566-10AS-V	8
											6
											4
											2
				EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.		CKT. SIZE
5566-NAS-RE		5566-NAS-OR		5566-NAS-V							
				39-35-0248	5566-24A-400	24					
				39-35-0228	▲ -22A-400	22					
				39-35-0208	-20A-400	20					
				39-35-0188	-18A-400	18					
			39-33-3169	5566-16A-210-BU	39-35-0168	-16A-400	16				
					39-35-0148	-14A-400	14				
					39-35-0128	-12A-400	12				
			39-33-4100	5566-10A-210-RE	39-33-3109	5566-10A-210-BU	39-33-0108	-10A-400	10		
46999-0091	5566-08AS-GRE						39-35-0088	-08A-400	8		
							39-35-0068	-06A-400	6		
				39-33-4040	5566-04A-210-RE	39-33-3049	5566-04A-210-BU	39-35-0048	▼ -04A-400	4	
50-36-2485	5566-02AS-GRE	39-34-5023	5566-02A-210-YE	39-33-4020	5566-02A-210-RE	39-33-3029	5566-02A-210-BU	39-35-0028	5566-02A-400	2	
EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	CKT. SIZE	
5566-NAS-GRE		5566-NA-210-YE		5566-NA-210-RE		5566-NA-210-BU		5566-NA-400			
										24	
										22	
										20	
										18	
				39-33-3166	5566-16A-RE	39-33-3164	5566-16A-BU			16	
39-33-3145	5566-14A-GR							39-33-3143	5566-14A-BL	14	
				39-33-3126	5566-12A-RE	39-33-3124	5566-12A-BU			12	
				39-33-3106	5566-10A-RE	39-33-3104	5566-10A-BU			10	
		39-33-3087	5566-08A-YE	39-33-3086	5566-08A-RE	39-33-3084	5566-08A-BU	39-33-3083	5566-08A-BL	8	
		39-33-3067	5566-06A-YE	39-33-3066	5566-06A-RE	39-33-3064	5566-06A-BU	39-33-3063	5566-06A-BL	6	
				39-33-3046	5566-04A-RE	39-33-3044	5566-04A-BU	39-33-3043	5566-04A-BL	4	
		39-33-3027	5566-02A-YE	39-33-3026	5566-02A-RE	39-33-3024	5566-02A-BU	39-33-3023	5566-02A-BL	2	
EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	ENG. NO.	CKT. SIZE	
5566-NA-GR		5566-NA-YE		5566-NA-RE		5566-NA-BU		5566-NA-BL			

PARTS WITHOUT DRAIN HOLES

SEE SHEET 1

EC NO: UCP2014-2112

2013/11/13

DRW:NGUYEN

2013/11/13

CHKD:JBELL

2013/11/13

APPR:FSMITH

2013/11/13

REV

QUALITY SYMBOLS

▽=0

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .---	± .---
3 PLACES	± .---	± .005
2 PLACES	± .13	± .010
1 PLACE	± .25	± .---

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY

H.HIRAMOTO

DATE

'89/04/03

CHECKED BY

M.FUKUSHIMA

DATE

'94/04/20

APPROVED BY

FSMITH

DATE

2012/05/04

SCALE

1:1

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

MINI FIT JR VERTICAL HEADER ASSEMBLIES WITHOUT PEGS

MOLEX INCORPORATED

SD-5566-002

SHEET NO.

4 OF 5

MATERIAL NO.

SEE TABLE

DOCUMENT NO.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J														J
I														I
H														H
G														G
F														F
E														E
D														D
C														C
B														B
A														A

TRAY PACKED PART NUMBERS

PARTS WITHOUT DRAIN HOLES						39-53-9249	5566-24A-210-TA	39-53-9248	5566-24A-TA	24
							↑ -22A-210-TA	↑ -9228	↑ -22A-TA	22
							-20A-210-TA	-9208	-20A-TA	20
			39-34-1180	5566-18A-210-TR			-18A-210-TA	-9188	-18A-TA	18
							-16A-210-TA	-9168	-16A-TA	16
							-14A-210-TA	-9148	-14A-TA	14
							-12A-210-TA	-9128	-12A-TA	12
							-10A-210-TA	-9108	-10A-TA	10
							-08A-210-TA	-9088	-08A-TA	8
	46999-0630	5566-06AGS2-BL-TA					-06A-210-TA	-9068	-06A-TA	6
	46999-0629	5566-04AGS2-BL-TA					↓ -04A-210-TA	↓ -9048	↓ -04A-TA	4
							5566-02A-210-TA	39-53-9028	5566-02A-TA	2
	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	CKT.	
5566-NAGS2-BL-TA		5566-NA-210-TR		5566-NA-210-TA		5566-NA-TA		SIZE		

SEE SHEET 1 EC NO: UCP2014-2112 DRAWN:NGUYEN CHKD:JBELL APPR:FSMITH	2013/11/13 2013/11/13 2013/11/27	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	TITLE					
						IN/MM		1:1	METRIC							
					=0	mm	INCH	DRAWN BY	DATE			MOLEX INCORPORATED				
					=0	4 PLACES ± .005	3 PLACES ± .005	H.HIRAMOTO	'89/04/03							
					=0	2 PLACES ± .13	2 PLACES ± .010	M.FUKUSHIMA	'94/04/20							
					=0	1 PLACE ± .25	1 PLACE ± .005	APPROVED BY	DATE							
						ANGULAR ± 3 °	FSMITH	2012/05/04	DOCUMENT NO.							
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		SD-5566-002		SHEET NO.
												SIZE				5 OF 5

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION