

SERIES 19X MAXI® CIRCUIT BREAKERS



Series 19X MAXI® Circuit Breakers

Auto, Manual & Modified Reset

SPECIFICATIONS

Single Pole Thermal Type Breakers

Rating: 8-50A; 14VDC; 28VDC (Series 193, 194, & 195).

Interrupt Rating: 150A @ 14VDC (8-10A versions); 225A @ 14VDC (15A version); 300A @ 14VDC (20A version); 450A @ 14VDC (25-30A versions); 600A @ 4VDC (35-40A versions); 750A @ 14VDC (50A version).



Operating Temperature Rating: -40°F (-40°C) to 185°F (85°C).

Storage Temperature Rating: -40°F (-40°C) to 260°F (125°C).


Materials: Grey UL-Rated 94V-0 thermoplastic.

Termination: Compatible with fuse blocks accepting MAXI® or ATC® blade fuses.

Compliances: SAE J553.



DIMENSIONS (Dims. shown are for reference only. Consult factory for latest prints) TERMINAL OPTIONS



PART NUMBERING SYSTEM

Series	Rating	Terminal	Cover	Button (193 Series Only)	Marking
191 - Type I, 14 VDC 192 - Type II, 14 VDC 193 - Type III, 12V/28 VDC 194 - Type I, 28 VDC 195 - Type II, 28 VDC	08 - 8 amps 10 - 10 amps 15 - 15 amps 20 - 20 amps 25 - 25 amps 30 - 30 amps 35 - 35 amps 40 - 40 amps 50 - 50 amps (191, 193, 194 only)	01 - MAXI® 02 - Wide ATC® 03 - Long ATC® (w/dimple) 04 - Long ATC® (no dimple)	M - Metal* P - Plastic (193 only)	1 - Black 2 - White	(Consult factory for special markings.)

* All breakers have metal cover except 193 series.