




222A111-100/180-0 Product Details

[Share](#) [Print](#) [Email](#)

222A111-100/180-0

TE Internal Number: 292769-000


Molded Parts

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)
Product Highlights:

- Molded Part Type = Molded Boot
- Family Name = 222A1
- 90°
- Marine Application, Military Application, Rail Application
- Connector Accessory Outside Diameter (Min-Max) = 7.90 - 17.00 mm

[View all Features](#)
Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)
Documentation & Additional Information
Product Drawings:

- [Boot, 90 deg., Thin Wall](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)
Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Molded Boot
- Angle = 90°
- Size = 11
- Material = Low Fire Hazard Material

Body Features:

- Connector Accessory Outside Diameter (Min-Max) (mm [in]) = 7.90 - 17.00 [0.311 - 0.669]
- Cable Diameter Range (mm [in]) = 3.80 - 9.90 [0.150 - 0.390]

Contact Features:

- [Family Name](#) = 222A1

Housing Features:

- [Material Systems Code](#) = 100
- Adhesive Pre-Coating = With
- Adhesive Description = Good Water Blocking Pre-Coat Adhesive

Configuration Features:

- Material Code = 100
- [Adhesive Code](#) = 180

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -30 - +80

Operation/Application:

- Application = Marine, Military, Rail

Other:

- Brand = Raychem
- Comment = Adhesive not used with Transitions.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

 Enter your email address
