


SPECIFICATION CONTROL DRAWING		SCD		44A032X																																																															
Title TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, GENERAL PURPOSE, 2500 VOLT		Date 11-3-15		Revision D																																																															
This specification sheet forms a part of the latest issue of Raychem Specification 44.																																																																			
COMPONENT WIRES - 44A031X  <table border="1" style="width: 100%; border-collapse: collapse; font-size: 0.8em;"> <tr> <th colspan="5">CABLE CONSTRUCTION DETAILS</th> </tr> <tr> <th rowspan="2">PART NUMBER <u>1/</u></th> <th rowspan="2">CONDUCTOR SIZE (AWG)</th> <th colspan="2">OUTSIDE DIAMETER (inch)</th> <th rowspan="2">MAXIMUM WEIGHT (lbs/1000 ft.)</th> </tr> <tr> <th>NOMINAL</th> <th>MAXIMUM</th> </tr> <tr><td>44A032X-26-*</td><td>26</td><td>.106</td><td>.111</td><td>4.5</td></tr> <tr><td>44A032X-24-*</td><td>24</td><td>.114</td><td>.120</td><td>6.5</td></tr> <tr><td>44A032X-22-*</td><td>22</td><td>.138</td><td>.144</td><td>9.2</td></tr> <tr><td>44A032X-20-*</td><td>20</td><td>.156</td><td>.163</td><td>13.0</td></tr> <tr><td>44A032X-18-*</td><td>18</td><td>.176</td><td>.183</td><td>18.6</td></tr> <tr><td>44A032X-16-*</td><td>16</td><td>.194</td><td>.202</td><td>23.3</td></tr> <tr><td>44A032X-14-*</td><td>14</td><td>.230</td><td>.238</td><td>34.7</td></tr> <tr><td>44A032X-12-*</td><td>12</td><td>.262</td><td>.272</td><td>51.9</td></tr> <tr><td>44A032X-10-*</td><td>10</td><td>.322</td><td>.338</td><td>78.2</td></tr> <tr><td>44A032X-8-*</td><td>8</td><td>.438</td><td>.450</td><td>133.</td></tr> </table> CABLE RATINGS AND ADDITIONAL REQUIREMENTS TEMPERATURE RATING: 150°C Maximum continuous conductor temperature VOLTAGE RATING: 2500 volts (rms) at sea level DIELECTRIC WITHSTAND: 5000 volts (rms), 60 Hz, 1 minute INSULATION FLAWS: Spark Test, 8.0 kV (rms) at 3 kHz Impulse Dielectric Test, 13.0 kV (peak) <u>1/</u> PART NUMBER: The "X" in the part numbers above shall be replaced with a conductor material designator as follows: 1 tin-coated copper 2 silver-coated copper (AWG 24-8 only) 3 nickel-coated copper (AWG 24-8 only) 4 silver-coated high-strength copper alloy (AWG 26-18 only) The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors. Example: AWG 20, tin-coated copper conductors; black and brown component wires: 44A0321-20-0/1 NOTE: Nominal values are for information only. Nominal values are not requirements.						CABLE CONSTRUCTION DETAILS					PART NUMBER <u>1/</u>	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)	NOMINAL	MAXIMUM	44A032X-26-*	26	.106	.111	4.5	44A032X-24-*	24	.114	.120	6.5	44A032X-22-*	22	.138	.144	9.2	44A032X-20-*	20	.156	.163	13.0	44A032X-18-*	18	.176	.183	18.6	44A032X-16-*	16	.194	.202	23.3	44A032X-14-*	14	.230	.238	34.7	44A032X-12-*	12	.262	.272	51.9	44A032X-10-*	10	.322	.338	78.2	44A032X-8-*	8	.438	.450	133.
CABLE CONSTRUCTION DETAILS																																																																			
PART NUMBER <u>1/</u>	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)																																																															
		NOMINAL	MAXIMUM																																																																
44A032X-26-*	26	.106	.111	4.5																																																															
44A032X-24-*	24	.114	.120	6.5																																																															
44A032X-22-*	22	.138	.144	9.2																																																															
44A032X-20-*	20	.156	.163	13.0																																																															
44A032X-18-*	18	.176	.183	18.6																																																															
44A032X-16-*	16	.194	.202	23.3																																																															
44A032X-14-*	14	.230	.238	34.7																																																															
44A032X-12-*	12	.262	.272	51.9																																																															
44A032X-10-*	10	.322	.338	78.2																																																															
44A032X-8-*	8	.438	.450	133.																																																															
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.																																																																			
<u>1/</u> COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.																																																																			
Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.		 Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297																																																																
	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL																																																																		
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.																																																																		