


2mm x 5mm Rectangular LED CBI® Circuit Board Indicator

Dialight

566-xx06



PART NO.

566-0206
566-0306
566-0406

COLOR

Green
Yellow
Red

Features

- Multiple CBIs form horizontal LED arrays on 3.96mm (0.156") center-lines
- High Contrast, UL 94 V-0 rated, black housing
- Oxygen index: 32%
- Polymer content: PBT, 0.309 g
- Housing stand-offs facilitate PCB cleaning
- Solderability per MIL-STD-202F, method 208F
- LEDs are safe for direct viewing per IEC 825-1, EN-60825-1

Tolerance note: As noted, otherwise:

- LED Protrusion: ±0.04 mm [±0.016]
- CBI Housing: ±0.02mm[±0.008]

Typical Operating Characteristics (T_A=25°C)

See LED data sheet for additional information
See Page 5-20 and 5-21 for Reference Only LED Drive Circuit Example
See Page 5-22 for Pin Out

Part Number	Color	Peak Wavelength nm	I _v mcd	V _F Volts	Test Current (mA)	Viewing Angle 2θ _{1/2}	LED Data sheet	Page #
566-0206	Green	565	4	2.2	20	110°	521-9332	5-16
566-0306	Yellow	583	3.5	2.1	20	110°	521-9452	5-16
566-0406	Red	635	7.4	2	20	140°	521-9499	5-16

2mm x 5mm Discrete LED
Rectangular
Tinted, Diffused

Dialight

521-9332, -9452, -9499, -9718



PART NO.	COLOR	DRAWING
521-9332	Green	A
521-9452	Yellow	A
521-9499	Red	B
521-9718	Blue	B

ABSOLUTE MAXIMUM RATINGS ($T_A=25^{\circ}\text{C}$)	Green -9332	Yellow -9452	Red -9499	Blue -9718
Power Dissipation (mW)	135	85	100	189
Forward Current (mA)	30	20	30	30
Derating (mA/ $^{\circ}\text{C}$) From 50°C 1. mW/ $^{\circ}\text{C}$ From 25°C	.5	.34	.4	.45 ¹
Peak Current (mA)	500*	500*	120	180
Pulse width = 1 ms *Pulse width = 10 μs				
Operating Temperature ($^{\circ}\text{C}$)	-20/+100	-55/+100	-55/+100	-25/+75
Storage Temperature ($^{\circ}\text{C}$)	-55/+100	-55/+100	-55/+100	-25/+100
Soldering Temperature	260 $^{\circ}\text{C}$, 5 seconds, 1.6 mm from case			

Solder Adherence per MIL-STD-202E, Method 208C

OPERATING CHARACTERISTICS ($T_A=25^{\circ}\text{C}$)		Green -9332	Yellow -9452	Red -9499	Blue -9718
Luminous Intensity (mcd)	Min.	2.6	2.2	3	9
	Typical	4	3.5	7.4	18
Peak Wavelength (nm)	Typical	565	583	635	430
λ Peak					
Viewing Angle ($2\theta^{\circ}$)	Typical	110 $^{\circ}$	110 $^{\circ}$	140 $^{\circ}$	120 $^{\circ}$
Forward Voltage (V)	Typical	2.2	2.1	2	5.3
	Max.	3	2.6	2.8	6
Reverse Voltage (V), $I_R=100\mu\text{A}$	Min.	5	5	5	5

θ° is the off axis angle at which the luminous intensity is half the axial luminous intensity