



GP 6120

6V 12.0Ah

GP 6120 is a general purpose battery with 3-5 years in standby service or more than 260 cycles at 100% discharge in cycle service. As with all CSB batteries, all are rechargeable, highly efficient, leak proof and maintenance free.




Specification

Cells Per Unit	3
Voltage Per Unit	6
Capacity	12Ah @ 20hr-rate to 1.75V per cell @25 °C (77°F)
Weight	Approx. 1.94kg(4.3 lbs)
Maximum Discharge Current	150A/180A(5sec)
Internal Resistance	Approx. 7.5mΩ
Operating Temperature Range	Discharge: -20°C~50°C (-4°F~122°F) Charge: 0°C~40°C (32°F~104°F) Storage: -20°C~40°C (-4°F~104°F)
Nominal Operating Temperature Range	25°C±3°C (77°F±5°F)
Float Charging Voltage	6.75 to 6.9 VDC/unit Average at 25°C (77°F)
Recommended Maximum Charging Current Limit	3.6A
Equalization and Cycle Service	7.2 to 7.5 VDC/unit Average at 25°C (77°F)
Self Discharge	CSB Batteries can be stored for more than 6 months at 25°C (77°F). Please charge batteries before using. For higher temperatures the time interval will be shorter.
Terminal	Faston Tab 187/250
Container Material	-ABS (UL94-HB)*Flammability resistance of UL94-V2 can be available upon request.



CSB-manufactured batteries are UL-recognized components under UL924 and UL1989. CSB is also certified by ISO 9001 and ISO 14001.

Dimensions



Constant Current Discharge Characteristics Unit:A (25°C ,77°F)


F.V/Time	5MIN	10MIN	15MIN	30MIN	1HR	2HR	3HR	4HR	5HR	8HR	10HR	20HR
1.60V	48.20	31.40	24.10	14.80	8.83	5.12	3.66	2.89	2.33	1.53	1.23	0.63
1.67V	44.70	30.00	23.40	14.66	8.72	5.06	3.65	2.88	2.32	1.52	1.22	0.61
1.70V	43.20	29.40	23.10	14.60	8.67	5.03	3.64	2.88	2.31	1.52	1.21	0.60
1.75V	40.10	28.05	22.25	14.35	8.50	4.93	3.62	2.86	2.30	1.51	1.20	0.59
1.80V	37.00	26.70	21.40	14.10	8.33	4.83	3.60	2.84	2.28	1.50	1.18	0.57
1.85V	33.90	25.35	20.55	13.85	8.16	4.73	3.58	2.82	2.27	1.49	1.17	0.55

Constant Power Discharge Characteristics Unit:W (25°C ,77°F)


F.V/Time	5MIN	10MIN	15MIN	30MIN	1HR	2HR	3HR	4HR	5HR	8HR	10HR	20HR
1.60V	289.00	189.00	145.00	89.00	53.00	30.70	22.00	17.40	14.00	9.24	7.35	3.75
1.67V	268.00	180.60	140.80	87.95	52.30	30.35	21.93	17.33	13.93	9.19	7.28	3.68
1.70V	259.00	177.00	139.00	87.50	52.00	30.20	21.90	17.30	13.90	9.17	7.25	3.65
1.75V	240.50	168.50	134.00	86.00	51.00	29.60	21.75	17.20	13.80	9.11	7.15	3.54
1.80V	222.00	160.00	129.00	84.50	50.00	29.00	21.60	17.10	13.70	9.04	7.05	3.42
1.85V	203.50	151.50	124.00	83.00	49.00	28.40	21.45	17.00	13.60	8.98	6.95	3.31

● All mentioned values are average values.


Trickle (or Float) Service Life




Capacity Retention Characteristic




Battery Voltage and Charge Time for Standby Use




Cycle Service Life



Battery Voltage and Charge Time for Cycle Use



Terminal Voltage (V) and Discharge Time (25°C 77°F)



Charging Procedures

Application	Charge Voltage (V/Cell)			Max. Charge Current
	Temperature	Set Point	Allowable Range	
Cycle Use	25°C (77°F)	2.45	2.40~2.50	0.3C
Standby	25°C (77°F)	2.275	2.25~2.30	

Discharge Current VS. Discharge Voltage

Final Discharge Voltage V/Cell	1.75	1.70	1.55	1.30
Discharge Current (A)	0.2C>(A)	0.2C<(A)<0.5C	0.5C<(A)<1.0C	(A)>1.0C

Sales Office URL:WWW.CSB-BATTERY.COM

CSB BATTERY CO., LTD.

TAIWAN OFFICE

Tel: +886-2-8751-5000

Fax: +886-2-8751-6161

E-mail: service@csb-battery.com.tw

CSB BATTERY OF NETHERLANDS B.V.

NETHERLANDS OFFICE

Tel: +31(0) 180 418 140

Fax: +31(0) 180 418 327

E-mail: eurosales@csb-battery.com

CSB BATTERY LOGISTICS (SHANGHAI) CO., LTD.

SHANGHAI OFFICE

Tel: +86-21-5046-1622, 5046-0833

Fax: +86-21-5064-3314

CSB BATTERY TECHNOLOGIES, INC.

USA OFFICE

Tel: +1-817-244-7777/1-8003 CSBUSA(272872)

Fax: +1-817-244-4445

E-mail: csb@csb-battery.com

CSB BATTERY LOGISTICS (SHANGHAI) CO., LTD.

BEIJING OFFICE

Tel: +86-10-6597-8060, 6597-8070

Fax: +86-10-6597-8050

E-mail: chinasl@csb-battery.com

CSB BATTERY LOGISTICS (SHANGHAI) CO., LTD.

SHENZHEN OFFICE

Tel: +86-755-2694-2788/2606/2706

Fax: +86-755-2694-2748

E-mail: she@csb-battery.com.tw