


PRODUCT NUMBER
75915-YXXXLF


RoHS COMPATIBLE, SEE NOTE 6
OPTIONAL LETTER.

G: HIGH TEMPERATURE BLACK PRODUCT.
H: HIGH TEMPERATURE GREY PRODUCT.
NUMBER OF POSITIONS: 02 TO 50.

PLATING CODE
3 = 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
4 = 2µm MIN MATTE TIN FULL PLATED
8 = 0.38µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
1.27µm Ni MIN UNDERPLATING



(N x 2.54) - 0.08




2.5 REF

- NOTES:
- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED FLAME RETARDANT PER UL 94 V-0.
LOW TEMPERATURE: COLOR BLUE.
HIGH TEMPERATURE: COLOR GREY OR BLACK.
 - 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
 - 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS
EXAMPLE: 8 POS: (N x 2.54) - 0.08 = 20.24 mm
 - 5 - HE13 PRINTING ON 75915-3xx PRODUCT.
 - 6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - d - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
 - 7 - PRINTING & HOLE PATTERN SEE NEXT SHEET.

mat'l. code				surface		tolerance		projection		product family	
ltr	ecm no	dr	date	ISO 1302	ISO 406	ISO 1101	ISO 1101	ISO 1101	ISO 1101	title	DUBOX
AD	F06-0204	DLE	06.06.20	tolerances unless otherwise specified	±0.3					BtB RECEIPT.	
AE	F07-0108	DLE	07.01.16	angles						VERT SR TMT	
AF	F09-0036	LMU	09.03.16	linear							
AG	B-19123	LMU	14.10.21	dr	D.L.EGRAND	96.04.01	scale 5:1			dwg no	sheet 1 of 2
				engr	P.NIZZI	96.04.01				75915	A3
AB	F05-0236	DLE	05.08.08	cht	D.L.EGRAND	96.04.01				type	CUSTOMER
AC	F06-0156	DLE	06.03.17	appd	P.NIZZI	96.04.01				Drawing	
sheet	revision	AG	D								
index	sheet	1	2								

A

A





B

B

C

C

mat'l. code SEE SHEET 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX																			
ltr		ecn no		dr		date		tolerances unless otherwise specified				 mm scale N/A		title BtB RECEPT. VERT SR TMT															
A		F04-0347		DLE		04.09.23		angles linear		±0.3																			
B		F05-0230		DLE		05.08.08																							
C		F06-0204		DLE		06.06.20				±2'																			
D		F07-0109		DLE		07.01.16		dr		D.LEGRAND		04.09.23				dwg no 75915 sheet 2 of - size A4													
								enr		P.NIZZI		04.09.23																	
								chr		D.LEGRAND		04.09.23																	
								appd		P.NIZZI		04.09.23																	
sheet index		revision sheet																											

D

D