



# PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	REL. NRN 32069	09/13/04	STW
B	REV. DCN 35434	10/05/07	STW




MATERIALS;  
 BODY, CONTACT,  
 EMI/  
 ANTI-ROCK RING: BERYLLIUM COPPER PER ASTM B196  
 INSULATOR: PTFE PER ASTM D1710  
 CABLE STOP: TORLON

FINISHES:  
 BODY, CONTACT,  
 EMI/  
 ANTI-ROCK RING: GOLD PER ASTM B488, TYPE II  
 GRADE C, CLASS 1.27, OVER NICKEL  
 PER ASM-QQ-N-290, CLASS 1

ELECTRICAL:  
 IMPEDANCE: 50 OHMS  
 FREQ. RANGE: DC TO 40 GHZ  
 D.W.V.: 500 VOLTS DC  
 INSULATION RES.: 5,000 MEGOHMS MINIMUM

REF. DSCC 94008ZCG-2



CABLE STOP

CONTACT  
SOLDER TO CABLE

DIMENSIONS ARE IN INCHES WITH METRIC EQUIVALENTS IN BRACKETS [ ]

MATERIAL:	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 10'$ DECIMAL: $.X \pm .030$ $.XX \pm .010$ $.XXX \pm .005$	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE AFTER PLATING. 2) BREAK CORNERS & EDGES .005 R. MAX. 3) CHAM. 1ST & LAST THREADS. 4) SURFACE ROUGHNESS 63 V MIL-STD-10. 5) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 6) REMOVE ALL BURRS	SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409
FINISH: PER BOM	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	DRAWN: JMC 04/16/04	TITLE: SMP CABLE JACK FOR Ø .047 S.R. CABLE
SURFACE AREA:	THIRD ANGLE PROJECTION	CHECKED: STW 09/13/04	SIZE CAGE CODE DWG. NO. B 95077 1203-4000
PROPRIETARY		APPROVED: STW 09/13/04	E.M. SIMULATION: SVG 05/03/04
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		SCALE: 1:0.2	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1203-4000](#)