









PRODUCT NUMBER
70234-XXX
70234-XXYLF



PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-Ayy	TELCORDIA CO	SEE NOTE 9
-Myy	.38μm GOLD MIN.	-
-NIyy	TELCORDIA CO (NXT)	-
-N5yy	TELCORDIA UE (NXT)	-
-Iyy	TELCORDIA CO	-
-2yy	TELECOM CLASS	-
-3yy	IEC CLASS I	-
-5yy	TELCORDIA UE	-
-AyyLF	TELCORDIA CO	SEE NOTE 10
-NIyyLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 10
-N5yyLF	TELCORDIA UE (NXT)	SEE NOTE 10
-IyyLF	TELCORDIA CO IEC CLASS I	SEE NOTE 10
-2yyLF	TELECOM CLASS	SEE NOTE 10
-5yyLF	TELCORDIA UE	SEE NOTE 10

mat'l code				--				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0. X ±0.3				COPY					title METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT					
AG	V06-0498	DCH	2006-05-31		0. XX ±0.13				projection										
AH	DG09-0256	TER	2009-08-19		. XXX ±.051														
-	-	-	-	angles	0° ±2°														
AC	V04-0554	TAB	06/07/04	dr	T.BRUNGARD	11/19/99							product family		METRAL		code		
AD	V05-0079	HTB	02/03/05	enrg	M.STRAWER	11/19/99							size		dwg no		213		
AE	V05-0359	DAI	04/21/05	chr	M.STRAWER	11/19/99			scale 2:1				A		70234		sheet		
AF	V05-1030	LP	11/18/05	appd	M.STRAWER	02/29/00							AH		AH		1 of 12		
sheet index	revision sheet	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH	AH		
		1	2	3	4	5	6	7	8	9	10	11	12						


This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
12	7.25	17.00
13	8.25	4.30
14	8.25	13.60
15	8.25	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com					
lfr	ecn no.	dr	date	linear	0.X ±0.3		projection 	title METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT					
AH					0.XX ±0.13								
					.XXX ±.051								
				angles	0° ±2°			product family METRAL	code 213				
					dr	T.BRUNGARD							11/19/99
					enrg	M.STRAWSE							11/19/99
				chr	M.STRAWSE	11/19/99	scale 1:1	size A	dwg no 70234	sheet 2			
				appd	M.STRAWSE	02/29/00							
sheet index		revision sheet											

cage code 22526

Pro/E

PDM: Rev:AH

STATUS:Released

Printed: Feb 20, 2010



PRODUCT NUMBER
70234-XXX
70234-XXYLF

1 | 2

3 |

4

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
70234 -XXX IS SnPb
70234-XXYLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- A PLATING HAS Au FLASH IN PRESS FIT
AREA (LEAD FREE).
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 70234-X01LF
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com			
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY					
AH					0.XX ±0.13	projection					
					.XXX ±.051						
				angles	0° ±2°			titleMETRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT			
				dr	T.BRUNGARD 11/19/99	MM					
				enrg	M.STRAWSE 11/19/99	scale		size		dwg no	213
				chr	M.STRAWSE 11/19/99	1:1		A		70234	sheet
				appd	M.STRAWSE 02/29/00						12
sheet index		revision sheet									

1 | 2

Pro/E

3 |

cage code 22526

4