


RF & MICROWAVE TRANSISTORS UHF TV/LINEAR APPLICATIONS

- 860 MHz
- 25 VOLTS
- COMMON EMITTER
- GOLD METALLIZATION
- CLASS A LINEAR OPERATION
- $P_{OUT} = 4.0 \text{ W MIN. WITH } 7.0 \text{ dB GAIN}$



.280 4L STUD (M122)
epoxy sealed

ORDER CODE
SD1448


BRANDING
TCC598

DESCRIPTION

The SD1448 is a silicon NPN bipolar device specifically designed for high linearity applications in the UHF frequency range including TV Bands IV and V.

Gold metallization and emitter ballasting assure high reliability under Class A linear amplifier operation.

PIN CONNECTION



- | | |
|--------------|------------|
| 1. Collector | 3. Base |
| 2. Emitter | 4. Emitter |

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^{\circ}\text{C}$)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	45	V
V_{CEO}	Collector-Emitter Voltage	25	V
V_{EBO}	Emitter-Base Voltage	4	V
I_C	Device Current	1.6	A
P_{DISS}	Power Dissipation	31.8	W
T_J	Junction Temperature	+200	$^{\circ}\text{C}$
T_{STG}	Storage Temperature	- 65 to +150	$^{\circ}\text{C}$

THERMAL DATA

$R_{TH(j-c)}$	Junction-Case Thermal Resistance	5.5	$^{\circ}\text{C/W}$
---------------	----------------------------------	-----	----------------------

SD1448 (TCC598)

ELECTRICAL SPECIFICATIONS ($T_{case} = 25^{\circ}C$)

STATIC

Symbol	Test Conditions		Value			Unit
			Min.	Typ.	Max.	
BV_{CBO}	$I_C = 10mA$	$I_E = 0mA$	45	—	—	V
BV_{CEO}	$I_C = 20mA$	$I_B = 0mA$	25	—	—	V
BV_{EBO}	$I_E = 2.5mA$	$I_C = 0mA$	3.0	—	—	V
I_{CBO}	$V_{CB} = 28V$	$I_E = 0mA$	—	—	0.9	mA
h_{FE}	$V_{CE} = 20V$	$I_C = 500mA$	10	—	—	—

DYNAMIC

Symbol	Test Conditions			Value			Unit
				Min.	Typ.	Max.	
P_{OUT}^1	$f = 860\text{ MHz}$	$V_{CE} = 25\text{ V}$	$I_C = 850\text{ mA}$	4.0	—	—	W
G_P^2	$f = 860\text{ MHz}$	$V_{CE} = 25\text{ V}$	$I_C = 850\text{ mA}$	7.0	—	—	dB
IMD_3^3	$P_{SYNC} = 4\text{ W}$	$V_{CE} = 25\text{ V}$	$I_C = 850\text{ mA}$	—	—	-60	dBc
C_{OB}	$f = 1\text{ MHz}$	$V_{CB} = 25\text{ V}$		—	—	20	pF

Note 1: $P_{IN} = 0.8W$

Note 2: $P_{OUT} = 4\text{ W}$

Note 3: Levels relative to $P_{SYNC} = 4\text{ W}$


$f_1 = 860.0\text{ MHz}$ -8dBc

$f_2 = 863.5\text{ MHz}$ -16dBc


$f_3 = 864.5\text{ MHz}$ -7dBc

TYPICAL PERFORMANCE


POWER OUTPUT vs POWER INPUT




INTERMODULATION DISTORTION vs POWER OUTPUT



THERMAL RESISTANCE vs CASE TEMPERATURE




TEST CIRCUIT




C1	: 22mF, 63V Sprague	L7	: 4 Ω Transmission Line, Length 8% λ at 860 MHz
C2, C6,		L8	: 55 Ω Transmission Line, Length 7.5% λ at 860 MHz
C8, C15	: 4.7nF Chip LCC	L9	: 7.5 Ω Transmission Line, Length 8% λ at 860 MHz
C3, C7, C9,		L10	: 100 Ω Transmission Line, Length 8% λ at 860 MHz
C11, C16	: 100nF Chip LCC	L11	: 20 Ω Transmission Line, Length 8% λ at 860 MHz
C4, C10	: 4.7 μ F, 40V Sprague	L12	: 50 Ω Transmission Line, Length 5mm
C5, C15	: 4.7 μ F, 63V Sprague	L13	: 50 Ω Transmission Line, Length 12mm
C12, C17,		P1	: 3.3k Ω Adjustable
C18	: 470pF Chip LCC	R1	: 2.2 Ω , 3W SFERNICE
C13, C25	: 47pF ATC 100B	R2	: 100 Ω , 1/2W
C19	: 47pF ATC 100A	R3	: 51 Ω , 1/2W
C20	: 0.5 - 4.5pF Adjustable Airtronic	R4, R6	: 100 Ω , 1/2W
C21, C24	: 0.8 - 5pF Adjustable Johanson	R5, R7	: 56 Ω , 1W
C22	: 10pF ATC 100A	T1	: BDX 54 B
C23	: 15pF ATC 100B	S1	: 6 Turns, Wire Diameter 0.5mm on 2.5mm Internal Diameter
D1	: 1N 4001 or 1N 914	S2	: 10 to 12 Turns on R6, Wire Diameter 0.5mm
L1	: 50 Ω Transmission Line, Length 18mm	PC Board	
L2	: 50 Ω Transmission Line, Length 22mm	Material	: Er = 2.5, .020" Thick
L3	: 16.4 Ω Transmission Line, Length 12mm		
L'3	: 10.5 Ω Transmission Line, Length 3.5mm		
L4	: 20 Ω Transmission Line, Length 13mm		
L5	: 50 Ω Transmission Line, Length 2.5mm		
L6	: 20 Ω Transmission Line, Length 23mm		

TEST CIRCUIT LAYOUT



PACKAGE MECHANICAL DATA

Ref.: Dwg. No.12-0122



SGS-THOMSON MICROELECTRONICS		
	MINIMUM Inches/mm	MAXIMUM Inches/mm
A	1.010/25,65	1.055/26,80
B	.220/5,59	.230/5,84
C	.270/6,86	.285/7,24
D	.003/0,08	.007/0,18
E	.117/2,97	.137/3,48
F	.572/14,53	
G	.130/3,30	
H	.245/6,22	.255/6,48
I	.640/16,26	
J	.175/4,45	.217/5,51
K	.275/6,99	.285/7,24

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may results from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

© 1994 SGS-THOMSON Microelectronics - All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES
Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands -
Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A