



PCK-124D2M,000 Product Details

[Share](#) [Print](#) [Email](#)


PCK-124D2M,000

TE Internal Number: 1461370-5

 [Active](#)

Industrial Relays (General Purpose)

 [Converted to EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Relay Type = Miniature Power PCB Relay
- Relay Style = PCB
- PCK Series
- Contact - Arrangement = 1 Form A, SPST-NO, 1 N/O
- Contact - Rated Current = 16 A

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = PCK
- [Termination Type](#) = Through Hole

Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 16
- [Coil - Resistance \(\$\Omega\$ \)](#) = 1150
- [Coil - Rated Power, DC \(mW\)](#) = 500
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 24
- Insulation - Special Features = None

Contact Features:

- Relay Type = Miniature Power PCB Relay
- [Mounting Options](#) = PC Board
- [Enclosure Type](#) = Flux-Tight
- [Contact Base Material](#) = Silver Tin Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 24.30 x 11.60 x 26.70 [.957 x .457 x 1.052]

Configuration Features:

- Relay Style = PCB
- [Contact - Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Coil - Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive
- Approved Standards = UL, CSA

Other:

- Brand = OEG

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

