

Pomona[®]

ELECTRONICS

**Professionals Trust
Pomona Performance**

Test and Measurement
Calibration
RF
Audio/Video
Automotive
Telecom

2006 - 2007

Table of Contents


For over half a century the name Pomona Electronics has been synonymous with reliability and outstanding value.



We are proud to have built our reputation for the delivery of quality products by using only the finest materials available and designing to match real world applications... where you live – everyday. Pomona Electronics is proud to be there, at your side.

3	New Products
8	Customized Products
9	Coaxial Cable Assemblies and Breakouts
18	Coaxial Connectors, Adapters and Kits
30	Banana Plugs and Jacks
42	Patch Cords and Test Lead
52	Boxes and Enclosures
58	DMM Accessories and Kits
72	Grabbers and Test Clips
75	SMD/Micro Format Test
79	Oscilloscope Probes and Accessories
83	Audio/Video
86	Automotive
87	IC Test Clips and Adapters
91	Static Control Products
93	Telecom Products
99	Temperature Probes
101	Index
107	Technical Support

SMD/ Micro Format Test



SMD High Density Circuit Test Kit Model# 72935

- SMD test kit includes the critical clips needed for probing high density circuits.
- Plus, you get the leads and adapters needed to get from micro-scale test up to the 4mm plugs needed for your DMM.
- Kit includes 2 DMM leads with 4mm plugs, 2 test probes with spring-loaded tips, 6 micro SMD grabbers, 6 adapter leads 0.8mm female to 0.4mm jack, 2 mini SMD grabbers with 4mm connectors, 2 holding rods.

Shown on page 75.



Micro SMD Grabber Test Clips Model# 72902-0

- Easily attach to SMD chips with pitches down to 0.008in (0.20 mm).
- Thin yet durable design permits attachment with close spacing in tight spaces.
- Insulated tip minimizes shorting on adjacent pins. Gold plating for low resistance connections.

Shown on page 76.



Mini SMD Grabber Test Clips Model# 72906-2

- Designed for easy attachment to SMD chips with pitches down to 0.032in (0.80 mm).
- Insulated shaft can be bent up to 36 degrees for versatile attachment in awkward locations or close proximity to other clips.
- Thin (3mm) profile allows close placement to adjacent clips.

Shown on page 76.



Clip Leads for SMD Grabbers Model# 72905-0

- Clip lead attaches from either Micro SMD Grabber or Mini SMD Grabber to standard test leads.
- (See many more new products in the new SMD/Micro Format Test Section).

Shown on page 76.

Pomona's quality connectors are the one answer you need when a reliable signal is demanded.

Pomona
ELECTRONICS

Pomona's test accessories are made from the finest materials available – designed and built for long service life and exceptional reliability.

RF Connector Kits



Multi-RF Direct Adapter Kit

Model# 72934

- A consolidated kit including the most frequently used 50Ω RF adapters in a rugged pistol-grip case.
- Allows for direct adaptation without intermediate couplers.
- All parts are precision machined brass, not die-cast, with tarnish resistant nickel plating.

See more new RF kits on page 18.

IEC Insulated Cable Assemblies, Breakouts and Adapters



IEC Insulated BNC Male 50Ω Cable

Model# 72926-C-40

- IEC Insulated BNCs allow safe attachment in 500V CAT 1 applications.
- Rugged design for dependable service.

Shown on page 10.

Insulated BNC (m) to Stackable/Retractable 4mm Plugs

Model# 72908 IEC

- Safe and convenient adaptation from BNC format to banana plug format.
- Stackable/retractable 4 mm plugs permit multiple attachments to test points.

Shown on page 16.




Insulated BNC (f) to 2 Male Banana 4mm Plugs

Model# 72911 IEC

- Safe connections from BNC format to banana plug format.
- Rugged, insulated design for dependable safety.

Shown on page 20.

2mm Test



Multi-stacking 2mm Safety Sheathed Patch Cords

Model# 72920-39-2

- Thin profile, highly flexible leads allow fine control and minimal strain on circuit board measurements.
- Multi-stacking safety sheathed design for easy multiple connections to test points.

Shown on page 77.

SMD Test Probe with Sharp, Spring-Mounted Tip

Model# 72923-2

- Provides ultra-fine control for probing high density SMD circuits.
- Very fine 0.03in (0.7mm) diameter stainless steel tip is spring-mounted for controlled pressure.
- Removable, clear IC insulator cap prevents shorting of adjacent IC pins.

Shown on page 77.

2mm Safety Sheathed Jacks

Model# 72921-0

- 2mm sizing for convenient connection in tight spaces.
- Safety sheathed jack with 1.9mm wire wrap connecting pin for quick attachment.

Shown on page 75.

4mm Safety Banana Jack to 2mm Banana Plug Adapter

Model# 72914-02

- For easy conversion from 4mm test leads to more compact 2mm test accessories.
- Accepts 4mm safety-sheathed banana plugs.

Shown on page 78.

AC Voltage Detector and Flashlight



LumaVolt Model# 7290

- AC Voltage Detector – Detects voltages from 40 Vac to 300 Vac from 1 to 15 inches away from the source.
- Flashlight feature includes ultra-bright white LED with 100,000 hour bulb.

Shown on page 65.

New Panel Mount Jacks

IEC 1010 4mm Banana Jacks for Sheathed Plugs

Model# 72912-2

- Designed for fast panel construction.
- Gold-plated stud and nuts for high conductivity.
- Rating: 1000V Cat III, 36A Mx.



2mm Safety Sheathed Jacks Model# 72922-2

- 2mm jack increases possible connections in a limited space.
- Broad solder tab for easy soldering.
- Rating: 600V Cat II, 10A.

Shown on page 78.



Our test accessories
compliment the
best test instruments
and continue to
be the choice
of professionals
worldwide.

Pomona
ELECTRONICS

Need a Quality Connection?

For Distributor Locations:

United States and International
www.pomonaelectronics.com

Europe
www.pomona.cc

Technical Support:

U.S.: 1-800-241-2060
Europe: +31(0) 40 2675 150
Rest of World: 1-425-446-5500

Classics – Back by Popular Demand



SMD Microtip Test Probe Set Model# 6235

- Probe microtip specially designed to probe SMD contacts.
- Features a stainless steel needle tip that is curved to aid in probing hard to reach areas.

Shown on page 68.

BNC Shielded Test Probe Kit Model# 5292-48

- Shield extends to within 1.5in (3.8cm) of probe tip.
- Alligator or Minigrabber test clip can be quickly threaded onto ground lead.
- Stainless steel dog leg tip excellent for SMD probing.

Shown on page 68.



Antistatic Ground Cord Model# 5534

- These patch cords feature a molded-in 1 MΩ resistor at the snap end for added Safety.
- Extended length is 72in (183cm).

Shown on page 92.



RF Coax Plugs, Jacks and Adapters

Type N (m) 75 Ω Plug, Crimp RG59

Model# 6767

- 3 GHz performance with VSWR of 1.1 maximum from 0 to 1 GHz and 1.35 from 1 to 3 GHz.
- 75 Ω impedance for communications applications.
- Male center pin contacts are gold plated brass.

Shown on page 25.



TNC (f) 50 Ω Bulkhead Receptacle, Crimp RG55, 142, 223, 400 Model# 7063

- 11 GHz performance with VSWR of 1.3 maximum from 0 to 11 GHz.
- Precision machined brass, not die-cast, with tarnish resistant nickel plating.
- Female center contacts are gold plated heat treated beryllium copper.

Shown on page 24.



BNC (m) 50 Ω Compression Style RG-223 Model# 7207

- 4 GHz performance with VSWR of 1.3 maximum from 0 to 4 GHz.
- Precision machined brass, not die-cast, with tarnish resistant nickel plating.
- Male center pin contacts are gold plated brass.

Shown on page 22.



TNC (m) 50 Ω Plug RG58, 141, 55A, 142, 223, 499 Model# 7048

- 11GHz performance with VSWR of 1.3 maximum from 0 to 11GHz.
- Precision machined brass, not die-cast, with tarnish resistant nickel plating.
- Male center pin contacts are gold plated brass.

Shown on page 24.



Type N (f) 50 Ω Panel Mount Model# 7074

- 11 GHz performance with VSWR of 1.3 maximum from 0 to 11 GHz.
- Precision machined brass, not die-cast, with white bronze plating.
- Female center contacts are gold plated (30 micro-inches) brass.

Shown on page 26.

Customized Products

Pomona responds to a wide range of special or custom requirements by providing accessories tailored to your needs. Whether we simply modify an existing catalog product or create a unique combination of products, we use only the finest materials to deliver top quality products.

8

Think of the possibilities!
You can now define your own custom product or kit made of many combination of cables, wires, connectors, or probes in this catalog. Can't find the length or color you need? Pomona makes it easy. Want a unique combination of connectors and cables you just can't find anywhere? Just ask Pomona!



Combinations of coaxial connector/adaptor assemblies can include strain-relief sheathing, marking and lengths.

Call Pomona at **1-800-490-2361** or

Fax your requirements to **425-446-5844**.

Coaxial Cable Assemblies and Breakouts


Pomona is the professional's choice, whether in the lab, plant or in the field. Using high-quality materials such as beryllium copper, brass and nickel plating ensures the precision you rely on. With a huge selection of cables and breakouts offering almost every connector and clip combination, Pomona provides you the solution for any application.

Pomona
ELECTRONICS

9

How to Order

Example: A 48in (1.2m) coaxial cable assembly with matching BNC (m) ends, stress relief boots on RG58 C/U, 50Ω cable.





Typical Pomona Part Number: 2249-C-48
Cable Type _____
Cable Length in Inches _____
(Measured Inside Connectors)

Model#	Length
2249-C-12	12.0in (0.3m)
2249-C-24	24.0in (0.6m)
2249-C-36	36.0in (0.9m)
2249-C-48	48.0in (1.2m)
2249-C-60	60.0in (1.5m)

Cable Assembly Holders

Model#	Color	"A" Max Cable Dia.	Number of Slots
1508	Orange	0.210in (5.33mm)	14
4408	Black	0.320in (8.13mm)	10
2708	Blue	0.450in (11.43mm)	9



Technical Specifications for Wire and Cable

Cable Designation	Type	Impedance Ω	Capacitance per 1ft/ 0.304m	Insulation/ Dielectric	AWG	Stranding Strands X AWG	Wire Type	Jacket Material	Cable O.D.	Shield	Temperature (w/o connectors)
A	twisted pair, 2 conductor	NA	27.0 pf	PVC	18	65X36	TC	PVC	0.25in (6.35mm)	NA	-4 to 221°F (-20 to +105°C)
C	Coax, RG58C/U	50	30.8 pf	PE	20	19X36	TC	PVCNC	0.195in (4.95mm)	TCB	-40 to 185°F (-40 to +85°C)
E	Coax, RG59B/U	75	22.5 pf	PE	23	Solid	BCCS	PVCNC	0.242in (6.15mm)	BCB	-40 to 140°F (-40 to +60°C)
J	Microphone, 2 conductor, shielded	90	18 / 32 pf*	PE	22	16X34	TC	PVC	0.231in (5.84mm)	TCB	-40 to 176°F (-40 to +80°C)
K	Coax, RG174/U	50	30.8 pf	PE	26	7X34	BCCS	PVC	0.110in (2.79mm)	TCB	-40 to 167°F (-40 to +75°C)
T	Coax, RG214/U	50	30.8 pf	PE	13	7X22	SPC	PVCNC	0.425in (10.8mm)	SCCB / SCCB	-40 to 176°F (-40 to +80°C)
X	Coax, RG142B/U	50	29.0 pf	TFE	18	Solid	SPCCS	FEP	0.195in (4.05mm)	SPC / SPC	-94 to 392°F (-70 to +200°C)
Y	Coax, RG223/U	50	30.8 pf	PE	19	Solid	SPC	PVCNC	0.212in (5.38mm)	SCB / SCB	-40 to 140°F (-40 to +60°C)
BB	Coax, RG316/U	50	29.0 pf	TFE	26	7X37	SPCCS	FEP	0.096in (2.44mm)	SPC	-94 to 392°F (-70 to +200°C)
SS	Coax, RG58/U, low noise	50	37.0 pf	CPE / PE	22	7X30	TC	PVC	0.195in (4.95mm)	BAF / TCB	-40 to 176°F (-40 to +80°C)
V	Coax, RG59/U	75	20.4 pf	PE	23	Solid	BCCS	PVC	0.242in (6.15mm)	BCB	-40 to 176°F (-40 to +80°C)
Triaxial	Coax, RG 58A/U, double shielded	50	30.8 pf	PE / PE	20	7X28	TC	PVC	0.240in (6.10mm)	TCB / TCB-40	to 167°F (-40 to +75°C)

* Capacitance between conductors / Capacitance between conductor and shield

AWG = American Wire Gauge
BAF = Bonded Aluminum Foil Polyester Tape
BCB = Bare Copper Braid
BCCS = Bare Copper Covered Steel
CPE = Conductive Polyethylene

FEP = Fluorinated Ethylene Propylene
OD = Outside Diameter
NA = Not Applicable
PE = Polyethylene
PVC = Polyvinyl Chloride

PVCNC = Polyvinyl Chloride Non Contaminating
SCB = Silver Coated Braid
SPC = Silver Plated Copper
SCCB = Silver Coated Copper Braid

SPCCS = Silver Plated Copper Covered Steel
SSPE = Semi-Solid Polyethylene
TC = Tinned Copper
TCB = Tinned Copper Braid
TFE = Tetrafluoroethylene

Ratings: The components in this section have a hands free rating for use in controlled voltage environments. However, for CE compliance these products are not intended for hand held use at voltages above 33 Vrms/70 Vdc.

www.pomonaelectronics.com

BNC Male Cable with Molded Strain Relief



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max., ("Y" Cable 176°F (+80°C).)

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

Length	50Ω Cable O.D. .195in (4.95mm) RG58C/U	50Ω Cable O.D. .206in (5.23mm) RG223	75Ω Cable O.D. .242in (6.15mm) RG59B/U	50Ω Cable O.D. .100in (2.54mm) RG174/U	50Ω Cable O.D. .195in (4.95mm) RG58C/U
.5ft (0.2m)	2249-C-6		2249-E-6	2249-K-6	
1ft (0.3m)	2249-C-12	2249-Y-12	2249-E-12	2249-K-12	5266-C-12
2ft (0.6m)	2249-C-24	2249-Y-24	2249-E-24	2249-K-24	
3ft (0.9m)	2249-C-36	2249-Y-36	2249-E-36	2249-K-36	
4ft (1.2m)	2249-C-48	2249-Y-48	2249-E-48	2249-K-48	5266-C-48
5ft (1.5m)	2249-C-60	2249-Y-60	2249-E-60	2249-K-60	5266-C-60
6ft (1.8m)	2249-C-72	2249-Y-72	2249-E-72	2249-K-72	
8ft (2.4m)	2249-C-96	2249-Y-96		2249-K-96	
10ft (3.0m)	2249-C-120	2249-Y-120	2249-E-120	2249-K-120	
12ft (3.7m)	2249-C-144	2249-Y-144	2249-E-144		
15ft (4.6m)	2249-C-180	2249-Y-180	2249-E-180	2249-K-180	
20ft (6.1m)	2249-C-240	2249-Y-240	2249-E-240	2249-K-240	
25ft (7.6m)	2249-C-300		2249-E-300	2249-K-300	
30ft (9.1m)	2249-C-360		2249-E-360		
50ft (15.2m)	2249-C-600		2249-E-600		

Model 2249-C is Pomona Electronics' most popular cable. The 50Ω RG58C/U cable makes it ideal for most test and measurement applications.

Model 2249-Y is a 50Ω, RG223/U cable with double shield. Use when additional shielding is required.

Model 2249-E RG59B/U is a 75Ω cable, making it the right choice for use with TV, video and LAN applications.

Model 2249-K RG174/U offers superior flexibility in a 50Ω cable.

Model 5266-C is the same high quality construction as Model 2249-C with a connector on (one end only.)

BNC Male Low-Noise Cable



Model#	Length
4964-SS-6	6in (0.2m)
4964-SS-12	12in (0.3m)
4964-SS-24	24in (0.6m)
4964-SS-36	36in (0.9m)
4964-SS-48	48in (1.2m)
4964-SS-60	60in (1.5m)
4964-SS-72	72in (1.8m)
4964-SS-120	120in (3.0m)
4964-SS-240	240in (6.1m)

Model 4964-SS uses a special low-triboelectric cable which has noise attenuating layers surrounding the center conductor. The cable is ideal for low power, low frequency measurements.

Recommended Frequency Range: DC to 10KHz

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

BNC Male True 75Ω High Flex Cable



Model#	Length
6510-V-12-0	12in (0.3m)
6510-V-24-0	24in (0.6m)
6510-V-36-0	36in (0.9m)
6510-V-48-0	48in (1.2m)
6510-V-60-0	60in (1.5m)
6510-V-72-0	72in (1.8m)

Model 6510-V uses a true 75Ω connector for superior VSWR and low return loss up to 3 GHz. The highly flexible RG59/U type cable has a gas injected foam polyethylene dielectric with PVC jacket for low loss and superior shield coverage. Highly flexible cable and molded strain relief prevent excessive bending or kinking. An ideal product for HDTV and digital video as well as test and measurement.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

Flexible Color-coded Sleeves for BNC Cables



Model#	Pkg. Qty
6291	20

PVC sleeves which help prevent inadvertent contact with the outer shell of the BNC and allow for color-coding. Available in 10 colors. Fit most BNC male connectors. Perfect for use with any of the Model 2249- type cables.

Colors: contains 2 ea. of 10 colors.

IEC Insulated BNC Male 50Ω Cable



Model#	Length
72926-C-40	40in (100cm)
72926-C-80	80in (200cm)

Rating: 500V Cat 1, 150V Cat II, 3A.

Color: Black.



BNC Male 50Ω Cable: Field Servicable Connector



Model#	Length
BNC-C-6	6in (0.2m)
BNC-C-12	12in (0.3m)
BNC-C-18	18in (0.5m)
BNC-C-24	24in (0.6m)
BNC-C-36	36in (0.9m)
BNC-C-48	48in (1.2m)
BNC-C-60	60in (1.5m)
BNC-C-72	72in (1.8m)
BNC-C-96	96in (2.4m)
BNC-C-600	600in (15.2m)

Clamp nut and silicone gasket seal out moisture. Gold-plated center contact and Teflon® insulation assure premium performance.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass contact soldered to cable; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.


BNC Male to BNC Male Right Angle 50Ω Cable


Model#	Length
1383-C-24	24in (0.6m)
1383-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

BNC Male Right Angle Connector Cable with Molded Strain Relief



Model#	Length
4276-C-12	12in (0.3m)
4276-C-24	24in (0.6m)
4276-C-36	36in (0.9m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

BNC Male 50Ω Cable



Model#	Length
5697-6	6in (0.2m)
5697-12	12in (0.3m)
5697-24	24in (0.6m)
5697-36	36in (0.9m)
5697-48	48in (1.2m)
5697-60	60in (1.5m)
5697-72	72in (1.8m)
5697-120	120in (3.0m)
5697-180	180in (4.6m)
5697-240	240in (6.1m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

Cable Type: 50Ω, RG58 type 0.19in (4.95mm) O.D.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass contact crimped to cable; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief (on retractile cable)


Model#	Extended Length
4487-48	48in (1.2m)
4487-60	60in (1.5m)
4487-72	72in (1.8m)

Rating: Hands free testing in controlled voltage environment: 270 Vdc/90 Vac cont. duty*, +122°F (+50°C) max.

Cable Type: Shielded microphone cable.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

BNC Male 50Ω Cable with Insulated Push-on Connector


Model#	Length
6253-C-24	24in (0.6m)
6253-C-36	36in (0.9m)

Unique locking feature assures secure retention with the convenience of a push-on connector.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Outer Shell: blue thermoplastic; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.


See chart on page 9 for additional wire and cable specifications.

One End Only

Strain-relief connector on one end only

Model#	Extended Length
5260-72	72in (1.8m)

BNC Male to BNC Female with Molded Strain Relief



Model#	Length
4524-C-36	36in (0.9m)
4524-C-48	48in (1.2m)
4524-C-60	60in (1.5m)

Use to extend BNC Cables.


Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

BNC Female 50Ω Cable with Molded Strain Relief



Model#	Length
4277-C-24	24in (0.6m)
4277-C-48	48in (1.2m)


Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated beryllium copper; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

BNC Male to UHF Male, Molded Strain Relief



Model#	Length
1367-C-60	60in (1.5m)


Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC/UHF: Body: tarnish resistant nickel-plated brass; Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.



SMA Male 50Ω Cable



RG 174/U	Length
4846-K-24	24in (0.6m)
4846-K-48	48in (1.2m)
4846-K-60	60in (1.5m)


RG 316/U	Length
4846-BB-24	24in (0.6m)
4846-BB-48	48in (1.2m)
4846-BB-60	60in (1.5m)

RG 142B/U	Length
4846-X-24	24in (0.6m)
4846-X-48	48in (1.2m)
4846-X-60	60in (1.5m)

SMA: Body/Fittings: passivated stainless steel; Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

BNC Male to SMA Male 50Ω Teflon Insulated Cable



RG 316/U	Length
4935-BB-24	24in (0.6m)
4935-BB-48	48in (1.2m)
4935-BB-60	60in (1.5m)


Rating: Hands free testing in controlled voltage environment: 335 Vrms*.

SMA: Body /Fittings: passivated stainless steel; Contact: gold-plated brass; Dielectric: PTFE.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

SMA Male to SMA Male Right Angle - 50Ω




RG 316/U	Length
4814-BB-24	24in (0.6m)
4814-BB-48	48in (1.2m)
4814-BB-60	60in (1.5m)

SMA: Body/Fittings: passivated stainless steel; Contact: gold-plated brass. Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

SMA Male to SMA Female



RG 174/U	Length
4528-K-48	48in (1.2m)

RG 316/U	Length
4528-BB-60	60in (1.5m)

RG 142B/U	Length
4528-X-24	24in (0.6m)
4528-X-48	48in (1.2m)

SMA: Body/Fittings: passivated stainless steel; Contact: gold-plated brass; Dielectric: PTFE.

SMA (F): gold-plated, beryllium copper center contact; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

**SMA Male Right Angle
50Ω Cable**

 0.90in
(22.86mm)


RG 316/U	Length
4813-BB-24	24in (0.6m)

SMA: Body/Fittings: passivated stainless steel; Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

Type 'N' Male 50Ω Cable

 1.48in
(37.59mm)



Model#	Length
1658-T-18	18in (0.5m)
1658-T-24	24in (0.6m)
1658-T-36	36in (0.9m)
1658-T-48	48in (1.2m)
1658-T-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 1,000 Vrms*.

Type 'N': Body: white bronze-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

**SMA Male to Type 'N' Male
50Ω Cable**

 1.40in
(35.56mm)


Model#	Length
5058-X-12	12in (0.3m)
5058-X-24	24in (0.6m)
5058-X-36	36in (0.9m)
5058-X-48	48in (1.2m)
5058-X-60	60in (1.5m)

SMA: Body/Fittings: passivated stainless steel; Contact: gold-plated brass; Dielectric: PTFE.

Type 'N': Body: white bronze-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

Type 'N' Male 50Ω Cable


 1.40in
(35.56mm)


Model#	Length
2256-X-48	48in (1.2m)
2256-C-36	36in (0.9m)
2256-C-60	60in (1.5m)

Type 'N': Body: white bronze-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

**BNC Male to Type 'N' Male,
50Ω Cable**

 1.40in
(35.56mm)


Model#	Length
1366-C-24	24in (0.6m)
1366-C-36	36in (0.9m)
1366-C-48	48in (1.2m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Dielectric: PTFE.

Type 'N': Body: white bronze-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

**Triaxial Male to
Three Alligator
Test Clips, Double
Shielded**


Model#	Cable Type	Lugs	Length
4725	Triaxial	2	36in (0.9m)
5342	Triaxial	3	36in (0.9m)

Rating: Hands free testing in controlled voltage environment: 150 Vrms*.

Jaw Opening: 0.30in (7.62mm) Max.



Triaxial: Body/Fittings: tarnish resistant nickel-plated brass; Intermediate and Center Contacts: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.





 2.25in
(57.15mm)

6.0in (152.40mm)



*see rating message at start of section.

Triaxial Male Cables



Model#	Cable Type	#Lugs	Length
5223-36	Triaxial	3	36in (0.9m)
5223-60			60in (1.5m)
5054-36	Triaxial	2	36in (0.9m)
5054-60			60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

Triaxial: Body/Fittings: tarnish resistant nickel-plated brass; Intermediate and Center Contacts: gold-plated brass; Dielectric: PTFE.


Cable Type: Double Shielded, 50Ω, RG58A/U.

Colors: 5223: Yellow, 5054: Yellow.

Triaxial to BNC Adapters on page 24.

See chart on page 9 for additional wire and cable specifications.

BNC Male to Minigrabber® Test Clips



Model#	Length
3787-C-18	18in (0.5m)
3787-C-24	24in (0.6m)
3787-C-36	36in (0.9m)
3787-C-48	48in (1.2m)
3787-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Minigrabber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional wire and cable specifications.

BNC Male to TNC Male, 50Ω Cable




Model#	Length
1948-C-12	12in (0.3m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC/TNC: Body: tarnish resistant nickel-plated brass; Contact: gold-plated brass; Dielectric: PTFE.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Minipincer® Test Clips



Model#	Length
5423-C-24	24in (0.6m)
5423-C-36	36in (0.9m)
5423-C-48	48in (1.2m)
5423-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.


Strain Relief: PVC molded directly to cable and connectors.

Minipincer: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional wire and cable specifications.

Phono (RCA) Male to BNC Male with Molded Strain Relief



Model#	Length
4963-E-24	24in (0.6m)
4963-E-36	36in (0.9m)
4963-E-48	48in (1.2m)
4963-E-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Phone Plug: Body and Center Contact: nickel-plated brass.

Strain Relief: PVC molded directly to cable and connectors.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Micrograbber® Test Clips



Model#	Length
4777-C-24	24in (0.6m)
4777-C-36	36in (0.9m)
4777-C-48	48in (1.2m)
4777-C-60	60in (1.5m)
4777-K-24	24in (0.6m)
4777-K-36	36in (0.9m)
4777-K-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 150 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Micrograbber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional wire and cable specifications.



BNC Male with Molded Strain Relief to Alligator Test Clips


Model#	Length
4531-C-18	18in (0.5m)
4531-C-24	24in (0.6m)
4531-C-30	30in (0.76m)
4531-C-36	36in (0.9m)
4531-C-48	48in (1.2m)
4531-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 150 Vrms*.

Jaws Opening: 0.3in (7.62mm) max.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Alligator: Body: steel-plated nickel.

Colors: Vinyl boots: one black and one red.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Maxigrabber® Test Clips


Rating: Hands free testing in controlled voltage environment: 300 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Maxigrabber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional

BNC Male with Molded Strain Relief to Minigrabber® Test Clips


Model#	Length
5187-C-24	24in (0.6m)
5187-C-36	36in (0.9m)
5187-C-48	48in (1.2m)
5187-C-60	60in (1.5m)
5187-K-24	24in (0.6m)
5187-K-36	36in (0.9m)
5187-K-48	48in (1.2m)
5187-K-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Minigrabber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Minigator® Test Clips


Rating: Hands free testing in controlled voltage environment: 45 Vrms*.

Jaws Opening: to 0.18in (47.50mm) max.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Minigator: Body: steel-plated nickel.

Colors: Vinyl boots: one black and one red.

Rating: +122°F (+50°C) max.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to SMD Grabber® Test Clips


Model#	Length
5304-K-24	24in (0.6m)
5304-K-36	36in (0.9m)

Rating: Hands free testing in controlled voltage environment: 150 Vrms*.


BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass; Dielectric: PTFE.

Strain Relief: PVC molded directly to cable and connectors.

Grabber: Contacts: gold-plated stainless steel; Insulation: glass filled nylon.

Colors: One black and one red.

See chart on page 9 for additional wire and cable specifications.

BNC Male to Multi-Stacking Double Banana Plugs


Model#	Length
2BC-BNC-36	36in (0.9m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.


Cable Type C: RG58C/U, 0.19in (4.95mm) O.D.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass.

2nd End: Double Banana Plugs. Body: nickel-plated brass beryllium copper spring; Insulation: polypropylene. Color: Black.

Strain Relief: PVC molded directly to cable and connectors.

BNC Male to Stacking Pin Tip Plugs



Model#	Length
2882-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

Cable Type: RG58C/U, 0.19in (4.95mm) O.D.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass.

Pin Tip Plug: Body: gold-plated brass; Insulation: polypropylene.

Colors: One black and one red.

Strain Relief: contact soldered to cable

See chart on page 9 for additional wire and cable specifications.

Insulated BNC Male / 4mm Plugs



Model#	Length
72927-C-40	40in (100cm)
72927-C-80	80in (200cm)

Impedance: 50Ω

Rating: 500V Cat I, 150 V Cat II, 3A.

Color: Black.

NEW

IEC Insulated BNC Male to Stackable/Retractable 4 mm plugs



Model#	Length
72908	10in (25cm)


Impedance: 50Ω

Rating: 33 Vrms / 70 Vdc, 6A.

Color: Black.

NEW

IEC Insulated BNC Female to Stackable/Retractable 4 mm plugs



Model#	Length
72909	10in (25cm)


Impedance: 50Ω

Rating: 33 Vrms / 70 Vdc, 6A.

Color: Black.

NEW

BNC Male to ... the ends listed below



1st End: Crimp BNC Male with Molded Strain Relief.

Body: tarnish resistant nickel-plated brass; Center contact: gold-plated brass; Impedance: 50Ω, Boot, PVC; Color: black.

Cable Type C: RG58C/U


Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated brass

Strain Relief: PVC molded directly to cable and connectors.

Match to any end shown below

BNC Male with Molded Strain Relief to Multi-Stacking Banana Plugs




Model#	Length
5268-C-24	24in (0.6m)
5268-C-36	36in (0.9m)
5268-C-48	48in (1.2m)
5268-C-60	60in (1.5m)

2nd End: Stacking Banana Plugs. Body: nickel-plated brass beryllium copper spring; Insulation: polypropylene; Colors: one black and one red.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Multi-Stacking Double Banana Plug




Model#	Length
4530-C-18	18in (0.5m)
4530-C-24	24in (0.6m)
4530-C-36	36in (0.9m)
4530-C-48	48in (1.2m)
4530-C-60	60in (1.5m)

2nd End: Double Banana Plugs. Body: nickel-plated brass beryllium copper spring; Insulation: polypropylene. Color: black.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Retractable Sheath Banana Plugs




Model#	Length
5343-C-12	12in (0.3m)
5343-C-24	24in (0.6m)
5343-C-36	36in (0.9m)
5343-C-48	48in (1.2m)
5343-C-60	60in (1.5m)

Ideal for use with binding posts.

2nd End: Sheathed Banana Plugs. Body: nickel-plated brass beryllium copper spring; Insulation: nylon.

See chart on page 9 for additional wire and cable specifications.

BNC Male with Molded Strain Relief to Square Pin Receptacles



Model#	Length
4945-K-18	18in (0.5m)
4945-K-24	24in (0.6m)
4945-K-36	36in (0.9m)
4945-K-48	48in (1.2m)
4945-K-60	60in (1.5m)

2nd End: 0.025in (0.6mm) Square Pin Receptacles Center Contact: gold-plated brass; Insulation: ABS; Colors: one black and one red.



See chart on page 9 for additional wire and cable specifications.

BNC Male or Female to ... the ends listed below
BNC Male (1st End):

Body: tarnish resistant nickel-plated brass;
 Center Contact: gold-plated brass;
 Insulation: polypropylene; Dielectric: PTFE.

Nominal impedance: 50Ω.

Colors: Black.



Overall length = BNC length + wire length + clip/plug length

Match to any end shown below

BNC Female (1st End):

Body: tarnish resistant nickel-plated brass;
 Center Contact: beryllium gold-plated copper;
 Insulation: polypropylene; Dielectric: PTFE.

Nominal impedance: 50Ω.

Colors: Black.


...Minigrabber® Test Clips (2nd End)


Male Model#	Female Model#	Wire Length
3789	3788	5.5in (140mm)

Minigrabber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon

Colors: One black and one red.

Rating: Hands free testing in controlled voltage environment: 300 Vrms*, +131°F (+55°C) max.


...Micrograbber® Test Clips (2nd End)


Male Model#	Female Model#	Wire Length
5189	5188	5.4in (137mm)

Micrograbber: Contacts: beryllium gold-plated copper; Insulation: glass filled nylon.

Colors: One black and one red.

Rating: Hands free testing in controlled voltage environment: 150 Vrms*, +131°F (+55°C) max.


... SMD Grabber® Test Clips (2nd End)


Male Model#	Female Model#	Wire Length
5410	5305	5.5in (140mm)

Grabber: Contacts: gold-plated stainless steel; Insulation: glass filled nylon.

Colors: One black and one red.

Rating: Hands free testing in controlled voltage environment: 150 Vrms*, +131°F (+55°C) max.


... Multi-Stacking Banana Plug (2nd End)


Male Model#	Female Model#	Wire Length
3957	3073	5.4in (137mm)

Banana Plug: Body: brass, Spring: beryllium copper; gold-plated. Insulation: polypropylene.

Colors: One black and one red

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.


... Stacking Miniature


Male Model#	Female Model#	Wire Length
4815	3966	5.5in (140mm)

Banana Plug: Body: brass, Spring: beryllium copper; gold-plated. Insulation: polypropylene.

Colors: One black and one red

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

... Alligator Test Clips (2nd End)


Male Model#	Female Model#	Wire Length
2885	2630	5in (127mm)


Alligator: Body: steel-plated nickel.

Colors: Vinyl boots: one black and one red.

Rating: +122°F (+50°C) max.

Rating: Hands free testing in controlled voltage environment: 150 Vrms*.

Jaw Opening: 0.30in (7.62mm).

... Minigator Test Clips (2nd End)



Male Model#	Female Model#	Wire Length
2886	2631	5.9in (149mm)

Minigator: Body: steel-plated nickel.

Colors: Vinyl boots: one black and one red.

Rating: Hands free testing in controlled voltage environment: 45 Vrms*, +122°F (+50°C) max.

Jaw Opening: 0.18in (47.50mm).

... Stacking Pin Tip Plugs (2nd End)


Male Model#	Female Model#	Wire Length
3901	3221	5.5in (140mm)

Pin Tip Plug: Body: gold-plated brass; Insulation: polypropylene.

Colors: One black and one red.


Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

... 20 AWG Leads (2nd End)


Male Model#	Female Model#	Wire Length
4970	4969	5.9in (149mm)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

2nd End: None.


Female only ... to #8 Spade Lugs (2nd End)


Female Model#	Length
5051	5.4in (136mm)

Spade Lug: Body: Copper, tin-plated; Insulation: vinyl.

Colors: One black and one red.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

Female only ... to .025 Square Pin Receptacles (2nd End)


Female Model#	Length
5069	5.6in (143mm)

Square Pin: Gold-plated phosphor bronze, ABS insulation.

Colors: One black and one red.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

*see rating message at start of section.

RF Coaxial Connectors, Adapters and Kits

Self constructed cable assemblies for specific applications or deluxe assortments that enable you to be ready for anything. Pomona has everything from a single reliable adapter to versatile kits packaged in lightweight, foam padded cases containing all the connections and terminations you might need. Pomona – connecting with quality.

Universal Adapter Kit

Model# 5698



Kit contains two each: BNC (m), BNC (f), TNC (m), TNC (f), SMA (m), SMA (f), N (m), N (f), four intermediate couplers, one double Banana Plug, one double Banana Jack, and case.



Multi-RF Direct Adapter Kit

Model# 72934



A comprehensive kit including the most frequently used 50Ω RF adapters in a rugged pistol-grip case. Allows for direct adaptation without intermediate couplers. All parts are precision machined brass, not die-cast, with tarnish resistant nickel plating. Male center pin contacts are gold plated brass. Female center contacts are gold plated heat treated beryllium copper. Insulation material is high density PTFE.



Kit contains:

3535 BNC (m)/Type N (f)
3288 BNC (f)/Type N (m)
3844 TNC (m)/BNC (f)
4288 SMA(m)/BNC(M)
4290 SMA (m)/BNC (f)
4289 SMA (f)/BNC (m)
4291 SMA (f)/BNC (F)
4298 SMA (m)/Type N (f)
4297 SMA (f)/Type N (M)
4299 SMA (f)/Type N (f)
4292 SMA (m)/TNC (m)
4294 SMA (m)/TNC (f)
4293 SMA (f)/TNC (m)

4295 SMA (f)/TNC (f)
4296 SMA (m)/Type N (m)
3283 BNC (f-f)
3533 BNC (m-m)
3285 BNC (f-m-f) TEE
3284 BNC (f-f-f) TEE
4940 TNC (f-f) Adapter
3841 TYPE N (f-f)
3842 TYPE N (m-m)
4282 SMA (m-f) Rt Angle
4283 SMA (m-m)
4284 SMA (f-f)
4286 SMA Termination, 50Ω (m)

Maxi Universal Adapter Kit

Model# 5748



Kit contains two each: BNC (m), BNC (f), TNC (m), TNC (f), SMA (m), SMA (f), N (m), N (f), UHF (m), UHF (F), Mini UHF (m), Mini UHF (f), F (m), F (f), RCA (m), RCA (f), six intermediate couplers, one double Banana Plug, one double Banana Jack, one sampler, and case.

Adapter Kit Accessories

Individual adapters for the Universal Adapter Kits are also available.

Coupling nut Adapter to	Model#	5698	5748
BNC (m)	5735	2	2
BNC (f)	5739	2	2
TNC (m)	5736	2	2
TNC (f)	5740	2	2
SMA (m)	5737	2	2
SMA (f)	5741	2	2
N (m)	5734	2	2
N (f)	5738	2	2
UHF (m)	5752	2	
UHF (f)	5756	2	

Coupling nut Adapter to	Model#	5698	5748
Mini UHF (m)	5753		2
Mini UHF (f)	5757		2
RCA (m)	5754		2
RCA (f)	5758		2
F (m)	5759		2
F (f)	5755		2
Coupler	5742	4	6
Dbl Banana Plug	5743	1	1
Dbl Banana Post	5744	1	1
Sampler	5760		1

SMA Adapter Kit

Model# 72931



A consolidated kit including the most frequently used SMA adapters in a rugged pistol-grip case. Allows for direct adaptation without intermediate couplers. All parts are precision machined brass, not die-cast, with tarnish resistant nickel plating. Male center pin contacts are gold plated brass. Female center contacts are gold plated heat treated beryllium copper. Insulation material is high density PTFE.



Kit contains:

4282 Right Angle SMA Female to SMA Male
4283 Inline SMA Male to SMA Male
4284 Inline SMA Female to SMA Female
4286 SMA Male Terminator Plug
4289 SMA Female to BNC Male
4290 SMA Male to BNC Female
4291 SMA Female to BNC Female

4292 SMA Male to TNC Male
4293 SMA Female to TNC Male
4294 SMA Male to TNC Female
4295 SMA Female to TNC Female
4296 SMA Male to N Male
4297 SMA Female to N Male
4298 SMA Male to N Female
4299 SMA Female to N Female

N Adapter Kit

Model# 72932



A consolidated kit including the most frequently used Type N adapters in a rugged pistol-grip case. Allows for direct adaptation without intermediate couplers. All parts are precision machined brass, not die-cast, with tarnish resistant nickel plating. Male center pin contacts are gold plated brass. Female center contacts are gold plated heat treated beryllium copper. Insulation material is high density PTFE.



Kit contains:

3288 N Male to 50Ω BNC Female
3535 N Female to 50Ω BNC Male
3841 Inline N Female to N Female
3842 Inline N Male to N Male
3843 Right Angle N Female to N Male
4286 N Male to SMA Male
4297 N Male to SMA Female

4298 N Female to SMA Male
4299 N Female to SMA Female
5089 T Style N Female to N Female
to N Female
4240-50 50Ω N Terminator Plug
4240-75 75Ω N Terminator Plug

Broadcast BNC Adapter Kit

Model# 72933



A comprehensive kit including the most frequently used 75Ω BNC adapters in a rugged pistol-grip case. Allows for direct adaptation without intermediate couplers. All parts are precision machined brass, not die-cast, with tarnish resistant nickel plating. Male center pin contacts are gold plated brass. Female center contacts are gold plated heat treated beryllium copper. Insulation material is high density PTFE.



Kit contains

6737 75Ω BNC f/f Adapter
6738 75Ω BNC f/f/f Adapter
6739 75Ω BNC f/m/f Adapter
6740 75Ω BNC m/m Adapter
6754 BNC (F/M/F) Adapter, In-Line, 75Ω
6779 BNC (m) / f (f), 75Ω
6780 BNC (f) / f (f), 75Ω
6781 BNC (f) / F (m), 75Ω
6782 BNC (m) / F (m), 75Ω

1297 Adapter, BNC(f), Phono Plug
3837 BNC (f)/Tini Plug
4043 Adapter, BNC(M), Phono Jack
4267 BNC (f)/Microplug
5319 BNC Female to Phono Plug
4054 BNC (m) to Phono Jack Adapter
4719 BNC (f)/Bantam Plug
5008 BNC (f)/.090 Video Plug
6519 BNC TO Mini-WECO Adapter
3840-75 BNC (m) Resistor Terminator Plug, 75Ω

7/16 DIN Adapter Kit

Model# 6254



This kit will enable the field service technician to connect equipment that has 7/16 DIN connectors to other equipment that has Type N connectors. These connectors are not compatible, but both are commonly found on the same types of telephone equipment and test equipment.


The key feature of the 7/16 DIN connector is the extremely high resistance to inter-modulation interference. These connectors are used in cellular phone and PCS systems to reduce interference in crowded cell sites and also in radio, television and repeater sites.

An assortment of the most useful adapters for conversion between 7/16 DIN and Type N.

Kit contains one each:

6256 7/16 DIN Male to Type N Male Adapter
6257 7/16 DIN Male to Type N Female Adapter
6259 7/16 DIN Female to Type N Male Adapter
6260 7/16 DIN Female to Type N Female Adapter
7/16 DIN Male to 7/16 DIN Female Right Angle Adapter
7/16 DIN Female to 7/16 DIN Female Splice
All parts are protected by a custom zippered case with die cut foam padding.

Universal Adapter Cable



Model#	Length
5749-24	24in (0.6m)
5749-36	36in (0.9m)
5749-48	48in (1.2m)
5749-60	60in (1.5m)
5749-72	72in (1.8m)

Make cable assemblies with any of the adapters in the universal adapter kits.

Coaxial LAN Test Accessory Kit

Model# 6201




An assortment of products to test or troubleshoot coaxial cable local area networks.

Kit contains: two 50Ω BNC Cables, Male to Male and Male to Female; 2 break-outs, BNC (M) to minigrabber® test clips and BNC (M) to minigrabbers; 3 BNC (M) termination plugs for 50, 75, and 100 Ω impedance; 8 BNC and type N adapters, BNC (F-F), BNC T (F-M-F), BNC Rt angle (M-F), BNC (M-M), BNC (F)/Type N (M), BNC (M)/Type N (F), Type N (F-F), and Type N (M-M); and 2 Type N (M) termination plugs for 50 and 75 Ω impedance.



BNC Female to Double Stacking Banana Plug


Model# 1269



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.
Material: Banana Plug Jack: brass; Spring: heat treated berylliumcopper; Finish: nickel plating.

BNC Male to Double Stacking Banana Plug


Model# 1270



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.
Material: Banana Plug Jack: brass; Spring: heat treated berylliumcopper; Finish: nickel plating.

BNC Female to Double Banana Plug

Model# 1468



4 solder turrets provide access between BNC and isolated banana plugs.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.


BNC: isolated from Banana Plugs.

Material: Banana Plug Jack: brass; Spring: heat treated berylliumcopper; Finish: nickel plating.

Insulated BNC (m) to 2 male banana 4 mm plugs

Model# 72910


Rating: 500V Cat I, 150V Cat II.



Insulated BNC (f) to 2 male banana 4 mm plugs


Model# 72911

Rating: 500V Cat I, 150V Cat II.



BNC Male to Stackable Binding Posts

Model# 1296



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

4mm Safety Banana Jack to 2mm Banana Plug Adapter

Model#

Color

72914-02	Set, Black and Red
72914-0	10 pack, Black
72914-2	10 pack, Red




Accepts 4mm safety-sheathed banana plugs.

Rating: 33 Vac / 70 Vdc, 36A.

BNC Female to Stackable Binding Posts


Model# 1452



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

BNC Male to Stackable Isolated Binding Posts with 4 Terminals

Model# 1469




4 solder turrets for component attachments.

Use to make your own attenuator, balun, or filter.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

BNC Male with Binding Post

Model# 3430-*




Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red.

BNC Female to Single Banana Plug


Model# 1894



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

BNC Female to Miniature Double Banana Plug

Model# 3269




Allows a BNC male to be used with equipment having 0.50in (12.70mm) spaced miniature banana jacks.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.


BNC Male to Miniature Stackable Binding Posts

Model# 3296



Binding posts also accept miniature double banana plugs.


Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

BNC Female to Single Banana Plug with Ground Lead

Model# 4684

Use with equipment having banana plugs or binding posts with non-standard spacing.

18 AWG Ground wire, 2.5in (63.50mm) long.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +131°F (+55°C) max.

BNC Male/Female with DC-Blocking Series Capacitor

Model# 5297

Use for sensitive RF measurements.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +216°F (+102°C) max.


Capacitor: 1000 pF, 600 Vdc.

Type N Male Terminator Plugs


Model#	Ω
4240-50	50
4240-75	75

Rating: Frequency Range DC to 500 MHz, Power: 1W @ 158°F (70°C) max.


Accuracy: 1%.

BNC Male Terminator Plugs


Model#	Ω
3840-50	50
3840-75	75
3840-93	93
3840-100	100
3840-600	600

Rating: Frequency Range DC to 500MHz, Power .5W @ 158°F (70°C) max.

Accuracy: 1%.

BNC Feed-Thru Termination


Model#	Ω
4119-50	50
4119-75	75
4119-93	93
4119-600	600

Rating: 2W Carbon film resistor.

Accuracy: 2%.



Frequency Range: DC to 500 MHz, +216°F (+102°C) max.

BNC 50Ω Attenuator


Model#	dB
4108-3dB	3dB
4108-6dB	6dB
4108-10dB	10dB
4108-14dB	14dB
4108-20dB	20dB

Rating: 2W Avg. @ 77°F (25°C) max.

50Ω impedance. Metal film resistor attenuator.

BNC In-Series Resistor Attenuator


Model#	Ω
4391-25	25
4391-50	50
4391-75	75
4391-600	600

Rating: Frequency Range DC to 500 MHz, +216°F (+102°C) max.

Add series resistance to coaxial lines.

1%, 2W, non-inductive film resistor.

BNC to Banana Plug and Binding Post Adapter Kit
Model# 5510

An assortment of many of Pomona's most popular BNC

Kit contains one each:

BNC Female to Stacking Double Banana Plug
 BNC Male to Stacking Double Banana Plug
 BNC Male to Stackable Binding Posts
 BNC Female to Stackable Binding Posts
 BNC Female to Female
 BNC Male to Male adapters.


BNC 50Ω Attenuator Kit
Model# 5513

Kit contains five Model 4108 BNC 50Ω attenuators, one each of 3dB, 6dB, 10dB, 14dB and 20dB.

(Same as Model 4108).


BNC Male Terminator Plug Kit
Model# 5512

Kit contains five BNC Male terminator plugs for 50, 75, 93, 100, and 600 Ω impedance.

(Same as Model 3840 below.)



50Ω BNC Straight RF Plugs




Fig. 1: Compression Style




Fig. 2: Crimp Style




Fig. 3: Crimp Style

Rating: Hands free testing in controlled voltage environment: 500 Vrms.

BNC: Body: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.

***Performance:** 4 GHz with VSWR of 1.3 maximum from 0 to 4GHz.


7035 and 7037: Use with crimp die set model 7278, crimp tool model 7277.

7040 and 7041: Use with crimp die set model 7279, crimp tool model 7277.


NEW

Model#	Type	Special Features	Fig.	Cable Group	RG /U BNC
4488	BNC (m)	50Ω Impedance	1	142, 142A, 142B, 223, 58, 5B, 5BA, 5BC, 8C, 141, 141A	
4997	BNC (m)	50Ω Impedance	1	RG58 only	
5079	BNC (m)	75Ω Impedance	1	59, 59A, 59B, 62, 62A, 62B, 62C, 210	
5286	BNC (m)		2	59, 59A, 59B, 62, 62A, 62B, 62C, 210	
5307	BNC (m)	50Ω Impedance Crimp	1	174, 174A, 179B, 187, 187A, 188, 188A, 316	
5285	BNC (m)		2	58, 58A, 58C, 141, 141A	
5344	BNC (f)		3	58, 58A, 58C, 141, 141A	
7035*	BNC (m)		2	RG55A, 142, 142A, 223, 400	
7037*	BNC (m)		2	RG58, 58A, 58C, 141, 141A	
7040*	BNC (m)		2	RG174, 188, 188A, 316	
7041*	BNC (m)		2	RG179, 179B, 187, 187A, 174, 188, 188A, 316	
7207*	BNC (m)		1	RG-223	


BNC Within Series Adapters




3284




3534




6700




3285




3283




4896




6701




3533



3847
See Cutout



3846
See Cutout



Panel Cut-Out
for 3846/3847

Model#	Type	Special Features
3283	BNC (f/f)	
3533	BNC (m/m)	
3285	BNC (f/m/f)	
3284	BNC (f/f/f)	
4896	BNC (m/f/f)	
3534	BNC (f/m)	Right Angle
3847	BNC (f/f)	Hermetically Sealed (b)
3846	BNC (f/f)	Isolated Ground (a)
6700	BNC (f/m/f)	In-line
6701	BNC (f/m/f)	Right Angle

Notes: (a) Mounting hardware is isolated from outer conductor of BNC. (b) Leakage rate less than 10^{-7} cc/sec of tracer gas at one atmosphere.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, -85°F to +329°F (-65°C to +165°C).

Impedance: 50Ω.

BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.

Bandwidth: to 4 GHz.

BNC Within Series

Model# 5511

An assortment of Pomona's popular BNC within series adapters.

Kit contains one each:

BNC Female to Female 3283
BNC T (Female/Female/Female) 3284
BNC T (Female/Male/Female) 3285
BNC Male to Male 3533
BNC Right Angle Male to Female 3534
BNC T (Male /Female/Female) 4896




BNC Shorting Cap or Dust Cap




Model#	Type
5085	Shorting cap
3839	Dust cap

Shorting cap provides protection and supplies a short across an input.
Dust cap protects sensitive instrument inputs and is non-shortening.
Tarnish resistant plating.
3in (76.20mm) long chain.

BNC Panel Receptacles – 50Ω


Model#	Type	Special Features
2447	BNC (m)	0.531in (13.46mm) hole
2451	BNC (f)	spacing ctr. to ctr.
2447A	BNC (m)	0.50in (12.70mm) hole
2451A	BNC (f)	spacing ctr. to ctr.

BNC: Shell: tarnish resistant nickel-plated brass; *Center Contact:* male: gold-plated brass; female: gold-plated beryllium copper; *Dielectric:* PTFE.


BNC Female PCB Mount


Model#	Type	Material	Ω
4578	Vertical BNC		50Ω
4788	R/A BNC	Brass	50Ω
6717	Dual R/A BNC	White Valox	50Ω
6718	Dual R/A BNC	White Valox	75Ω
7073*	Straight	Brass	50Ω

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, Impedance: 50Ω, -85 to +329°F (+165 to -65°C)

BNC: Body: tarnish resistant nickel-plated brass; *Contact:* gold-plated beryllium copper. *Dielectric:* PTFE.


***Performance:** 4 GHz with Vswr of 1.3 maximum from 0 to 4GHz.

BNC Bulkhead Receptacles – 50Ω


Model#	Type	Special Features	Max. Panel Thickness
4160	BNC (f)		0.10in (2.54mm)
4159	BNC (f)	Hermetically Sealed*	0.37in (9.40mm)
4979	BNC (m)		0.19in (4.83mm)

* Leakage rate less than 10⁻⁷ cc/sec of tracer gas at one atmosphere.

BNC: Body: tarnish resistant nickel-plated brass; *Center Contact:* male: gold-plated brass; female: gold-plated beryllium copper (except as noted); *Dielectric:* PTFE.


Isolated Ground BNC Female Bulkhead Receptacles


Model#	Special Features	Max. Panel Thickness
3778	50Ω Teflon Insulation	0.175in (4.45mm)
5148	50Ω Valox Insulation	0.18in (4.57mm)

BNC: Body: tarnish resistant nickel-plated brass; *Center Contact:* male: gold-plated brass; female: gold-plated beryllium copper.

Mounting hardware is isolated from outer conductor of BNC.

BNC Male with Strain Relief Boot



Make your own cable with strain relief.

5076: Black boot with nut only.

For use with connectors using a 7/16-28 clamp nut. Simply replace supplied nut with the one on the boot.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

Fits Cable		
Model#	Types	For Cable O.D.
5066-*	RG 58, 141	0.185in - 0.200 (4.70mm - 5.08mm)
5068-*	RG 174, 187, 188	0.090in - 0.110in (2.29mm - 2.79mm)
5076-*	RG 58, 141	0.185in - 0.200in (4.70mm - 5.08mm)

*Specify color

Strain Relief Boot



Rating: +122°F (+50°C) Max.


Use with crimp type connectors.

Sold in packages of 10.

Fits Cable			Colors
Model#	Types	For Cable O.D.	
5155-*	RG 58, 141	0.185in - .200 (4.70mm - 5.08mm)	-0 Black, -2 Red
5156-*	RG 59, 62, 210	0.237in - .247in (6.02mm - 6.27mm)	-0 Black -2 Red
5157-*	RG 174, 187, 188	0.090in - .110in (2.29mm - 2.79mm)	-0 Black

*Specify color

TNC Style RF Plugs and Jacks



Frequency Range: 11 GHz with VSWR of 1.3 maximum from 0 to 11GHz.

Impedance: 50Ω.

TNC: *Shell:* tarnish resistant nickel-plated brass; *Contact:* male: gold-plated brass; female: gold-plated heat treated beryllium copper; *Dielectric:* PTFE.

7049: Use with crimp die set model 7278, crimp tool model 7277.


7063 and 7064: Use with crimp die set model 7278, crimp tool model 7277.

7066: Use with crimp die set model 7279, crimp tool model 7277.



Model#	Type	Special Features	Cable Group RG _/U
7048	TNC (m)	50Ω Captive	RG58, 58A, 58C, 141, 141A, 55A, 142, 142A, 223, 499
7049	TNC (m)	50Ω Crimp and Captive	RG55A, 142, 142A, 223, 400
7050	TNC (m)	50Ω Crimp and Captive	RG58, 58A, 58C, 141, 141A, 55A, 142, 142A, 223, 499
7063	TNC (f)	50Ω Bulkhead Receptacle, Crimp	RG55, 142, 223, 400
7064	TNC (f)	50Ω Panel Receptacle, Crimp	RG58, 58A, 58C, 141, 303, LMR195, Belden 7806A
7065	TNC (f)	50Ω Bulkhead Receptacle, Solder	RG174, 188A, 316, B7805A
7066	TNC (f)	50Ω Bulkhead Receptacle, Crimp	RG174, 188A, 316, B7805A

SMA Connector




Model#	Fits Cable Types
4804	RG174, RG179, RG187
4805	RG188, RG316
4859	RG55, RG142

Supplied with center conductor and sleeve.

Impedance: 50Ω.

SMA: *Shell:* passivated steel; *Dielectric:* PTFE.

SMA Male Terminator Plug



Model# 4286

Rating: Hands free testing in controlled voltage environment: 335 Vrms*.


Impedance: 50Ω 1/2 W., 1%.

VSWR: 1.25 max. to 18GHz, 1/2 W, 85°F to +329°F (65°C to +165°C).

Resistor Terminator.

Gold-plated stainless steel with Teflon insulation.

SMA within Series Adapters




Model#	Type
4282	SMA (f) to (m), Rt. Angle
4283	SMA (m) to (m)
4284	SMA (f) to (f)

SMA: *Shell:* gold-plated brass; *Center Contacts:* gold-plated brass; *Dielectric:* PTFE.

Frequency Range: 4283, 4284: 186Hz; 4282: 12GHz.


SMA Shorting Cap



Model#	Outer Shell
5088	Gold Plated


Screw onto SMA female. Protects sensitive instrument inputs or provides a necessary reference short. Gold-plated steel center contact.

SMA Bulkhead



Model#	Type
4285	SMA (f) to (f)

SMA: *Shell:* gold plated brass; *Center Contacts:* gold plated brass; *Dielectric:* PTFE.


SMA Female Panel Receptacle
Model# 4850


Rating: Hands free testing in controlled voltage environment: 335 Vrms*, -85°F to +329°F (-65°C to +165°C).

Impedance: 50Ω.

SMA: Body: gold-plated stainless steel; Center Contact: gold-plated beryllium copper; Dielectric: PTFE.

Flange thickness: 0.065in (1.65mm).

SMA PCB Mounting Female
Model# 4959


Rating: Hands free testing in controlled voltage environment: 335 Vrms*, -85°F to 329°F (-65°C to +165°C).

Impedance: 50Ω.

SMA: Body: gold-plated stainless steel; Center Contact: gold-plated beryllium copper; Dielectric: PTFE.

SMB Cable Plugs/Jacks

Model#	Type
5375	SMB (f) Connector Crimp Type
5379	SMB (m) Connector Crimp Type
Fit Cable Types	RG 174, 179, 187, 188, 316

These SMB (Subminiature "B") connectors snap together for quick assembly.


Rating: Hands free testing in controlled voltage environment: 335 Vrms*, -85°F to +329°F (-65°C to +165°C).

Impedance: 50Ω.

Frequency Range: DC to 4GHz.

SMB: Shell: tarnish resistant nickel-plated brass; Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.


5375

5379
Type N Striaght RF Plugs and Jacks


Model#	Type	Special Features	Cable Group RG _/U	Performance
7057	N (m)	50Ω Crimp	RG55, 142, 223, 400	11 GHz with Vswr of 1.3 maximum from 0 to 11 GHz
7058	N (m)	50Ω Compression Style	58, 58A, 58C, 141, 141A	
6767	N (m)	75Ω Plug, Crimp	RG59	3 GHz with Vswr of 1.1 maximum from 0 to 1 GHz and 1.35 from 1 to 3 GHz
6768	N (f)	75Ω Jack, Crimp	RG59	

N: Body: bronze-plated white brass; Center Contact: male: gold-plated brass; female: gold-plated heat treated beryllium copper; Dielectric: PTFE.

7057: Use with crimp die set model 7281, crimp tool model 7277.

Type N Connectors

Model#	Type	Description
4787	N (m)	Cable connection for RG58 and 142, 223, 141

N: Body: bronze-plated white brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.

Impedance: 50Ω.


Rating: Hands free testing in controlled voltage environment: 1,000 Vrms*.


4787
Type N Male Terminator Plugs

Model#	Ω
4240-50	50
4240-600	600

Rating: Frequency Range DC to 500 MHz, Power: 1W @ 158°F (70°C) max.

Accuracy: 1%.



Type N RF Panel Mount

0.66in
(16.8mm)



NEW

Model#	Type	Ω	Performance
6769	N (f)	75 Ω	3GHz with VSWR of 1.1 maximum from 0 to 1GHz and 1.35 from 1 to 3GHz
7074	N (f)	50 Ω	11GHz with VSWR of 1.3 maximum from 0 to 11GHz

Material: Body: bronze-plated white brass; Contacts: female (6769): gold-plated heat treated beryllium copper; female (7074): gold plated (30 micro-inches) brass; Dielectric: PTFE.

Type N RF Adapter

1.42in
(36.1mm)



NEW


Model#	Type
6770	N (f/f)
6771	N (m/m)
6772	N (f/f/f)

Performance: 3GHz with VSWR of 1.1 maximum from 0 to 1GHz and 1.35 from 1 to 3GHz

N: Body: bronze-plated white brass; Contacts: female: gold-plated heat treated beryllium copper; male: gold-plated brass; Dielectric: PTFE.

Impedance: 75 Ω .

Type N Panel Mount Receptacle



2455


Panel Cut-Out for 2455

Model#	Type
2455	N (f)
4956	N (f)

N: Body: bronze-plated white brass; Center Contact: female: gold-plated beryllium copper; Dielectric: PTFE.

Impedance: 50 Ω .


Rating: Hands free testing in controlled voltage environment: 1,000 Vrms*.




4956

Panel Cut-Out for 4956


Type N Adapters




3841



3842



3843



5089


Model#	Type
3841	N (f/f)
3842	N (m/m)
3843	N (f/m)
5089	N (f/f/f)

N: Body: bronze-plated white brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.


Impedance: 50 Ω .

Rating: Hands free testing in controlled voltage environment: 1,000 Vrms*.

Triaxial Cable Plugs and Jacks




2 Lug



3 Lug




3600/5056
(Mates with 3850 and 4388)



5218
(Mates with 5219)



4661




Panel Cut-Out for 4661


Model#	Lugs	Max. Panel Thickness	Fits Cable Types
3600	2 Lug (m)		Belden twinaxial 9272 0.242in (6.15mm) O.D.
4661	2 Lug (f)	0.14in (3.56mm)	Microdot 293-3930 0.175in (4.45mm) O.D.
5056	2 Lug (m)		Belden triaxial 9222 0.242in (6.15mm) O.D.
5218	3 Lug (m)		

Triaxial: Body/Fittings: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Outer Contact: gold-plated beryllium copper; Dielectric: PTFE.


Triaxial Adapters



5290




5178



Cut-Out for 5178

Model#	Lugs	Max. Panel Thickness
5178	2 Lug (f)	0.25in (6.35mm)
5290	2 Lug (f)	

Triaxial: Body/Fittings: tarnish resistant nickel-plated brass; Center Contact: female: gold-plated beryllium copper; Outer Contact: gold-plated beryllium copper; Dielectric: PTFE.

Triaxial Female Bulkhead Receptacles


Model#	Lugs	Max. Panel Thickness
3580	2 lug (f)	0.25in (6.35mm)
4388	2 lug (f) Hermetically Sealed (a)	0.25in (6.35mm)
5219	3 lug (f)	0.14in (3.56mm)

Note: (a) Leakage less than 10^{-7} cc/sec tracer gas at one atmosphere.

Triaxial: Body/Fittings: tarnish resistant nickel-plated brass; Center Contact: female: gold-plated beryllium copper; Outer Contact: gold-plated beryllium copper; Dielectric: PTFE.


Twinax Cable Plug
Model# 4957

Use on twinaxial cable types RG108 and Belden 9272.

Polarized Contact (One Male, One Female).

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, -85 to +329°F (-65 to +165°C).


Material: Body: tarnish resistant nickel-plated brass; Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.


Twinax Bulkhead Receptacle
Model# **Max. Panel Thickness**
4958 0.13in (3.30mm)

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, -85 to +329°F (-65 to +165°C).

Polarized Contact (One Male, One Female).

Material: Body: tarnish resistant nickel-plated brass; Contact: male: gold-plated Bbrass; female: gold-plated beryllium copper; Dielectric: PTFE.



Panel Cut-Out
Crimp Tools

NEW

Model#	Type	Features
7277	Crimp Tool (handle only)	Professional grade crimp tool handle for consistent crimping. Accommodates multiple cable sizes. Ratchet style locking with cushioned grips for easy handling. Body is high carbon steel tool; steel is powder coated
7278	Crimp, Die Set RG 55/58/59/62/141/142/223/303/400	Professional grade precision die set. Cavity dimensions are 0.255 in, 0.213 in and 0.068 in. Easily interchangeable. Use with Pomona Crimp Tool 7277
7279	Crimp, Die Set RG 174/178/179/180/187/188/195/196/316	Professional grade precision die set. Cavity dimensions are 0.178 in, 0.128 in and 0.068 in. Easily interchangeable. Use with Pomona Crimp Tool 7277
7280	Crimp, Die Set RG 6/59/Belden 8281	Professional grade precision die set. Cavity dimensions are 0.324 in, 0.255 in, 0.068 in and 0.042 in. Easily interchangeable. Use with Pomona Crimp Tool 7277
7281	Crimp, Die Set 5 Cavity RG 58/59 N, BNC, TNC, SMA	Professional grade precision die set. Cavity dimensions are 0.255 in, 0.213 in, 0.100 in, 0.068 in and 0.052 in. Easily interchangeable. Use with Pomona Crimp Tool 7277.
7282	Crimp, Die Set for sizes 7.11 mm, 6.60 mm, 1.78 mm, 1.02 mm (0.28 in, 0.26 in, 0.07 in, 0.04 in)	Professional grade precision die set. Cavity dimensions are 0.278 in, 0.255 in, 0.068 in and 0.022 in. Easily interchangeable. Use with Pomona Crimp Tool 7277

*see rating message at start of section.

SMA to BNC




Model#	Type
4288	SMA (m) to BNC (m)
4290	SMA (m) to BNC (f)
4289	SMA (f) to BNC (m)
4291	SMA (f) to BNC (f)

Rating: Hands free testing in controlled voltage environment: 335 Vrms*.

Impedance: 50Ω.

SMA: Shell: gold-plated brass; Center Contacts: gold-plated brass; Dielectric: PTFE.

SMA to Type N




Model#	Type
4296	SMA (m) to type N (m)
4298	SMA (m) to type N (f)
4297	SMA (f) to type N (m)
4299	SMA (f) to type N (f)

Rating: Hands free testing in controlled voltage environment: 335 Vrms*.

Impedance: 50Ω.

Material: Shell: gold-plated brass; Center Contacts: gold-plated brass; Dielectric: PTFE.

SMA to TNC




Model#	Type
4292	SMA (m) to TNC (m)
4294	SMA (m) to TNC (f)
4293	SMA (f) to TNC (m)
4295	SMA (f) to TNC (f)

Rating: Hands free testing in controlled voltage environment: 335 Vrms*.

Impedance: 50Ω.

Material: Shell: gold-plated brass; Center Contacts: gold-plated brass; Dielectric: PTFE.

Type N to BNC




Model#	Type	Special Features
3535	BNC (m)/N (f)	
3288	BNC (f)/N (m)	Beryllium Copper Male Contact

Rating: 500 Vrms max., -85 to +325°F (-65 to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

N: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

UHF to BNC



Model#	Type	Special Features
3287	BNC (m)/UHF (f)	Phos. Bronze Contact Nonconstant Impedance
3286	BNC (f)/UHF (m)	Nonconstant Impedance

Rating: Hands free testing in controlled voltage environment: 335 Vrms*, -85 to +325°F (-65 to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

UHF: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

BNC to TNC

Model#	Type
3844	BNC (f)/TNC (m)

1.23in
(31.24mm)



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, -85°F to +325°F (-65°C to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

TNC Female/Female Adapter

Model#	Type
4940	TNC (f/f)

1.30in
(33.02mm)



Impedance: 50Ω.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*.

TNC: Body: tarnish resistant nickel-plated brass; Center Contact: gold-plated beryllium copper.


BNC to F

1.00in
(25.40mm)



6779

1.05in
(26.67mm)



6780

1.25in
(31.75mm)



6781

1.22in
(31.0mm)



6782

Model#	Type
6779	BNC (m)/F (f)
6780	BNC (f)/F (f)
6781	F (m)/BNC (f)
6782	BNC (m)/F (m)

BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

Triaxial to BNC

1.37in (34.80mm)



5299

1.50in (38.10mm)



5298

1.35in (34.29mm)



5090


1.35in (34.29mm)




5300

Model#	Description
5299	3 Lug Triax (f)/BNC (m) adapter
5298	2 Lug Triax (f)/BNC (m) adapter
5090	BNC (f)/2 Lug Triax (m) adapter
5300	BNC (f)/3 Lug Triax (m) adapter

Triaxial: Body: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Outer Contact: gold-plated beryllium copper; Dielectric: PTFE.





Triax BNC



BNC Traix


Triaxial shell is shorted to outer shield



Banana Plugs and Jacks

Just need a reliable plug or jack? Making your own test set? Pomona Electronics' selection is designed to meet demanding electrical characteristics. Nickel-plated plugs feature brass bodies and one-piece heat-treated beryllium copper springs with nylon or ABS insulation. Choose Pomona for the reliable and dependable connections your work demands.

Double Banana Plug with Wire Guide, Stackable, Solderless




Model#	Plating	Insulation	*Std. Colors
MDP-*	Nickel	ABS	-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White
4892-*	Gold	ABS	-0 Black, -2 Red
4898-*	Nickel	Polyphenylene Sulfide	-0 Black, -6 Blue
4914			set screws 8-32 x 0.210in (5.33mm), 100/pk

Set screws secure wire. Simplifies cable construction or component mounting. Accepts cables to 0.22in (5.59mm) dia. max., (18-22 AWG wire).

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; finish: nickel plating.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max. (Model 4898, +302°F (+150°C) max.).

Double Banana Plug with Shorting Bar



Model# MDP-S*

Banana plugs internally shorted with #18 AWG wire.

X-hole accepts standard banana plug.

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; Finish: nickel plating; Insulation: ABS.


Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red, -9 White.

Model# 4914

Set screws 8-32 x 0.210in (5.33mm), 100/pk

Double Banana Plug with Solder Turret Terminals



Model# MDP-ST

Similar to MDP above except with bright tin plated solder turrets. Accepts cables to 0.215in (5.46mm) dia. max.

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; Finish: nickel plating; Insulation: polypropylene.


Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

Color: Black

Model# 4914

Set screws 8-32 x 0.210in (5.33mm), 100/pk

Double Banana Plug, Stackable, Solderless



Model# 1330-*

Similar to MDP without cable loop.

Features recess for mounting small components with set screws.

Model 1330 has setscrews like MDP.

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; Finish: nickel plating; Insulation: ABS.


Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Model# 4914

Set screws 8-32 x 0.210in (5.33mm), 100/pk.

Double Banana Plug with Solder Turret Terminals



Model# 1330-ST-*


Similar to Model 1330 above, but features bright tin plated solder turrets.

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; Finish: nickel plating; Insulation: polypropylene.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Single Banana Plug Splice



Model# 1829-*

Provides rapid method for splicing single banana plug patch cords.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +55°C (+131°F) max.

*Std. Colors: -0 Black, -2 Red.

Sold in pkgs. of 10.


Isolated Double Banana Plug with Four Solder Terminals
Model# MDP-X

Use to make your own attenuator, balun or filter.

Jacks are isolated from plugs.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium, bopper; *Finish:* nickel plating; *Insulation:* polypropylene; *Solder turrets;* bright tin plated.


Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

Color: Red.

Triple Banana Plug, Stackable, Solderless
Model# 2970-*

Use for balanced line 2 conductor shielded cable assemblies. Accepts cables to 0.250in (6.35mm) dia. max., Setscrews secure wires.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper; *Finish:* nickel plating; *Insulation:* ABS.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.


***Std. Colors:** -0 Black, -2 Red.

Isolated Double Banana Plug with Three Solder Terminals
Model# 1837

Use to make your own attenuator, balun or filter.

One jack is isolated.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper; *Finish:* nickel plating; *Insulation:* polypropylene; *Solder turrets;* bright tin plated.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

Color: Blue.

4mm Safety Banana Jack to Banana Plug Adapter
Model# 6728

Accepts safety-sheathed 4mm banana plug and adapts to standard banana plug.

Material: nickel plated brass.


Rating: *For CE compliance:* Not intended for hand held use at voltages above 33 Vrms/70 Vdc, -10 to +55°C.

***Std. Colors:** -0 Black, -2 Red.

Double Banana Plug Splice
Model# 1823-*

Provides rapid method for splicing cables.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.


***Std. Colors:** -0 Black, -2 Red.

Isolated Single Banana Plug with Two Solder Terminals
Model# 1390-*

Ideal for computers, lab circuit design and testing.

Jack is isolated from plug.


Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper; *Finish:* nickel plating; *Insulation:* polypropylene; *Solder turrets;* bright tin plated.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

Single Banana Plug Splice
Model# 1829-*

Provides rapid method for splicing single banana plug patch cords.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +55°C (+131°F) max.


***Std. Colors:** -0 Black, -2 Red.

QUAD Stacking Plug
Model# 3364-*

Features one in-line stacking and three cross-stacking connections.

All jacks are connected to plug.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper; *Finish:* nickel plating; *Insulation:* ABS.


Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) Max.

***Std. Colors:** -0 Black, -2 Red.

Insulated Double Banana Plug Shorting Bar
Model# 5145

Shorting bar is completely insulated in clear ABS thermoplastic.

Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* nickel plating.

Rating: 15A, +122°F (+50°C) max., resistance less than 1.5mΩ.


Do-It-Yourself 4mm Stackable Banana Plug, Solder

Model# 6721


Build your own safety stacking leads with do-it-yourself safety-sheathed 4mm stackable banana plugs.

Material: *Contacts:* nickel-plated brass, *Insulation:* lucel acetal polymer.

Rating: IEC1010 1000V Category III**, 20A, 14 to 176°F (-10 to +95°C).

***Std. Colors:** -0 Black, -2 Red.

** When plug is correctly assembled and terminated.



Do-It-Yourself Retractable Sheath Banana Plug

Model# Color

122505A Black


122506A Red

Do-It-Yourself Retractable Sheath Banana Plugs provide fast simple assembly and reliable performance.

Rating: For CE CAT II 300V, 150V CAT III.

Rating: *Hands free testing* in controlled voltage environment: 1000 Vrms, 20A, ≤ 2 mΩ.

Accepts 18-22 AWG wire.



Do-It-Yourself In-Line Sheathed (4mm) Banana Plug and Jack

Model#

6383-*

6383-02

Plug

6384-*

6384-02

Jack

Safety-rated plugs and jacks for use with any wire from 22 to 18 AWG with flexible insulation.

Attaches to wire by crimp or soldering.

Plugs fit most sheathed DMM jacks and DMM test leads to make up your own banana plug or jack test lead or jumper.


See mating panel jacks (6387 on page 32).

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper; *Insulation:* Santoprene®.

Rating: CAT II 300V, 15A, +275°F (+135°C) max.

***Std. Colors:** -0 Black, -2 Red, -02 Black and Red (2 per pkg).

*Sold in pkgs of 10.



Do-It-Yourself Solderless Stackup Banana Plug with Safety Shield

Internal set screw holds wire firmly.


Safety collar insulates exposed wire leads.

Accepts standard banana plug and fits 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max. (Model 4899, +302°F (+150°C) max.).

Accepts 18-22 AWG wire.



Model#	Plating	Insulation	Std. Colors
1825-*	Nickel	ABS	-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White. Sold in pkgs of 10
4897	Gold	ABS	-0 Black, -2 Red
4899	Nickel	Polyphenylene Sulfide	-0 Black, -6 Blue. Sold in pkgs of 10
6545	Nickel	ABS	Pkg of 1 ea. of all 10 colors

Do-It-Yourself Solderless Stackup Banana Plug

4914 set screws 8-32 x 0.210 (5.33mm), 100/pk.


Internal set screw holds wire firmly.

Accepts standard banana plug, fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug/Jack:* brass; *Spring:* heat treated beryllium copper.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max. (Model 5230, +302°F (+150°C) max.).

Accepts 18-22 AWG wire.



Model#	Plating	Insulation	Std. Colors
1325-*	Nickel	ABS	-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White.
5406	Gold	ABS	-0 Black, -2 Red
5230	Nickel	Polyphenylene Sulfide	-0 Black, -6 Blue
6546	Nickel	ABS	Pkg. of 1 ea. of all 10 colors

*Sold in pkgs of 10.

Do-It-Yourself 4mm Right Angle Banana Plug

Model# 6729

Build your own safety leads with do-it-yourself safety-sheathed 4mm right angle banana plug.


Material: *Contacts:* nickel-plated brass; *Insulation:* lucel acetal polymer.

Rating: IEC1010 1000V Category III**, 20A, 14 to 176°F (-10 to +55°C).


***Std. Colors:** -0 Black, -2 red.

** When plug is correctly assembled and terminated.



**Do-It-Yourself
In-Line Sheathed
Banana Plug/
Banana Jack**


4933/4986 Plugs



4934/4982 Jacks

Model#	Accepts wire AWG	Wire Access Hole	Description
4933-*	22, 20, 18	0.159in (4.04mm) Dia.	Plug
4986-*	16, 14	0.200in (50.8mm) Dia.	Plug
4934-*	22, 20, 18	0.159in (4.04mm) Dia.	Jack
4987-*	16, 14	0.200in (50.8mm) Dia.	Jack

These plugs and jacks are designed to fit together and provide protection from accidental shorting.

Material: *Banana Plug/Jack:* brass; *Spring:* beryllium copper; *Insulation:* nylon.

Rating: *Hands free testing* in controlled voltage environment: 1200V ac/dc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

**Insulated Banana
Plug and Jack
with Flexible Boot,
Solder or Crimp**

Model#	Accepts wire AWG	Mates with...	
5169-*	22, 20, 18	Plug	Jack 5167
5170-*	16, 14		Jack 5168
5167-*	22, 20, 18	Jack	Plug 5169
5168-*	16, 14		Plug 5170



5169/5170 Boots



5167/5168 Jacks


Ideal for making patch cords or field repairs. Snap-on flexible PVC boot allows wire to be crimped or soldered to banana plug or jack. Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Boot:* Banana Plug Body: brass; *Spring:* beryllium copper; *Finish:* nickel plating; *Jack:* nickel plated brass.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Rivet Type Banana Plug

 Rivet
I.D. - 0.14in (3.56mm)
O.D. - 0.25in (6.35mm)



Model#	"X"	Panel
3257	0.094in (2.39mm)	0.062in (1.57mm)
3258	0.125 (3.17mm)	0.093in (2.36mm)

Excellent for riveting to panels or boards. Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* nickel plating.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Sold in pkgs. of 10.


**Rivet Type Banana Plug
with Turret**

Model# 3261

Excellent for riveting to panels or boards. Solder turret for rapid attachment of wires. Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* nickel plating.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Sold in pkgs. of 10.

**Banana Plug with
Threaded Stud and
Solder Lug**



Model#	Thread
3263	6-32 x .50in (12.70mm)
3264	8-32 x .50in (12.70mm)
4512	8-32 x .63in (16.00mm)

Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* nickel plating.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Sold unassembled, in pkgs. of 10.

**Banana Plug with Screw
and Soldering Lug**



Model#	Thread
3265	6-32 x 0.25in (6.35mm)
3266	8-32 x 0.25in (6.35mm)

Fits standard 0.166in (4.22mm) dia. banana jack.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* nickel plating.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Sold unassembled, in pkgs. of 10.

**4mm Banana Plug with
Threaded M3 Stud**

Model# 72918

4mm plug with threaded M3 stud, 2 nuts; 12mm (0.5in) stud length.

Sold unassembled, in pkgs. of 10.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 36A.

NEW

Panel Mt IEC1010 Banana Jacks for Sheathed Plugs

1.34in (34mm)



72912



72913



72930

Model#	Color	Terminal
72912-0	Black	Threaded Stud
72912-2	Red	
72913-0	Black	Solder Tab
72913-2	Red	
72930*		Threaded Stud, Hexagonal Nut

Material: Gold-plated nickel (72912 and 72913).

Rating: 1000V Cat III, 36A Max.


***Std. Colors:** -0 Black, -1 Brown, -2 Red, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White.

Sold in packages of 10 per color.



Panel Mount Banana Jacks with Mounting Base


1.38in (35.05mm)



1.22in (31.0mm)

0.75in (19.05mm)
Typical

2.13in (54.10mm)



1.22in (31.0mm)

0.75in (19.05mm)
Typical

Model#	Mounting Base
2269*	Double
5233-0	Double High-Temp
4601*	Triple


Mounts in panels from 0.063in (1.60mm) to 0.375in (9.53mm) thick. One black, one red. Triple has green.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Temp: +239F (+115°C) [5233-0: +220°F (+428°C)].

***Mounting base color:** -0 Black, -2 Red.

Replacement hex nuts available on page 36.



Panel Cut-Out

Panel Mount Banana Jack

1.22in (31.00mm)



1/4-32 thread

0.375in (9.52mm)

0.35in (88.90mm)

Panel Cut-Out

Terminal Strip Adapter, 4mm Safety Banana Jack to 6/32

1.56in (39.62mm)



Model# 6720

Easily connect your DMM safety sheathed test leads to terminal strips via this handy 6/32 thread adapter.


Material: Contacts: nickel-plated brass, Insulation: lucel acetal polymer.

Rating: For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, (14 to 212°F) -10 to +100°C.


***Std. Colors:** -0 Black, -2 Red.

Panel Mount Banana Jacks for Sheathed Plugs

50 x 28 thread



Panel Cut-Out



6387-T-P-C

Model#	Std. Colors
6387-BC-G-*	-0 Black, -2 Red, -9 White
6387-ST-T-*	-0 Black, -2 Red
6387-TS8-N-*	-0 Black, -2 Red

These banana jacks fit most DMM plugs and all sheathed Pomona plugs. Available with several different terminals. Threaded and press-in style.

Rating: Designed to meet IEC1010 Cat III 1000 Vrms., 15A.

Sold in packages of 10.

Comes with Hex Nut and Lock Washer.

Replacement hex nuts available on page 36.

Color Options:	-0 Black, -2 Red, -9 White.
Plating Options:	T = Tin, G = Gold, N = Nickel
Terminal Type:	BC = Bifurcated Cup ST = Solder Turret TS8 = Threaded Stud #8-32

Panel Mount IEC1010 4 mm (0.16in) Banana Jack for Sheathed Plugs

Model# 5931*

Accepts flexible test lead sets 5907A, 5908A, 5909A available on page 68.


Max. Panel Thickness: 0.28in (7.0mm).

Insulation: Nylon.

Rating: 1000 V Cat III per IEC61010-031 and IEC61010-1, 25A.

***Std. Colors:** -0 Black, -2 Red, -6 Blue, -9 White.

Sold in pkgs. of 10 per color.



0.57in (14.5mm)

0.42in (10.75mm)

0.47in (12.0mm)

Panel Cut-Out

Model#	Plating	Insulation	Std. Colors
1581*	Bright tin	Polycarbonate	-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White
2854*	Gold	Polycarbonate	-0 Black, -1 Brown, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
4900*	Bright tin	Polyphenylene Sulfide	-0 Black, -6 Blue

Mounts in panels ranging in thickness from 0.063in (1.60mm) to 0.375in (9.53mm).

Material: Brass.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use


at voltages above 33 Vrms/70 Vdc, 15A, +239°F (+115°C) max. (Model 4900, +428°F (+220°C) max.).

Mounting Bases and replacement hex nuts available on page 36.

Sold in pkgs. of 10 per color.

Uninsulated Banana Jack

Model# 3267



Fits standard banana plug.

Material: nickel-plated brass.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A.

Replacement hex nuts available on page 36.

Binding Posts


Model# Material

3750-*	Gold-plated brass
3760-*	Bright tin-plated brass
3770-*	Gold-plated tellurium copper

Insulation: Polycarbonate.


Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +239°F (+115°C) max.

*Std. Colors: 3750 and 3760: all 10 colors. 3770: -0 Black, -2 Red. Sold unassembled.



Banana Jack with Wire Wrap Terminal

Model# 4005-*



Material: Jack: nickel-plated brass; Terminal: gold-plated phosphor bronze; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red.

Sold in pkgs. of 10 per color.

Replacement hex nuts available on page 36.

Hex Head Binding Post


Model# 5018-*

Meets MIL-P-55149/1A.


Material: Binding Post Body, Nuts, Lockwasher: gold-plated brass; Insulation: Nylon MIL-P-20693.

Rating: Hands free testing in controlled voltage environment: 1500 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 30A, +176° (+80°C) max.

*Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White.



Terminal Strip Banana Jack Adapter



Model#	Thread	Vrms	Torque In/Lb	X Stud Length
5699-*	6-32	1100	7	0.25in (6.35mm)
5700-*	8-32	1600	16	0.32in (8.13mm)
5701-*	10-32	1700	25	0.32in (8.13mm)

This adapter provides a banana jack connection by replacing the screw in a terminal strip. Secure connections can be made with standard banana plug patch cords without breaking the connection to the terminal strip. Banana jack 0.166in (4.22mm) dia.

Material: Banana Jack: nickel-plated brass; Insulation: Nylon.

*Std. Colors: -0 Black, -2 Red, -3 Orange, -4 Yellow, -9 White.

Ratings: Hands free testing in controlled voltage environment: (see chart for Vrms for each model#); For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 25A, +216°F (+102°C) max.

Binding Post with Wire Wrap Terminal


Model# 4098-*

Accepts standard banana plugs and 0.080in (2.03mm) pin tips, wires and probe tips in 0.100in (2.54mm) cross-hole.


Material: Binding Post: nickel-plated brass; Terminal: gold-plated phosphor bronze; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red.



Binding Post/Banana Jack Mounting Bases



For binding post models 3750, 3760, 3770

Model#	Type	Used with	A	B	C
3862-*	Double	Standard	1.19in (30.22mm)	0.75in (19.05mm)	0.44in (11.18mm)
3863-*	Triple	Binding Posts	1.94in (49.28mm)	0.75in (19.05mm)	0.44in (11.18mm)
4619-*	Double	Miniature	0.87in (22.09mm)	0.50in (12.70mm)	0.38in (9.65mm)
4614-*	Triple	Banana Jacks	1.38in (35.05mm)	0.50in (12.70mm)	0.38in (9.65mm)
4654-*	Double	Standard	1.38in (35.05mm)	0.75in (19.05mm)	0.63in (16.00mm)
4590-*	Triple	Banana Jacks	2.13in (54.10mm)	0.75in (19.05mm)	0.63in (16.00mm)


Mount banana jacks and binding posts at standard 0.75in (19.05mm) spacing.

Material: polycarbonate**Rating:** +239°F (+115°C) Max.

*Std. Colors: -0 Black.

Sold in pkgs. of 10.

Spring Loaded Binding Post




Model# 4995-*

Meets MIL-P-55149/8.

Silicone rubber O-rings provide water resistant seal when mounted in panels from 0.062in to 0.125in (15.75mm to 3.18mm) thick.


Material: Nickel-plated brass.

***Std. Colors:** -0 Black, -2 Red.



Panel Cut-Out

Spring Loaded Binding Post



Model# 4770-*

Mounts in panels from 0.06in (1.6mm) to 0.38in (9.53mm) thick.

Accepts wires or plugs up to 0.08in (2.16mm) dia. with insulation up to 0.16in (4.06mm).

Material: Body: tin plated brass; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 630 Vdc; For CE compliance: not intended for hand held use at voltages above 30 Vac/60 Vdc, 15A, +239°F (+115°C) max.

***Std. Colors:** -0 Black, -2 Red.

Replacement Hex Nuts




Model#	Qty.	Finish	Wrench Size	Nut Thickness	Thread
6549	500	Nickel	3/16in	0.65in (16.51mm)	4-40
6547	500	Nickel	1/4in	0.95in (24.13mm)	6-32
6440	500	Nickel	1/4in	0.95in (24.13mm)	8-32
6548	100	Gold	3/8in	0.95in (24.13mm)	10-32
6441	500	Nickel	3/8in	0.95in (24.13mm)	1/4-32
6389	100	Nickel	9/16in	0.95in (24.13mm)	1/2-28

Hex Nut Application Chart

Hex Nut	6549	6547	6440	6548	6441	6389
Fits on	3276	3263	2142	3770	5018	1581
	4513	4511	2143	4022	2269	6387
		6271	2382	4098		2854
		6387-TS6	2383	4243		3267
			2439	4512		4005
			2440	4543		4069
			3264	4773		4601
			3542	6272		4900
			3750	6387-TS8		5233
			3760			6270

Binding Post with Double Mounting



Model# 4243-*

Accepts standard banana plugs and 0.080in (2.03mm) pin tips, wires and probe tips in 0.10in (2.54mm) cross-hole.


One black and one red binding post.

Material: Binding Post: bright tin-plated brass; Insulation: polycarbonate.


Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +239°F (+115°C) max.

***Mtg. Base Colors:** -0 Black, -2 Red.

Dual Binding Posts



6883




6884

Model#	Base
6883	Standard
6884	Raised Base

5-way binding post with 3.91 mm (0.154 in) cross-hole that accepts up to 12 AWG wire and standard banana plugs. Posts are spaced at the standard 3/4 inch spacing to mate to dual banana plugs.


Material: Binding Post: nickel-plated brass. Insulators: nylon.

Rating: 30A current.



Panel Cut-Out for 6883/6884

Shorting Link for Standard Binding Posts



Model# 4115

Solid shorting link for binding posts.


Material: nickel-plated brass.

Rating: 15A.

Sold in pkgs. of 10.

Fits Binding Posts on 0.750in (19.05mm) centers.

Miniature Double Banana Plug with Set Screws, Stackable, Solderless



Model# 2244-*

Internal set screws secure cable up to 0.15in (3.81mm) dia. or components.


Plugs fit miniature 0.104in (2.64mm) dia. jacks.

Material: Banana Plug/Jack: brass; Spring: beryllium copper; Finish: gold plating; Insulation: ABS

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red.

Miniature Solderless Type Triple Banana Plug with Wire Guide




Model# 4653-0

Use for balanced line 2 conductor shielded cable assemblies.

Material: Banana Plug/Jack: brass; Spring: beryllium copper; Finish: gold plating; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

Cable strain relief I.D. 0.19in (4.82mm). Setscrews secure wires.

Miniature Solder Type Banana Plug



Model#	Insulator Length (X)
3690-*	0.45in (11.43mm)
4617-*	1.00in (25.14mm)

Sold in pkgs. of 10

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* gold plating; *Insulation:* nylon.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

Miniature Banana Plug with Threaded Stud


Fits miniature 0.104in (2.64mm) dia. banana jacks.


Furnished with 4-40 hex nut, 4-40 threaded stud.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* gold plating.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A.

Replacement hex nut available on page 36.

Sold unassembled, in pkgs. of 10.

Do-It-Yourself Miniature Banana Plug, Stackable, Solderless



Model# 2944-*

Fits miniature 0.104in (2.64mm) dia. banana jacks. Wire firmly held in place with internal set screw.

Material: *Banana Plug/Jack:* brass; *Spring:* beryllium copper; *Finish:* gold plating; *Insulation:* ABS.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Do-It-Yourself Miniature Banana Plug with Safety Shield, Stackable, Solderless


Model# 2945-*


Fits miniature 0.104in (2.64mm) dia. banana jacks.

Wire firmly held in place with internal set screw.

Material: *Banana Plug/Jack:* brass; *Spring:* beryllium copper; *Finish:* gold plating; *Insulation:* ABS.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Miniature Double Banana Plug with Shorting Bar


Model# 2035-*


Plugs fit miniature 0.104in (2.64mm) dia. banana jacks.

Banana plugs internally shorted with 18 AWG wire.

Material: *Banana Plug/Jack:* brass; *Spring:* beryllium copper; *Finish:* gold plating; *Insulation:* ABS.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Miniature Double Banana Plug Shorting Bar



Model# 3030

Center hole accepts 4-40 screw.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* gold plating.

Rating: 5A. Resistance less than 1.5 mΩ.

Fits Miniature Binding Posts and Miniature Banana Jacks on 0.5in (12.70mm) centers.

Miniature Rivet Type Banana Plug




Model#	Panel	X Dim.
3268	0.062in (1.57mm)	0.094in (2.39mm)
3271	0.093in (2.36mm)	0.125in (3.17mm)
3272	0.125in (3.17mm)	0.156in (3.96mm)
3273	0.062in (1.57mm)	0.105in (2.67mm)

Fits miniature 0.104in (2.64mm) dia. banana jacks.

Material: *Banana Plug Body:* brass; *Spring:* beryllium copper; *Finish:* gold plating.

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A.

Sold in pkgs. of 10.

Miniature Binding Post


Panel Cut-Out

Model#	Plating
2382-*	Gold
2439-*	Tin

Accepts miniature banana plug.

8-32 hex nut and lockwasher included.


Material: *Binding Post Body, Nut:* brass; *Lockwasher:* steel; *Insulation:* polycarbonate.

Rating: *Hands free testing* in controlled voltage environment: 1500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red, -3 Orange, -5 Green, -6 Blue, -9 White.

Replacement hex nuts available on page 36.

Miniature Insulated Binding Post with Double Mounting Base




Model#	Plating
2383-*	Gold
2440-*	Tin

Accepts miniature banana plugs.
8-32 hex nut and lockwasher included.
Material: Binding Post Body, Nut: brass; Lockwasher: steel; Insulation: polycarbonate.
Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (+115°C) max.

***Mounting Base Colors:** -0 Black, -2 Red.
***Std. Colors:** 2383: -0 Black, -2 Red. 2440: -0 Black.
Replacement hex nuts available on page 36.


Do-It-Yourself Pin Tip Plug with Safety Shield, Stackable, Solderless



Model# 3548-*


Accepts miniature banana plug.
Wire firmly held in place with internal set screw.
Material: Pin Tip Plug/Jack: gold-plated brass; Insulation: ABS.
Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.
***Std. Colors:** -0 Black, -2 Red.

Miniature Banana Jack, Panel Mount




Model# 2142-*

Accepts miniature banana plugs. Mounts in panels up to 0.250in (6.35mm) thick.
Material: gold-plated brass; Insulation: polycarbonate.
Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (+115°C) max.
***Std. Colors:** Available in 10 colors.
Uses hex nut 6440.
Replacement hex nuts available on page 36.
Sold unassembled, in pkgs. of 10 per color.




Miniature Banana Jack with Wire Wrap Terminal



Model# 4022-*

Accepts miniature banana plugs.
Mounts in panels up to 0.250in (6.35mm) thick.
Material: Jack: nickel-plated brass; Terminal: gold-plated phosphor bronze; Insulation: polycarbonate.
Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +239°F (+115°C) max.
***Std. Colors:** -0 Black, -2 Red.
Sold unassembled, in pkgs. of 10.


Miniature Rivet Type Banana Jack with Turret



Model# 3277


Accepts miniature banana plugs.
Mounts in panels up to 0.062in (1.57mm) thick.
Material: Gold-plated brass.
Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A.
Sold in pkgs. of 10.
Rec. Mounting Hole: .140 ± .002 (9/64 Drill).
Panel Thickness: 0.062in (1.57mm)

Miniature Banana Jack in Double Mounting Base, Panel Mount



Model# 2143-*

Accepts miniature banana plugs. Mounts in panels up to 0.188in (4.78mm) thick.
Material: gold-plated brass; Insulation: polycarbonate.
Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (+115°C) max.
***Std. Mounting Base Colors:** -0 Black, -2 Red.
Colors: One black and one red jack.


Double Pin Tip Plug with Shorting Bar

Model# 3452-*

Accepts pin tip plugs. Internally shorted with 20 AWG wire. Use as connecting link for 0.50in (12.70mm) spaced pin tip jacks.

Material: Pin Tip Plug/Jack: brass; Spring: beryllium copper; Finish: gold plating; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red.

Do-It-Yourself .080in (20.32mm) Dia. Pin Tip Plug with Flexible Boot, Solder or Crimp


Model#	Accepts Wire AWG
5173-*	22, 20, 18



Ideal for making patch cords or field repairs. Snap-on flexible PVC boot allows wire to be crimped or soldered to pin tip plug.

Material: nickel-plated brass.

Accepts 18-22 AWG wire.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: Available in 10 colors.

Pin Tip Jacks with Double Mounting Base


Panel Cut-Out

Model# 4543-*


Accepts 0.08in (2.03mm) dia. pin.

Max. panel thickness 0.188in (4.78mm).

Material: Jack: gold-plated brass; Spring: beryllium copper; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (115°C) max.

*Mtg. Base Colors: -0 Black, -2 Red.

Pin Tip Jack


Panel Cut-Out

Model# 3542-*


Accepts 0.080in (2.03mm) dia. pin.

Material: Jack: gold-plated brass; Spring: beryllium copper; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +239°F (115°C) max.

*Std. Colors: Available in 10 colors.

Sold in pkgs. of 10.

Insulated Pin Jack with Wire Wrap Terminal


Panel Cut-Out


Model# 4773-*

Accepts 0.080in (2.03mm) dia. pin. Max. panel thickness 0.25in (6.35mm).

Material: Jack: nickel-plated brass; Spring: gold-plated beryllium copper; Terminal: gold-plated phosphor bronze; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 1500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +239°F (+115°C) max.

*Std. Colors: -0 Black, -2 Red, -6 Blue, -9 White.


Double Banana Jack to Miniature Double Banana Plug

Model# 2952

Converts standard banana plugs to miniature.

Material: Jack: nickel-plated brass; Spring: nickel-plated beryllium copper; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

Color: Black.

Banana Jack to Miniature Banana Plug

Model# 2138-*


Use to mate standard 0.166in (4.22mm) dia. banana plug to equipment having miniature banana jacks.

Material: Jack: nickel-plated brass; Spring: nickel-plated beryllium copper; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Color: -0 Black, -2 Red.

Sold in pkgs. of 10.

Miniature Banana Jack to Banana Plug

Model# 2477-*

Converts miniature banana plugs to standard.

Material: Jack: nickel-plated brass; Spring: nickel-plated beryllium copper; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Color: -0 Black, -2 Red.

Sold in pkgs. of 10.

Pin Tip Jack to Banana Plug

Model# 1809-*


Accepts 0.080in (2.03mm) pin tip plug or probe tip. Fits standard 0.166in (4.22mm) dia. banana jack.

Material: gold-plated beryllium copper.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

***Std. Color:** -0 Black, -2 Red.

Sold in pkgs. of 10.



Banana Jack to Pin Tip Plug

Model# 1432-*


Use to mate standard banana plug patch cords to equipment having pin jacks.

Material: Jack/Plug: nickel-plated brass; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red.

Sold in pkgs. of 10.



Insulated Double Banana Plug Shorting Bar with Binding Post

Model# 5165-*


Fits standard banana jack.

Shorting bar is completely insulated in clear ABS thermoplastic.

Material: Binding Post/Banana Plug Body/Shorting Bar: nickel-plated brass; Spring: nickel-plated beryllium copper; Insulation: polycarbonate.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

***Binding Post Colors:** -0 Black, -2 Red.



Double Banana Plug with Binding Posts, Stackable, Solderless

Model# Plating

1286 Nickel


5405 Gold

Features insulated binding posts on 0.750in (19.05mm) centers for rapid mounting and interchangeability of components. Center cross hole 0.166in (4.22mm) dia. provides side stackup connection.

Material: Binding Post/Banana Plug Body: brass; Spring: beryllium copper; Insulation: ABS.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

Color: Black.



2 mm Banana Plug

Model# 5936-*

Solder type wire connection.

Accepts 18-22 AWG wire.

Rating: Hands free testing in controlled voltage environment: 500 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, ≤ 2 mΩ.

***Std. Colors:** -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue.

Assembled Length: 1.07in (27.2 mm).

Sold unassembled, in pkgs. of 10 per color.

Not compatible with Miniature Banana Plug or Pin Tip.



2 mm Banana Jack

Model# 5935-*

Max. Panel Thickness: 0.31in (8mm).


Material: Insulation: nylon; Finish: nickel plating.

Rating: Hands free testing in controlled voltage environment: 500 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, ≤ 2 mΩ.

***Std. Colors:** -0 Black.

Sold in pkgs. of 10 per color.

Not compatible with Miniature Banana Plug or Pin Tip.



Panel Cut-Out


Connector Test Adapters

Pin type

Socket type

2.75 - 3.18in (69.9 - 80.8mm)

2.49in (63.2mm)



Model#	Contact Size	Type	Current Rating
4690-*	22 0.030in (0.76mm)	Socket	3A
4691-*		Pin	
3560-*	20 0.040in (1.02mm)	Socket	3A
3561-*		Pin	
3562-*	16 0.063in (1.60mm)	Socket	3A
3563-*		Pin	
3564-*	12 0.093in (2.36mm)	Socket	3A
3565-*		Pin	

An ideal test adapter for rapid testing of the hard-to-get at contacts of multi-pin/socket connectors. Flexible tip allows testing of adjacent contacts. Flexibility and full insulation protects against shorting or contact damage. Model 4690 also fits 0.025in (0.63mm) sq. pins.

Material: Banana Jack: nickel-plated brass; Socket: gold-plated copper; Pin: gold-plated brass; Insulation: PVC.

Rating: Hands free testing in controlled voltage environment: 2500 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red.

Test Connector Adapter Set
Model# 6481

Full set of pin and socket adapters.
 18 piece set includes one black and red pin and socket of each size.
 Includes Silicone insulated 4ft (1.21m) leads to fit most DMMs from Fluke, Amprobe, Greenlee and others.


Banana Jack to .080in (2mm) Dia. Pin Tip Jack
Model# 3834-*

Adapts standard 0.166in (4.22mm) dia. banana plug to 0.080in (2.03mm) dia. pin tip plug.

Material: *Banana Jack:* nickel-plated brass; *Pin Jack:* gold-plated beryllium copper; *Insulation:* polypropylene.

Rating: *Hands free testing* in controlled voltage environment: 3000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

***Std Colors:** -0 Black.


Do-It-Yourself In-Line 4 mm (0.16in) Banana Plug
Model# 5934-*


Wire connection by set screw. Accepts 18, 20 and 22 AWG wire.

Material: *Insulation:* Nylon.

Rating: *Hands free testing* in controlled voltage environment: 750 V ac/dc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 25A.

***Std. Colors:** -0 Black, -2 Red.

Sold in pkgs. of 10 per color.



Binding Post to Banana Plug
Model# 2894-*

Features insulated binding post for rapid mounting and interchangeability of components. Accepts standard banana plug. Center cross hole 0.166in (4.22mm) dia. provides side stackup connection.

Material: *Binding Post/Banana Plug Body:* nickel-plated brass; *Spring:* nickel-plated beryllium copper; *Insulation:* ABS

Rating: *Hands free testing* in controlled voltage environment: 2500 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

***Binding Post Colors:** -0 Black, -2 Red.



Low Thermal EMF Insulated Spade Lug to Banana Jack
Model# 2305

Special alloy and plating preserve the accuracy of low voltage measurement equipment. Thermal effects are minimized. Heavy construction for minimum voltage loss. Mates with low voltage banana plug patch cords and binding posts.

Material: *Jack and Spade Lug:* gold-plated tellurium copper; *Insulation:* ABS.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

Set of one red and one black.



4 mm (0.16in) Binding Post
Model# 5932-*

Max. Panel Thickness: 0.12in (3.0mm) Crosshole 0.08in (2.0mm).

Rating: *Hands free testing* in controlled voltage environment: 750 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 25A, ≤ 2 mΩ.

***Std. Colors:** -0 Black, -2 Red.

Sold in pkgs. of 10 per color.


Spade Lug to DMM Banana Jack


Model#	A	B	Lug Size
3744A-*	0.14in (3.56mm)	0.24in (6.10mm)	4, 5, 6
3777A-*	0.2in (5.0mm)	0.30in (7.7mm)	8, 10

Plugs into DMM leads. Permits DMM leads to be used with equipment having barrier strips, or binding post.

Material: *Banana Jack:* nickel-plated brass; *Spade Lug:* tin-plated copper; *Insulation:* polypropylene.

Rating: *Hands free testing* in controlled voltage environment: 5000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red, -02 Set of one black and one red.




Patch Cords and Test Leads

Pomona has made it easy for you to have exactly what you need with a huge selection of patch cords and test leads designed for reliable, convenient connections. Whether you need a test lead that can access an IC pin without shorting or a patch cord that accommodates multiple stacking, Pomona Electronics' design and reliability are your connection with quality.


Wire Specifications

Wire Designation	AWG	Description	O.D.	Jacket	Temperature Range	Color
B	18	65/36 copper	0.144in (3.66mm)	PVC	-4 to 221°F (-20 to +105°C)	10 Colors
Silicone	18	65/36 copper	0.144in (3.66mm)	Silicone	-58 to 302°F (-50 to +150°C)	Black and Red
P	20	41/35 copper	0.087in (2.20mm)	PVC	-4 to 221°F (-20 to +105°C)	10 colors
PTO	22	26/36 copper	0.064in (1.62mm)	PVC	-4 to 221°F (-20 to +105°C)	10 colors
	12	7 x 38/36 copper	0.144in (3.66mm)	PVC	140°F (+60°C)	Black, Red, Green

How To Order



Multi-Stacking Banana Plug Patch Cord



Model#	Length
B-4-*	4in (0.1m)
B-8-*	8in (0.2m)
B-12-*	12in (0.3m)
B-18-*	18in (0.5m)
B-24-*	24in (0.6m)
B-36-*	36in (0.9m)
B-48-*	48in (1.2m)
B-60-*	60in (1.5m)
B-72-*	72in (1.8m)

Model B: Multi-Stacking Banana Plug Patch Cord features a nickel-plated finish.

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.


***Std. Colors:** Available in 10 Colors.

Model#	Length	Special Features
2948-12-*	12in (0.3m)	gold-plated finish
2948-24-*	24in (0.6m)	"
2948-36-*	36in (0.9m)	"
2948-48-*	48in (1.2m)	"
2948-60-*	60in (1.5m)	"

Model 2948 Multi-Stacking Banana Plug Patch Cord features a gold-plated finish.

***Std. Colors:** -0 Black, -2 Red.

Cross Stacking Banana Plug Patch Cord




Model#	Length
1440-12-*	12in (0.3m)
1440-18-*	18in (0.5m)
1440-24-*	24in (0.6m)
1440-36-*	36in (0.9m)
1440-48-*	48in (1.2m)
1440-60-*	60in (1.5m)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

Test Lead Holders

Model#	Color	"A" Max Cable Dia.	Number of Slots
1508	Orange	0.210in (5.33mm)	14
4408	Black	0.320in (8.13mm)	10
2708	Blue	0.450in (11.43mm)	9



Multi-stacking sheathed (4mm) Banana Plug Patch Cord



Model# 6727-*

4ft (1.2 meter) stackable safety lead.

Material: Contacts: nickel-plated brass; Wire: multi-strand copper, Insulation: silicone.

Rating: IEC1010 1000V Cat III, 20A max (10A cont.), 14 to 176°F (-10 to +80°C).

***Std. Colors:** -0 Black only, -2 Red only.

Horizontal Stacking Banana Plug Patch Cord




Model#	Length
HB-12-*	12in (0.3m)
HB-24-*	24in (0.6m)
HB-36-*	36in (0.9m)
HB-48-*	48in (1.2m)
HB-60-*	60in (1.5m)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug Coiled Patch Cord


Model#	Ext. Length
2484*	48in (1.23mm)

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.
Extended Length: 48in (1.2mm).
 One patch cord replaces many different lengths.
Rating: Hands free testing in controlled voltage environment: 270 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug Patch Cord with In-Line Fuse Holder



Model#	Length
4274-24-*	24in (0.6m)
4274-36-*	36in (0.9m)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.
Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C).
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug to Miniature Stacking Banana Plug


Model#	Length
3014-36-*	36in (0.9m)

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.
Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug to Stacking Pin Tip Plug



Model#	Length
1126-12-*	12in (0.3m)
1126-24-*	24in (0.6m)
1126-36-*	36in (0.9m)
1126-48-*	48in (1.2m)
1126-60-*	60in (1.5m)

20 AWG Wire, 0.087in (2.21mm) O.D.
Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.
***Std. Colors:** -0 Black, -2 Red.

Right Angle Stacking BananaPlug Patch Cord



Model#	Length
2864-24-*	24in (0.6m)

Cable: 18 AWG Wire, 0.14in (3.56mm) O.D.
Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug to Minigrabber® Test Clip


Model#	Length
3782-12-*	12in (0.3m)
3782-24-*	24in (0.6m)
3782-36-*	36in (0.9m)
3782-48-*	48in (1.2m)
3782-60-*	60in (1.5m)

Hook attaches to component leads up to 0.060in (1.52mm) O.D.
Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.
Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.
***Std. Colors:** Available in 10 colors.

Multi-Stacking Banana Plug to Minigrabber® Test Clip


Model#	Length
6249-12-*	12in (0.3m)
6249-24-*	24in (0.6m)
6249-36-*	36in (0.9m)

Features a slim 0.36in (9.14mm) body width. Hook attaches to component leads up to 0.060in (1.52mm) O.D.
Cable: 18 AWG Silicone insulated wire, 0.144in (3.56mm) O.D.
Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A.
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug to Minigrabber® Test Clip (Coiled) Patch Cord


Model#	Ext. Length
4538-*	48in (1.2m)

Hook attaches to components up to 0.060in (1.52mm) O.D.
Cable: 20 AWG Retractable Cord, 0.087in (2.21mm) O.D.
Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C).
***Std. Colors:** -0 Black, -2 Red.

Multi-Stacking Banana Plug to Micrograbber® Test Clip



Model#	Length
5053-12-*	12in (0.3m)
5053-24-*	24in (0.6m)
5053-36-*	36in (0.9m)
5053-48-*	48in (1.2m)


Hook attaches to components up to 0.040in (1.02mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 150V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Multi-Stacking Banana Plug to Maxigrabber® Test Clip



Model#	Length
4996-36-*	36in (0.9m)
4996-48-*	48in (1.2m)
4996-60-*	60in (1.5m)


Hook attaches to components up to 0.060in (1.52mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Multi-Stacking Banana Plug to MiniPincer® Test Clip



Model#	Length
5421-24-*	24in (0.6m)
5421-36-*	36in (0.9m)

Pincer Opening: 0.090in (2.29mm).

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Minigrabber® Test Clip with Sheathed Banana Jack



Model#	Plug Type	Ratings
6248-12-*	Sheathed Banana Jack	IEC1010 2-031 CAT II 300V

Test Lead Extender.

Silicone insulated 1ft (0.3m) leads fit on the end of modular test leads such as Pomona 5907A.

Std. Colors: -0 Black, -2 Red.

Multi-Stacking Banana Plug to SMD Grabber® Test Clip



Model#	Length
5302-12-*	12in (0.3m)
5302-24-*	24in (0.6m)
5302-36-*	36in (0.9m)


Pincer Opening: 0.040in (1.02mm).

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: Hands free testing in controlled voltage environment: 150V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 0.5A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Double Banana Plug with Safety Shrouds



Model#	Length
6283-C-36	36in (0.9m)
6283-C-48	48in (1.2m)
6283-C-60	60in (1.5m)

Fits Digital Multi-meters and other instruments with shrouded jacks.

Offset design designates hot and ground leads.

Black and red banana plug shrouds.

Molded strain relief for long life.

MIL spec coaxial cable.

Overvoltage CAT II, 600V, 5A per IEC1010-2-031.

Minigrabber® Test Clip Leads



6244



5428/6231



6245

Model#	Plug Type	Ratings
6244-48-*	Right-angle DMM	CAT II 300V
5428-48-*	Right-angle DMM	300 Vrms*
6231	Right-angle DMM	300 Vrms*
6245-48-*	Straight DMM	CAT II 300V

Silicone insulated 4ft (122m) leads fit most meters from Fluke, Wavetek (Meterman), HP, Amprobe, Greenlee and others

Std. Colors: -0 Black, -2 Red


*Hands free testing in controlled voltage environments: 300 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vac.

Multi-Stacking Double Banana Plugs on Retractable (Coiled) Cord

Model#	Extended Length
3864-48	48in (1.2m)
3864-72	72in (1.8m)

Rating: Hands free testing in controlled voltage environment: 90 Vac/270 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

Cable Type: Shielded Microphone Cable.


Multi-Stacking Double Banana Plug, One End Only

Model#	Length
1326-A-60	60in (1.5m)
1326-C-60	60in (1.5m)


Rating: Hands free testing in controlled voltage environment: A: 300 Vrms, C: 1400 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +131°F (+55°C) max. See chart on page 9 for additional cable specifications.


Multi-Stacking Double to Multi-Stacking Single Banana Plugs

Model#	Length
1368-A-18	18in (0.5m)
1368-A-24	24in (0.6m)
1368-A-30	30in (0.76m)
1368-A-36	36in (0.9m)
1368-A-48	48in (1.2m)
1368-A-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.


See chart on page 9 for additional cable specifications.


Double Banana Plug to Stacking Pin Tip Plugs

Model#	Length
28C-PP-36	36in (0.9m)
28C-PP-48	48in (1.2m)
28C-PP-60	60in (1.5m)

Cable Type: RG58C/U 0.195in (4.95mm) O.D.


Rating: Hands free testing in controlled voltage environment: 1400 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.


Two Conductor shielded Balanced Line

Model#	Length
1167-18	18in (0.5m)
1167-24	24in (0.6m)
1167-30	30in (0.76m)
1167-36	36in (0.9m)
1167-48	48in (1.2m)
1167-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 1000 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +131°F (+55°C) max.

Cable Type I: See chart on page 9 for additional cable specifications.


Multi-Stacking Banana Plugs, Two Each End

Model#	Length
2239-C-24	24in (0.6m)
2239-C-36	36in (0.9m)
2239-C-48	48in (1.2m)


Rating: Hands free testing in controlled voltage environment: 1400 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +131°F (+55°C) Max.

See chart on page 9 for additional cable specifications.


Multi-Stacking Double Banana Plug Cables

Model#	Cable Type	Length
2BA-18	Two Conductor Twisted Pair, 18 AWG, 0.25in (6.35mm) O.D.	18in (0.5m)
2BA-24		24in (0.6m)
2BA-36		36in (0.9m)
2BA-48		48in (1.2m)
2BA-60		60in (1.5m)
2BC-24	RG58C/U, 0.195in (4.95mm) O.D.	24in (0.6m)
2BC-36		36in (0.9m)
2BC-48		48in (1.2m)
2BC-60		60in (1.5m)


Rating: Hands free testing in controlled voltage environment: 2BA: 300 Vrms, 2BC: 1400 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +131°F (+50°C) max.


Multi-Stacking Double Banana Plug to Minigrabber® Test Clips


Model#	Length
3786-C-18	18in (0.5m)
3786-C-24	24in (0.6m)
3786-C-36	36in (0.9m)
3786-C-48	48in (1.2m)
3786-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

See chart on page 9 for additional cable specifications.



Double Banana Plug to Micrograbber® Test Clips




Model#	Length
4768-K-24	24in (0.6m)
4768-K-36	36in (0.9m)
4768-K-48	48in (1.2m)
4768-K-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 150 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

See chart on page 9 for additional cable specifications.

Miniature Double Banana Plug Cable



Model#	Length
2247-K-24	24in (0.6m)

Rating: Hands free testing in controlled voltage environment: 1000 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +131°F (+55°C) max.

Cable Type: RG174/U, 0.100in (2.54mm) O.D.

Double Banana Plug to Alligator Test Clips



Model#	Length
2BA-AL-36	36in (0.9m)
2BA-AL-48	48in (1.2m)
2BA-AL-60	60in (1.5m)

Cable Type: Two cond. Twisted Pair.


Model#	Length
2BC-AL-60	60in (1.5m)

Cable Type: RG58C/U50.Ω

Rating: Hands free testing in controlled voltage environment: 150 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

Jaw Opening: 0.30in (7.62mm) max.

Multi-Stacking Double Banana Plug to Minipincer® Test Clips




Model#	Length
5422-C-60	60in (1.5m)

Rating: Hands free testing in controlled voltage environment: 300 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

See chart on page 9 for additional cable specifications.

Double Banana Plug to Minigator Test Clips



Model#	Length
2BC-MG-36	36in (0.9m)

Cable Type: RG58C/U.

Rating: Hands free testing in controlled voltage environment: 45 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.

Jaw Opening: 0.187in (4.75mm) max.

Minigator Clips to Miniature Double Banana Plug



Model#	Length
3027-K-24	24in (0.6m)

Rating: Hands free testing in controlled voltage environment: 45 Vrms; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, +122°F (+50°C) max.


Jaw Opening: 0.187in (4.75mm)

See chart on page 9 for additional cable specifications.

Low Thermal EMF Patch Cords

Special alloy plating and construction preserve the accuracy of microvolt and nanovolt measurement equipment. Designed to greatly minimize the effect of Thermal Electric Voltage (Thermal EMF). Thermal EMF is generated at the junction of dissimilar metals at different temperatures and is common source of error in micro- and nano- volt measurements.

Shielded Low Thermal EMF Spade Lug Patch Cord




Model#	Length
1756-24	24in (0.6m)
1756-48	48in (1.2m)

Cable: 12 AWG Wire, Shield Leads: 18 AWG.

Material: *Spade Lug:* gold-plated Electrolytic Tough Pitch (ETP) 110 Copper Alloy, 1/2 hard.

Rating: *Hands free testing* in controlled voltage environment: 2000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 20A, 131°F (+55°C) max.

Low Thermal EMF Spade Lug Patch Cord



Model#	Length
1693-36*	36in (0.9m)
1693-60*	60in (1.5m)


Cable: 12 AWG Wire, 0.144in (3.56mm) O.D.

Material: *Spade Lug:* gold-plated Electrolytic Tough Pitch (ETP) 110 Copper Alloy, 1/2 hard.

Rating: *Hands free testing* in controlled voltage environment: 2000 Vdc; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 20A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

Low Thermal EMF Retractable Sheath Banana Plug Patch Cord



Model#	Length
5291A-12*	12in (0.3m)
5291A-36*	36in (0.9m)
5291A-60*	60in (1.5m)

Cable: 12 AWG Wire, 0.144in (3.56mm) O.D.

Material: *Plug Body:* gold-plated tellurium copper; *Spring:* gold-plated Beryllium Copper.

Rating: 1000V per IEC1010-2-031, 7A, +131°F (+55°C).

***Std. Colors:** -0 Black, -2 Red.

Low Thermal EMF Retractable Sheath Banana Plug to Spade Lug



Model#	Length
5295-36*	36in (0.9m)

Cable: 12 AWG Wire, 0.144in (3.56mm) O.D.

Material: *Spade Lug:* gold-plated Electrolytic Tough Pitch (ETP) 110 Copper Alloy, 1/2 hard; *Plug End:* gold-plated tellurium copper.

Rating: *Hands free testing* in controlled voltage environment: 1000V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 7A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

Minigrabber® Test Clip Patch Cord



Model#	Length
3781-8*	8in (0.2m)
3781-12*	12in (0.3m)
3781-18*	18in (0.5m)
3781-24*	24in (0.6m)
3781-36*	36in (0.9m)
3781-48*	48in (1.2m)
3781-60*	60in (1.5m)

Hook attaches to component leads up to 0.060in (1.52mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 300V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +216°F (+102°C) max.

***Std. Colors:** Available in 10 colors.

Minigrabber® Test Clip Patch Cord Kit

Model# 5523

Kit contains 10 pcs. of Model 3781-24, one of each color.

One End Only

Model#	Length
3780-60*	60in (1.5m)

***Std. Colors:** -0 Black, -2 Red.

Minigrabber® Test Clip Patch Cord



Model#	Length
6246-12*	12in (0.3m)
6246-24*	24in (0.6m)
6246-36*	36in (0.9m)

Features a slim 0.36in (9.14mm) body width. Hook attaches to component leads up to 0.060in (1.52mm) O.D.

Cable: 18 AWG silicone insulated wire, 0.144in (3.56mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 300V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A per IEC1010-2-031 CAT II

***Std. Colors:** -0 Black, -2 Red.

Minigrabber® Test Clip (Coiled) Patch Cord



Model# 4537*

Cable: 20 AWG Retractable Cord, 0.087in (2.21mm) O.D. Extended Length: 48in (1.22mm).


Rating: *Hands free testing* in controlled voltage environment: 300V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, 140°F (+60°C) max.

***Std. Colors:** -0 Black, -2 Red.

One End Only

Model# 4536*

Minipincer® Test Clip Patch Cord



Model#	Length
5419-12-*	12in (0.3m)
5419-24-*	24in (0.6m)

Pincer Opening: 0.090in (2.29mm).

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 300V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

SMD Grabber® Test Clip Patch Cord

1.71in (43.43mm)



Model#	Length
5301-6-*	6in (0.15m)
5301-12-*	12in (0.3m)
5301-24-*	24in (0.6m)
5301-36-*	36in (0.9m)

Pincer Opening: 0.04in (1.63mm).

Cable: 22 AWG Wire, 0.064in (1.60mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 150V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 0.5A, +216°F (+102°C) max.


*Std. Colors: -0 Black, -2 Red.

SMD Grabber® Test Clip Patch Cord Kit

Model# 5521

Kit contains 10 pcs. of Model 5301-24, one each of ten colors.

MicroGrabber® Test Clip Patch Cord



Model#	Length
4613-12-*	12in (0.3m)
4613-24-*	24in (0.6m)
4613-36-*	36in (0.9m)
4613-48-*	48in (1.2m)

Hook attaches to components up to 0.040in (1.02mm) O.D.

20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 150V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +216°F (+102°C) max.


*Std. Colors: -0 Black, -2 Red.

MicroGrabber® Test Clip Patch Cord Kit

Model# 5525

Kit contains 10 pcs. of Model 4613-24, one each of ten colors.

Ultra-Thin MicroGrabber® Test Clip Patch Cord



Model#	Length
6091-10-*	10in (0.25m)
6091-20-*	20in (0.51m)

Designed especially for today's fine pitched SMD's. Clips have a narrow body 0.120in (3.05mm) wide, and a small flexible shaft 0.050in (12.70mm) dia. x 0.910in (23.11mm) long.

Pincer Opening: 0.024in (0.61mm).

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/60 Vdc, 1A, <15mΩ, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

One End Only

Model#	Length
6090-40-*	40in (1.02m)

Same as 6091 with one end only.

Rating: *Hands free testing* in controlled voltage environment: 45 Vac; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 2A, <15mΩ, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

Minigrabber® Test Clip to Minigator Test Clip



Model#	Length
4652-12-*	12in (0.3m)
4652-24-*	24in (0.6m)

Hook attaches to component leads up to 0.060in (1.52mm) O.D.

Jaw Opening: 0.187in (4.75mm).

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: *Hands free testing* in controlled voltage environment: 45V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Multi-Stacking Banana Plug to Alligator Test Clip



Model#	Length
1166-8-*	8in (0.2m)
1166-12-*	12in (0.3m)
1166-24-*	24in (0.6m)
1166-36-*	36in (0.9m)
1166-48-*	48in (1.2m)
1166-60-*	60in (1.5m)

Jaw Opening: 0.300in (7.62mm).

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.


Rating: *Hands free testing* in controlled voltage environment: 150V; *For CE compliance:* not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

Banana Plug to Alligator Clip Patch Cord Kit

Model#	Length
6357-36	36in (0.9m)

Kit contains 10 pcs. of Model 1166 patch cords, one each of 10 colors.

**Minigator Test Clip
Patch Cord**


Model#	Length
MG-B-4-*	4in (0.1m)
MG-B-8-*	8in (0.2m)
MG-B-12-*	12in (0.3m)
MG-B-24-*	24in (0.6m)
MG-B-36-*	36in (0.9m)
MG-B-48-*	48in (1.2m)

Jaw Opening: 0.187in (4.75mm).

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 45V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/45 Vdc, 5A, +122°F (+50°C) max.


*Std. Colors: -0 Black, -2 Red.

Model#	Length
1236-24-*	24in (0.6m)

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 45V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/45 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

**1000V Alligator
Patch Cord**


Model#	Length
6576-24-*	24in (0.6m)
6576-36-*	36in (0.9m)
6576-48-*	48in (1.2m)


Jaw Opening: 0.300in (7.62mm).

Material: Body: nickel-plated steel; Boot: santoprene rubber.

Cable: 18 AWG Wire, silicone insulated.

Rating: Hands free testing in controlled voltage environment: 1000V, 10A, -13 to 176°F (-25°C to 80°C).

*Std. Colors: -0 Black, -2 Red.

**Alligator Test Clip
Patch Cord**


Model#	Length
AL-B-4-*	4in (0.1m)
AL-B-8-*	8in (0.2m)
AL-B-12-*	12in (0.3m)
AL-B-18-*	18in (0.5m)
AL-B-24-*	24in (0.6m)
AL-B-36-*	36in (0.9m)
AL-B-48-*	48in (1.2m)
AL-B-60-*	60in (1.5m)

Jaw Opening: 0.300in (7.62mm).

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 150V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

**Alligator Test
Clip Patch Cord Kit**

Model#	Length
6356-12	12in (0.3m)
6356-24	24in (0.6m)
6356-36	36in (0.9m)
6356-60	60in (1.5m)

Kit contains 10pcs. of Model AL-B patch cords, one each of 10 colors.

**Multi-Stacking Banana
Plug to Minigator Test
Clip**


Model#	Length
3220-8-*	8in (0.2m)
3220-12-*	12in (0.3m)
3220-24-*	24in (0.6m)
3220-36-*	36in (0.9m)
3220-48-*	48in (1.2m)
3220-60-*	60in (1.52mm)

Jaw Opening: 0.187in (4.75mm).

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 45V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/45 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.


**5 Way Alligator to
Sheathed Right
Angle Set**


Model#	Length
6483-48-02	48in (1.2mm)

Clip includes bed of nails and single needle tip for easy, versatile piercing of wire insulation to contact inner conductor for measurement.

Pierces 19 to 26 AWG wire.

Std. Colors: Set of one black and one red.


**Retractable Sheath
Banana Plug Patch
Cord**


Model#	Length
4911A-12-*	12in (0.3m)
4911A-18-*	18in (0.5m)
4911A-24-*	24in (0.6m)
4911A-36-*	36in (0.9m)
4911A-48-*	48in (1.2m)
4911A-60-*	60in (1.5mm)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: 1000V per IEC1010-2-031, 10A, +176°F (+80°C) max.

*Std. Colors: -0 Black, -2 Red.

**Extra Large Alligator
Test Clip to Sheathed
Banana Plug
Patch Cord**


Model#	Length
6570-36-*	36in (0.9m)

Alligator length: 3.6in (91.44mm).

Jaw Opening: 0.8in (20.32mm).


Rating: Conforms to IEC1010-2-031, Overvoltage.

Category III, 1000V, 10A.

Cable: High flex 18 AWG Silicone wire.

*Std. Colors: -0 Black, -2 Red.

Retractable Sheath Stacking Banana Plug Patch Cord



Model#	Length
5403-12-*	12in (0.3m)
5403-24-*	24in (0.6m)
5403-36-*	36in (0.9m)
5403-48-*	48in (1.2m)
5403-60-*	60in (1.5m)


This retractable sheath banana plug has a stacking feature allowing the insertion of standard or other retractable plugs.

Cable: 18 AWG wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 1200 V ac/dc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 7A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Minigrabber® Test Clip to Retractable Sheath Banana Plug Patch Cord



Model#	Length
5270-36-*	36in (0.9m)

Hook attaches to component leads up to 0.060in (1.52mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.

Minigrabber® Test Clip to Straight Banana Plug Patch Cord



Model#	Length
4650-24-*	24in (0.6m)
4650-36-*	36in (0.9m)


Hook attaches to component leads up to 0.060in (1.52mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

0.025in (0.64mm) Square Pin Jack to Straight Banana Plug




Model#	Length
4771-24-*	24in (0.6m)
4771-36-*	36in (0.9m)
4771-48-*	48in (1.2m)

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: Hands free testing in controlled voltage environment: 45 Vac/60 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/60 Vdc, 3A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

0.025in (0.64mm) Square Pin Jack Patch Cord



Model#	Length
4741-6	6in (0.15m)
4741-12	12in (0.3m)
4741-24	24in (0.6m)

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.


Rating: Hands free testing in controlled voltage environment: 45 Vac/60 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/60 Vdc, 3A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

0.025in (0.64mm) Square Pin Jack Patch Cord Kit

Model# 5948
Kit contains 10 pcs. of Model 4741-6, one ea. of 10 colors.

0.025in (0.64mm) Square Pin Jack to 0.080in (2.03mm) Pin Tip Plug




Model#	Length
4772-24-*	24in (0.6m)

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: Hands free testing in controlled voltage environment: 45 Vac/60 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/60 Vdc, 3A, +122°F (+50°C) max.

*Std. Colors: -0 Black, -2 Red.

0.080in (2.0mm) Dia. Pin Tip Plug Patch Cord





Model#	Length
PT080-4-*	4in (0.1m)
PT080-8-*	8in (0.2m)
PT080-12-*	12in (0.3m)
PT080-18-*	18in (0.5m)
PT080-24-*	24in (0.6m)
PT080-36-*	36in (0.9m)
PT080-48-*	48in (1.17m)
PT080-60-*	60in (1.52m)

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: Hands free testing in controlled voltage environment: 1000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 3A, +131°F (+55°C) max.

*Std. Colors: -0 Black, -2 Red.



**0.025in (0.64mm)
Square Pin Jack Pin to
SMD Grabber® Test Clip**


Model#	Length
5412-12-*	12in (0.3m)
5412-24-*	24in (0.6m)
5412-36-*	36in (0.9m)

Pincer Opening: 0.04in (1.02mm).

Cable: 22 AWG Wire, 0.064in (1.63mm) O.D.

Rating: Hands free testing in controlled voltage environment: 150V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 0.5A, +122°F (+50°C).

***Std. Colors:** -0 Black, -2 Red.

**0.025in (0.64mm)
Square Pin Jack Pin
to SMD Grabber® Kit**

Model# 5924

Kit contains 10 pcs. of Model 5412-12, one ea. of 10 colors.

**Stacking Pin Tip Plug
Patch Cord**


Model#	Length
P-4-*	4in (0.1m)
P-8-*	8in (0.2m)
P-12-*	12in (0.3m)
P-18-*	18in (0.5m)
P-24-*	24in (0.6m)
P-36-*	36in (0.9m)
P-48-*	48in (1.2m)
P-60-*	60in (1.5m)

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

**Miniature Banana Plug
Patch Cord**


Model#	Length
2842-12-*	12in (0.3m)
2842-36-*	36in (0.9m)

Cable: 20 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

**Banana Plug to
Banana Jack**


Model#	Length
4702-12-*	12in (0.3m)
4702-24-*	24in (0.6m)
4702-36-*	36in (0.9m)
4702-48-*	48in (1.2m)
4702-60-*	60in (1.52m)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 5000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 15A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

**Minigrabber® Test Clip
to Miniature Stacking
Banana Plug**



Model#	Length
3784-24-*	24in (0.6m)
3784-36-*	36in (0.9m)

Hook attaches to component leads up to 0.06in (1.52mm) O.D.

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 300V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.


**Miniature Stacking
Banana Plug Patch Cord**


Model#	Length
1081-4-*	4in (0.1m)
1081-8-*	8in (0.2m)
1081-12-*	12in (0.3m)
1081-18-*	18in (0.5m)
1081-24-*	24in (0.6m)
1081-36-*	36in (0.9m)
1081-48-*	48in (1.2m)
1081-60-*	60in (1.5m)

Cable: 20 AWG Wire, 0.087in (2.21mm) O.D.

Rating: Hands free testing in controlled voltage environment: 3000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.


**Retractable Sheath
Banana Plug to
Banana Jack**


Model#	Length
5259-36-*	36in (0.9m)

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 1000 Vdc; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 7A, +131°F (+55°C) max.

***Std. Colors:** -0 Black, -2 Red.

**Alligator Test Clip to
Insulated Spade Lug**


Model#	Length
1960-36-*	36in (0.9m)

Jaw Opening: 0.30in (7.62mm).

Cable: 18 AWG Wire, 0.144in (3.56mm) O.D.

Rating: Hands free testing in controlled voltage environment: 150V; For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc, 5A, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red.



Boxes and Enclosures

Pomona – the place to make your connections. From setting up system electronics to circuitry prototyping to creating permanent junctions, Pomona provides you with the boxes and enclosures to securely seal signal sensitive cables and wires. The large variety of die-cast aluminum connectorized enclosures and phenolic or molded thermoplastic boxes are ready to house components in styles and sizes that will simplify your interconnections.

Miniature Size Die Cast Aluminum Box with Cover

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
3754	None	–	–	–	–
3753	BBE	–	–	–	–
3751	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)
3752	BBE	BNC (F)	0.72in (18.29mm)	BNC (M)	0.85in (21.59mm)
4507	BBE	BNC (F) x 2	0.53in (13.36mm)	BNC (M)	0.85in (21.59mm)
4742	Replacement cover				
4864	Cover screws, 100/pkg				
2352	Connector screws with solder turret				



BBE = Blue Baked Enamel Cover and screws included with all boxes.



“A” Size Die Cast Aluminum Box with Cover

Model#	Finish	Connector: A		Connector: B		Connector: C	
		Type	Length	Type	Length	Type	Length
2400	None	–	–	–	–	–	–
2397	BBE	–	–	–	–	–	–
2390	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	–	–
2391	BBE	BNC (M)	0.85in (21.59mm)	BNC (F)	0.72in (18.29mm)	–	–
2392	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)
2401	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	BNC (M)	0.85in (21.59mm)
2393	BBE	BNC (F)	0.72in (18.29mm)	BNC (M)	0.85in (21.59mm)	PDB	0.82in (20.83mm)
2398	BBE	SMA (F)	0.38in (9.69mm)	SMA (M)	0.38in (9.69mm)	–	–
2399	BBE	SMA (F)	0.38in (9.69mm)	SMA (F)	0.38in (9.69mm)	–	–
4245	Replacement cover						
3728	Flange mounting cover						
4864	Cover screws, 100/pkg						
2352	Connector screws with solder turret						

BBE = Blue Baked Enamel PDB = Post, Double Binding Cover and screws included with all boxes.



“B” Size Die Cast Aluminum Box with Cover


2417/2428



3230



3231



3239




2411



3232



2420




3234

Model#	Finish	Connector: A		Connector: B		Connector: C		Connector: D	
		Type	Length	Type	Length	Type	Length	Type	Length
2428	None	—	—	—	—	—	—	—	—
2417	BBE	—	—	—	—	—	—	—	—
3230	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	—	—	—	—
3231	BBE	BNC (F)	0.72in (18.29mm)	BNC (M)	0.85in (21.59mm)	—	—	—	—
2411	BBE	N (M)	0.81in (20.57mm)	N (F)	0.75in (19.05mm)	—	—	—	—
3239	BBE	IBNC	0.47in (11.94mm)	IBNC	0.47in (11.94mm)	—	—	—	—
2420	BBE	BNC (F)	0.72in (18.29mm)	N (M)	0.75in (19.05mm)	—	—	—	—
3232	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	—	—
3234	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)
4246	Replacement cover								
3719	Flange mounting cover								
4864	Cover screws, 100/pkg								
2352	Connector screws with solder turret								

BBE = Blue Baked Enamel

IBNC = Isolated BNC

Cover and screws included with all boxes.


“C” Size Die Cast Aluminum Box with Cover


2901 / 2906




2902

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
2906	None	—	—	—	—
2901	BBE	—	—	—	—
2902	BBE	BNC (F)	0.72 (18.29mm)	BNC (F)	0.72 (18.29mm)
4248	Replacement cover				
2352	Connector screws with solder turret				

BBE = Blue Baked Enamel

Cover and screws included with all boxes.



"D" Size Die Cast Aluminum Box with Cover



3602




3603



3601/3606

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
3606	None	—	—	—	—
3601	BBE	—	—	—	—
3602	BBE	BNC (F)	0.72 (18.29mm)	BNC (F)	0.72 (18.29mm)
3603	BBE	BNC (F)	0.72 (18.29mm)	BNC (M)	0.85 (21.59mm)
4726	Replacement cover				
3958	Flange mounting cover				
2352	Connector screws with solder turret				

BBE = Blue Baked Enamel Cover and screws included with all boxes.




"E" Size Die Cast Aluminum Box with Cover

Model#	Finish
5186	None
4226	Blue Baked Enamel
4416	Replacement cover
6268	Cover screws, 100/pkg


Cover and screws included.

Recommended Circuit Board Sizes:

8.00in x 1.49in x .062in,
(203.2mm x 37.85 x 1.57mm) Thick.
3.90in x 1.49in x .062in,
(99.06mm x 37.85 x 1.57mm) Thick.
7.60in x 3.40in x .062in,
(193.04mm x 86.36mm x 1.57mm) Thick.




4226



"F" Size Extruded Aluminum Box with Covers




3301/3306



3302

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
3306	None	—	—	—	—
3301	BBE	—	—	—	—
3302	BBE	BNC (F)	0.72in (18.29mm)	BNC (F)	0.72in (18.29mm)
4247	Replacement cover				
3328	Flange mounting cover				
4862	Cover screws, 100/pkg				
2352	Connector screws with solder turret				


BBE = Blue Baked Enamel Cover and screws included with all boxes.



Recommended Circuit Board Sizes:

3.90in x 1.48in x 0.062in,
(99.06mm x 37.59 x 1.57mm) Thick. 2.40in x 1.48in x 0.062in,
(60.96mm x 37.59mm x 1.57mm) Thick.

“G” Size Extruded Aluminum Box with Cover



3316


Model#	Finish
3316	None
3311	Blue Baked Enamel
4247	Replacement cover
3328	Flange mounting cover
4862	Cover screws, 100/pkg

Cover and screws included.


Recommended Circuit Board Sizes:

3.90in x 2.98in x .062in,
(99.06mm x 75.69mm x 1.57mm) Thick.

2.40in x 2.98in x .062in,
(60.96mm x 75.69mm x 1.57mm) Thick.



“H” Size Extruded Aluminum Box with Cover



3742


Model#	Finish
3743	None
3742	Blue Baked Enamel
4247	Replacement cover
3328	Flange mounting cover
4862	Cover screws, 100/pkg

Cover and screws included.

Recommended Circuit Board Sizes:

3.90in x 5.98in x .062in,
(99.06mm x 75.69mm x 1.57mm) Thick.


2.40in x 5.98in x 0.062in,
(60.96mm x 75.69mm x 1.57mm) Thick.



“J” Size Die Cast Aluminum Box with Cover




4655/5255



4656

		Connector: A		Connector: B to E	
Model#	Finish	Type	Length	Type	Length
5255	None	—	—	—	—
4655	BBE	—	—	—	—
4656	BBE	BNC (F)	0.72 (18.29mm)	BNC (F)	0.72 (18.29mm)
4658	Replacement cover				
4864	Cover screws, 100/pkg				

BBE = Blue Baked Enamel Cover and screws included with all boxes.



Recommended Circuit Board Sizes:

4.13in x 0.87in x 0.062in,
(104.9mm x 22.10mm x 1.57mm) Thick

1.38in x 0.87in x .062in
(35.05mm x 22.10mm x 1.57mm) Thick

"L" Size Die Cast Aluminum Box with Cover




4903

Model#	Finish
5203	None
4903	Blue Baked Enamel
5198	Replacement cover
4864	Cover screws, 100/pkg

Cover and screws included.

Recommended Circuit Board Sizes:

5.88in x 1.48in x .062in,
(149.35mm x 37.59mm x 1.57mm) Thick
2.88in x 1.48in x .062in,
(73.15mm x 37.59mm x 1.57mm) Thick




Black Phenolic Box with Cover



2105



2259



2098




2096

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
2105	EGP	—	—	—	—
2259	EGP	PDB	0.80in (20.32mm)	DBP	0.70in (17.78mm)
2098	EGP	DBJ	—	DBP	0.70in (17.78mm)
2096	EGP	—	—	DBP	0.70in (17.78mm)

EGP = Electrical Grade Phenolic
PDB = Post, Double Binding

DBJ = Double Banana Jack
DBP = Double Banana Plug

Cover and screws included
with all boxes.



Black Phenolic Box with Cover



2103




2099

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
2103	EGP	—	—	—	—
2099	EGP	BNC (M)	0.85 (21.59mm)	BNC (F)	0.72 (18.29mm)

EGP = Electrical Grade Phenolic
DBJ = Double Banana Jack

DBP = Double Banana Plug

Cover and screws included
with all boxes.



Black Phenolic Box with Cover


2224




2104

Model#	Finish	Connector: A		Connector: B	
		Type	Length	Type	Length
2104	EGP	—	—	—	—
2224	EGP	DBJ	—	DBP	0.70 (17.78mm)

EGP = Electrical Grade Phenolic
 DBJ = Double Banana Jack

DBP = Double Banana Plug

Cover and screws included
 with all boxes.


Molded Thermoplastic Box with Card Guides and Cover



3850-0

Model#	Finish
3850-0	Black - Thermoplastic
3850-6	Blue - Thermoplastic
3850-9	White - Thermoplastic
4864	Cover screws, 100/pkg

Cover and screws included.

Recommended Circuit Board Sizes:

2.51in x 1.60in x .062in,
 (63.35mm x 40.64mm x 1.57mm) Thick


Molded Thermoplastic Box with Card Guides and Cover



4384-0

Model#	Finish
4384-0	Black - Thermoplastic
4384-6	Blue - Thermoplastic
4864	Cover screws, 100/pkg

Cover and screws included.

Recommended Circuit Board Sizes:

3.93in x 1.58in x 0.062in
 (99.82mm x 40.13mm x 1.57mm) Thick
 3.90in x 2.98in x 0.062in,
 (99.06mm x 75.69mm x 1.57mm) Thick



DMM Accessories and Kits

Connecting with the industry's leading digital multimeter brands, Pomona provides the world's largest selection of test leads and probes.

Superior materials and outstanding design, assure conformity with industry-leading reliability and performance standards.

From high-density IC leads to voltage on a distribution panel, Pomona connects you with the right solution.

Deluxe Multi-Use DMM Maxi-Kit

Model# 5677B



1. Silicone insulated 4ft (1.2m) leads with right angle plug.
2. Modular probe set with replaceable tips.
3. 5 sets of replacement tips.
4. Retractable tip test probe set.
5. Test lead coupler set.
6. Medium alligator clip set.
7. Large alligator clip set.
8. Spade lugs.
9. IC probe tip adapter.
10. Minigrabber® test clip leads.
11. Minipincer® test clip leads.
12. Nylon storage pouch.

- Modular probes with interchangeable tips.
- Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs for most meters from Fluke, HP, Meterman, Amprobe, and others.
- New retractable tip probe with 3in (76.2mm) long tip and silicone leads.
- Minigrabber® and Minipincer® test clip leads attach to test leads.
- Test lead coupler connects leads to probe set for 16ft (4.8m) reach.
- Nylon storage pouch with compartments for accessories.

Electronic DMM Maxi-Kit

Model# 6340



1. Silicone insulated 4ft (1.2m) leads.
2. Modular probe set.
3. Precision electronic probes.
4. 4 sets of replacements tips.
5. Test lead couplers.
6. Medium alligator clips.
7. Large alligator clips.
8. Minigrabber® test clip leads.
9. Minipincer® test clip leads.
10. Spade lugs.
11. Nylon storage pouch.

- Modular probes with caged-spring tips fit 4mm sockets.
- Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs fit most meters from Fluke, HP, Meterman, Amprobe, Greenlee and others.
- Precision Electronic probe with replacement tips offers flexibility in testing.
- Minigrabber® and Minipincer® test clip leads for smaller test points.
- Nylon storage pouch with compartments for accessories.

Deluxe Electronic DMM Test Lead Kit

Model# 5674C



1. Silicone insulated 4 ft (1.2m) leads with right-angle plug.
 2. Modular probe set with standard tips.
 3. Extended probe tip adapters.
 4. Medium alligator clips.
 5. IC probe tip adapters.
 6. Minigrabber® test clip leads.
 7. Minipincer® test clip leads.
 8. Maxigrabber® test clips with pincer tip.
 9. Nylon storage pouch.
- Modular probes with standard probe tips.
 - Insulated 4ft (1.2m) test leads with right-angle DMM plugs fit most meters from Fluke, HP, Metorman, and others.
 - Probe tip extender with 3in (76.2mm) long tip.
 - Minigrabber® test clip leads attach to test leads.
 - Minipincer® test clip leads for fine pitch chip leads.
 - Maxigrabber® test clips attach to test leads.
 - Nylon storage pouch with compartments for accessories.

Electronic DMM Test Lead Kit

Model# 5543B



1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
 2. Modular electronic test probes with standard tips.
 3. Extended fine-tip probe adapter -red.
 4. Medium alligator clip -black.
 5. IC probe tip adapter -red.
 6. Insulated spade lug -black.
 7. Minipincer® test clip lead -red.
 8. Minigrabber® test clip lead -red.
 9. Nylon storage pouch.
- Silicone insulated 4ft (1.2m) test leads fit meters from Fluke, HP, Metorman, and others.
 - Modular electronic test probes attach to leads.
 - Extended fine-point adapter attaches to probe tips.
 - IC adapter attaches to probe for secure probing on chip leads.
 - Minipincer® test clip lead for fine pitch chip leads.
 - Minigrabber® test clip lead extend the reach of the test leads.

Basic Electronic DMM Test Lead Kits



Model#	Plug Type	Ratings
6343	Right-angle DMM plugs	UL IEC1010, CAT III 1000V
5672A	Right-angle banana plug	33 Vac/70 Vdc
6344	Straight DMM plugs	UL IEC1010, CAT III 1000V
5325A	Stacking banana plugs	33 Vac/70 Vdc
6456	Retractable sheath banana plug	UL IEC1010, CAT III 1000V

1. Comfort-grip DMM test probes.
 2. Silicone insulated 4ft (1.2m) leads.
 3. Extended probe tip adapters.
 4. Alligator clip probe tip adapters.
 5. Plastic storage case (not shown).
- Note:** Model 5672A has HEAVY-DUTY stainless-steel tips.
- See page 66 for banana plug types.
- Featuring Pomona's new comfort-grip probes.
 - Monolithic probes with fixed tips.
 - DMM plugs fit most meters from Fluke, Metorman, HP, Amprobe, Greenlee, and others.
 - Extended tip adapter has sharp needle point.
 - Alligator clip adapter snaps onto the probe tip.


Deluxe Electronic Bench DMM Test Lead Kit



Model#	Features	Ratings
6204A	Straight DMM plugs	CAT III, 600V per IEC 1010-2-031

1. Silicone insulated 4ft (1.2m) test leads with straight DMM plugs.
 2. Modular electronic test probes with standard tips.
 3. Extended fine-tip probe adapters.
 4. Medium alligator clips.
 5. IC lead probe tip adapters.
 6. Insulated spade lugs.
 7. Minipincer® test clip leads.
 8. Minigrabber® test clip leads.
 9. Nylon storage pouch.
- Silicone insulated 4ft (1.2m) leads fit meters from Fluke, HP (Agilent), Keithley and others.
 - Modular electronic test probes attach to leads.
 - Extended fine-point adapters attach to probe tips.
 - IC adapters attach to probes for secure probing on chip leads.
 - Minipincer® test clip leads for fine pitch chip leads.
 - Minigrabber® test clip leads extend the reach of the test leads.


Electronic Bench DMM Test Lead Kit



Model#	5901B
--------	-------


1. Silicone insulated 4ft (1.2m) test leads with straight DMM plugs.
 2. Modular electronic test probes with replaceable tips.
 3. 5 sets of replacement probe tips
 4. Medium alligator clips.
 5. Insulated spade lugs.
 6. Minigrabber® test clip leads.
 7. Nylon storage pouch.
- DMM plugs fit meters from Fluke, HP (Agilent), Keithley and others.
 - Modular electronic test probes with replaceable tips adapt to many different modes.
 - Replacement probe tips offer a wide variety of probing solutions.
 - Alligator clips attach to test lead for reliable connections.
 - Spade lugs attach to test leads for binding posts or terminal screws.
 - Minigrabber® test clip leads extend the reach of the test leads.
 - Uses 080 probe tips, see page 14 for replacement tips.
 - Rated CAT II 600V 10A.

Deluxe Automotive DMM Test Lead Kit



Model#	6530A
--------	-------

1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
 2. Heavy-duty modular test probes with stainless-steel tips.
 3. Heavy-duty alligator clips.
 4. Insulation piercing clips.
 5. Maxigrabber® test clips with alligator jaws.
 6. Maxigrabber® test clips with hook.
 7. Backprobe pins.
 8. Nylon storage pouch.
- Alligator clips attach to test lead for reliable connections.
 - Sharp stainless-steel probe tips resist wear.
 - Insulation piercing clips make connections without stripping insulation from wires.
 - Backprobe pins access contacts through the back side of automotive connectors.
 - DMM plugs fit meters from Fluke, Mettman, Amprobe, Greenlee and others.
 - Maxigrabber® test clips with alligator jaws for quick and easy connections.

Industrial/Automotive DMM Test Lead Kit
Model# 5903A


1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
2. Heavy-duty modular test probes.
3. Heavy-duty alligator clips.
4. Insulation piercing clips.
5. Maxigrabber® test clips with alligator jaws.
6. Nylon storage pouch.

- DMM plugs fit meters from Fluke, Meterman, Amprobe, Greenlee and others.
- Sharp stainless-steel probe tips resist wear.
- Alligator clips attach to test lead for reliable connections.
- Insulation piercing clips make connections without stripping insulation from wires.
- Maxigrabber® test clips with alligator jaws for quick and easy connections.

Deluxe Electrical DMM Test Lead Kit
Model#
Plug Type
Ratings
5904A

Right-angle DMM plug

CAT III 1000V per IEC 1010-2-031



1. Silicone insulated 4ft (1.2m) test leads.
2. Modular electrical test probes with stainless-steel tips.
3. Maxigrabber® test clips with jaws.
4. Maxigrabber® test clips with hooks.
5. Maxigrabber® test clips with pincers.
6. Large alligator clips.
7. Nylon Storage pouch.

- DMM plugs fit meters from Fluke, Meterman, Amprobe, Greenlee and others.
- Alligator clips attach to the test leads for secure connections.
- Maxigrabber® test clips attach to test leads.
- Nylon storage pouch to contain all kit components.

Electrical DMM Test Lead Kit
Model#
Ratings
5673B

CAT III 1000V per IEC 1010-2-031



1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
2. Modular electrical test probes with stainless-steel tips.
3. Extended tip probe adapters.
4. Insulated spade lugs.
5. Medium alligator clips.
6. Large alligator clips.
7. Nylon storage pouch.

- DMM plugs fit meters from Fluke, Meterman, Greenlee, Amprobe and others.
- Spade lugs connect to test leads and can be secured to binding posts or terminals.
- Alligator clips plug into the test leads.


Basic Electrical DMM Test Lead Kit



Model#	Plug Type	Ratings
5900A	Right-angle DMM plug	CAT III 1000V per IEC 1010-2-031

1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
 2. Modular electrical test probes with standard tips.
 3. Maxigrabber® test clips.
 4. Nylon storage pouch.
- DMM plugs fit meters from Fluke, Meterram, Greenlee, Amprobe and others.
 - Maxigrabber® test clips with jaws attach to test leads.
 - Nylon carrying pouch included.


Multi-Use DMM Test Lead Kit



Model#	Ratings
5899A	CAT III 1000V per IEC 1010-2-031

1. Silicone insulated 4ft (1.2m) test leads with right-angle DMM plugs.
 2. Modular electrical test probes with standard tip.
 3. Maxigrabber® with pincer tips.
 4. Medium alligator clips.
 5. Nylon storage pouch.
- DMM plugs fit meters from Fluke, Meterram, Greenlee, Amprobe and others.
 - Alligator clips attach to test lead for reliable connections.
 - Maxigrabber® test clips with pincers for quick and easy connections.

Deluxe Industrial Test Companion™ Kit



Model# 6173A

Includes shoulder-pack style Cordura carrying case plus the following IEC1010 compliant test accessories:

1. Modular Electrical Test Probe Set with Banana Plug Tip.
2. Flexible Test Lead Set with Right-Angle and Straight Banana Plugs.
3. Probe Lead Set with Sharp Stainless Steel Tip.
4. Maxigrabber® Test Clip Set with Pincer Tip.
5. Maxigrabber® Test Clip Set with Hook Tip.
6. Maxigrabber® Test Clip Set with Jaws.
7. Extra Large Alligator Clip Set.
8. Medium Alligator Clip Set.
9. Insulated Spade Lug Sets (2).

Deluxe Electronic Test Companion™ Kit
Model# 6345

Includes large briefcase style Cordura carrying case plus the following test accessories:

1. Modular Electronic Probe Set with Replaceable Tip.
2. Assorted Replacement Tips.
3. Flexible Test Lead Set with Right Angle and Straight Banana Plugs.
4. SMD Test Tweezer® to Banana Plugs.
5. Minigrabber® Test Clip Leads.
6. Minipincer® Test Clip Leads.
7. Micrograbber® Test Clip Leads.
8. SMD Grabber® Test Clip Leads.
9. Medium Alligator Clip Set.
10. Slide-on Extended Tip Set.
11. Slide-on IC Tip Set.
12. Spade Lug Adapter Set.

Industrial Test Companion™ Kit
Model# 6172A

Includes shoulder-pack style Cordura carrying case plus the following IEC1010 compliant test accessories:

1. Modular Electrical Test Probe Set with Banana Plug Tip.
2. Flexible Test Lead Set with Right-Angle and Straight Banana Plugs.
3. Probe Lead Set with Sharp Stainless Steel Tip.
4. Maxigrabber® Test Clip Set with Pincer Tip.
5. Maxigrabber® Test Clip Set with Hook Tip.
6. Medium Alligator Clip Set.
7. Insulated Spade Lug Adapter Set.

Electronic Test Companion™ Kit
Model# 6174

Includes shoulder-pack style Cordura carrying case plus the following test accessories:

1. Modular Electronic Probe Set with 0.080in (2.03mm) diameter tip.
2. Flexible Test Lead Set with Right-Angle and Straight Banana Plugs.
3. SMD Test Tweezer® to Banana Plugs.
4. Minigrabber® Test Clip Leads.
5. Micrograbber® Test Clip Leads.
6. SMD Grabber® Test Clip Leads.
7. Medium Alligator Clip Set.
8. Slide-on Extended Tip Set.
9. Slide-on IC Tip Set.
10. Spade Lug Adapter Set.

Test Companion Kits include your favorite probes, clips, and leads in their own specially designed carrying case. Select from the following table.

	Kit Model#													
Model#	6112A	6120	6162	6163	6166	6171	6172A	6173A	6174	6175	6200	6237	6345	Page
Test Probes														
5689A Probe with Replaceable Tip					•	•				•			•	67
5906A Probe with 0.16in (4mm) Banana Tip	•		•	•			•	•						67
6232A Probe with 0.080in (2.03mm) Brass Tip	•	•							•	•	•			67
Test Leads														
5678 SMD Test Tweezers with DMM Plugs									•	•			•	70
5898 Right-Angle Banana/Probe							•	•						66
5907A Straight/Right-Angle Banana	•	•	•	•	•	•	•	•	•	•			•	67
5908A Straight/Straight Sheath Banana Plugs											•			67
Alligator Clips														
5916A Medium Alligator Clips (2)	•	•	•	•	•	•	•	•	•	•	•		•	69
6041B Large Alligator Clips (2)	•	•						•						68
Grabbers														
5910B Maxigrabber Set with Pincer Tips (2)	•	•		•			•	•						68
5911B Maxigrabber with Hook Tip Set							•	•						68
5912B Maxigrabber Alligator Clip Set		•						•						68
Patch Cords														
6242 Micrograbber to Banana Plug						•			•	•			•	—
6243 SMD Grabber to Banana Plug						•			•	•			•	—
6244 Minigrabber to Right-Angle Sheathed Banana Plug					•									84
6248 Minigrabber to Sheathed Banana Jack	•					•			•	•	•		•	84
Oscilloscope Probes														
4550B Oscilloscope Probe												•		79
6035 Oscilloscope Probe, Fully Insulated Switchable		•												82
Probe Tips/Tip Adapters														
5133 Probe Tip Stainless Steel, Dog Leg Micro (2)						•				•			•	70
5246 IC Test Tip Adapter														
5682 Extended Tip Adapter						•				•	•		•	69
6262 Extended Tip Adapter					•				•					69
6263 IC Test Tip Adapter					•				•					69
Spade Lug Adapters														
6203 Insulated Spade Lug			•	•			•	•						69
Coaxial Cable Assemblies/Adapters														
2249 BNC (M) Cable Assembly												•		10
3788 BNC (M) to Minigrabber Adapter												•		17
Carrying Cases														
5955 Tri-fold Pouch			•											64
6146 Briefcase	•	•											•	64
6147 Medium Shoulder-pack				•	•	•	•	•	•	•				64

Pomona's Test Companion™ Accessory Cases and Pouches



6146

6147

5955

Model#	Description
6146	Briefcase style with carrying strap
6147	Medium shoulder-pack with carrying strap
5955	Folding case with Velcro



Precision Electronic Test Probe Set



Model#	Features	Ratings
6341	Probe set with complete set of 5 tips	IEC1010 CAT III 1000V*
6342	Probe set with sharp point gold pogo pin tips	CAT III 1000V
6275	Probe set with sharp stainless steel rigid tips	CAT III 1000V
6354	Replacement probe tips. Set of 5 types.	

- Replaceable 0.04in (1.52mm) pogo-pin tips.
- Small outline for tight test situations.
- Replaceable pogo-pin tips.
- Comfort-grip textured surface.
- Fits all meters including Fluke, HP (Agilent), Keithley, Metorman and others.
- Silicone insulated leads resist abrasion and heat.

Replacement Tips

1. Sharp-point gold pogo-pin.
2. Tri-point gold pogo-pin.
3. Quad-point gold pogo-pin.
4. Sharp stainless steel rigid.
5. 5.3in (134.6mm) long extended. Stainless steel.

*except when used with 3in (76.2mm) tip which is 33Vrms/70Vdc.

See page 64 for more probe tips.

Safety 2mm/4mm Test Probe Set



Model#	Ratings
6601	IEC1010 1000V CAT III

- Versatile 2mm probe tip with screw-on 4mm tip.
- Each probe includes Protective Cap designed to meet Guidance Note GS38.
- Silicon insulated 4ft (1.2m) test leads with right-angle DMM plugs.
- Comfort-grip textured surface.

Retractable Needle Tip Test Probes



Model#	Plug Type	Ratings
5953A	Right-angle DMM	CAT II 600V*
5952A	Stacking banana	600V**

*per IEC1010

- Silicone insulated 4ft (1.2m) leads fits most meters from Fluke, Metorman, HP, Amprobe, Greenlee and others.
- Fully insulated tip extends to 3in (76.2mm).
- Durable 0.040in (1.02mm) stainless-steel needle tips reach into inaccessible areas.
- Set of 2 probes, one black and one red.

See page 63 for banana plug types.

**Ratings: Hands free testing in controlled environments: 600 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Test Probes with Screw-on Alligator Clips



Model#	Ratings
6723	IEC1010 1000V CAT III 20A (probe alone) IEC1010 300V, CAT II 10A (with alligator clip attached) 10A

- Probe set includes 2 screw-on alligator clips.
- 8-32 threaded tips allow secure attachment of alligator clips.
- Silicon insulated 4ft (1.2m) test leads with right-angle DMM plugs.
- Comfort-grip textured surface.
- Wide temperature range of 14 to 131°F (-10 to +55°C).

Additional Screw-on Alligator Clip Set for 6723



Model#	Ratings
6726	300V, CAT II 10A

- Set of 2 screw-on alligator clips.
- Designed for use with 8-32-UNC 2A threaded probe like the Pomona 6723.
- 8-32 threaded tips allow secure attachment of alligator clips.
- Wide temperature range of 14 to 131°F (-10 to +55°C).

AC Voltage Detector and Flashlight



Model#	7290
--------	------

AC Voltage Detector – Detects voltages from 40VAC to 300VAC from 1 to 15 inches away from the source. Flashlight feature includes ultra-bright white LED with 100,000 hour bulb. Offers long battery life with standard alkaline AAA battery. No lithium battery needed.

Replacement DMM Test Lead Sets with Fixed Tips

5.5in (139.7mm)



Model#	Features	Plug Type	Ratings
5519A	Standard tip Nickel/brass	Right-angle DMM (1)	CAT III 1000V*
6365	Standard tip Nickel/brass	Straight DMM (2)	CAT III 1000V*
6366	Standard tip Nickel/brass	Retractable sleeve (5)	CAT III 1000V*
5898	Stainless steel heavy-duty tip	Right-angle DMM (1)	CAT III 1000V*
5309A	Stainless steel heavy-duty tip	Stacking banana (3)	1000V**
5517A	Standard tip Nickel/brass	Right-angle Simpson Plugs (1)	1000V**

*per IEC1010-2-031


- Monolithic probes with fixed tips.
- Durable Ø80 tips for long life.
- Comfort-grip probe.
- Silicone insulated 4ft (1.2m) leads fit most DMMs from Fluke, HP (Agilent), Metorman, Amprobe, Greenlee and others.

For Plug Type, see below.

**Ratings: Hands free testing in controlled environments: 1000 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Probe Kit with Full Set of 5 0.060in (1.52mm) Replacement Tips

4.85in (123.19mm)



Model#	Description	Plug Type	Ratings
5676A	Hand held DMM probe set	Right-angle DMM (1)	CAT III 1000V*

- Two test probes with a full set of all 5 probe tips (10 tips total).
- Silicone insulated 4ft (1.2m) leads.
- 0.06in (1.52mm) tip diameter.

Replacement Tips

*per IEC1010-2-031


1. Sharp gold-plated plunger tip.
2. Triple-point gold-plated pogo pin.
3. Gold plated micro tip pogo.
4. Stainless-steel sharp-point.
5. Standard brass.

See page 70 for more probe tips.

**Ratings: Hands free testing in controlled environments: 1000 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Replaceable Tip Probes

4.85in (123.19mm)



Model#	Probe Tip	Plug Type	Ratings
6469	Gold-plated Microtip pogo	Right-angle DMM (1)	CAT III 1000V*
6470	Gold-plated Microtip pogo	Straight DMM (2)	CAT III 1000V*
6472	Gold-plated Microtip pogo	Stacking banana (3)	1000V**
6477	Stainless-steel sharp-point	Right-angle DMM (1)	CAT III 1000V*
5950A	Stainless-steel sharp-point	Straight banana (4)	1000V**
5951A	Nickel-plated brass	Right-angle banana (6)	1000V**

*per IEC1010-2-031

- New 0.06in (1.52mm) diameter solid and pogo-pin probe tips can be easily replaced without tools making this versatile probe the perfect tool for nearly every test.
- Comfort-grip probe handle.

Replacement Tips

1. Sharp gold-plated plunger tip.
2. Triple-point gold-plated pogo pin.
3. Gold-plated micro tip pogo.
4. Stainless-steel sharp-point.
5. Standard brass.


See page 70 for more probe tips.

**Ratings: Hands free testing in controlled environments: 1000 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Plug Types

1. Right-angle DMM plug*
2. Straight DMM plug*
3. Stacking banana plug
4. Straight banana plug
5. Retractable sleeve banana plug
6. Right-angle banana plug

* Shrouded DMM plugs fit most DMMs from Fluke, Metorman, HP (Agilent), Amprobe, Greenlee and others.



Replacement DMM Test Leads



Choose plug for this end from below

Plugs into probes below



Model#	Application	Features	Ratings
5907A	Hand held DMM modular test leads	Right-angle DMM plug (1)	CAT III 1000V*
5908A	Bench-top DMM modular test leads	Straight DMM plugs (2)	CAT III 1000V*
5909A	Hand held DMM modular test leads	Right-angle DMM plug at both ends (1)	CAT III 1000V*
6358	Universal DMM test leads	Retractable sheath DMM plugs (3)	CAT III 1000V*

*per IEC1010-2-031

- Leads for Pomona Modular Test Probes.
- Plugs fit most popular DMMs from Fluke, Metorman, HP (Agilent), Amprobe, Greenlee and others.
- Silicone insulated 4ft (1.2m) leads.
- Retractable sleeve plug fits all banana jacks, binding posts and DMM input jacks.

Plug Types

1. Right-angle DMM.
2. Straight DMM.
3. Retractable sheath 0.16in (4mm).

**Ratings: Hands free testing in controlled environments: 1000 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Replacement Modular Test Probes



6232A



5906A



6479



5689A

Model#	Probe Type	Features	Ratings
6232A	Modular electrical probe	Standard 0.08in (2.03mm) tip	CAT III 1000V*
6479	Industrial modular probe	Stainless-steel 0.08in (2.03mm) sharp-point	CAT III 1000V*
5906A	Lantern tip	Fits 4mm Jack	CAT III 1000V*
5689A	Replaceable tip modular probe	Stainless-steel 0.08in (2.03mm) sharp-point	CAT III 600V*

*per IEC1010-2-031

- Modular probes fit all Pomona test leads.
- Lantern tip probes fit into banana jacks.

Replacement Modular Test Probe Sets

Model#	Description	Probe Type	Test Lead Type	Ratings
6286	Standard tip with right-angle DMM plug	6232A	5907A	CAT III 1000V*
6288	Stainless-steel tip with right-angle DMM plug	6479	5907A	CAT III 1000V*
6304	Lantern tip probe with right-angle DMM plug	5906A	5907A	CAT III 1000V*

*per IEC1010-2-031



6232A



6479



5906A



5689A

- Modular test probes sets contain one set of modular probes and test leads in one package.
- Silicone insulated 4ft (1.2m) leads fit most meters from Fluke, Metorman, HP (Agilent), Amprobe, Keithley, Greenlee and others.

**Ratings: Hands free testing in controlled environments: 1000 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

SMD Micro Tip/Test Probe

NEW



Model#	Color
5144-48-0	Black
5144-48-2	Red
6235	Set of two probes: one Black and one Red

The probe microtip is specially designed to probe SMD contacts. It features a stainless steel needle tip that is flexible to help prevent damage to SMD lands. The tip is curved to aid in probing hard to reach areas. Black.

Ratings: Hands free testing in controlled environments: 1200 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Maxigrabber® Test Clip Set with Pincer




Model#	5910B
--------	-------

Includes set of 2, one red and one black.

Pincer Opening: 0.080in (2.03mm) dia. test point.

Rating: Overvoltage CAT III, 1000V, 10A per IEC1010-2-031.

Maxigrabber® Test Clip Set with Hook



Model#	5911B
--------	-------

Includes set of 2, one red and one black.

Hook Fits Test Points to: 0.060in (1.52mm) diameter.

Hook Opens to: 0.25in (6.5mm).

Rating: Overvoltage CAT III, 1000V, 10A per IEC1010-2-031.

Maxigrabber® Test Clip Set with Jaws



Model#	5912B
--------	-------

Includes set of 2, one red and one black.

Jaw Opening: 0.50in (12.70mm) dia.

Rating: Overvoltage CAT III, 1000V, 10A per IEC1010-2-031.

Insulation Piercing Maxigrabber® Test Clip Set



Model#	5913
--------	------

Includes set of 2, one red and one black.

Pierces insulation to make connection on wire up to 0.144in (3.66mm) diameter.

Rating: Overvoltage per IEC1010-2-031 CAT III, 1000V, 5A.

BNC Shielded Test Probe Kit

Model#	5292-48
--------	---------




NEW

Shield extends to within 1.5in (3.8cm) of probe tip. Compatible with DMM banana plug inputs when using Pomona 1269 BNC to double banana plug adapter. Alligator or Minigrabber test clip can be quickly threaded onto ground lead. Stainless steel dog leg tip excellent for SMD probing. Kit includes: Shielded test probe, Minigator with 6-32 thread for ground lead and insulated flex boot for Minigator, Minigrabber test clip with 6-32 thread for ground lead, Dog leg probe tip.

Ratings: Hands free testing in controlled environments: 500 Vrms Max. For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Insulation Piercing Clip Sets

Model#	Features	Colors
6405	Attach to test leads 4in (10.2cm) long	Set of red/black
6413	Attach to 0.080in (2.03mm) Probe tip (10.2cm) long	Set of red/black
6580-12	12in (304.8mm) long	-0 blk, -2 red
6580-24	24in (609.6mm) long	-0 blk, -2 red



- Double V block centers wire
- Set of 2, (red and black jacks)
- Bright yellow for easy location
- Attach to test leads

Large Alligator Clip Set



Model#	Color
6041B	Set of 2: Black, Red
6042B-*	1 Clip

Fits on any DMM or banana plug test lead.


Rating: IEC1010-2-031 CAT III 1000V 20A.

Jaw Opening: 1.0in (25.40mm).

*For singles, order: -0 Black, -2 Red.

← 3.58in (90.9mm) →

Industrial Alligator Clip Set



Model#	5914
--------	------

Fits on any DMM or banana plug test lead.

Rating: IEC1010-2-031 CAT III 600V 10A.

Jaw Opening: to 1.0in (25.40mm).

*Std. Colors: -0 Black, -2 Red.

← 3.20in (81.3mm) →

Medium Alligator Clip Set



Model#	Color
5916A	Set of 2: Black, Red
5787A*	1 Clip

Fits on any DMM or banana plug test lead.

Rating: IEC1010-2-031 CAT II 300V 5A.

Jaw Opening: to 0.30in. (7.62mm).

***For singles, order:** -0 Black, -2 Red.

Test Lead Couplers



Model# 6252

Banana plug splice.

Maintains overvoltage rating up to CAT III 1000V per IEC1010-2-031.

Use with any Pomona DMM test leads, even 0.16in (4mm plugs).

Test Probe Tip Adapters



Model# 6264*

Alligator Clip.


Attach to probe tip.

Rating: IEC1010-2-031 CAT II. 300V. 5A

Works with comfort-grip style and modular electrical probes.

***Std. Colors:** -0 Black, -2 Red.

Test Probe Tip Adapters



Model#	Application
6262*	fits comfort-grip style and modular probes 6232A and 6479
5682*	fits modular probe 5689A

Extended Fine Point.

Insulated probe for hard to reach test points.

Maximum 3A.

Std. Colors: -0 Black, -2 Red, -02 1 ea. Black, Red.

Alligator Clip with Boot for 0.166in (4mm) Sheathed Banana Plug



Model#	Fits Sheathed Banana
6573A*	0.16in (4mm)

Clip plugs onto 0.16in (4mm) sheathed banana plug, as on Pomona model 5907A test leads.

Jaw opening: 0.30in (7.6mm) max.

Materials: *Alligator clip:* nickel-plated steel, *Boot:* Santoprene rubber.

Length: 2.91in (73.9mm).

Rating: 1000V CAT III per IEC1010-2-031, 10A, -13 to 176°F (-25 to 80°C).

***Std. Colors:** -0 Black, -2 Red, -02 two alligator clips, 1 Black, 1 Red.

Insulated Spade Lug Adapters



Model#	Color
6203	Set of 2: Black, Red
1614A*	1 Clip

Connect banana plug patch cords to binding posts.

Fits screws or binding posts from #10: 0.32in to 0.25in (8.13mm to 6.35mm).

Compatible with any Pomona banana jack shrouded or unshrouded

***For singles, order:** -0 Black, -2 Red.

Test Probe Tip Adapters



6263
Fits 5519A etc.

Model#	Application
6263*	fits comfort-grip style and modular probes 6232A and 6479


IC Probe Tip.

Attach to 0.08in (2mm) probe tips.

Rating: IEC1010 CAT II, 300V, 5A.


***Std. Colors:** -0 Black, -2 Red.

0.08 (2.03mm) Replacement Probe Tips




Model#	Item	Features
5133	3	SMD Microtip™ stainless-steel tip
6364	Full set	Set of all tips
	1	Nickel-plated standard tip
	2	Stainless-steel sharp point
	3	SMD Microtip™ stainless-steel tip
	4	Sharp needle-point stainless-steel

0.04 (1.01mm) Replacement Probe Tips



Model#	Item	Features
6212	3	Quad-point gold-plated pogo pin
6354	Full set	Set of all tips
	1	Sharp gold-plated
	2	Triple-point gold-plated pogo pin
	3	Quad-point gold-plated pogo pin
	4	Sharp stainless-steel
	5	5.3in (134.6mm) long extended. Stainless steel

0.06 (1.52mm) Replacement Probe Tips



Model#	Item	Features
6475	Full set	Set of all tips
	1	Sharp gold-plated plunger tip
	2	Triple-point gold-plated pogo pin
	3	Gold-plated micro tip pogo
	4	Stainless-steel sharp-point
	5	Standard brass

SMD Test Tweezer Products



Model#	Features	Ratings
5143-K-48	Stacking Banana Plug	30 Vac/ 70 Vdc, 3A
5142-K-48	BNC Male	30 Vac/ 70 Vdc, 3A
5678-K-48	Right-Angle DMM Plug	30 Vac/ 70 Vdc, 3A

Length: 48in (1.22m)



RF Detector Test Probes



Model#	Turn-On Voltage (mV)	Bandwidth (MHz)	Input Capacitance (pF)	Peak AC Input (V)	DC Isolation Incl. Peak AC (V)
6106	350	1MHz-1GHz ± 1.5 dB	6	30	100

Displays RF voltages on multimeter.
Manufactured with high reliability SMD components.
Slim-line probes will show AC voltages with sine wave shapes between 500 Hz and 1 GHz.
Display will show 1 VDC for 1 VRMS of the sine wave signal.
Comes complete with ground lead, sprung hook, BNC adapter and extra tip.
Works best on multimeters with 10 MΩ input impedance.
Cable Length: 4ft (1.2m).

Create Your Own Test Leads for Your Own Specific Needs with the Following:

Test Lead Wire with Silicone or PVC Insulation



Model#	Insulation Type	Length
6733-*	Silicone	50ft (15.2m)
6734-*	PVC	50ft (15.2m)

- 50ft (15.2m) of unterminated 18 AWG test lead wire 50ft (15.2m lengths only.)
 - Choose from heat-resistant silicone or PVC insulation.
 - Very flexible with 65 strands of 36 AWG tinned copper conductor.
 - Create your own test leads with the adapters shown below.
 - Wide temperature range of -58 to 302°F (-50 to 150°C) with PVC insulation.
- *Std. Colors: -0 Black, -2 Red.

See page 32 for more do-it-yourself plugs.

Do-It-Yourself 4mm Right Angle Banana Plug

1.28in
(32.4mm)



Model# 6729

Build your own safety leads with do-it-yourself safety-sheathed 4mm right-angle banana plug.

Material: Contacts: nickel-plated brass; Insulation: lucel acetal polymer.

Rating: IEC1010 1000V Category III**, 20A, 14 to 131°F (-10 to +55°C).

*Std. Colors: -0 Black, -2 Red.

** When plug is correctly assembled and terminated.

Do-It-Yourself 4mm Stackable Banana Plug

2.3in (58.4mm)



Model# 6721

Build your own safety stacking leads with do-it-yourself safety-sheathed 4mm stackable banana plugs.

Material: Contacts: nickel-plated brass; Insulation: lucel acetal polymer.

Rating: IEC1010 1000V Category III**, 20A, 14 to 131°F (-10 to +55°C).

*Std. Colors: -0 Black, -2 Red.

** When plug is correctly assembled and terminated.

Do-It-Yourself In-Line Sheathed (4mm) Banana Plug and Jack

3.01in (76.45mm) 1.44in (36.58mm)



6383



6384

Kelvin Probes

Model# 6303



For 4-wire and 2-wire measurements.

Patented design for high precision rapid testing.

Gold-plated for accuracy.

Easily move from one test point to another for rapid readings.

For use with 4-wire Kelvin meters such as Agilent 34401A, and 3458A.

Rating: For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Length: 48in (122cm)

Kelvin Lead Set with Kelvin Clips

Model# 6730



- Gold-plated Kelvin clip jaws allow 4-wire resistive measurements.
- Silicone insulated 3.3ft (1m) test lead.
- Safety sheathed straight DMM plugs for convenient bench use.
- Clips firmly grip test points for low-loss connection.

Rating: For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Kelvin Clip Set

Model# 5940



Two gold-plated clips connect to test points for 4-wire resistive measurement.

Clips open to 0.25in (6.35mm) maximum.

Gold-plated plugs and clips.

Rating: For CE compliance: not intended for hand held use at voltages above 33 Vrms/70 Vdc.

Overall Length: 26.5in (67.3cm).

Model#	
6383-*	Plug
6383-02	
6384-*	
6384-02	Jack

- Safety-rated plugs and jacks for use with any wire from 22 to 18 AWG with flexible insulation.
- Plugs fit most sheathed DMM jacks and DMM test leads to make up your own banana plug or jack test lead or jumper.

See mating panel jacks (6387 on page 34).

Material: Banana Plug/Jack: brass; Spring: heat treated beryllium copper; Insulation: Santoprene®.

Attaches to wire by crimp or soldering.

Rating: IEC1010 CAT II 300V, 15A, +275°F (+135°C) max.

*Std. Colors: -0 Black, -2 Red, -02 Black and Red (2 per pkg).

*Sold in pkgs of 10.

Grabbers and Test Clips

Pomona Electronics' Grabber[®] Test Clips connect rapidly to component test leads, terminals and IC leads. Specially designed tips slide easily onto wire-wrap terminals. And do-it-yourself Grabber test clips can be assembled quickly and easily by the user.



**Minipincer
SMD Grabber**
Page 73



Minigrabber
Page 72



Micrograbber
Page 73



**Rotating
Micrograbber**
Page 73

SMD


0.016in - 0.02in
(0.4mm - 0.5mm)



Page 73

Micro

0.04in (1.02mm)




1.71in (43.43mm)



Page 73

Micro

0.10in (2.54mm)



1.71in (43.43mm)



Page 73

Mini

0.09in (2.29mm)



0.12in (3.05mm)

2.54in (64.52mm)




Page 72

SMD

0.087in (2.21mm)




2.59in (65.79mm)



Page 73

Maxi

0.09in (2.29mm)




6.22in (158.0mm)



Page 73

Maxi

0.14in (3.56mm)



6.22in (158.0mm)



Page 73

Minigrabber[®] Test Clip with Banana Jack



Model# 4723-*

Banana Jack built into plunger.

Overall Length: 2.54in (64.52mm).

Rating: Hands free testing in controlled environment: 300V*, 5A, 216°F (+102°C) max.

*Std Colors: -0 Black, -2 Red.

Do-It-Yourself Minigrabber[®] Test Clips



Model#	Max. Wire Dia.	Temperature
3925-*	0.090in (2.29mm)	216°F (102°C)
4555-*	0.144in (3.55mm)	300°F (149°C)

Overall Length: 2.54in (64.52).

Rating: Hands free testing in controlled environment: 300V*, 5A, +302°F (+150°C) max.

*Std Colors: Available in 10 colors. Sold in pkgs of 10 per color.

Model# Features

4176-02	Kit contains 2 pcs. of 3925, one black/one red
5522	Kit contains 10 pcs. of 3925, one of each color

Minigrabber[®] Test Clip with Pin Tip Jack



Model# 4826-*

A pin jack is built right into the plunger, allowing this test clip to be attached directly to the end of a pin tip patch cord. It can also be used as an adapter for test probes with 0.080in (2.03mm) tips.

Overall Length: 2.54in (64.52).

Rating: Hands free testing in controlled environment: 300V*, 5A, +216°F (+102°C) max.

*Std Colors: -0 Black, -2 Red.

Minigrabber[®] Test Clip with 6-32 Thread



Model# 4011-*

Clip can be used with oscilloscope leads equipped with a 6-32 screw.


Overall Length: 2.54in (64.52mm)

Rating: Hands free testing in controlled environment: 300V*, 5A, +216°F (+102°C) max.


*Std Colors: -0 Black, -2 Red.

Threaded Tip Adapter

Model# 4311



*Color Code: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, 5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Oscilloscope Probe Tip Adapters


6443

Model#	Probe Type
6443	Monolithic Series
6553	Modular Series

- Adapter attaches directly to the oscilloscope probe tip.
- Designed for use with Micro SMD Grabber Test Clips.



6553

Micrograbber® Test Clip with 0.025in (0.635mm) Square Pin


Model#	Features
4521*	Sold individually
5925	Micrograbber w/ 0.025in (0.635mm) Sq. Pin Kit. Contains 10 Model 4521 clips, one of each color.

*Std Colors: -0 Black, -2 Red.

SMD Grabber® Test Clip with 0.025in (0.635mm) Square Pin


Model#	Features
5360	Sold Individually
5927	SMD Grabber® Test Clip w/ 0.025in (0.635mm) Sq. Pin Kit. Contains 10 Model 5360 clips, one of each color.

Pincer type contact designed for testing 0.05in (1.25mm) lead pitches such as SOJ, SOIC and PLCC surface mounted packages.

0.15in (3.81mm) sq. access hole leads to 0.025in (0.635mm) sq. pin.

Overall Length: 1.73in (43.94mm).

Rating: Hands free testing in controlled environment: 150V*, 0.5A, +216°F (+102°C) max.

*Std Colors: Available in 10 colors.

0.025in (0.635mm) Square Pin Patch Cords available, see page 50.

Do-It-Yourself Maxigrabber® Test Clips


Model#	Max. Wire Dia.
4225-*	0.090in (2.29mm)
4565-*	0.144in (3.66mm)

Fits entry holes as small as 0.25in (6.35mm) dia.

Overall Length: 6.00in (152.4mm).

Rating: Hands free testing in controlled environment: 300V*, 5A, +216°F (+102°C) max.

*Std Colors: -0 Black, -2 Red.

For hook dimensions see page 72.

Do-It-Yourself SMD Grabber® Test Clips


Model#	Features
5520	Kit containing 10 pcs of 5243 one of each color

Pincer type contact designed for testing 0.05in (1.27mm) lead pitches such as SOJ, SOIC and PLCC surface mounted packages.

Overall Length: 1.71in (43.43mm).

Wire Opening: 0.09in (2.29mm) dia. max.

Rating: Hands free testing in controlled environment: 150V*, 0.5A, +216°F (+102°C) max.

Colors: -0 Black, -2 Red, -5 Green.

Do-It-Yourself Flexible Maxigrabber® Test Clips


Model#	5830-*
--------	--------

Rotating pincer type contact for easier access. Standard banana jack and screw for direct wire termination.

Overall Length: 6.22in (157.9mm).

Rating: Hands free testing in controlled environment: 250V*.

*Std Colors: -0 Black, -2 Red.

For pincer dimensions see page 72.

Do-It-Yourself Micrograbber® Test Clips


Model#	Features
4233-*	Sold in pkgs of 10 per color
5524	Kit containing 10 pcs of 4233, one of each color

Overall Length: 1.71in (43.43mm).

Material: Gold plated brass

Rating: 150V, 3A, +216°F (+102°C) max.

*Std Colors: Available in 10 colors.

For hook dimensions see page 72.

Insulated Minigator Test Clip to Pin Tip Jack

Model# 3491-*

Jaw Opening: Alligator clip has 0.187in (4.75mm) max.

Overall Length: 2.05in (52.07mm).

Rating: *Hands free testing* in controlled environment: 45V*, 5A, +122°F (+50°C) max.

***Std Colors:** -0 Black, -2 Red.



Do-It-Yourself Minipincer® Test Clip

Model# 5418-*

Pincer type contact.

Overall Length: 2.59in (65.79mm).

Rating: *Hands free testing* in controlled environment: 300V*, 5A, +176°F (+80°C) max.

***Std Colors:** -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue.



Medium Alligator Clip Set

Model# Features

5916A Set of 2 Clips Black and Red

Insulated clip with sheathed 0.16in (4mm) receptacle accepts flexible lead sets 5907A, 5908A, 5909A (p. 64).

Jaw Opening: 0.30in (7.62mm) max.

Overall Length: 2.25in (57.15mm).

Rating: Conforms to IEC1010-2-031, Overvoltage Cat II, 300V, 5A max.



Miniature Alligator Test Clip with 2mm Banana Jack

5788-*

Jaw Opening: 0.24in (6.10mm) max.

Overall Length: 1.57".

Rating: 45V, +80°C (+176°F) max.

***Std. Colors:** -0 Black, -2 Red.

Sold in pkgs of 10 per color.



Mini-alligator Clip with 2mm Jack

NEW

Model# Color

72924-0 Black

72924-2 Red

Rating: 600V Cat II, 10A.



Alligator Test Clip to Pin Tip Jack with Insulator

Model# 1437-*

Jaw Opening: Alligator clip has 0.30in (7.62mm) max.

Accepts 0.08in (2.03mm) dia. pin.

Overall Length: 2.16in (54.86mm).

Rating: *Hands free testing* in controlled environment: 150V*, 5A, +122°F (+50°C) max.

***Std. Colors:** -0 Black, -2 Red.

Sold in pkgs of 10 per color.

(Sold unassembled) 10 clips and 10 insulators per pkg.



Large Alligator Clip Set

Model# Features

6041B Set of 2 Clips Black and Red

6042B-1 Clip

Insulated clip with sheathed 0.16in (4mm) receptacle accepts flexible lead sets 5907A, 5908A and 5909A (p. 64).

Jaw Opening: 1.0in (25.40mm) max.

Overall Length: 3.5in (88.90mm).

Rating: Conforms to IEC1010-2-031, Overvoltage Cat III, 1000V, 20A max.

***Std. Colors:** -0 Black, -2 Red.



Alligator Clip with Boot for 0.166in (4mm) Sheathed Banana Plug

Model# Fits Sheathed Banana

6573A* 0.16in (4mm)

Clip plugs onto 0.16in (4mm) sheathed banana plug, as on Pomona model 5907A test leads.

Jaw opening: 0.30in (7.6mm) max.

Materials: *Alligator clip:* nickel-plated steel, *Boot:* Santoprene rubber.

Length: 2.91in (73.9mm).

Rating: 1000V CAT III per IEC1010-2-031, 10A, -13 to 176°F (-25 to 80°C).

***Std. Colors:** -0 Black, -2 Red, -02 two alligator clips, 1 Black, 1 Red.



Alligator Test Clip to Banana Jack, with Insulator, Solderable

Model# Plating Features

3289-* Gold 1 clip and insulator/pkg.

2240-* Nickel 10 clips and insulators/pkg.

6567 Nickel 10 clips w/o insulators/pkg.

Jaw Opening: Alligator clip has 0.30in (7.62mm) max.

Overall Length: 2.16in (54.86mm).

Rating: *Hands free testing* in controlled environment: 150V*, 5A, +122°F (+50°C) max.

***Std Colors:** -0 Black, -2 Red.

Sold unassembled.



SMD/Micro Format Test

Components and circuit boards are getting smaller and smaller. Pomona makes your job easier by providing clips and leads designed for micro-test, including a variety of 2mm connectors for use in tight spaces. From clips designed for chip pitches down to 0.008" (0.2 mm), to patch cords, and even complete SMD test kits, Pomona has the connection you need.

Pomona
ELECTRONICS

75

SMD Multi-Use Test Kit

Model# 72928

SMD test kit designed for multiple test small format test applications.

Kit includes:

1. 72902-0 Micro SMD Grabber Test Clips, (Black)
2. 72902-2 Micro SMD Grabber Test Clips, (Red)
3. 72906-0 Mini SMD Grabber Test Clips, (Black)
4. 72906-2 Mini SMD Grabber Test Clips, (Red)
5. 72905-0 Clip lead for Micro SMD Grabber - 0.8mm female/4 mm female, (Black)
6. 72905-2 Clip lead for Micro SMD Grabber - 0.8mm female/4 mm female, (Red)
7. 5908A Bench-top DMM Modular Test leads
8. 72920-39-0 stacking 2mm safety sheathed patch cords, PVC, 39in (100mm), (Black)
9. 72920-39-2 Multi-stacking 2mm safety sheathed patch cords, PVC, 100mm (39in), (Red)
10. 72923-0 SMD test probe with sharp, spring mounted tip, 2mm jack, (Black)
11. 72923-2 SMD test probe with sharp, spring mounted tip, 2mm jack, (Red)
12. 72917-0 4mm banana plug to 2mm sheathed banana jack adapter, 10/pkg (Black)
13. 72917-2 4mm banana plug to 2mm sheathed banana jack adapter, 10/pkg (Red)
14. 72924-0 Mini-alligator clip with 2mm jack, (Black)
15. 72924-2 Mini-alligator clip with 2mm jack, (Red)

Large Folding Test Kit Pouch



SMD High Density Circuit Test Kit

Model# 72935

SMD test kit designed for probing high density circuits.

Kit includes: 2 DMM leads with 4mm plugs, 2 test probes with spring-loaded tips, 6 micro SMD grabbers (72902), 6 adapter leads 0.8mm female to 0.4mm jack, 2 mini SMD grabbers with 4mm connectors, 2 holding rods (72903).



Micro SMD Grabber Test Clips Kit

NEW




Model#	Includes
72902	12 clips, 12 leads, 6 rods

Kit of 12 Micro SMD Grabbers in 6 colors. Grabbers are designed for easy attachment to SMD chips with pitches down to 0.008" (0.20 mm). Thin yet durable design permits attachment with close spacing in tight areas. Insulated tip minimizes shorting on adjacent pins. Gold plating for low resistance connections. Kit also includes 6 holding rods to reinforce connection positions during side-by-side measurements (order Model# 72903). In addition, kit includes 12 micro leads with 0.8mm female / 0.8mm male connectors.

Micro SMD Grabber Test Clips

NEW



Model#	Color
72902-0	Singles - Black
72902-2	Singles - Red

Designed for easy attachment to SMD chips with pitches down to 0.008" (0.20 mm). Thin yet durable design permits attachment with close spacing in tight spaces. Insulated tip minimizes shorting on adjacent pins. Gold plating for low resistance connections. Holding rods available to reinforce connection positions during side-by-side measurements (order Pomona model number 72903). Order Pomona model number 72905-0 for clip lead for Micro SMD Grabber - 0.8mm female/4 mm female (black) or 72905-2 (red) for easy attachment to standard test leads. 72902 includes one black and one red clip. (Black).

Holding Rods for Micro SMD Clips

NEW



Model#	72903
--------	-------

Holding rods reinforce 72902 connection positions during side-by-side measurements. (10/pkg).



Clip lead for Micro SMD Grabber 0.8mm/2mm



Model#	Color
72904-0	Black
72904-2	Red

Clip lead for easy attachment of Micro SMD Grabber to test leads with 2mm plugs. 0.8mm female/2 mm female.

NEW

Clip lead for Micro SMD Grabber 0.8mm/4mm



Model#	Color
72905-0	Black
72905-2	Red

Clip lead for easy attachment of Micro SMD Grabber (Pomona 72902) or Mini SMD Grabber (Pomona 72906) to standard test leads. 0.8mm female/4 mm female.

NEW

Mini SMD Grabber Test Clips

NEW



Model#	Color
72906-0	Black
72906-2	Red

Designed for easy attachment to SMD chips with pitches down to 0.032" (0.80 mm). Insulated shaft can be bent up to 36 degrees for versatile attachment in awkward locations or close proximity to other clips. Rotating jaws increase versatility in connection and stacking. Thin (3mm) profile allows close placement to adjacent clips. Compatible with leads with Ø0.8 mm female connectors. Order Pomona model number 72905-0 for clip lead for SMD Mini Grabber - 0.8mm female/4 mm female (black) or 72905-2 (red) for easy attachment to standard test leads.

Mini SMD Grabber Test Clip with Lead and 2mm Jack

NEW



Model#	Color
72907-20-0	Black
72907-20-2	Red

Mini SMD Grabber Test Clip (Pomona 72906) with 20 inch (50cm) lead and 2mm Jack.

Mini SMD Grabber Test Clip with Lead and 4mm Jack

NEW

Model#	Color
72929-20-0	Black
72929-20-2	Red

Mini SMD Grabber Test Clip (Pomona 72906) with 20 inch(50cm) lead and 4mm Jack for easy attachment to DMM leads.


Do-it-yourself 2mm Stackable Safety Sheathed Plug

NEW

Model#	Color
72925-0	Black
72925-2	Red

Rating: 600V Cat II 10A.


SMD Test Probe with Sharp, Spring Mounted Tip

NEW

Model#	Color
72923-0	Black
72923-2	Red

SMD test probe with sharp, spring mounted tip and 2mm jack. Provides ultra-fine control for probing high density SMD circuits. Very fine 0.03in (0.7mm) diameter stainless steel tip is spring-mounted for controlled pressure. Removable, clear IC insulator cap prevents shorting of adjacent IC logos. Sheathed 2mm receptacle adapts to 2mm test leads and adapters.

Rating: 600V Cat III, 1A.


Mini-alligator Clip with 2mm Jack

NEW

Model#	Color
72924-0	Black
72924-2	Red

Rating: 600V Cat II, 10A.



Multi-stacking 2mm Safety Sheathed Patch Cords

NEW

Model#	Length	Color
72920-20-0	20in (50cm)	Black
72920-20-2	20in (50cm)	Red
72920-39-0	39in (100cm)	Black
72920-39-2	39in (100cm)	Red

Multi-stacking 2mm safety sheathed male/male patch cords, PVC.

Rating: 600V Cat II, 10A Max.


2mm Safety Sheathed Patch Cords

NEW

Model#	Length	Color
72919-20-0	20in (50cm)	Black
72919-20-2	20in (50cm)	Red
72919-39-0	39in (100cm)	Black
72919-39-2	39in (100cm)	Red

2mm safety sheathed male/male patch cords, PVC, .



2mm/4mm Male-male Test Leads

NEW

Model#	Length	Color
72936-0	39in (991mm)	Black
72936-2	39in (991mm)	Red



4mm Safety Banana Jack to 2mm Banana Plug Adapter




Model#	Color
72914-02	One Black and One Red
72914-0	Black
72914-2	Red

Accepts 4mm safety-sheathed banana plugs. 10/pkg.

Rating: 33 Vac / 70 Vdc, 36A



2mm Sheathed Jack to 2mm Unsheathed Plug Adapter



Model#	Color
72915-0	Black
72915-2	Red

Accepts 2mm safety-sheathed banana plugs. 10/pkg.

Rating: 33 Vac / 70 Vdc, 10A.



4mm Banana Jack to 2mm Banana Jack Adapter




Model#	Color
72916-0	Black
72916-2	Red

Accepts 2mm and 4mm safety-sheathed banana plugs. 10/pkg.

Rating: 33 Vac / 70 Vdc, 10A.



4mm Banana Plug to 2mm Sheathed Banana Jack Adapter




Model#	Color
72917-0	Black
72917-2	Red

Accepts 2mm safety-sheathed banana plugs. 10/pkg.

Rating: 33 Vac / 70 Vdc, 10A.



2mm Safety Sheathed Jacks



Model#	Color
72921-0	Black
72921-2	Red

2mm safety sheathed jack with 1.9mm wire wrap connecting pin.

Materials: Contacts: Nickel plated brass.
Insulation: Polyamide.

Rating: 600V Cat II, 10A.



2mm Safety Sheathed Jack with Solder Tab



Model#	Color
72922-0	Black
72922-2	Red


Materials: Contacts: Nickel plated brass.
Insulation: Polyamide.

Rating: 600V Cat II, 10A.



Micro SMD Grabber® Test Clip for 0.05 to 0.01in (1.25 to 0.2 mm) Lead Pitch

Model#	Profile Height	Lead Pitch	Tip	Qty	Colors
6442	0.28in (7mm) low	0.05 - 0.01in (1.25 - 0.3mm)	Long	10	10
6311	0.55in 14mm	0.03in - 0.01in 0.85 - 0.2mm	Long	2	2
6351	0.55in 14mm	0.03in - 0.01in 0.85 - 0.2mm	Long	10	2
6312	0.55in 14mm	0.05 - 0.01in 1.25 - 0.3mm	Long	2	2
6352	0.55in 14mm	0.05 - 0.01in 1.25 - 0.3mm	Long	10	2
6313	0.55in 14mm	0.05 - 0.01in 1.25 - 0.3mm	Short	2	2
6353	0.55in 14mm	0.05 - 0.01in 1.25 - 0.3mm	Short	10	2



- Use with PQFP, SOIC, TSOP and SSOP packages with lead pitches down to 0.01 to 0.02in (0.2 to 0.5 mm).
- Thin body allows an unlimited number of clips to be stacked side by side.
- Maximum frequency is 100MHz.

Rating: Hands free testing in controlled environment: 70 vrms max. For CE compliance: Not intended for hand-held use at voltages above 33 Vrms / 70 Vdc.

Rotating Micrograbber® Test Clip with Two 0.025in (0.635mm) Square Pins



Model#	Features
5790-*	Sold individually
5929-*	Rotating Micrograbber® Test Clip Kit. -0 kit contains 10 Model 5790 black clips, -2 kit contains 10 red clips.
5930	Rotating Micrograbber® Test Clip Kit. Kit contains 5 Black & 5 Red Model 5790 clips.

Use when testing IC leads at 0.05in (1.25mm) pitch or in other tight situations. Pincers rotate for ease of access.

Overall Length: 2.12in (53.85mm)

Rating: 30 Vac / 60 Vdc max, 2A max..

*Std Colors: -0 Black, -2 Red.

Micro SMD Grabber® Test Clip for 0.05 to 0.02in (1.25 to 0.5 mm) Lead Pitch



Model#	6490-*
•	Use with PQFP & SOIC packages with 0.02in (0.5mm) lead pitch or greater.
•	Pincers and 0.03in (0.76mm) pin plug are directly connected; no sliding parts.
•	Pincers are stationary. Housing moves to close tips together.
•	Device under test must be inactive when connecting pincers.
Rating:	Hands free testing in controlled environment: 70 vrms max. For CE compliance: Not intended for hand-held use at voltages above 33 Vrms / 70 Vdc.
*Std Colors:	-0 Black, -2 Red.

Oscilloscope Probes and Accessories

Pomona's oscilloscope probes give you the full range you need. Designed, rated, and specified to match the bandwidth of your instrument, they provide you with full voltage read-out over the entire rated bandwidth of each probe.

Pomona
ELECTRONICS

79



Replacement Passive Oscilloscope Probes

These general purpose monolithic passive voltage probes feature high performance for greater test flexibility. Complete accessory kit included.

See selection guide below.

Monolithic Passive Oscilloscope Probes


Model#	Probe Ratio	Maximum Input Voltage CAT I ¹	System Bandwidth MHz (-3 dB)	System Rise time (ns)	Probe Input Resistance (MΩ)	Probe Input Capacitance (pF)	Compensation ⁵ Range (pF)	Readout Actuator ⁴	Cable Length
5800A	1:1	300 ²	Up to 30 ³	< 11.66 ³	1	< 57 + O-Scope	NA	No	4ft (1.2m)
6265	10:1	300	60	< 5.83	10	< 10.5	10 - 60	No	4ft (1.2m)
6266	1:1 10:1	300 ² 300	Up to 20 ³ 60	< 17.5 ³ < 5.83	1 10	< 65 + O-Scope < 11	NA 10 - 60	No	4ft (1.2m)
5795A	10:1	300	100	< 3.50	10	< 9.5	10 - 60	No	4ft (1.2m)
4550B	1:1 10:1	300 ² 300	Up to 15 ³ 100	< 23.33 ³ < 3.50	1 10	< 64 + O-Scope < 10.5	NA 10 - 60	No	4ft (1.2m)
6049A	10:1	300	150	< 2.33	10	< 10.5	10 - 30	No	4ft (1.2m)
6101A	10:1	300	150	< 2.33	10	< 10.5	10 - 30	Yes	4ft (1.2m)
SP150B	1:1 10:1	300 ² 300	Up to 15 ³ 150	< 23.33 ³ < 3.33	1 10	< 50+ O-Scope < 15	NA 10 - 60	No	4ft (1.2m)
5803A	10:1	300	200	< 1.75	10	< 10	10 - 60	No	4ft (1.2m)
5806A	1:1 10:1	300 ² 300	Up to 20 ³ 200	< 17.5 ³ < 1.75	1 10	< 77 + O-Scope < 11.5	NA 10 - 60	No	4ft (1.2m)
5827	100: 1	300	200	< 1.75	10	< 5.5	15 - 50	No	6.6ft (2.0m)
6069A	10:1	300	250	< 1.40	10	< 10	10 - 30	No	4ft (1.2m)
6102A	10:1	300	250	< 1.40	10	< 10	10 - 30	Yes	4ft (1.2m)
5809A	10:1	300	300	< 1.17	10	< 17	10 - 60	No	4ft (1.2m)
5812A	10:1	300	300	< 1.17	10	< 17	10 - 60	Yes	4ft (1.2m)

Replacement Accessory Kit: 6267

Kit includes:

Retractable Hook Tip
BNC Adapter
IC Adapter
Insulating Tip
Trimmer Tool
6in (0.15m) Ground Lead with Alligator Clip


Oscilloscope Probe Tip Adapter Model# 6443



This adapter provides an easy, fast, and reliable way to connect your oscilloscope probe to IC test adapters, test clips and grabbers using 0.025in (0.635mm) connection pins.

Pomona adapters with 0.025in (0.635mm) pins

5360 6313 6490
5790 6351 6442
6311 6352 6444
6312 6353 All "IC" test clips



- Rating:** All probes are rated 300V (DC + Peak AC), CAT I, per IEC1010-2-031. Maximum voltage allowed on the LO connection including shell and housing must not exceed 30V.
- Maximum input voltages are dependent on the oscilloscope input characteristics; take the lesser of the two specifications.
- Dependent upon oscilloscope input characteristics.
- Any oscilloscope that uses the Tektronix® style range actuator.
- For oscilloscopes with 1 MΩ input resistance.

Modular Passive Oscilloscope Probes



Featuring a new, compact, ergonomically designed probe handle, these modular general purpose passive voltage probes are ideal for use with a wide variety of oscilloscopes. They also feature a spring-loaded, pogo-pin replaceable tip. The fine tip probes are perfectly suited for probing high-density chip leads with less than 0.060in (1.52mm) spacing. Modular in design, the probe handle is capable of receiving a variety of spring-loaded and fixed tips, providing greater testing versatility. An affordable, versatile probe for many uses.


Probe sets feature probe handle, insulated adjusting tool, sprung hook, BNC adapter, 9.06in (230mm) ground lead, 0.98in (25mm) ground adapter, IC tip adapter, tip cover, rigid tip and spring-loaded tip (1 each), and complete set of instructions and specifications.

Model#	Probe Ratio	Maximum Input Voltage CAT II ¹	System Bandwidth MHz (-3 dB)	System Rise time (ns)	Probe Input Resistance (M Ω)	Probe Input Capacitance (pF)	Compensation ⁵ Range (pF)	Readout Actuator ⁴	Cable Length
6491	1:1	100 V ²	Up to 25 ³	< 14.0 ³	1	< 38 + O-Scope	NA	NA	4ft (1.2m)
6493	10:1	300 V	60	< 5.90	10	< 10	10 - 60	No	4ft (1.2m)
6494	10:1	300 V	60	< 5.90	10	< 10	10 - 60	Yes	4ft (1.2m)
6499	1:1	100 V ²	20 ³	< 17.5 ³	1	< 40 + O-Scope	NA	No	4ft (1.2m)
	10:1	300 V	60	< 5.90	10	< 10	10 - 60		
6495	10:1	300 V	100	< 3.50	10	< 10	10 - 60	No	4ft (1.2m)
6500	1:1	100 V ²	20 ³	< 14.0 ³	1	< 42 + O-Scope	NA	No	4ft (1.2m)
	10:1	300 V	100	< 3.50	10	< 10	10 - 60		
6496	10:1	300 V	350	< 1.00	10	< 12	5 - 40	No	4ft (1.2m)
6497	10:1	300 V	350	< 1.00	10	< 12	5 - 40	Yes	4ft (1.2m)
6498	100:1	1.5 kV	350	< 1.20	50	< 6	10 - 50	No	6.6ft (2.0m)
6501	10:1	300 V	350	< 1.00	10	< 12	8 - 45	No	4ft (1.2m)
6492	10:1	300 V	350	< 1.00	10	< 12	8 - 45	Yes	4ft (1.2m)

Replacement Accessory Kit: 6552

Kit includes:
Retractable Hook Tip
BNC Adapter
IC Adapter
Insulating Tip
Trimmer Tool
6in (0.15m) Ground Lead with Alligator Clip
Right-Angle Ground Lead
Spring
1 ea. Rigid Probe Tip
1 ea. Spring Probe Tip (not sold separately)


Oscilloscope Probe Tip Adapter Model# 6553



This adapter provides an easy, fast, and reliable way to connect your oscilloscope probe to IC test adapters, test clips and grabbers using 0.025in (0.635mm) connection pins.

Pomona adapters with 0.025in (0.635mm) pins

5360 6351 6442
5790 6352 6444
6311 6353 All "IC" test clips
6312 6490 6151
6313



- ¹ **Rating:** Per IEC1010-2-031. Maximum voltage allowed on the LO connection including shell and housing must not exceed 30V.
- ² Maximum input voltages are depended on the oscilloscope input characteristics; take the lesser of the two specifications.
- ³ Dependent upon oscilloscope input characteristics.
- ⁴ Any oscilloscope that uses the Tektronix[®] style range actuator.
- ⁵ For oscilloscopes with 1 M Ω input resistance.

Microline Passive Oscilloscope Probes



500 MHz x 10 Passive Voltage Probe
4ft (1.2m) cable, 500V peak.

The perfect solution for accessing hard-to-reach test points, particularly fine pitch IC leads. The Microline Probe features a 500 MHz X10 passive voltage probe compactly designed for on-the-go field service or in the lab.

Tips can be replaced with Pomona 0.60in (1.52mm) probe tips model number 6475, see page 68.


Model#	Probe Ratio	Maximum Input Voltage CAT I ¹	System Bandwidth MHz (-3 dB)	System Rise time (ns)	Probe Input Resistance (M Ω)	Probe Input Capacitance (pF)	Compensation ⁵ Range (pF)	Readout Actuator ⁴	Cable Length
6551	10: 1	500 V	500	< 0.70	10	< 10.5	8 - 20	Yes	4ft (1.2m)
6554	10: 1	500 V	500	< 0.70	10	< 10.5	8 - 20	No	4ft (1.2m)

Replacement Accessory Kit: 6552

Kit includes:

Retractable Hook Tip
BNC Adapter
IC Adapter
Insulating Tip
Trimmer Tool
6in (0.15m) Ground Lead with Alligator Clip
Right-Angle Ground Lead
Spring
1 ea. Rigid Probe Tip⁶
1 ea. Spring Probe Tip⁶
(not sold separately)


Oscilloscope Probe Tip Adapter Model# 6553



This adapter provides an easy, fast, and reliable way to connect your oscilloscope probe to IC test adapters, test clips and grabbers using 0.025in (0.635mm) connection pins.

Pomona adapters with 0.025in (0.635mm) pins

5360 6351 6442
5790 6352 6444
6311 6353 All "IC" test clips
6312 6490 6151
6313



1 **Rating:** Per IEC1010-2-031. Maximum voltage allowed on the LO connection including shell and housing must not exceed 30V.

4 Any oscilloscope that uses the Tektronix[®] style range actuator.

5 For oscilloscopes with 1 M Ω input resistance.

6 For replacement tips: Model 6475 may be ordered for Models 6551 and 6554.

RF Detector (demodulator) Probe



Model# 5815A

Model 5815 is a miniature RF Detector Probe intended for use with a wide range of oscilloscopes. This probe is very useful for measuring RF signals up to 800 MHz. It provides an output of 1 Vdc for an input of 1 Vrms sinewave.

Diode Turn-On Voltage: 200 mV.

Input Capacitance: 5 pF.

Peak AC Input: 50V.

DC Isolation Incl. Peak AC: 200V.

Cable Length: 4ft (1.2m).

1 Vdc output for input of 1 Vrms.

Bandwidth: 1 MHz - 400 MHz $\pm$ 3dB,
500 KHz - 1 MHz $\pm$ 4dB,
400 MHz - 800 MHz $\pm$ 4dB.

Rating: Maximum voltage allowed on the LO connection including shell and housing must not exceed 30V from earth ground.

Insulated Oscilloscope Probes for Portable Applications



These passive voltage oscilloscope probes provide additional safety for portable instrument users. Pomona's Insulated Probes provide insulation coverage for the entire probe including the BNC connector. A spring-loaded sheath covers the tip ground point. Compensation point in BNC end.

- Offered in two styles:
6006 Fixed Attenuation X10.
6035 Switchable Attenuation X1/X10.
- Cable length 4ft (1.2m).
- Model 6033 is a set of two 6006 Probes (one red, one gray).

Accessories Included:

Sprung Hook
Trimmer Tool
IC Tip
Insulating Tip
BNC Adapter
Replacement Tip
Ground Lead
Sheathed Banana Plug Adapter

Rating: Maximum voltage allowed on the LO connection including shell and housing must not exceed 30V from earth ground.

Replacement Accessory Kit

Model# 6034-*

* Std. Colors: -2 Red, -8 Gray

Model#	Attenuation	Bandwidth (MHz)	Resistance (M Ω) ²	Input Impedance Capacitance (pF)	Approx. Rise time (ns)	Voltage (V Max) ³	Compensation ³ Range (pF)
6006-*	X10	200	10	15	1.8	250	10-60
6033 (set)	X10	200	10	15	1.8	250	10-60
6035-*	X1/X10	20/200	1/10	47/15	17.5/1.8	250	10-60

* -2 Red, -8 Gray

1 When connected to an oscilloscope with 1 M Ω input resistance.

2 Derated with frequency.

3 For oscilloscopes with 1 M Ω input resistance.

Active Differential Probe



Pomona **Model 6731** differential voltage probe allows users to safely make floating high voltage measurements while using general purpose oscilloscopes. Using a built-in differential amplifier, the floating signal is converted and scaled to a low-voltage signal referenced to earth ground. The probe can be used on circuits associated with electronic high-power converters, motor speed controls, switching mode power supplies, and other high voltage circuits requiring isolation.

Features include switchable attenuation, high impedance to ground for both positive and negative side of the balanced input, and maximum differential voltage up to 1000V. The probe input uses shrouded banana test probe tip. The output to the oscilloscope is made with a BNC cable with a safety insulated BNC male connector.

Included with the 6731:

Large Jaw Alligator clips (one red and one black).
Pin-Grabber Test Clips (one red and one black).
9V Alkaline Battery.

Optional:

Model 6732: Universal Power Adapter.

Input Characteristics	
Input Probe	Shrouded banana test probe
Input Cable Length	60in (1.5m)
Probe Ratio	20:1 / 200:1
Voltage to Ground	600V CAT III 1000V CAT II
Maximum Input	1000 Vdc
Maximum Differential Input Voltage	1000 Vrms 1200V (DC + Peak AC)
Maximum Floating Voltage / Frequency	600V Category III /400 Hz (from shielding to ground)
Probe Input Resistance	5 M Ω (input to shielding) 10 M Ω (input to input)
Probe Input Capacitance	6 pF (input to shielding) 5 pF (input to input)
Operating Temperature	+32 to +122°F (0 to +50°C)
Output Characteristics	
Output Cable	BNC cable
Output Cable Length	20in (0.5mm)
Output Voltage Range	$\pm$ 6.5V (into 1MW)
Accuracy	$\pm$ 2.5%
Bandwidth	DC to 20 MHz (-3 dB)
Risetime	17.5 ns
CMRR	20:1 @ 60Hz =>70dB 20:1 @ 1MHz =>40 dB 200:1 @ 60Hz => 80dB 200:1 @ 1 MHz =>50dB
Power	
9V Alkaline Battery	8 hours operation. 400 hours in standby. Unit goes into standby mode after 30 minutes (battery mode only).
Model 6732 Optional Universal Power Adapter	For continuous operation


Audio/Video

Whether setting up your own home theater or looking for connectors for that next broadcast event, Pomona audio/video accessories get you connected reliably. From F connectors to phono jacks, look to Pomona for parts you can depend on.

Pomona
ELECTRONICS

83


High Definition 75Ω BNC Connectors



6702



6703



6704

Model#	For Cable
6702	RG59B/U, 20 AWG, Belden 1505A
6703	RG6B/U, 18 AWG, Belden 1694A
6704	RG59B/U, 23 AWG

Precision matched to Belden cable for digital and analog SDI/HDTV signals.

Performance: 3 GHz with VSWR of 1.15

Impedance: 75Ω.

BNC: *Shell:* precision machined tarnish resistant black nickel-plated brass; *Center Contact:* male: gold-plated brass (20 micro inches).

Dielectric: PTFE.

XLR Triple Binding Post



Model#	Type	RJ11
7288	(m)	•
7289	(f)	•
7286	(m)	—
7287	(f)	—

Adapter makes it easy to split out the signals from the three XLR audio conductors for access via 5-way binding posts. RJ11 jack also simplifies connection to phone for ring down tests of audio lines or for phone communications across audio cables. Includes three color-coded 5-way binding posts for high, low, and ground terminals. Cables can be connected to rugged binding posts via banana plug, spade lug, alligator clip, or simply fed into the through-hole or wrapped around the post.

XLR Straight Cable Connectors – Rugged



Male



Female

Model#	Type	Pins	Shell	IDC	Contacts	Lbs of Pull
5109A	(f)	3	Nickel		Silver	100
5110	(m)	3	Nickel		Silver	100
5125A	(f)	5	Nickel		Silver	45
5126A	(m)	5	Nickel		Silver	45
6852	(f)	3	Black Nickel		Gold	100
6853	(m)	3	Black Nickel		Gold	100
7273	(m)	3	Nickel	•	Silver	100
7274	(f)	3	Nickel	•	Silver	100
7275	(m)	3	Black Nickel	•	Silver	100
7276	(f)	3	Black Nickel	•	Silver	100


Passes the 100 pound stress test.

When connection failure is simply not an option, depend on Pomona XLR connectors. The patented XLR cable retention system can withstand up to 100 pounds (45.35 kg) of pull and up to 50,000 bends under stress. By securely capturing the cable, our system relieves strain from the solder joints between the cable and the connector, protecting your connections from workplace abuse.

Ratings: The components in this section have a hands free rating for use in controlled voltage environments. However, for CE compliance these products are not intended for hand held use at voltages above 33 Vrms/70 Vdc.

www.pomonaelectronics.com

BNC Male Terminator Plugs




Model#	Ω
3840-50	50
3840-75	75

Rating: Frequency Range DC to 500 MHz, Power 0.5W @ 158°F (70°C) Max.

Accuracy: 1%.

BNC Within Series Adapters



Model#	Type	Special Features
6754	BNC (f/m/f)	In-line

In-line design improves cable routing.


Performance: 3 GHz.

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, -85°F to +329°F (-65°C to +165°C).

Impedance: 75Ω.

BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Dielectric: PTFE.

F Between Series Adapters



6714




6715

Model#	Type
6714	BNC (m)/F (f)
6715	BNC (f)/F (f)
6716	F (m)/BNC (f)


BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted).

Dielectric: PTFE.



6716

F Within Series Adapters



6712


Model#	Type
6712	F (m/f) Right angle
6713	F (m/f) In line, Push-on

Material: Machined, nickel-plated brass



6713


F Bulkhead Receptacle



Model#	Type
6706	F (f/f) In line, with nut and washer

Material: Machined, nickel-plated brass.

F Connectors



6707

6708

Model#	Type	For Cable
6707	F (m)	RG6
6708	F (m)	RG59

Easy installation. Simply strip the cable and push-on the connector. No crimp tool required.

Material: Gold-plated brass.

40lb (18.1kg) minimum cable retention.

Impedance: 75Ω.

F Female PCB Mount



Model#	Type
6711	F (f) Reflow type with TFE insulator

For RG59 and RG6 cable.

True 75Ω.

Mounts and locks onto circuit board edge.

RCA Plug/RCA Plug Cable Assemblies




Model#	Plugs	Plug Color at each end
6896-180	2 RCA / 2 RCA	White / Red
6898-180	1 RCA / 1 RCA	Black
6900-180	3 RCA / 3 RCA	Red / Green / Blue
6901-180	1 RCA / 1 RCA	Yellow

Material: Center Contact: gold-plated brass.

Length: 4.6 m (15 ft).

BNC Female to Phono (RCA) Male




Model#
5319

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, 216°F (+102°C) max.

BNC: Center Contact: gold-plated.


BNC Male to Phono Jack



Model#
4054

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

BNC Female to 1/4in (6.35mm) Phone Plug




Model#
1297

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

Convert 2 conductor audio jacks to BNC.

BNC Female to Two Conductor, 0.14in (3.5mm) Dia. Mini Phone Plug




Model#
3837

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

Convert 2 conductor audio jacks to BNC.

BNC Male to 1/4in (6.35mm) Two Conductor Phone Jack

Model# 4043




Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

Convert 2 conductor phone plugs to BNC.

Phono Jack to Double Stacking Banana Plug

Model# 1442




Rating: Hands free testing in controlled voltage environment: 500 Vdc*, +122°F (+50°C) max.

Permits phono plug to be used with equipment having standard banana jacks or binding posts.

1/4in (6.35mm) Phone Plug Adapter with Binding Posts

Model# 1285




Rating: Hands free testing in controlled voltage environment: 500 Vdc*, +122°F (+50°C) max.

2 Conductor phone plug.

Cross holes fit double banana plug.

1/4in (6.35mm) Phone Jack to Double Stacking Banana Plug

Model# 4044



Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +122°F (+50°C) max.

2 conductor 0.25in (6.35mm) dia. phone jack.

True 75Ω BNC Male Cable


Model#	Length
6510-V-12-0	12in (0.3m)
6510-V-24-0	24in (0.6m)
6510-V-36-0	36in (0.9m)
6510-V-48-0	48in (1.2m)
6510-V-60-0	60in (1.5m)
6510-V-72-0	72in (1.8m)


BNC connectors are perfectly matched to 75Ω impedance for superior VSWR & return loss performance.

Ideal for digital video and telecommunication applications

Cable Type: High Flex, Multi-strand center conductor, RG59 Type, Black.

BNC Female to Two Conductor Micro Phone Plug

Model# 4267




Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

Permits BNC male to be used with equipment having micro jacks.


Phono plug cables are available see page 14.

Wall/Floor Mount Female XLR Receptacle

Model#	Sockets
5113A	3


Wall/Floor Mount Male XLR Receptacle

Model#	Pins
5117A	3


Rugged XLR Plug to XLR Jack Audio Cable


Model#	Length
6902-120	3.0 m (10 ft)
6902-180	4.6 m (15 ft)
6902-240	6.1 m (20 ft)
6902-300	7.6 m (25 ft)

Rugged audio cables constructed with Belden 1172A Starquad cable includes a 3-pin rugged XLR male connector and a 3 contact rugged XLR female connector. Constructed to withstand 45.35 kg (100 lbs) of pull and up to 50,000 bends under stress.

Material: *Shell:* precision machined tarnish resistant black nickel-plated brass; *Center Contact:* male: gold-plated brass (20 micro inches); female: gold-plated heat treated beryllium copper.

6869 XLR Plug to XLR Jack Low Noise Cable Assembly


Model#	Length
6869-180	4.6 m (15 ft)
6869-300	7.6 m (25 ft)

Low noise audio cable includes a 3-pin XLR male connector and a 3 contact XLR female connector.

Pull: 45.35 kg (100 lbs).

Material: *Shell:* tarnish resistant black nickel-plated brass; *Center Contact:* gold-plated brass.

Automotive

Offering a variety of test accessories designed specifically for the automotive environment, Pomona simplifies automotive diagnostics. Pomona automotive accessories give you access to wiring or cables in congested engine compartments, under-dash wiring harnesses, and other generally hard-to-reach places.

Insulation Piercing Clip Sets

Model#	Features	Colors
6405	Attach to test leads	Set of red/black
6413	Attach to 0.080in (2.03mm) Probe tip	Set of red/black
6580-12	12in (304.8mm) long	-0 blk, -2 red
6580-24	24in (609.6mm)	-0 blk, -2 red



- Double V block centers wire.
- 6405, 6413: set of 2, (red and black jacks).
- Bright yellow for easy location.
- Attach to test leads.

Insulation Piercing Maxigrabber[®] Test Clip Set

Model# 5913



- Insulated probe for hard to reach test points.
- Set of 2, red and black.

Test Lead Rack

Model# 4408M



- Magnetic, attach to tool box or other steel cabinet.
- Neat storage for leads.
- Easy access.

Basic Backprobe Pins


Model# 6411



- Make connection to terminals inside connectors up to 1in (25.40mm) deep.
- For low voltage use < 30V.
- Pkg of 10.

Rigid Backprobe Pin

Model# 6544-02



- Sharp point to pierce insulation or weather boot up to 2in (50.8mm) deep.
- For low voltage use < 30V.
- Set of 2 (red + black).
- Fits comfort-grip style and modular probes 6232A and 6479.

Shielded Test Lead Set


Model# 6480



- Stacking double banana plug mates with instrument interface.
- 12in silicone leads connect to test probes or clips (See page 64).
- Silicone leads resist high temperatures.
- Shielded 4ft (1.22m) cable is stiff enough to keep away from moving parts.

Test Connector Adapter Set

Model# 6481



- Full set of pin and socket adapters
- 18 piece set includes one black and red pin and socket of each size.
- Contact sizes: 0.03in (0.75mm), 0.04in (1mm), 0.06in (1.5mm), 0.10in (2.5mm).
- Includes Silicone insulated 4ft (1.22m) leads to fit most DMMs from Fluke, Amprobe, Greenlee and others.

Coaxial Lead Set Lead Set

Model# 6534



- Complete set of coaxial leads.
- Molded strain relief.
- Seven piece set from 1 to 10ft (0.3 to 3.05m).
- Standard BNC connectors fit oscilloscopes and other instruments.


IC Test Clips and Adapters

Innovative solutions. Pomona Electronics' IC Test Clips – designed for your chip. Uniquely designed for testing surface mount devices – easily, securely and successfully. Low-profile fine-pitch chips, densely populated boards, or vertical boards, POMONA test clips connect you with confidence.



Pomona
ELECTRONICS

87

Pomona® JEDEC IC Test Clip Features




How to Measure or Calculate the Critical Dimension for Your QFP Test Clip



Test Clip Selection Made Easy


To select the Pomona IC Test Clip specifically designed for your chip, find the table for your chip type and follow the selection procedure outlined in this section.



JEDEC QFP

To find your JEDEC QFP test clip, turn to the JEDEC QFP table on page 88 and reference the following characteristics of your target chip:


1. Number Of Leads
2. Body Size



SSOP/QSOP

To find your SSOP/QSOP test clip, turn to the SSOP/QSOP table on page 80 and reference the following characteristics of your target chip:


1. Lead Pitch and Body Size
2. Number Of Leads
3. Locking Feature (see Fig. 1, 2 & 3, page 88)



Metric QFP

To find your Metric (EIAJ) QFP test clip, turn to the Metric QFP table on page 89 and reference the following characteristics of your target device:


1. Number of leads
2. Body size
3. Lead pitch
4. Critical dim. (See below)



PLCC

To find your PLCC Quad Clip® test adapter, turn to the PLCC table on page 89 and reference the following characteristics of your target chip:


1. Number Of Leads
2. Body Size



DIP

To find your DIP test clip, turn to the DIP table on page 82 and reference the following characteristics of your target chip:

1. Number Of Leads
2. Test Clip Contact Style (see Fig. 1 & 2, page 90)



SOIC/SOJ

To find your SOIC Clip® test clip, turn to the SOIC/SOJ table on page 82 and reference the following characteristics of your target chip:

1. Number Of Leads
2. Confirm Body Width Compatibility
3. For Lower and Top Test Clip Width (see Fig. 1, 2 & 3, page 90)

JEDEC PQFP Test Clips




Fig. 1




Fig. 2

Model#	No. Leads	Body Size	Typical Applications	Fig.
5713	100	0.75in X 0.75in (19.05mm x 19.05mm)	Intel 80C186EC, 80386SX,	1
5777			AMD 29205, 386EM, 386SXLP	2

Pomona's JEDEC QFP test clips are designed to fit on surface-mounted plastic and ceramic JEDEC chips. Choose from two clip types designed to give you optimum functionality and ease of use for testing, troubleshooting and custom-design evaluation with logic analyzers and oscilloscopes.

Lead Pitch: 0.025in (0.635mm).

Fig. 1: The basic JEDEC QFP test clip is designed for use on densely-populated boards where space is at a minimum. Leads at the top of the clip are 0.022in x 0.012in (0.56mm x 0.30mm) and are spaced 0.075in (1.9mm) apart.

Fig. 2: Pomona's most popular JEDEC QFP test clip features a large board with 0.025in (0.635mm) pins at 0.100in x 0.100in (2.54mm x 2.54mm) spacing for easy connection to logic analyzers and oscilloscopes. The board is elevated to avoid other board components near the target chip.

SSOP/QSOP Test Clips




Fig. 1



Fig. 2




Fig. 3

Model#	No. Leads	Lead Pattern	Body Size	Lead Pitch	Pkg. Type	Typical Applications	Fig.
5969	20	10+10	0.21in	0.026in	SSOP	TI SN74ABT245, IDT 74FCT244,	1
5969A			(5.3mm)	(0.65mm)		Maxim MAX153	2
5972	24	12+12	0.21in	0.026in	SSOP	IDT 74FCT244TPY, Phillips 80C751, MAXIM MAX120, MAX153	1
5893	48	24+24	0.3in	0.025in	SSOP	TI ABT16244, ACT16245	3
			(7.62mm)	(0.65mm)			
5894	56	28+28	0.3in	0.025in	SSOP	IDT FCT16223, FCT162511	3
			(7.62mm)	(0.635mm)			

With Pomona's SSOP and QSOP test clips, technicians can now access all of the leads on popular low-profile, fine-pitch SSOP and QSOP chips. Each clip has 0.025in (0.635mm) sq. pins at 0.100in x 0.100in (2.54mm x 2.54mm) spacing to allow connections with jumpers or Pomona's flying leads.

Fig. 1: Clip is located and held with a cantilevered plastic guide that holds the ends of the chip under test. Ideal for densely-populated boards, this clip can attach onto a chip that is spaced only 0.050 (1.27mm) away from an adjacent board component.

Fig. 2: Clip features spring-loaded fingers to attach easily and hold firmly onto the ends of the chip. Clip fingers are opened by finger pressure on the upper handles. A clearance of 0.125in (3.17mm) is required at the ends of the chip under test.

Fig. 3: Clip features spring-loaded contact housings that clamp onto the side of the chip body. Gold-plated contacts are individually cantilevered to maintain positive connections. User interface provides 0.025 (0.635mm) sq. pins at 0.10 (2.54mm) centers.

Lead Pitch: 0.025in (0.635mm).

Pomona offers a wide variety of Micro-SMD Grabber® Test Clips for use in testing fine pitch PQFP devices. See SMD/Micro Format Test section for complete selection.



Metric QFP Test Clips



Fig. 1: Press-on clip




Fig. 2: PGA interface*




Fig. 3: Clip with locking fingers*





Fig. 4: Clip with internal locking feature

Model#	No. Leads	Body Size	Lead Pitch	Max. Height	Critical Dim.†	Typical Applications	Fig.	
5961	44	0.39in x 0.39in (10mm x 10mm)	0.03in (0.80mm)	0.13in (3.4mm)	0.48in (12.3mm)	Motorola 68HC11	1	
5961-2					0.46in (11.6mm)	NEC µPD71054, Altera EPM70320C44	1	
5888	64	0.55in x 0.55in (14mm x 14mm)	0.03in (0.80mm)	0.13in (3.4mm)	0.64in (16.3mm)	Intel 82078, Phylon PHY1002	1	
5888-2					0.61in (15.6mm)	Motorola 68HC05, Hitachi H8/3714	1	
5751L	80	0.55in x 0.79in (14mm x 20mm)	0.03in (0.80mm)	0.13in (3.4mm)	0.64in x 0.88in (16.3mm x 22.3mm)	Intel 80C186XL, Cirrus Logic CL-SH260, Adaptec AIC-6360Q	1 4	
5751L-2						0.61in x 0.85 (15.6mm x 21.6mm)	AMD 80C186, AMD S80L188, Phillips 9XC1X0, AMD S80L186	4
5643	100	0.55in x 0.79in (14mm x 20mm)	0.26in (0.65mm)	0.13in (3.4mm)	0.64in x 0.88in (16.3mm x 22.3mm)	Motorola 68EC020F, AT&T 3042, Fujitsu MB86600	1 4	
5643L						0.61in x 0.85in (15.6mm x 21.6mm)	Altera EPM5130, Cirrus Logic CL-SH3620, Xilinx XC4003, Xilinx XC3042	4
5643L-2								
6150		0.55in x 0.55in (14mm x 14mm)	0.02in (0.50mm)	0.06in (1.4mm)	0.59in (15.0mm)	TI TMS320C52	3	
5868L	112	0.79in x 0.79in (20mm x 20mm)	0.26in (0.65mm)	0.13in (3.4mm)	0.83in (21.0mm)	Hitachi H8 / 510, H8 / 570, SH 7032	3	
5868L-2						0.85in (21.7mm)	Motorola DSP56156	3
5773-2	144	1.10in x 1.10in (28mm x 28mm)	0.26in (0.65mm)	0.13in (3.4mm)	1.17in (29.6mm)	Siemens SAB-C167, SGST STLC5444	1	
6151		0.79in x 0.79in (20mm x 20mm)	0.02in (0.50mm)	0.06in (1.4mm)	0.83in (21.0mm)	Motorola 68302	3	
5645L	160	1.10in x 1.10in (28mm x 28mm)	0.26in (0.65mm)	0.13in (3.4mm)	1.19in (30.3mm)	Actel A1280, Emulex FAS256	4	
5645L-2							Motorola MPC403	4
6152	176	0.94in x 0.94in (24mm x 24mm)	0.02in (0.50mm)	0.06in (1.4mm)	0.98in (25.0mm)	Intel 486SX	3	
5770	208	1.10in x 1.10in (28mm x 28mm)	0.02in (0.50mm)	0.13in (3.4mm)	1.17in (29.6mm)	Intel 80486DX2E, Motorola MC68HC05,	1	
5770L							Actel A1480, Altera EPF8636, EPF8820	4
5770-2					1.16in (29.3mm)	Most Ceramic + Metal Packages	3&4	
5998A	240	1.26in x 1.26in (32mm x 32mm)	0.02in (0.50mm)	0.16in (4.0mm)	1.33in (33.8mm)	Motorola XC68360 Ceramic	2	
5998AL						Analog Devices ADSP-21060, LSI L1A7747, Altera EPF81188	2 3	
						Xilinx XC4025-MQ240	2&3	

* Includes male to male adapter pins

† For instructions on calculating the critical dimension, see page 79.


PLCC Test Clips



Pomona's low-cost Quad Clip® test clips quickly lock onto J-leaded PLCCs, providing easy access for testing surface-mounted devices. PLCC test clips attach to PLCC chips with a sliding cam that clamps onto the chip body. Access to chip leads is provided by 0.025in (0.635mm) pins at 0.100in (2.54mm) spacing. Pomona offers a Quad Clip® test clip to fit all currently available PLCC chip sizes.


Lead Pitch: 0.050in (1.27mm)

	X Min.	Y Min.
Single Testing	0.120in (3.1mm)	0.110in (2.8mm)
Adjacent Testing	0.325 (8.3mm)	0.285 (7.2mm)



Model#	No. Leads	Lead Pattern	Body Size	Typical Applications
5279	20	5 X 5	0.36in X 0.36in (9.14mm x 9.14mm)	Intel 85C220
5280	28	7 X 7	0.46in X 0.46in (11.68mm x 11.68mm)	Intel 5C60, 85C224, Philips 8XC751, Raytheon TMC1173
5733	32	7 X 9	0.46in X 0.56in (11.68mm x 14.22mm)	AMD 29F040, Xicor X28TC256, Cypress CY7B991
5281	44	11 X 11	0.63in X 0.63in (16.00mm x 16.00mm)	AMD MACH110, 80C88, Seimens SAB-C501
5312	52	13 X 13	0.75in X 0.75in (19.05mm x 19.05mm)	Intel 87C196, 87C196, Motorola 68008
5401	68	17 X 17	0.95in X 0.95in (24.13mm x 24.13mm)	Intel 80C188, AMD MACH220, Hitachi H8/330
5402	84	21 X 21	1.15in X 1.15in (29.21mm x 29.21mm)	AMD MACH130, Altera EPF8452, Cirrus Logic CLi6005
5515A	20-84			PLCC Clip Kit containing 1 of each size PLCC Clip

PLCC Pin Breakout



Use these test adapters to test socket mounted PLCC's. The PLCC test adapter is placed between the socket and the PLCC, 0.025in (0.635mm) square pins at 0.10in (2.54mm) spacing allow easy access testing for all leads of the PLCC. An overlay template provides easy pin identification.

Lead Pitch: 0.100in (2.54mm).

Model#	No. Leads
5451	28
5878	32
5452	44
5453	52
5454	68

DIP Test Clips



Fig. 1



Fig. 2

Oxide Penetrating Dip Clips (Fig. 1)

No. of Model#	Pins
5692	16

Model#	No. Leads	Chip Width	Contact Style	Contact Material	Typical Applications	Fig.
5108	8	0.3in (7.62mm)	Closed	Gold Plate		1
5208	8	0.3in (7.62mm)	Open	Gold Plate		2
5014	14	0.3in (7.62mm)	Closed	Nickel Silver		1
5214	14	0.3in (7.62mm)	Closed	Gold Plate		1
5114	14	0.3in (7.62mm)	Open	Nickel Silver		2
5314	14	0.3in (7.62mm)	Open	Gold Plate	Motorola 68HC11	2
3916A	16	0.3in (7.62mm)	Closed	Nickel Silver	Analog Devices AD7715	1
5116	16	0.3in (7.62mm)	Closed	Gold Plate		1
4236A	16	0.3in (7.62mm)	Open	Nickel Silver		2
5216	16	0.3in (7.62mm)	Open	Gold Plate		2
5120	20	0.3in (7.62mm)	Closed	Gold Plate	Intel 85C220	1
5220	20	0.3in (7.62mm)	Open	Gold Plate		2
4124A	24	0.6in (15.24mm)	Closed	Nickel Silver	Intel 85C224, 85C22C10	1
5124	24	0.6in (15.24mm)	Closed	Gold Plate	Mitsubishi M66251	1
4324A	24	0.6in (15.24mm)	Open	Nickel Silver		2
5224	24	0.6in (15.24mm)	Open	Gold Plate		2
4140A	40	0.6in (15.24mm)	Closed	Nickel Silver	Dallas DS80C320, Goldstar GM82V765B1, Phillips 87C575	1
4340A	40	0.6in (15.24mm)	Open	Nickel Silver		2
5240	40	0.6in (15.24mm)	Open	Gold Plate		2

Pomona DIP Test Clips provide fast, reliable and secure connections to socketed and through-hole DIP chips. Available in two styles, DIP Test Clips give you the option of full coverage of clip contacts for maximum durability or open contacts at the board level for easier access to chip leads.

Fig. 1: Spring-actuated clip features gold-plated beryllium copper or spring-tempered nickel silver pins to assure positive contact in a firm wiping action for hands-free testing.

Fig. 2: Clip features same construction as Figure 1 except for an opening on the outside of the contact housing to permit probing while the clip is attached to the DIP.

SOIC/SOJ Test Clips



Fig. 1



Fig. 2



Fig. 3

SOIC Clip® test clips feature a narrow-profile design that makes testing SOIC and SOJ chips on densely-populated boards easier and safer.

Fig. 1: Spring-loaded SOIC Clip® attaches to target chip and holds on with spring pressure against the chip body. Contacts on top of the clip are 0.025in (0.635mm) pins at 0.10in (2.54mm) spacing. Designed to attach to surface-mounted chips with either gull wing or "J" leads.

Fig. 2: This 14-pin clip features a slider that presses the contact housings against the chip and provides a more secure connection

on surface mounted chips with gull wing or "J" leads. Compact design is ideal for testing on densely-populated boards.

Fig. 3: New 32-, 40- & 44-pin SOIC/SOJ test clip is a new design of the spring-loaded clip that features double-row .025 wire wrap pins for easy connection to ribbon cable. This clip will fit all SOIC/SOJ chips between 0.30in (7.62mm) and 0.60in (15.24mm) width.

Lead Pitch: 0.050in (1.27mm).

Model#	No. Leads	Lower Width (A)	Body Widths	Top Width (B)	Typical Applications	Fig.
5250	8	0.26in (6.60mm)	0.15in to 0.3in (3.81mm to 7.62mm)	0.430in (10.92mm)	Analog Devices AD834JR, Triquint TQ9122N	1
5251	14	0.410 (10.41mm)	0.15in to 0.3in (3.81mm to 7.62mm)	0.755in (19.18mm)	Motorola HCT08A, Philips 74HC125	1
5413	14	0.410 (10.41mm)	0.15in (3.81mm)	0.520in (13.20mm)	Harris HFSP43280, Goldstar GM76C256	2
5252	16	0.460 (11.68mm)	0.15in to 0.3in (3.81mm to 7.62mm)	0.830in (21.08mm)	Maxim MAX791, Microlinear ML6509, AMD 26LS31	1
5253	20	0.560 (14.22mm)	0.15in to 0.3in (3.81mm to 7.62mm)	1.030in (26.16mm)	Linear Tech. LT1130, Maxim MX7226, Motorola HCT373A	1
5254	24	0.660 (16.76mm)	0.15in to 0.3in (3.81mm to 7.62mm)	1.230in (31.24mm)	Altera EP610APC, Linear Tech. LT1130, Motorola MC22V10S	1
5437	28	0.760 (19.30mm)	0.15in to 0.3in (3.81mm to 7.62mm)	1.430in (36.32mm)	Texas Inst. SN74F32D, Altera EPM5032, Raytheon TMC1171	1
6107	32	0.870 (22.10mm)	0.30in to 0.60in (7.62mm to 15.24mm)	0.870in (22.10mm)	Toshiba TMPN3120, Hitachi HM628128, NEC D431000AGW	3
6108	40	1.070 (27.18mm)	0.30in to 0.60in (7.62mm to 15.24mm)	1.070in (27.18mm)	—	3
6109	44	1.170 (29.72mm)	0.30in to 0.60in (7.62mm to 15.24mm)	1.170in (29.72mm)	—	3
5514					SOIC Clip® Test Kit contains 1 each 8 - 28 pin clips	

Static Control Products

Working with static sensitive devices? Pomona enables you to work with confidence when using our static control accessories. Whether you choose to purchase our selection of grounding systems or build your own ESD set-up, Pomona gives you a variety of individual accessories. Our accessories also make a perfect addition to our Test Companion Kits.

Pomona
ELECTRONICS

91

Large Service Kit

Model# 6088



Provides a larger working area than Model 6087. This kit provides a static-safe 24in x 24in (609.6mm x 609.6mm) laminated red vinyl mat. The mat includes a 10mm snap socket and two 8in x 11in (203.2mm x 279.4mm) pockets. Carry those often used tools right with the mat. A common point ground connector with two Banana Plug Jacks and a 15ft (4.5m) ground lead. An adjustable elastic wrist strap and a resistive coil cord complete the kit. Folds down to fit into your tool box.

Adjustable Elastic Wrist Strap Kit

Model# 6082



A complete wrist strap kit features adjustable elastic wrist strap. Also included: Resistive Coil Cord (1M Ω resistor molded in) extendable to 6ft (1.8m) with a Straight Banana Plug and Alligator Clip.

Field Service Kit

Model# 6087



A complete and durable service kit for static sensitive work. Features a static-safe 18in x 22in (460mm x 558.8mm) laminated red vinyl mat. The kit includes a mat with two 0.39in (10mm) snap sockets, common point ground connector with two Banana Plug Jacks and a 15ft (4.5m) ground lead, an adjustable elastic wrist strap and a resistive coil cord. Folds down to fit into your tool kit.

Model# 6088 and 6087

Mat Color: Red.

Thickness: 0.018in (0.46mm).

Surface Resistivity: 108 to 109 Ω / Sq.

Volume Resistivity: 109 Ω cm.

Static Decay: 0.01sec 5000V to 0V
12%RH.

Wrist Strap Tester

Model# 6086



Test any wrist strap connected to utility ground with a simple touch. The tester has two Banana Plug Sockets for Wrist Strap cord attachments. Once connected, the user simply touches the unit and a green light and audible sound indicate a proper ground. (Audible indicator has selectable on or off).

The tester can be mounted near your work area with Velcro® strips (supplied) or, using an integral button 10mm snap stud, attached directly to your static-safe work mat. Powered by a 120 VAC wall adapter (supplied), the tester has a "Power on" indicator. It is practical for both a quick test or as a continuous ground point connection. UL listed.

Touch Type On-Demand Tester and Common Point Ground.

Adjustable Metal Wrist Strap Kit

Model# 6084



Complete wrist strap kit features the adjustable metal wrist strap. Also included: Resistive Coil Cord (1M Ω resistor molded in) extendable to 6ft (1.8m) with a Straight Banana Plug and Alligator Clip.

Wrist Straps



NEW
Sizes

Model#	Circumference – Min.
6083 Adjustable	5.5in (139mm) 13in (330.2mm)
5528 Large Expand	7.3in (185mm) 13in (330.2mm)
5529 Medium Expand	6.5in (165mm) 12in (304mm)

Made of non-allergenic stainless steel, each link has a 0.08in (2mm) PVF film laminated on top for electrical insulation. Quick and easy adjustment without tools, the wrist strap will fit most users. A standard 0.16in (4mm) snap stud allows attachment to resistive coil cords.

Material: Band: Stainless steel / PVF Insulation.

Cover: Thermoplastic.

Wrist Circumference: 5.5in to 13.0in
(139.7mm x 330.2mm).

Width: 0.63in (16.0mm).

Ring Terminal

NEW

Model# 5531

Attach this terminal to table or cabinet to create a banana jack for grounding wrist strap. Screw hole accepts up to #10 screw.



Stacking Snap Banana Jack

NEW

Model# 5532

Attach this jack to either banana snap stud (male) or banana snap socket (female). It allows multiple attachment to the same grounding point. Snap is 3/8in (9.52mm).

Material: High conductivity copper with tin plated finish.



Antistatic Ground Cord

NEW

Model# 5534

These patch cords feature a molded-in 1 Megohm resistor at the snap end. The 5534 has a straight banana plug, the 6085 has a right angle plug. Nominal extended length is 72in (183cm).



Antistatic Ground Cord with RT ANG B-Plug

NEW

Model# 6085

These patch cords feature a molded-in 1 Megohm resistor at the snap end. The 5534 has a straight banana plug, the 6085 has a right angle plug. Nominal extended length is 72in (183cm).



Adjustable Elastic Wrist Strap

NEW

Model# 6081

An adjustable, one size fits all, wrist strap. The wristband features a dual stainless steel cam that securely locks the plastic band, but allows easy adjustment without tools. The washable fabric band has silver impregnated nylon threads knitted into its inner surfaces. Only non-allergenic stainless steel and silver touch the skin. Standard 4mm snap stud allows attachment to resistive coil cords (Pomona models 5534 and 6085). Wrist circumference: 2.5in (64mm) to 13in (330mm). (183cm).



Telecom Products

Accuracy and repeatability – Pomona connects to the telecom industry with an impressive selection of test accessories. Ideal for network testing, troubleshooting, leave-in-the-line patching, or system prototyping, Pomona Electronics' traditional reliability adds up to the quality connection telecom professionals demand.



Universal DSX-3 Test Kit

Model# 6568



- Ideal for OSP/CO technicians.
- Kit reduces the need for multiple cables to service and test DSX-3 panels.
- Adapters quickly convert BNC cables to Mini or Standard WECO interfaces.
- Cables are color coded blue (transmit) and red (receive) for ease of testing.
- Strain reliefs are molded directly to the cable and BNC plugs for added pull strength.
- Test Companion pouch allows for convenient accessory storage.

Kit includes:

One blue BNC Male Cable Assembly
One red BNC Male Cable Assembly
Four Standard WECO to BNC Adapters
Four Mini-WECO to BNC Adapters
Test Companion Shoulder Pack

True 75Ω BNC Male Cable



Model#	Length
6510-V-12-0	12in (0.3m)
6510-V-24-0	24in (0.6m)
6510-V-36-0	36in (0.9m)
6510-V-48-0	48in (1.2m)
6510-V-60-0	60in (1.5m)
6510-V-72-0	72in (1.8m)

BNC connectors are perfectly matched to 75Ω impedance for superior VSWR & return loss performance.

Ideal for digital video and telecommunication applications.

Cable Type: High Flex, Multi-strand center conductor, RG59 Type, Black.

True 75Ω BNC Cable (Transmit/Receive)



Model#	Length	Color
6510-V-72-2	72in (1.8m)	Red
6510-V-72-6	72in (1.8m)	Blue

Cable and Strain Relief are color coded red and blue for easy identification of transmit and receive lines.

Cable Type: High Flex, Multi-strand center conductor, RG59 Type.

BNC Male to Bantam Plug Cable



Model#	Length
6517-96	96in (2.4m)

Cable Type: RG59 Type.

Bantam: Nickel-plated brass.

**BNC Female to WE309/
WE310 Plug Adapters**



Model#	Plug Type
2798	WE310
1794	WE309

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°) max.

**BNC Female to Bantam
Plug Adapters**



Model# 4719

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°) max.

Convert Bantam style jacks to BNC.

**75Ω BNC Male to Mini-WECO
Connector Cable**



Model#	Length
6515-96	96in (2.4m)

Cable Type: RG59 Type.

**75Ω BNC Male to Standard
WECO Connector Cable**



Model#	Length
6516-96	96in (2.4m)

Cable Type: RG59 Type.

**BNC Female to Mini/Standard
TO WECO Plug Adapters**



Model#	Plug Type
6519	Mini WECO
5008	Std. WECO

Permits BNC male to be used with equipment having Std. WECO or Mini WECO plugs.

Rating: Hands free testing in controlled environment: 500 Vrms*, +216°F (+102°C) max.

Mini-WECO Plug Patch Cord



Model#	Length
6502-96	96in (2.4m)

Cable Type: RG59 Type.

Bantam Plug Patch Cord



Model#	Length
4279-12	12in (0.3m)
4279-24	24in (0.6m)
4279-36	36in (0.9m)
4279-48	48in (1.2m)
4279-60	60in (1.5m)
4279-72	72in (1.8m)
4279-96	96in (2.4m)
4279-120	120in (3.0m)

Model#	Length
4279N-24	24in (0.6m)
4279N-36	36in (0.9m)
4279N-60	60in (1.5m)

Bantam Plug:

4279: Unplated brass.

4279N: Nickel-plated brass.

Rating: Hands free testing in controlled environment: 300 Vrms*, +122°F (+50°C) max.

Cable Type: 2 Conductor Shielded Twisted Pair, 0.180in (4.57mm) O.D.

Bantam Plug to Two Alligator Clips


Model#	Length
5026-36	36in (0.9m)
5026-60	60in (1.5m)

Model#	Length
5026N-60	60in (1.5m)

Bantam Plug:
 5026: Unplated brass.
 5026N: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 150 Vrms*, +122°F (+50°C) max.
Cable Type: 2 Conductor Shielded Microphone, 0.180in (4.57) O.D.

Bantam Plug to Three Alligator Clips


Model#	Length
6321-96	96in (2.4m)

Bantam Plug: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 150Vrms*.
Cable Type: 2 Conductor Shielded Twisted Pair.

Bantam Plug to Minigrabber® Test Clips


Model#	Length
5019-60	60in (1.5m)

Model#	Length
5019N-60	60in (1.5m)

Bantam Plug:
 5019: Unplated brass.
 5019N: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms*, +122°F (+50°C) max.
Cable Type: 2 Conductor Shielded cable, 0.180in (4.57) O.D.

Bantam Plug to Micrograbber® Test Clips


Model#	Length
4778-60	60in (1.5m)

Bantam Plug: Unplated brass.
Rating: Hands free testing in controlled environment: 150 Vrms*, +122°F (+50°C) max.
Cable Type: 2 Conductor Shielded cable, 0.180in (4.57mm) O.D.

Bantam Plug to Double Banana Plug


Model#	Length
6523-96	96in (2.4m)

Bantam Plug: Nickel-plated brass.
Cable Type: RG59 Type.

Bantam Plug to Double Banana Plug, Balanced Line


Model#	Length
4281-60	60in (1.5m)

Bantam Plug: Unplated brass.
Rating: Hands free testing in controlled environment: 500V Peak*, +131°F (+55°C) max.
Cable Type: 2 Conductor Shielded Microphone, 0.180in (4.57mm) O.D.

Bantam Plug to RJ11 Connector Cable



Model#	Length
6323-96	96in (2.4m)

Bantam Plug: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms.
Cable Type: 2 Conductor Shielded Twisted Pair.
Pin out: 3-Ring, 4-Tip

Bantam Plug to RJ48/RJ45 Connector Cable



Model#	Length
6324-96	96in (2.4m)

Bantam Plug: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms*.
Cable Type: 2 Conductor Shielded Twisted Pair.
Pin Out: 4-Ring, 5-Tip.

Two Single Bantam Plugs To RJ48/RJ45 Connectors



Model#	Length
6320-96	96in (2.4m)

Bantam Plug: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms*.
Cable Type: 2 and 4 Conductor Shielded Twisted Pair. Bantam "Y" (Tx and Rx) to RJ48 modular plug.
Pin out: 1-Ring, 2-Tip, 4-Ring, 5-Tip.

Bantam Plug to WE310 Plug Patch Cable



Model#	Length
4280-36	36in (0.9m)
4280-48	48in (1.2m)
4280-60	60in (1.5m)
4280-96	96in (2.4m)
4280N-48	48in (1.2m)
4280N-60	60in (1.5m)

WE310 and Bantam Plugs:
 4280: Unplated brass.
 4280N: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms*, +122°F (+50°C) max.
Cable Type: 2 Conductor Shielded Twisted Pair, 0.180in (4.57mm) O.D.

Bantam (Female) to WE310 Plug Adapter



Model#	Plating
4993	Unplated
6315	Nickel

Plug Body: Brass.
 3 Conductor adapter. Converts bantam cable into a WE310 plug-end patch cable.


Dual Bantam Plug Patch Cable



Model#	Length
6331-96	96in (2.4m)

Bantam Plugs: Nickel-plated brass.
Rating: Hands free testing in controlled environment: 300 Vrms*.
Cable Type: 4 Conductor Shielded Twisted Pair.

Bantam or WE310 Plug to Binding Post



Model#	Plug Type
2112	WE310
5001	Bantam

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.
 Adapts Bantam or WE310 style equipment to binding posts and double banana plugs.

WE310 Plug to Double Banana Plug Cable



Model#	Length
6524-96	96in (2.4m)

Cable Type: RG59.

WE310 Plug to Two Alligator Clips

Model#	Length
3352-A-36	36in (0.9m)
3352-A-60	60in (1.5m)
3352-A-84	84in (2.1m)


WE310 Plug:

3352: Unplated brass.

3352N: Nickel-plated brass.

Rating: Hands free testing in controlled environment: 150 Vrms*, +122°F (+50°C) max.

Cable Type: 2 Conductor Twisted Pair, 0.250in (6.35mm) O.D.

Piercing Clips to Sheathed Banana Test Leads

Model#	Clip Type	Length
6483-48-*	Bed of Nails and Single Needle	48in (1.2m)
6485-48-*	Bed of Nails	48in (1.2m)



Pierces 19 to 26 AWG Wire.

Wire: 18 AWG Silicone Test Lead Wire.

For use with DMM's from Fluke, Wavetek (Meterman), Amprobe, Greenlee and others.

***Colors:** -0 Black, -2 Red, -02 includes both Black and Red.

WE310 Plug to Minigrabber® Test Clips

Model#	Length
4812-J-60	60in (1.5m)


WE310 Plug: Unplated brass.

Rating: Hands free testing in controlled environment: 300 Vrms*, +122°F (+50°C) max.


Cable Type: 2 Conductor Shielded Twisted Pair.

Piercing Clip Styles for Test Leads and Patch Cords
Bed of Nails/Single Needle

Small wire and single penetration of heavier wire.

Bed of Nails

Small wire penetration.


Two Single WE310 Plugs to RJ48/RJ45 Plug

Model#	Length
6316-96	96in (2.4m)


WE310 Plugs: Nickel-plated brass.

Rating: Hands free testing in controlled environment: 300 Vrms*.

Cable Type: 2 and 4 Conductor Shielded Twisted Pair.

310 "Y" (Tx and Rx) to RJ48 modular plug.

Pin out: 1-2-4-5 (4 Conductor), 4-5 (2 Conductor).

Piercing Clips to Bantam Plugs Patch Cord

Model#	Clip Type	Length
6484-60	Bed of Nails and Single Needle	60in (1.52m)
6486-60	Bed of Nails	60in (1.52m)


Cable: Two Conductor Twisted Pair.

Breakout Wire: 18 AWG.

66 Block Adapter to Alligator Clip

Model#	Length
6336-96	96in (2.4m)


Rating: 300 Vrms.

284-1 plug connects to punch down pins on 66 blocks and RJ21's.

Wire: 18 AWG, silicone insulation.


BNC Female to WE310 Phone Plug

Model# 2798

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.




BNC Female to Mini-WECO Plug Adapter

Model# 6519

Rating: Hands free testing in controlled environment: 500V Peak*, +216°F (+102°C) max.

Permits BNC male to be used with equipment having mini-WECO jacks. Video plug equivalent to WE-090.



BNC Female to Bantam Phone Plug

Model# 4719

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.

Convert Bantam style jacks to BNC.




BNC Female to Standard WECO Plug Adapter

Model# 5008

Rating: Hands free testing in controlled environment: 500V Peak*, +216°F (+102°C) max.


Permits BNC male to be used with equipment having standard WECO jacks. Video plug equivalent to WE-090.



Bantam Phone Jack to WE310 Phone Plug

Model# 4993


Rating: Hands free testing in controlled environment: 500V Peak*. Use cords with Bantam style plugs on equipment with WE-310 jacks.



BNC Female to WE309 Phone Plug

Model# 1794

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.




Stackable Binding Posts to Bantam Phone Plug

Model# 5001

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.


Adapts Bantam style equipment to binding posts and double banana plugs.



Stackable Binding Posts to WE310 Phone Plug

Model# 2112

Rating: Hands free testing in controlled environment: 500V Peak*, +122°F (+50°C) max.



Temperature Probes


Pomona connects you to quality temperature readings with a versatile selection of interchangeable J, and K-Type thermocouple probes designed to fit a variety of applications.

All of these probes are compatible with K-type digital thermometers or DMM's with a temperature function.

Pomona
ELECTRONICS

99

General Purpose Temperature Probe with Round Tip



Model#	Calibration
6367	K-Type

General purpose probe for gas, air, gel and liquid measurements.

Measurement Range: -40 to 500°F (-40 to 260°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Probe Length: 6in (152.4mm); O.D. 0.125in (3.18mm).

Cable Length: 48in (1.22m).

Extended Range General Purpose Temperature Probe



Model#	Calibration
6373	K-Type

General purpose probe for gas, air, gels and liquid measurements.

Measurement Range: -320 to 1994°F (-196 to 1090°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Probe Length: 8in (0.2m); O.D. 0.125in (3.18mm).

Cable Length: 48in (1.22m).

K-Type.

Extended Length Temperature Probe



Model#	Calibration
6371	K-Type

Conveniently attaches to our Mini-Connector Extension Cable (Model 6539 and 6379).

Measurement Range: -40 to 2000°F (-40 to 1093°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Probe Length: 12in (0.3m); O.D. 0.070in (1.78mm).

Thermocouple Extension Wire Kit

Model#	Calibration	Temp. Range
6540K	K-Type	-40 to 500°F (-40 to +260°C)



Kit includes one pair of mini-connectors (male and female) and thermocouple wire (unassembled).

Length: 118in (3m).

Temperature Probe with Thermocouple Bead Tip

Model#	Calibration	Temp. Range
6378	K-Type	-40 to 500°F (-40 to +260°C)
6536	J-Type	+32 to 500°F (0 to +260°C)



General purpose probe for air and surface measurements.

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%

Cable Length: 39in (0.99m).

Thermocouple with Self-adhesive Backing

Model#	Calibration	Length	Temp. Range
6542K-48	K-Type	48in (1.22m)	-4 to 392°F (-20 to +200°C)



Designed for fast surface temperature measurements.

Self-adhesive backing for easy placement and removal.

Available in K Calibrations.

Surface Temperature Probe

Model# 6376



Ideal for measuring surface temperatures in a lab or more rugged environment.

Measurement Range: 32 to 500°F (0 to 260°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Probe Length: 4in (0.10m); O.D. 0.125in (3.18mm).

Cable Length: 48in (1.22m).

K-Type.

Do-It-Yourself Male Mini-Connector

Model#	Calibration	Temp. Range
6372	K-Type	-40 to 500°F (-40 to +260°C)
6559	J-Type	-40 to 500°F (-40 to +260°C)



Male mini-connector with Isothermal screw terminal for attachment to thermocouple wire (max. 20 AWG).

Measurement Range: -40 to 400°F (-40 to 204°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Do-It-Yourself Female Mini-Connector

Model#	Calibration	Temp. Range
6380	K-Type	-40 to 500°F (-40 to +260°C)
6562	J-Type	-40 to 500°F (-40 to +260°C)



Female mini-connector with Isothermal screw terminal for attachment to thermocouple wire (max. 20 AWG).

Measurement Range: -40 to 400°F (-40 to 204°C).

Temperature Tolerance: $\pm 3.9^\circ\text{F}$ ($\pm 2.2^\circ\text{C}$) or 0.75%.

Category Page#
Adapters

Adapter Accessories	18-22
Adapter Kit, Coaxial Cable	18-22
Banana Jack and Plug	30-41
[see separate Banana Plugs & Jacks section]	
Banana to Connector Pin and Socket	40-41
Banana to Pin Tip	41
Banana Plug to Phono Jack	85
Bantam to Binding Post	96, 98
Bantam to WE310	96
BNC Dust Cap	22
BNC to 1/4in Phone Plug	84
BNC to 3.5mm Plug	84, 85
BNC to Banana Plug	20
BNC to Bantam	98
BNC to Binding Post	20
BNC to BNC	18, 22
BNC to F	84
BNC to Micro Phone Plug	85
BNC to Mini Phone Plug	84
BNC to N	18, 28
BNC to Phone Plug	84, 85
BNC to Phono Jack	84
BNC to SMA	18, 28
BNC to TNC	29
BNC to Tini Plug	84, 85
BNC to Triax	29
BNC to UHF	18, 28
BNC to WE309	98
BNC to WE309 / 310	98
BNC to WECO	98
Coaxial Adapters and Kits	18-22
Coaxial Connectors and Adapters	18-29
F to F	84
N to N	19, 26
Oscilloscope Probe Tip	79-82
Phone Plug 1/4in to Banana Plug	85
Phone Plug to Banana Plug	85
Safety Banana Jack to Banana Plug	31
SMA to "N"	18, 28
SMA to SMA	18, 24
SMA to TNC	28
Terminal Strip to Banana Jack	34, 35
Test Probe, DMM	58-71
Thermocouple	99-100
Pin Tip to Banana	41
TNC to TNC	29
Triax to Triax	26
Triaxial	26, 27
Type N to BNC	18, 28
Universal Kits	18-22
WE310 to Binding Post	98

Alligator Clips, Regular Size

To Banana Jack	69, 74
Breakout to BNC	15, 17
DMM Test Lead	97, 64, 48-50
Extra Large	68, 74
Patch Cord to Alligator Clip	48-50
Patch Cord to Bantam	94-96
Patch Cord to BNC	15, 17
Patch Cord to 1000V Alligator Clip	48-50

Category Page#
Alligator Clips, Mini

To 2mm Banana Jack	74, 77
Breakout to BNC	15, 17
DMM Test Lead	48-50
Patch Cord to Banana, double	46
Patch Cord to Banana, single	49
Patch Cord to Banana, mini, double	46
Patch Cord to Mini Alligator Clip	46, 49
Patch Cord to Mini Grabber	48
To Pin Tip	74

Alligator Clips, Micro

Patch Cord to Micro Alligator Clip	46, 49
------------------------------------	--------

Attenuators

BNC Attenuator	21
----------------	----

Audio

Audio	83-85
XLR Connector	83-85

Automotive

Automotive	86
Backprobe Pin	86
Connector Test Probe	86
Connector Test Socket	86
Lead Holder	86
Piercing Probes	86
Test Pins and Sockets	86

Banana Plugs and Jacks (Binding Posts too)

Banana Jack Mounting Base	85
Banana Jack, panel mount with wire wrap	85-86
Banana Jack to Banana Jack	31, 44, 69
Banana Jack to Miniature Banana Plug	37, 39
Banana Jack Miniature Panel Mount	38
Banana Jack to Pin Tip Jack	40
Banana Jack Panel Mount	34, 38, 39
Banana Miniature Jack to Banana Plug	39
Banana Miniature Plug Panel Mount	34, 35
Banana Miniature Plug Shorting Bar	37
Banana Plug Adapters	40
Banana Plug Panel Mount	34
Banana Plug to Pin Tip Plug	43, 45
Banana Plugs and Jacks	30-40
Banana Shorting Bar	37
Binding Post	35-41
Binding Post, Double	36
Binding Post Miniature	37
Binding Post Mounting Base	35
Binding Post Shorting Bar	36
Binding Post, Spring Loaded	36
Binding Post, with Wire Wrap	35
Binding Post to Banana Plug	41
Connector Test Probe	41
Connector Test Socket	41
Coupler	31, 41, 69
Double Banana Plugs	41
Double Banana Jacks, Panel Mount	34
Low Thermal	41
Miniature Banana Jack	41
Miniature Banana Plug	40, 44
Nut, Hex	36
Pin Tip Jack Panel Mount	39
Safety Banana Jack to Banana Plug adapter	31
Safety Banana, Jacks	31, 34, 35
Safety Banana, panel mount	39
Safety Banana Plugs	31, 32, 33
Safety Banana Plug, right angle	32
Safety Banana Plug, stackable	30-31

Category Page#

Single Banana Jacks	33
Single Banana, Plugs	31-33, 35
Solderless Banana Plug, double	30
Solderless Banana Plug, single	32
Solderless Banana Plug, triple	31
Solderless Binding Post, double	38, 40
Solderless Mini Banana Plug, double	36
Solderless Mini Banana Plug, single	37
Solderless Mini Banana Plug, triple	36
Spade Lug	39, 41, 67
Splice, Banana	30
Stackable Banana Plug, double	30
Stackable Banana Plug, single	32
Stackable Banana Plug, triple	31
Stackable Binding Post, double	40
Stackable Mini Banana Plug, double	36
Stackable Mini Banana Plug, single	37
Stackable Mini Banana Plug, triple	36
Stacking Banana Plug, quad, single	31
Test Pins and Sockets	40-41
Triple Banana Plugs	31
Triple Banana Jacks, panel mount	34

Boxes and Enclosures

Boxes and Enclosures	52-57
Box, Aluminum	52-56
Box, Plastic	56-57

Breakouts

Assemblies and Breakouts	9-17
BNC to Alligator Clips	17
BNC to Banana Plug	16-17
BNC to Pin Tip	16, 17
BNC to Spade lugs	17
BNC to Square Jack	16-17
BNC to Test Clips	17
BNC to Wire Lead	17

Broadcast

BNC Color-Coded Sleeves	10
BNC High Definition Coaxial Connectors	83
BNC Terminator	21, 84

Cable Assemblies

Assemblies and Breakouts	9-17
Banana Miniature Plug	17
BNC Color-Coded Sleeves	10
BNC to Alligator Clips	15, 17
BNC to Banana Plug	15, 16, 17
BNC to BNC	10-12, 85, 93
BNC to N	12
BNC to Phone Plug	14
BNC to Pin Tip	16, 17
BNC to SMA	12
BNC to Spade lugs	17
BNC to Square Jack	16, 17
BNC to Test Clips	14-15, 17
BNC to TNC	14
BNC to UHF	12
BNC to Wire Lead	17
Coaxial Cable Set	86
Lead Holder	9, 42
N to N	13
Phone Plug	84
SMA to "N"	13
SMA to SMA	12, 13
Triax to Alligator Clips	13
Triax to Triax	14
UHF to UHF	18

Category	Page#
Connectors	
Banana Plugs & Jacks [see separate Banana Plugs & Jacks section].....	30-41
Binding Post [see Banana Plugs & Jacks section].....	35-40
BNC 75Ω.....	10, 21, 83
BNC Bulkhead Receptacle, Hermetically Sealed.....	23
BNC Coaxial.....	18-24, 28, 29
BNC, Hermetically Sealed.....	23
BNC High Definition.....	83
BNC, Isolated, Bulkhead Receptacle.....	23
BNC Panel.....	23
BNC PCB.....	23
BNC Strain Relief Boot.....	24
Broadcast Connectors and Adapters.....	83-85
Coaxial Connectors and Adapters.....	18-29
F Coaxial.....	84
F Panel.....	84
F to BNC.....	84, 85
F to PCB.....	84
Grabber Type Clips.....	68, 72-78
N Coaxial.....	25
N Panel.....	26
N Terminator.....	21
Retractable Sheath Banana Plug.....	50
SMA Coaxial.....	18, 24, 25, 28
SMA Panel.....	25
SMA PCB.....	25
SMB Coaxial.....	26
Tip Pin, Plug.....	38, 39
Tip Pin, Panel Mount.....	39
Tip Pin, Panel Mount with Wire Wrap.....	39
TNC.....	24, 28
Triax Coaxial.....	22, 24, 26, 27
Triax Panel.....	27
Twinax Coaxial.....	27
Twinax Panel.....	27
XLR Connectors (many models in Broadcast Catalog).....	83-85
Crimp Tools	
Crimp Tools.....	27
DC Blocking	
BNC Blocking Capacitor.....	21
DMM Accessories	
0.04", 0.06" & 0.08" Replaceable Probe Tips.....	65
Alligator Clips.....	60, 61, 62, 69, 74, 75
Automotive Leads.....	86
Backprobe Pins.....	60, 87
Banana Jack to Banana Jack.....	37, 38, 66
Cases and Pouches.....	64
Couplers.....	31, 41, 69
Couplers, Test Lead, Banana.....	69
DMM Accessories and Kits.....	58-71
DMM Accessories Cases and Pouches.....	64
Do It Yourself DMM Accessories.....	71
Kelvin Clips with Leads.....	71
Kelvin Probe Set.....	71
Kit List.....	64
Piercing Alligator Clips to Banana Plug.....	89
Piercing Probes.....	61, 66, 86
Pogo Tip Probes.....	65, 66
Probe Tip Adapter.....	58, 59, 60, 61, 69
Probe Tips, Spring-Loaded (Pogo Pin).....	65, 66
Probe Tips, Replaceable.....	58, 63, 66, 67
Retractable Needle Tip Test Probes.....	65
RF Detector Test Probe.....	70

Category	Page#
Screw-on Alligator Clips Set.....	65
Shielded Leads.....	68
Spade Lug.....	41, 47
Spade Lug Adapter.....	69
Spring Loaded Probe tip sets.....	63
Test Clips.....	68, 72, 73, 74, 75
Test Lead Kits.....	58, 59, 60, 63
Test Lead Wire.....	71
Test Leads and Test Lead Kits.....	67
Test Leads, Modular.....	67
Test Probe RF Detector.....	70
Test Probe Selection Table.....	64
Test Probe SMD Tweezers.....	70
Test Probe Tip Adapters.....	58, 59, 60, 61
Test Probe with Leads.....	65, 67, 70, 71
Test Probe, Modular.....	67
Wire Piercing Test Clip.....	68
Wire, Test Lead.....	71
Do-It-Yourself	
Leads and Grabbers.....	71-73
IC Test Clips	
IC Test Clips and Adapter.....	87-90
Kelvin Clips	
Kelvin Probes, Clips with Leads.....	71
Oscilloscope Probes	
Differential Probe.....	82
Probes.....	79-82
Probes Accessory Kit.....	79-82
Probes and Accessories.....	79-82
RF Detector Test Probe.....	81
SMD.....	73, 76, 78, 81
SMD Adapter.....	79-81
Patch Cords	
66 Block to Alligator.....	97
Alligator to Alligator.....	49
Banana Jack to Banana Plug.....	49
Banana Jack to Minigrabber.....	44
Banana Jack, Sheathed to Minigrabber.....	44
Banana Jack to Test Clip.....	44
Banana Plug.....	30-40
Banana Plug to Maxigrabber.....	44
Banana Plug to Micrograbber.....	44
Banana Plug Miniature.....	43
Banana Plug Miniature to Test Clip.....	44
Banana Plug, Miniature to Minigrabber.....	51
Banana Plug to MiniPincher.....	44
Banana Plug to Minigrabber.....	44, 45
Banana Plug to Alligator Clip.....	46, 48, 49
Banana Plug to Pin Tip.....	43, 45
Banana Plug, Retractable Sheathed to Minigrabber.....	50
Banana Plug, Retractable Sheathed to Banana Plug, Retractable Sheathed.....	50
Banana Plug, Retractable Sheathed to SMD Grabber.....	68, 72-78
Banana Plug, Sheathed to Extra Large Alligator Clip.....	49
Banana Plug to Square Pin Jack.....	50
Banana Plug to Test Clip.....	44, 45, 48, 49, 83
Banana Plug, Miniature to Standard.....	43
Bantam.....	94
Bantam to Alligator.....	95
Bantam to Banana Plug.....	95
Bantam to RJ11.....	96
Bantam to RJ45 / RJ48.....	96

Category	Page#
Bantam to Test Clip.....	95
Bantam to WE310.....	96
BNC 75Ω.....	10, 21, 85
BNC to Alligator Clip.....	15, 17
BNC to Double Banana Plug.....	15
BNC to BNC.....	18, 22
BNC to Grabbers and Pincers.....	14, 15
BNC to Type N.....	18, 28
BNC to Bantam.....	98
BNC to Phono Plug.....	84
BNC to Pin Tip Plug.....	41
BNC to SMA.....	18, 28
BNC to TNC.....	29
BNC to UHF.....	18, 28
BNC to WE310.....	98
BNC to WECO I.....	98
Coax.....	18-29
Coiled Patch Cords.....	43, 45, 47
Double Shielded Coax, Triaxial.....	26, 27
Fuse Holder Banana Plug.....	43
Lead Holder.....	42
Large Alligator Clip.....	68
Low Thermal.....	41
Miniature Banana Plug to Minigrabber.....	51
Minigrabber to Pin Tip Plug.....	72
Type N.....	13
Patch Cords and Test Leads.....	42-51
Patch Cord to 66 Block.....	77
Patch Cord to Banana, Double.....	45, 46
Patch Cord to Banana, Single.....	42-44, 49-51
Patch Cord to Large Alligator Clip.....	74
Patch Cord to Spade Lug.....	47, 51
Patch Cord to Triaxial.....	13, 14
Patch Cord to WE310.....	94-98
Pin Tip.....	17, 39, 40, 43, 74
Pin Tip to Test Clip.....	50
Retractable Sheath Banana Plug to Minigrabber.....	50
Retractable Sheathed Banana Plug to Retractable Sheathed Banana Plug.....	50
Retractable Sheathed Banana Plug to SMD Grabber.....	75
Sheathed Banana Jack to Minigrabber.....	44
Sheathed Banana Plug to Extra Large Alligator Clip.....	49
Shielded, Double Banana.....	44
Shielded Twisted Pair, Triaxial.....	13
SMA.....	18, 24, 28
SMD Grabber to Square Pin Jack.....	51
SMD Test Clip.....	44, 48, 73, 75
Spade Lug.....	47, 51
Spade Lug to Alligator.....	51
Square Pin to Banana.....	50
Spade Lug to Banana Plug.....	47
Square Pin Jack.....	51
Square Pin Jack to Pin Tip.....	51
Square Pin Jack to Test Clip.....	51
Test Clip.....	48, 50
Test Clip to Alligator.....	48
Triaxial.....	13
Twisted Pair.....	9
UHF.....	13, 28
WE310.....	94, 96, 97, 98
WE310 to Alligator.....	97
WE310 to Banana Plug.....	96
WE310 to RJ45 / RJ48.....	97
WE310 to Test Clip.....	97
WECO.....	94, 98

Category	Page#
Shorting Cap	
BNC Shorting Cap	22
SMA Shorting Cap	24
Static Control	
Kit	91
Patch Cord	92
Static Control	91
Tester	91
Wrist Strap	91
Telecom	
BNC to Bantam	93, 98
Bantam	94, 96
Bantam to Alligator	95
Bantam to Banana Plug	95
Bantam to RJ11	96
Bantam to RJ45 / RJ48	96
Bantam to Test Clip	95
Bantam to WE310	96
BNC to Bantam	98
BNC to WE310	94, 98
BNC to WECO	94, 98
Patch Cords	93-97
WE310	94, 96, 98
WE310 to Alligator	97
WE310 to Banana Plug	96
WE310 to RJ45 / RJ48	97
WE310 to Test Clip	97
WECO	94, 98
Piercing Alligator Clips to Banana Plug	97
Telecom	93-98
Test Kit	93
Bantam to Binding Post	96, 98
Bantam to WE310	96, 98
Temperature Probes	
Temperature Probes	99-100
Connectors	100
Terminators	
BNC Terminator	21
SMA Terminator	24
Test Clips	
Banana Jack	72
Pin Tip	72
Solder Type	74
Grabbers and Test Clips	72-74
Kelvin Clips with Leads	71
Pin Tip to Alligator Clip	74
SMD	72, 75-78
Thread	72
Test Leads	
Patch Cords and Test Leads	42-51
Test Probes	
Test Probes	58-71
SMD Tweezers	70
Video	
Video	83-85
Wire	
Test Lead Wire	71

Category	Page#
Alphabetical Listed Items	
Alligator Clips	68, 69, 74
Attenuators, BNC	21
Automotive Leads	86
Backprobe Pins	86
Cases & Pouches	64
Coiled Patch Cords	43, 45, 47
Couplers	31, 41, 69
Differential Oscilloscope probe	82
ESD Control Products	91, 92
Grabber type clips	72-78
Hanging Rack	9, 86
Hardware, replacement	36
Hermetically Sealed BNC	23
Kit List, DMM Test Leads	64
Low Thermal Patch Cord	41
Low Thermal Lug	41
Magnetic Test Lead holder	86
Maxi Grabber Clips	68, 73
Micro Grabber Clips	73, 76
Mini Grabber Clips	71-74
Mini Pincer Clip	71-74
Mounting Bases, panel mount	35
Nuts, Hex, replacements	36
Piercing Probes	68
Pogo Tip Probes	65, 66, 70
Pouches & Cases	64
Retractable Sheath Banana Plug	32
RF Detector	81
Screw-on Alligator clip probes	65
Shielded Leads, DMM	68
Shorting Link, binding post	36
Shorting Plugs	30, 31, 37, 39
Sleeves, color-coded	10
SMD Grabber Clips	75-78
SMD Oscilloscope Grabber Clips	73, 76, 79-81
Spade Lugs	41, 47
Splices	31, 41, 69
Spring Loaded Tip Probes	65, 66, 70
Static Control Products	91-92
Strain Relief Boot	24
Terminators, BNC	21, 84
Terminators, Type N	21
Test Lead Rack Holders	9, 86
Tini Plug to BNC adapter	84
Thermocouple Adapters	99-100
Triaxial Adapters	26, 27
Triaxial Connectors	26, 27
Triaxial Patch Cords	13-14
Tweezers	70
Wire Wrap Items	35, 39
Wire Reference Table, Coax	9
Wire Reference Table, Patch Cord and Test Lead	42

Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#
AL-B	.49	2103	.56	2945	.37	3562	.40	4108	.21
B	.42	2104	.57	2948	.42	3563	.40	4115	.36
BNC-C	.11	2105	.56	2952	.39	3564	.40	4119	.21
HB	.42	2112	.96, 98	2970	.31	3565	.40	4124A	.90
MDP	.30	2138	.39	2BA	.45	3580	.27	4140A	.90
MDP-S	.30	2142	.38	2BA-AL	.46	3600	.26	4159	.23
MDP-ST	.30	2143	.38	2BC	.45	3601	.54	4160	.23
MDP-X	.31	2224	.57	2BC-BNC	.15	3602	.54	4176	.72
MG-B	.49	2239-C	.45	2BC-MG	.46	3603	.54	4225	.73
P	.51	2240	.74	2BC-PP	.45	3606	.54	4226	.54
PT080	.50	2244	.36	3014	.43	3690	.37	4233	.73
SP150B	.79	2247-K	.46	3027-K	.46	3719	.53	4236A	.90
1081	.51	2249-C	.9, 10	3030	.37	3728	.52	4240	.21, 25
1126	.43	2249-E	.10	3073	.17	3742	.55	4243	.36
1166	.48	2249-K	.10	3221	.17	3743	.55	4245	.52
1167	.45	2249-Y	.10	3230	.53, 49	3744A	.41	4246	.53
122505A	.32	2256-X	.13	3231	.53	3750	.35	4247	.54, 55
122506A	.32	2256-C	.13	3232	.53	3751	.52	4248	.53
1236	.49	2259	.56	3234	.53	3752	.52	4267	.85
1269	.20	2269	.34	3239	.53	3753	.52	4274	.43
1270	.20	2305	.41	3257	.33	3754	.52	4276-C	.11
1285	.85	2352	.52, 53, 54	3258	.33	3760	.35	4277-C	.12
1286	.40	2382	.37	3261	.33	3770	.35	4279	.94
1296	.20	2383	.38	3263	.33	3777A	.41	4279N	.94
1297	.84	2390	.52	3264	.33	3778	.23	4280	.96
1325	.32	2391	.52	3265	.33	3780	.47	4280N	.96
1326-A	.45	2392	.52	3266	.33	3781	.47	4281	.95
1326-C	.45	2393	.52	3267	.35	3782	.43	4282	.24
1330	.30	2397	.52	3268	.37	3784	.51	4283	.24
1330-ST	.30	2398	.52	3269	.20	3786-C	.45	4284	.24
1366-C	.13	2399	.52	3271	.37	3787-C	.14	4285	.24
1367-C	.12	2400	.52	3272	.37	3788	.17	4286	.24
1368-A	.45	2401	.52	3273	.37	3789	.17	4288	.28
1383-C	.11	2411	.53	3276	.37	3834	.41	4289	.28
1390	.31	2417	.53	3277	.38	3837	.84	4290	.28
1432	.40	2420	.53	3283	.22	3839	.22	4291	.28
1437	.74	2428	.53	3284	.22	3840	.21, 84	4292	.28
1440	.42	2439	.37	3285	.22	3841	.26	4293	.28
1442	.85	2440	.38	3286	.28	3842	.26	4294	.28
1452	.20	2447	.23	3287	.28	3843	.20	4295	.28
1468	.20	2447A	.23	3288	.28	3844	.29	4296	.28
1469	.20	2451	.23	3289	.74	3846	.22	4297	.28
1508/POM	.9, 42	2451A	.23	3296	.20	3847	.22	4298	.28
1581	.34	2455	.26	3301	.54	3850	.57	4299	.28
1614	.69	2477	.39	3302	.54	3862	.35	4311	.72
1658-T	.13	2484	.43	3306	.54	3863	.35	4324A	.90
1693	.47	2630	.17	3311	.55	3864	.45	4340A	.90
1756	.47	2631	.17	3316	.55	3901	.17	4384	.57
1794	.98, 94	2708	.42, 9	3328	.54, 55	3916A	.90	4388	.27
1809	.40	2798	.94, 98	3352-A	.97	3925	.72	4391	.21
1823	.31	2842	.51	3364	.31	3957	.17	4408	.9, 42
1825	.32	2854	.34	3430	.20	3958	.54	4408M	.86
1829	.30, 31	2864	.43	3452	.39	3966	.17	4416	.54
1837	.31	2882-C	.16	3491	.74	4005	.35	4487	.11
1894	.20	2885	.17	3533	.22	4011	.72	4488	.22
1948-C	.14	2886	.17	3534	.22	4022	.38	4507	.52
1960	.51	2894	.41	3535	.28	4043	.85	4512	.33
2035	.37	2901	.53	3542	.39	4044	.85	4513	.37
2096	.56	2902	.53	3548	.35	4054	.84	4521	.73
2098	.56	2906	.53	3560	.40	4057	.52	4524-C	.12
2099	.56	2944	.37	3561	.40	4098	.35	4528-BB	.12

Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#
4528-K	.12	4864	.52, 53, 55, 56, 57	5143-K	.70	5314	.90	5692	.90
4528-X	.12	4892	.30	5144	.68	5319	.84	5697	.11
4530-C	.16	4896	.22	5145	.31	5325A	.59	5698	.18
4531-C	.15	4897	.32	5148	.23	5342	.13	5699	.35
4532-C	.15	4898	.30	5155	.24	5343-C	.16	5700	.35
4536	.47	4899	.32	5156	.24	5344	.22	5701	.35
4537	.47	4900	.34	5157	.24	5360	.73	5713	.88
4538	.43	4903	.56	5165	.40	5375	.25	5733	.89
4543	.39	4911A	.49	5167	.33	5379	.25	5748	.18
4550B	.79	4914	.30	5168	.33	5401	.89	5749	.19
4555	.72	4933	.33	5169	.33	5402	.89	5751L	.89
4565	.73	4934	.33	5170	.33	5403	.50	5751L-2	.89
4578	.23	4935-BB	.12	5173	.39	5405	.40	5770	.89
4590	.35	4940	.29	5178	.26	5406	.32	5770-2	.89
4601	.33	4945-K	.16	5186	.54	5410	.17	5770L	.89
4613	.48, 13	4956	.26	5187-C	.15	5412	.51	5773-2	.89
4614	.35	4957	.27	5187-K	.15	5413	.90	5777	.88
4617	.37	4958	.27	5188	.17	5418	.74	5787A	.69
4619	.35	4959	.25	5189	.17	5419	.48	5788	.74
4648-C	.15	4963-E	.14	5198	.56	5421	.44	5790	.78
4650	.50	4969	.10, 17	5203	.56	5422-C	.46	5795A	.79
4652	.48	4970	.17	5208	.90	5423-C	.14	5800A	.79
4653	.36	4979	.23	5214	.90	5428	.44	5803A	.79
4654	.35	4986	.33	5216	.90	5437	.90	5806A	.79
4655	.55	4987	.33	5218	.26	5451	.89	5809A	.79
4656	.55	4993	.96, 98	5219	.27	5452	.89	5812A	.79
4658	.55	4995	.36	5220	.90	5453	.89	5815A	.81
4661	.26	4996	.44	5223	.14	5454	.89	5827	.79
4684	.21	4997	.22	5224	.90	5510	.21	5830	.73
4690	.40	5001	.96, 98	5230	.32	5511	.22	5868L	.89
4691	.40	5008	.94, 98	5233	.34	5512	.21	5868L-2	.89
4702	.51	5014	.90	5240	.90	5513	.21	5878	.89
4719	.94, 98	5018	.35	5250	.90	5514	.90	5888	.89
4723	.72	5019	.95	5251	.90	5515A	.89	5888-2	.89
4725	.13	5019N	.95	5252	.90	5517A	.66	5893	.88
4726	.54	5026	.95	5253	.90	5519A	.66	5894	.88
4741	.50	5051	.17	5254	.90	5520	.73	5898	.66
4742	.52	5053	.44	5255	.55	5521	.48	5899A	.62
4768-K	.46	5056	.26	5259	.51	5522	.72	5900A	.61
4770	.36	5058-X	.13	5260	.11	5523	.47	5901B	.60
4771	.50	5066	.24	5268-C	.16	5524	.73	5903A	.61
4772	.50	5068	.24	5270	.50	5525	.48	5904A	.61
4773	.39	5069	.17	5279	.89	5528	.91	5906A	.67
4777-C	.14	5076	.24	5280	.89	5529	.91	5907A	.67
4777-K	.14	5079	.22	5281	.89	5531	.92	5908A	.67
4778	.95	5085	.22	5285	.22	5532	.92	5909A	.67
4787	.25	5088	.24	5286	.22	5534	.6, 92	5910B	.68
4788	.23	5089	.26	5290	.26	5543B	.59	5911B	.68
4804	.24	5090	.29	5291A	.46	5643	.89	5912B	.68
4805	.24	5108	.90	5292	.6, 68	5643L	.89	5913	.68, 86
4812-J	.97	5109A	.83	5297	.21	5643L-2	.89	5914	.68
4814-BB	.12	5110	.83	5298	.29	5645L	.89	5916A	.69, 74
4814-K		5113A	.85	5299	.29	5645L-2	.89	5925	.73
4815	.17	5116	.90	5300	.29	5672A	.59	5927	.73
4826	.72	5117A	.85	5301	.48	5673B	.61	5929	.78
4846-BB	.12	5120	.90	5302	.44	5674C	.59	5930	.78
4846-K	.12	5124	.90	5304-K	.15	5676A	.66	5931	.34
4846-X	.12	5125A	.83	5305	.17	5677B	.58	5932	.41
4850	.25	5126A	.83	5307	.22	5678-K	.70	5934	.41
4859	.24	5133	.70	5309A	.66	5682	.69	5935	.40
4862	.54, 55	5142-K	.70	5312	.89	5689A	.67	5936	.40

Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#	Model#	Page#
5940	.71	6244	.44	6413	.68, 86	6700	.22	7066	.24
5948	.50	6245	.44	6440	.36	6701	.22	7073	.23
5950A	.66	6246	.47	6441	.36	6702	.83	7074	.7, 26
5951A	.66	6248	.44	6442	.78	6703	.83	7207	.7, 22
5952A	.65	6249	.43	6443	.73, 79	6704	.83	7273	.83
5953A	.65	6252	.69	6456	.59	6706	.84	7274	.83
5955	.64	6253	.11	6469	.66	6707	.84	7275	.83
5961	.89	6254	.19	6470	.66	6708	.84	7276	.83
5961-2	.89	6262	.69	6472	.66	6711	.84	7277	.27
5969	.88	6263	.69	6475	.70	6712	.84	7278	.27
5969A	.88	6264	.69	6477	.66	6713	.84	7280	.27
5972	.88	6265	.79	6479	.67	6714	.84	7281	.27
5998A	.89	6266	.79	6480	.86	6715	.84	7282	.27
5998AL	.89	6268	.54	6481	.41, 86	6716	.27, 84	7286	.83
6006	.82	6275	.65	6483	.49	6717	.23	7287	.83
6033	.82	6283-C	.44	6484	.97	6718	.23	7288	.83
6035	.82	6286	.67	6485	.97	6720	.34	7289	.83
6041B	.68, 74	6288	.67	6486	.97	6721	.32, 71	7290	.5, 65
6042B	.68, 74	6291	.10	6490	.78	6723	.65	72902	.3, 76
6049A	.79	6303	.71	6491	.80	6726	.65	72903	.76
6069A	.79	6304	.67	6492	.80	6727	.42	72904	.76
6081	.92	6311	.78	6493	.80	6728	.31	72905	.3, 76
6082	.91	6312	.78	6494	.80	6729	.31, 71	72906	.3, 76
6083	.91	6313	.78	6495	.80	6730	.71	72907	.76
6084	.91	6315	.96	6496	.80	6731	.82	72908	.4, 16
6085	.92	6316	.97	6497	.80	6732	.82	72909	.16
6086	.91	6320	.96	6498	.80	6733	.71	72910	.20
6087	.91	6321	.95	6499	.80	6734	.71	72911	.20
6088	.91	6323	.96	6500	.80	6754	.84	72912	.6, 34
6090	.48	6324	.96	6501	.80	6767	.7, 25	72913	.34
6091	.48	6331	.96	6502	.94	6768	.25	72914	.5, 20, 78
6101A	.79	6336	.97	6510-V	.10, 85	6769	.26	72915	.78
6102A	.79	6340	.58	6515	.94	6770	.26	72916	.78
6106	.70	6341	.65	6516	.94	6771	.26	72917	.78
6107	.90	6342	.65	6517	.93	6772	.26	72918	.33
6108	.90	6343	.59	6519	.94, 98	6779	.29	72919	.77
6109	.90	6344	.59	6523	.95	6780	.29	72920	.5, 77
6112A	.64	6345	.63, 64	6524	.96	6781	.29	72921	.5, 78
6120	.64	6351	.78	6530A	.60	6782	.29	72922	.6, 78
6146	.64	6352	.78	6534	.86	6852	.83	72923	.5, 77
6147	.64	6353	.78	6536	.100	6853	.83	72924	.74, 77
6150	.89	6354	.65, 70	6540K	.100	6869	.85	72925	.77
6151	.89	6356	.49	6542K	.100	6883	.36	72926	.4, 10
6152	.89	6357	.48	6544	.86	6884	.36	72927-C	.16
6162	.64	6358	.67	6545	.32	6896	.84	72928	.75
6163	.64	6364	.70	6546	.32	6898	.84	72929	.77
6166	.64	6365	.66	6547	.36	6900	.84	72930	.34
6172A	.63, 64	6366	.66	6548	.36	6901	.84	72931	.18
6173A	.62, 64	6367	.99	6549	.36	6902	.85	72932	.19
6174	.63, 64	6371	.99	6551	.81	7035	.22	72933	.19
6175	.64, 68	6372	.100	6553	.73, 80	7037	.22	72934	.4, 18
6177	.64	6373	.99	6554	.81	7040	.22	72935	.3, 75
6200	.64	6376	.100	6559	.100	7041	.22	72936	.77
6201	.19	6378	.100	6562	.100	7048	.7, 24		
6203	.69	6380	.100	6567	.74	7049	.24		
6204A	.60	6383	.32, 71	6568	.93	7050	.24		
6212	.70	6384	.32, 71	6570	.49	7057	.25		
6231	.44	6387	.34	6573A	.69, 74	7058	.25		
6232A	.67	6389	.36	6576	.49	7063	.7, 24		
6235	.6, 68	6405	.68, 86	6580	.68, 86	7064	.24		
6237	.64	6411	.86	6601	.65	7065	.24		

You can quickly find complete product specifications and discover Pomona's newest product announcements when you visit our website:

www.pomonaelectronics.com



Now there are three ways for you to find the product you are looking for.

1. Search by **Keywords**

Simply click on [Search by Keywords] in the left-hand column of the homepage. Then enter the description of the product in the keywords box and select [Search Now].

2. Search by **Category**

From the homepage select [View Products] under either "Test and Measurement" or "Broadcast/Multimedia". You will see a list of product categories from which to choose.

3. Search by **Model #**

Enter the model number of the Pomona product into the [Search by Model] box and select [Go].



Whichever method you choose you will be presented with model numbers and [pdf] hotkeys which will take you directly to specification information on the product you want.

Once you have a specific Pomona model number you are interested in, you can immediately find a distributor with stock on hand. From the left-hand navigation column select [View Distributor Stock], enter the model number into the box, and click [Go]. You will be presented with a list of distributors with that part on hand.

Make the Pomona site your "favorite" place to "go to" when you need the world's most complete line of quality test accessories.



Technical Support 1-800-443-5853

Because technical questions about products or applications can arise almost anywhere, Pomona offers immediate technical support. You can reach a qualified resource via e-mail or phone either by visiting the Pomona website, or dialing toll-free direct. While you are in the Technical Support section of our website, you can also refer to selector guides, view or request a catalog, or go directly to the specific product information you seek.

Nothing in this catalog is to be construed as an offer. Product availability, prices and delivery dates are subject to Pomona's order confirmation form. The same applies to orders based on development samples delivered. Pomona products are intended to be used in accordance with the specifications in this catalog. Any use or application that deviates from those specifications may be dangerous. **A limited warranty applies to Pomona products. Pomona will not be liable for any loss, damage, cost of repair, or incidental or consequential damages of any kind, arising in connection with the design, manufacture, sale, or repair of the products, whether based on express or implied contract, negligence or strict liability. Pomona will not be liable to buyer for any amount exceeding the purchase price of the product which proves to be defective.** Pomona will not be responsible or liable for any patent infringements or other rights of third parties, which may result from the use of this catalog. Registered trademarks used in this catalog are the property of their respective companies.



Pomona[®]

ELECTRONICS

In the United States:

Pomona Electronics
9028 Evergreen Way
Everett, WA 98204
United States

www.pomonaelectronics.com

Tel: 1-800-490-2361
Fax: 1-425-446-5844

Lit.#: 2074413 C-ENG-N Rev. C
Volume 51

In Europe:

Pomona Electronics
P.O.Box 1186
5602 BD Eindhoven
The Netherlands

www.pomona.cc

Tel: +31 (0) 40 2675 150
Fax: +31 (0) 40 2675 151

Pub ID: 11004-eng Rev 01

All other areas:

www.pomonaelectronics.com

Tel: 1-425-446-5500
Fax: 1-425-446-5844

Products in this catalog are available through:

