

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	39		0	RLSE NPR 5533 WAS 96-2258-1-1	24 MAY 96	-	-

D




RECOMMENDED PC BOARD LAYOUT

C




D

B





SECTION A-A
(POINT OF CONTACT)



SECTION A-A

- 1 HOUSING: POLYPHTHALAMIDE, BLACK.
CONTACT: PHOSPHOR BRONZE.
- 2 CONTACT: 1.30µm MIN TIN-LEAD ON SOLDER TAIL OVER
1.90µm MIN NICKEL ON ENTIRE CONTACT.



787802

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	C. OBERMAN	24 MAY 96	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm		CHK	R. STONE	28 MAY 96			
		APVD	R. KLINE	29 MAY 96	NAME		
		PRODUCT SPEC		108-1501	INSERT ASSEMBLY, 5 POSITION, DOVETAIL LOCATOR, WITH SOLDER TAIL, 5 mm ϕ , 10.8 VOLTS, BATTERY INTERCONNECT		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		-	SIZE		
0 PLC ±-		1 PLC ±-		2 PLC ±0.10	CAGE CODE		
3 PLC ±-		4 PLC ±-		ANGLES ±2°	DRAWING NO		
FINISH		WEIGHT		-	A2 00779		
MATERIAL		CUSTOMER DRAWING		-	SCALE		
1		2		-	SHEET		
				-	1 OF 1		
				-	REV		
				-	0		