

MH
KTB MH 262620 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Stainless steel housings for the use within explosive-risk zones

The Klippon® TB housing series features excellent performance characteristics, even under the most difficult environmental surroundings. And it meets the stricter requirements of explosive-risk zones found in the process or power generation industries

The new Klippon® TB MH housing series offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH housing series features the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 flange plates
- The seal is protected against compression
- Completely removable padlock mechanism
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable cover – no tools required
- Earth stud in housing cover and bottom section
- Welded-on mounting feet
- International approvals

General ordering data

Order No.	1194650000
Type	KTB MH 262620 S4E0
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 260 mm, 200 mm, 260 mm
GTIN (EAN)	4032248977406
Qty.	1 pc(s).

MH

KTB MH 262620 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	200 mm	Width	260 mm
Height	260 mm	Depth	200 mm
Mounting dimension - width	286 mm	Mounting dimension - height	170 mm
Net weight	4,400 g		

Cable glands, left

M12 (3)	25	M16 (3)	16
M20 (3)	11	M25 (3)	9
M32 (3)	4	M40 (3)	4
M50 (3)	2	M63 (3)	1
M75 (3)	1		

Cable glands, right

M12 (2)	25	M16 (2)	16
M20 (2)	11	M25 (2)	9
M32 (2)	4	M40 (2)	4
M50 (2)	2	M63 (2)	1
M75 (2)	1		

Cable glands, top/bottom

M12	33	M16	22
M20	14	M25	12
M32	6	M40	5
M50	2	M63	2
M75	1		

General information

AF size 1	10 mm	Access opening: height	207 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
	201 mm	Material thickness	1.5 mm
Installation advice	Terminal rail / mounting plate	Material thickness of flange	3 mm
Material thickness of cover	1.5 mm	Opening angle lid	125 °
Max. payload	27 kg	Position PE bolts	Page C
Overall dimensions	260 x 311 x 215	Seal material	Silicone
Material	Stainless steel 1.4404 (316L)	Operating temperature, min.	-60 °C
Surface finish	electropolished	Impact resistance	7 J ATEX version, 10 J version standard
Operating temperature, max.	135 °C	Note: protection class	For use in the temperature range over 105°C, the IP protection is limited to IP 66.
Protection degree		Cover attachment	4 hinges and M6 hex-head slotted screws SW10
	IP 66, IP 67		
Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross-shaped feet)		
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread		

Creation date April 25, 2013 9:49:41 PM CEST

MH
KTB MH 262620 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Housing earth

Earth, housing, internal	Welded-on M6 stainless-steel earth stud in lower part of housing and lid.
--------------------------	---

horizontal assembly

WDU 10 / ZDU 10	1x17	WDU 16 / ZDU 16	1x14
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x34	WDU 4 / ZDU 4	1x29
WDU 6 / ZDU 6	1x22		

vertical assembly

WDU 10 / ZDU 10 (2)	1x18	WDU 16 / ZDU 16 (2)	1x15
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	2x35	WDU 4 / ZDU 4 (2)	1x30
WDU 6 / ZDU 6 (2)	1x22		

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0050	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0015U	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

Approvals

Approvals



MH
KTB MH 262620 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

