





PLATING CONTACT AREA:

DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PRODUCT NR.	DIM "A"
88963-X01	5.00 REF.
88963-X11	3.35 REF.
88963-X01LF	5.00 REF.
88963-X11LF	3.35 REF.



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.



NOTES:

1. BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
3. PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR PURE FOR Sn FOR LF.
4. LOAD IN THIS DIRECTION (E.G. THROUGH CODING) 30 NEWTON PER 12 MM CONNECTOR LENGTH.
5. LOAD IN THIS DIRECTION 50 NEWTON MAXIMUM PER CONNECTOR.
6. TO ENSURE PROPER ALIGNMENT OF MULTIPLE MODULES ON A BOARD, THE USE OF A FIXTURE IS RECOMMENDED.
7. PRODUCT MARKING: PARTNUMBER & BATCH I.D.
8. DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
10. THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr no	dr	date	linear		projection		title	www.fciconnect.com
H	0008-0171	TER	8/26/08					STR FEMALE STB	
J	0009-0088	Cent	06/06/08					SIGNAL 48MM	
-	-	-	-	angles				product family	METRAL (tm)
D	H40355	DOB	940712	dr	H.Bouwknegt	930120		code	213
E	V91450	DOB	990827	engr	H.Bouwknegt	931122		size	dwg no
F	0005-0485	CLU	051121	chr	J.Wintjes	930121	scale	5:1	
G	0007-0170	Cent	05/22/07	app	H.Bouwknegt	930121			
sheet	revision	J							
index	sheet	1							