



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		G1	REVISED PER ECR-13-019898	24DEC2013	GRZ	JL

- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 8.38±0.08 [.330±.003] CENTERS.
- 2
- SLOT ACCEPTS 0.36–0.51mm [#27–#24] AWG COPPER MAGNET
WIRE. TWO WIRES OF THE SAME SIZE MAX PER SLOT
- 3
- IDENTIFICATION NUMBER 10 FOR THE MAGNET WIRE SLOT SIZE
- 4
- 0.25[.010] MAX CARRIER CUT-OFF TABS



OBSOLETE	082 PRE-MILLED BRASS	5 63718-2
	4M PRE-MILLED BRASS	63718-1
MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.A.MAYER 9-27-93		 TE Connectivity									
		CHK M.S. FEHER 9-27-93											
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME TAB, 6.35 [.250] FASTON, TM MAG-MATE TM Slim Line									
		APVD A.HUNT III 9-27-93											
		PRODUCT SPEC 108-1484											
		APPLICATION SPEC 114-2140											
MATERIAL SEE TABLE		FINISH 0.002032 [.000080] MIN TIN PLATE		SIZE A2		CAGE CODE 00779		DRAWING NO C-63718		RESTRICTED TO —			
				CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV G1	