

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

(C) COPYRIGHT

ALL RIGHTS RESERVED.

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			H2	REVISED PER ECO-11-005140	31MAR11	HMR



	2.300	23	2.505	2.585	25	2-103680-2
	2.200	22	2.405	2.485	24	2-1
OBSOLETE	2.100	21	2.305	2.385	23	2-0
3	2.000	20	2.205	2.285	22	1-9
	1.900	19	2.105	2.185	21	1-8
	1.800	18	2.005	2.085	20	1-7
	1.700	17	1.905	1.985	19	1-6
OBSOLETE	1.600	16	1.805	1.885	18	1-5
3	1.500	15	1.705	1.785	17	1-4
	1.400	14	1.605	1.685	16	1-3
	1.300	13	1.505	1.585	15	1-2
3 OBSOLETE	1.200	12	1.405	1.485	14	1-1
	1.100	11	1.305	1.385	13	1-0
	1.000	10	1.205	1.285	12	-9
3 OBSOLETE	.900	9	1.105	1.185	11	-8
	.800	8	1.005	1.085	10	-7
3 OBSOLETE	.700	7	.905	.985	9	-6
	.600	6	.805	.885	8	-5
3 OBSOLETE	.500	5	.705	.785	7	-4
	.400	4	.605	.685	6	-3
	.300	3	.505	.585	5	-2
	.200	2	.405	.485	4	103680-1

1. SHROUD ACCEPTS HOUSINGS
WITH GUIDE RIBS.2. DIMENSION APPLIES WITH ANY BOW OR WARPAGE
IN SHROUD WALLS REMOVED.

3. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm$ MATERIAL
THERMOPLASTIC
COLOR: BLACK

FINISH

CONTRACT NO

DR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

TE Connectivity

NAME

SHROUD, COUPLING,
SINGLE ROW, AMPMODU MTE

SIZE

FSCM NO

DRAWING NO

C

00779

103680

SCALE

SHEET

1 OF 1

CUSTOMER DRAWING