

Data Sheet

PR033xxVBHC

Page 1/5


P/N

312241xx

xx=number of poles

2017/05/04

Illustration



see enlarged drawing at the end of the document

Product specification

- pin header, THR solderable
- centerline 3.50 mm, direction of connection vertical 0°
- fittable without loss of poles
- color black
- Tape & Reel packaging

© 2017 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



Data Sheet

PR033xxVBHC

Technical Data

General Data

Solder pin length	3.6 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	2.5 mm		
protection category	IP 00		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200 V	500 V	500 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Approvals

 V / A	300 / 15
SEV Reg 130002	6 A / 200 V / 2.5 kV / 3 / IEC 61984

Material

insulating material	PA46
flammability class	V0
Glow-Wire Flammability GWFI	-
Glow-Wire Flammability GWIT	-
contact pin material	CuZn
contact pin surface	Ni + Ag

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

solderability	Acc. to IPC/JEDEC J-STD-020D-MSL 1
Tolerance	ISO 2768 -mH



Data Sheet

PR033xxVBHC

Page 3/5

P/N

312241xx

xx=number of poles

2017/05/04

Matching Part to

P/N	Product name
311661	RP023xxHBWC Typ 166



Data Sheet

PR033xxVBHC

Page 4/5

P/N


312241xx

xx=number of poles

2017/05/04

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 2.7 [0.106]$$



Data Sheet

PR033xxVBHC

Page 5/5

P/N

312241xx

xx=number of poles

2017/05/04

PCB Layout

