



2SK345, 2SK346


MAXIMUM SAFE OPERATION AREA




TYPICAL OUTPUT CHARACTERISTICS




TYPICAL TRANSFER CHARACTERISTICS




DRAIN-SOURCE SATURATION VOLTAGE VS. GATE-SOURCE VOLTAGE





FORWARD TRANSFER ADMITTANCE VS. DRAIN CURRENT





STATIC DRAIN-SOURCE ON STATE RESISTANCE VS. TEMPERATURE




TYPICAL CAPACITANCE VS.
DRAIN-SOURCE VOLTAGEFORWARD TRANSFER ADMITTANCE
VS. FREQUENCY


SWITCHING CHARACTERISTICS

MAXIMUM BODY-DRAIN DIODE
FORWARD VOLTAGE

DYNAMIC INPUT CHARACTERISTICS



SWITCHING TIME TEST CIRCUIT



WAVEFORMS

