


General purpose (dual digital transistors)

EMA4 / UMA4N / EMB4 / UMB4N / UMB8N / FMA4A / IMB4A

●Feature

1) Two DTA114T chips in a EMT or UMT or SMT package.

●Equivalent circuits



●Absolute maximum ratings (Ta=25°C)

Parameter	Symbol	Limits	Unit
Collector-base voltage	V_{CB0}	-50	V
Collector-emitter voltage	V_{CE0}	-50	V
Emitter-base voltage	V_{EB0}	-5	V
Collector current	I_C	-100	mA
Power dissipation	EMA4 / UMA4N / EMB4 / UMB4N / UMB8N	150(TOTAL)	mW *1
	FMA4A / IMB4A	300(TOTAL)	mW *2
Junction temperature	T_j	150	°C
Storage temperature	T_{stg}	-55~+150	°C

*1 120mW per element must not be exceeded.
*2 200mW per element must not be exceeded.

●Electrical characteristics (Ta=25°C)







Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage	BV_{CB0}	-50	—	—	V	$I_C = -50\mu A$
Collector-emitter breakdown voltage	BV_{CE0}	-50	—	—	V	$I_C = -1mA$
Emitter-base breakdown voltage	BV_{EB0}	-5	—	—	V	$I_E = -50\mu A$
Collector cutoff current	I_{CBO}	—	—	-0.5	μA	$V_{CB} = -50V$
Emitter cutoff current	I_{EBO}	—	—	-0.5	μA	$V_{EB} = -4V$
Collector-emitter saturation voltage	$V_{CE(sat)}$	—	—	-0.3	V	$I_C/I_E = -10mA/-1mA$
DC current transfer ratio	h_{FE}	100	250	600	—	$V_{CE} = -5V$, $I_C = -1mA$
Transition frequency	f_T	—	250	—	MHz	$V_{CE} = -10V$, $I_E = 5mA$, $f = 100MHz$ *
Input resistance	R_1	7	10	13	k Ω	—

*Transition frequency of the device.

●Package, marking, and packaging specifications

Type	EMA4	UMA4N	EMB4	UMB4N	UMB8N	FMA4A	IMB4A
Package	EMT5	UMT5	EMT6	UMT6	UMT6	SMT5	SMT6
Marking	A4	A4	B4	B4	B8	A4	B4
Code	T2R	TR	T2R	TN	TR	T148	T110
Basic ordering unit (pieces)	8000	3000	8000	3000	3000	3000	3000

●External dimensions (Units : mm)

EMA4  ROHM : EMT5 Each lead has same dimensions	UMA4N  ROHM : UMT5 EIAJ : SC-88A Each lead has same dimensions
EMB4  ROHM : EMT6 Each lead has same dimensions	UMB4N / UMB8N  ROHM : UMT6 EIAJ : SC-88 Each lead has same dimensions
EMA4A  ROHM : SMT5 EIAJ : SC-74A Each lead has same dimensions	IMB4A  ROHM : SMT6 EIAJ : SC-74 Each lead has same dimensions