


DASH NO	MODEL NO	JACK TYPE
-1	J152	3-LUG
-2	J152FL	4-LUG


INCH	MM	INCH	MM
.005	0.13	.295	7.40
.010	0.25	.308	7.82
.015	0.38	.347	8.81
.030	0.76	.436	11.07
.128	3.25	.638	16.21
.218	5.54	1.209	30.71
.264	6.71		

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS			3-0033 SH 1		
REV	EO	DESCRIPTION	DWN	APPROVED	DATE
B	5850	REV & REDRWN	JEB	DC Tm	6-1-83
C	7787	ADDED TOLS	FZ	BK;	9-28-87
D	8037	ADDED TOLS ±010; DWG NO WAS 3000 - 0033	FZ	BK;	4-12-88



-1 SHOWN



3. 3&4 LUG CONCENTRIC TWINAX/ TRIAX
TPS RECEPTACLE TO SUBMINIATURE
CONCENTRIC TWINAX / TRIAX PATCH JACK

2. TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED		TROMPETER		J152/J152FL	
.XX ±		ELECTRONICS, INC.			
.XXX ±.005					
.XXXX±					
ANGLES±					
DWN	JEB	4-22-83	MATERIAL	CODE IDENT	DRAWING NO.
CHK	DC	6-1-83	—	14949	3-0033
ENGR	Tm	6-1-83			
APPR	DC	6-1-83	SCALE 4/1	DATE 6-27-77	SHEET 1 OF 2

155-0472

155-0475

NEXT ASSY

DWN JEB 4-22-83

CHK DC 6-1-83

ENGR Tm 6-1-83

APPR DC 6-1-83

MATERIAL

—

SCALE 4/1

CODE IDENT

14949

DATE 6-27-77

DRAWING NO.

3-0033

SHEET 1 OF 2

REV

D